

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584207

Luminaire Tested: **HCC8S25D010MW-HM82555935-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584207  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S25D010MW-HM82555935-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2370.3 lumens  
Efficiency: N/A  
Efficacy: 88.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584207  
CATALOG NUMBER: HCC8S25D010MW-HM82555935-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584207

CATALOG NUMBER: HCC8S25D010MW-HM82555935-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	55638
5°	54916
10°	52902
15°	50836
20°	49426
25°	47940
30°	43016
35°	28199
40°	15590
45°	13000
50°	11854
55°	11311
60°	10521
65°	9544
70°	8628
75°	7792
80°	7068
85°	6793



TEST NUMBER: P584207  
 CATALOG NUMBER: HCC8S25D010MW-HM82555935-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.7	7.0
10°-20°	449.2	19.0
20°-30°	639.3	27.0
30°-40°	473.2	20.0
40°-50°	234.4	9.9
50°-60°	187.1	7.9
60°-70°	129.9	5.5
70°-80°	70.0	3.0
80°-90°	20.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1255.3	53.0
0°-40°	1728.4	72.9
0°-60°	2149.8	90.7
0°-90°	2370.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2370.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1804	
5°	1774	167
15°	1592	449
25°	1409	639
35°	749	473
45°	298	234
55°	210	187
65°	131	130
75°	65	70
85°	19	21
90°	0	



TEST NUMBER: P584207  
CATALOG NUMBER: HCC8S25D010MW-HM82555935-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1804.3
2.5°	1796.3
5°	1774.1
7.5°	1739.0
10°	1689.5
12.5°	1638.5
15°	1592.4
17.5°	1547.6
20°	1506.2
22.5°	1464.8
25°	1409.0
27.5°	1327.8
30°	1208.1
32.5°	1024.8
35°	749.1
37.5°	511.7
40°	387.3
42.5°	331.5
45°	298.1
47.5°	270.9
50°	247.1
52.5°	226.3
55°	210.4
57.5°	191.3
60°	170.6
62.5°	149.8
65°	130.8
67.5°	111.6
70°	95.7
72.5°	79.7
75°	65.4
77.5°	52.6
80°	39.8
82.5°	28.7
85°	19.2
87.5°	7.9
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)