

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584378

Luminaire Tested: **HCC8S35D010MW-HM82555827-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MW-HM82555827-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3802.2 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584378
CATALOG NUMBER: HCC8S35D010MW-HM82555827-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584378

CATALOG NUMBER: HCC8S35D010MW-HM82555827-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61688	61688	61688
5°	62503	61432	60850
10°	63144	60802	59884
15°	63781	59516	58325
20°	63458	57322	56009
25°	61982	53891	53166
30°	58872	50024	49835
35°	53590	45647	46050
40°	46984	40854	42359
45°	40535	36339	38908
50°	35495	31907	35236
55°	31450	27424	31020
60°	28332	23059	25699
65°	25530	18511	19686
70°	22387	13488	10837
75°	19099	7006	2871
80°	14704	1900	462
85°	9447	0	0



TEST NUMBER: P584378
 CATALOG NUMBER: HCC8S35D010MW-HM82555827-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.8	5.0
10°-20°	530.6	14.0
20°-30°	753.1	19.8
30°-40°	792.8	20.9
40°-50°	674.4	17.7
50°-60°	487.4	12.8
60°-70°	277.2	7.3
70°-80°	87.3	2.3
80°-90°	10.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1472.5	38.7
0°-40°	2265.3	59.6
0°-60°	3427.1	90.1
0°-90°	3802.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3802.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2000	2000	2000	2000	2000	
5°	2019	2009	1985	1971	1966	193
15°	1998	1947	1864	1830	1827	563
25°	1822	1731	1584	1557	1563	834
35°	1424	1341	1213	1205	1223	886
45°	930	895	833	855	892	723
55°	585	542	510	540	577	527
65°	350	302	254	251	270	347
75°	160	123	59	27	24	172
85°	27	16	0	0	0	35
90°	0	0	0	0	0	



TEST NUMBER: P584378

CATALOG NUMBER: HCC8S35D010MW-HM82555827-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5
2.5°	2011.2	2014.0	2008.6	2008.6	2014.0	2008.6	2011.2	2011.2	2008.6	2008.6	2005.9
5°	2019.2	2016.6	2016.6	2016.6	2019.2	2014.0	2011.2	2014.0	2008.6	2008.6	2008.6
7.5°	2022.0	2022.0	2019.2	2016.6	2016.6	2016.6	2014.0	2011.2	2008.6	2003.3	2000.5
10°	2016.6	2016.6	2019.2	2014.0	2014.0	2008.6	2008.6	2003.3	2003.3	1997.9	1989.9
12.5°	2011.2	2008.6	2008.6	2003.3	2003.3	1997.9	1997.9	1989.9	1987.2	1979.2	1971.2
15°	1997.9	1995.3	1989.9	1987.2	1984.6	1981.9	1976.6	1973.8	1965.8	1955.1	1947.1
17.5°	1971.2	1968.6	1965.8	1960.5	1955.1	1952.5	1949.9	1941.8	1931.2	1923.1	1909.7
20°	1933.8	1931.2	1931.2	1923.1	1920.4	1912.5	1909.7	1899.1	1891.0	1875.0	1864.3
22.5°	1883.0	1885.8	1880.4	1875.0	1869.7	1861.7	1856.3	1845.6	1832.3	1816.3	1802.9
25°	1821.7	1824.3	1818.9	1813.7	1805.6	1800.2	1795.0	1778.9	1765.5	1746.8	1730.8
27.5°	1744.2	1744.2	1744.2	1738.8	1725.5	1722.8	1717.5	1701.4	1682.7	1666.7	1650.7
30°	1653.4	1650.7	1650.7	1642.7	1637.3	1626.6	1618.6	1605.3	1591.9	1573.2	1554.5
32.5°	1543.9	1546.5	1538.5	1533.2	1525.2	1525.2	1514.5	1503.7	1487.8	1469.1	1450.3
35°	1423.6	1426.3	1420.9	1418.3	1404.9	1402.3	1399.6	1386.2	1375.5	1362.2	1340.8
37.5°	1300.8	1298.2	1295.4	1295.4	1287.4	1282.1	1276.7	1268.7	1252.7	1242.0	1231.3
40°	1167.2	1167.2	1167.2	1164.6	1161.9	1156.5	1153.9	1148.5	1137.9	1127.2	1119.2
42.5°	1047.1	1047.1	1044.4	1041.7	1036.4	1039.0	1033.6	1028.4	1017.7	1009.7	1004.3
45°	929.5	929.5	929.5	932.2	926.9	918.9	918.9	913.5	908.1	902.8	894.8
47.5°	825.3	833.3	828.1	825.3	828.1	817.3	817.3	812.0	806.6	801.3	790.6
50°	739.9	739.9	739.9	734.5	731.9	731.9	723.8	718.4	715.8	710.5	699.8
52.5°	662.4	657.1	657.1	654.3	651.7	646.4	646.4	641.0	630.4	625.0	617.0
55°	585.0	585.0	582.2	579.6	577.0	574.3	571.6	563.5	558.3	550.2	542.2
57.5°	515.5	520.9	518.1	512.9	507.5	507.5	502.2	496.8	488.8	480.8	472.7
60°	459.4	456.8	456.8	454.0	448.8	446.0	443.4	435.4	427.3	419.3	411.4
62.5°	400.6	400.6	400.6	395.3	389.9	387.3	384.7	379.3	368.6	360.6	355.2
65°	349.9	347.2	344.5	341.9	339.3	333.9	331.2	325.9	317.8	309.8	301.8
67.5°	299.1	296.5	296.5	293.9	285.8	283.1	283.1	275.1	267.2	259.1	251.1
70°	248.3	248.3	248.3	243.1	240.4	237.7	235.0	229.7	221.7	213.7	205.7
72.5°	205.7	202.9	202.9	200.3	192.3	189.6	187.0	181.6	173.6	168.3	162.9
75°	160.3	160.3	157.5	154.9	152.3	149.6	146.9	141.6	133.6	125.6	122.9
77.5°	122.9	120.2	120.2	117.5	112.1	109.5	109.5	104.2	96.2	90.8	85.4
80°	82.8	85.4	82.8	80.1	77.5	74.8	72.1	69.5	64.1	58.8	53.4
82.5°	50.8	53.4	50.8	50.8	48.0	45.4	45.4	40.0	37.4	34.7	32.1
85°	26.7	26.7	26.7	26.7	24.1	24.1	24.1	21.3	18.7	16.1	16.1
87.5°	8.0	10.7	8.0	8.0	8.0	8.0	8.0	8.0	5.4	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584378

CATALOG NUMBER: HCC8S35D010MW-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5
2.5°	2008.6	2005.9	2003.3	2003.3	2003.3	2003.3	2003.3	2000.5	1997.9	1997.9	1997.9
5°	2003.3	2003.3	2003.3	2000.5	1997.9	1997.9	1992.5	1989.9	1987.2	1984.6	1981.9
7.5°	1997.9	1992.5	1989.9	1987.2	1984.6	1984.6	1979.2	1973.8	1973.8	1968.6	1963.2
10°	1981.9	1979.2	1973.8	1968.6	1965.8	1963.2	1957.9	1949.9	1947.1	1941.8	1936.4
12.5°	1963.2	1957.9	1952.5	1941.8	1939.2	1936.4	1925.8	1917.8	1912.5	1909.7	1896.4
15°	1939.2	1928.4	1920.4	1907.1	1904.5	1899.1	1891.0	1883.0	1872.4	1864.3	1859.1
17.5°	1896.4	1885.8	1872.4	1859.1	1853.7	1853.7	1840.4	1829.6	1816.3	1810.9	1800.2
20°	1845.6	1832.3	1821.7	1805.6	1797.6	1789.6	1781.5	1765.5	1754.8	1746.8	1733.5
22.5°	1786.9	1768.2	1754.8	1738.8	1725.5	1717.5	1704.2	1690.7	1677.4	1669.4	1658.6
25°	1712.1	1696.1	1674.7	1658.6	1650.7	1639.9	1624.0	1610.6	1597.3	1583.9	1578.6
27.5°	1629.3	1608.0	1589.3	1570.6	1562.6	1554.5	1535.8	1519.8	1509.1	1495.7	1490.4
30°	1538.5	1517.1	1495.7	1479.8	1471.7	1458.3	1447.7	1429.0	1415.7	1404.9	1391.6
32.5°	1434.4	1418.3	1399.6	1375.5	1370.3	1359.5	1343.6	1335.5	1319.5	1311.5	1300.8
35°	1322.1	1311.5	1292.8	1274.1	1266.0	1260.7	1247.4	1231.3	1220.6	1212.6	1207.3
37.5°	1215.3	1202.0	1183.3	1169.8	1164.6	1156.5	1140.5	1132.5	1121.8	1116.5	1105.8
40°	1100.5	1087.1	1073.8	1065.7	1057.7	1052.3	1041.7	1033.6	1023.0	1014.9	1012.3
42.5°	988.2	980.2	969.5	958.9	956.2	948.2	942.8	934.8	926.9	924.1	916.1
45°	886.8	878.7	868.1	857.4	854.8	849.4	846.7	838.7	833.3	833.3	833.3
47.5°	785.3	777.3	766.6	761.2	764.0	753.2	753.2	750.5	745.2	745.2	747.9
50°	694.5	683.8	681.1	675.8	670.4	665.1	667.8	659.7	659.7	665.1	662.4
52.5°	608.9	598.3	595.6	590.3	587.6	587.6	585.0	585.0	582.2	585.0	585.0
55°	531.6	523.5	518.1	512.9	510.1	510.1	510.1	507.5	504.8	510.1	512.9
57.5°	462.1	459.4	454.0	446.0	443.4	440.7	438.0	438.0	438.0	438.0	440.7
60°	400.6	395.3	389.9	381.9	381.9	379.3	376.7	373.9	373.9	373.9	373.9
62.5°	347.2	339.3	331.2	325.9	323.2	320.5	317.8	312.6	312.6	312.6	312.6
65°	293.9	285.8	280.5	275.1	269.8	269.8	264.4	261.8	256.4	253.7	248.3
67.5°	243.1	237.7	232.4	224.4	221.7	219.0	213.7	211.0	202.9	200.3	197.7
70°	197.7	189.6	184.3	179.0	176.3	171.0	165.6	160.3	154.9	149.6	144.2
72.5°	154.9	146.9	141.6	136.2	130.8	130.8	122.9	117.5	109.5	104.2	96.2
75°	114.9	106.9	101.5	93.4	90.8	88.2	80.1	74.8	66.7	58.8	53.4
77.5°	77.5	72.1	66.7	58.8	53.4	53.4	45.4	40.0	34.7	26.7	24.1
80°	48.0	42.8	37.4	32.1	32.1	26.7	24.1	18.7	13.3	10.7	8.0
82.5°	26.7	24.1	21.3	16.1	16.1	13.3	10.7	8.0	5.4	2.6	2.6
85°	13.3	10.7	8.0	8.0	5.4	5.4	5.4	2.6	2.6	0.0	0.0
87.5°	5.4	2.6	2.6	2.6	2.6	2.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584378

CATALOG NUMBER: HCC8S35D010MW-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5
2.5°	1995.3	1995.3	1992.5	1992.5	1992.5	1989.9	1992.5	1989.9	1989.9	1989.9	1992.5
5°	1984.6	1979.2	1979.2	1976.6	1976.6	1973.8	1976.6	1973.8	1971.2	1968.6	1971.2
7.5°	1963.2	1957.9	1955.1	1952.5	1952.5	1952.5	1949.9	1947.1	1949.9	1941.8	1947.1
10°	1933.8	1931.2	1925.8	1923.1	1920.4	1923.1	1920.4	1915.1	1915.1	1915.1	1912.5
12.5°	1896.4	1891.0	1888.4	1885.8	1880.4	1880.4	1883.0	1877.7	1877.7	1872.4	1872.4
15°	1851.0	1845.6	1840.4	1840.4	1835.0	1835.0	1832.3	1832.3	1829.6	1827.0	1827.0
17.5°	1795.0	1786.9	1781.5	1784.2	1781.5	1778.9	1778.9	1773.5	1770.9	1773.5	1773.5
20°	1728.1	1722.8	1717.5	1720.1	1714.8	1712.1	1714.8	1706.8	1709.4	1709.4	1709.4
22.5°	1653.4	1650.7	1642.7	1642.7	1637.3	1634.7	1637.3	1637.3	1639.9	1637.3	1637.3
25°	1570.6	1565.2	1559.9	1559.9	1557.2	1554.5	1557.2	1559.9	1557.2	1559.9	1559.9
27.5°	1482.4	1474.4	1474.4	1469.1	1469.1	1471.7	1469.1	1471.7	1474.4	1474.4	1479.8
30°	1386.2	1383.6	1380.9	1378.2	1378.2	1380.9	1380.9	1380.9	1383.6	1389.0	1389.0
32.5°	1295.4	1290.1	1284.7	1284.7	1290.1	1287.4	1290.1	1290.1	1295.4	1295.4	1300.8
35°	1196.6	1196.6	1191.3	1193.9	1193.9	1193.9	1193.9	1199.3	1204.6	1207.3	1212.6
37.5°	1105.8	1097.7	1100.5	1100.5	1103.1	1100.5	1108.5	1108.5	1113.8	1113.8	1119.2
40°	1006.9	1006.9	1009.7	1006.9	1009.7	1009.7	1014.9	1020.3	1023.0	1028.4	1031.0
42.5°	913.5	918.9	913.5	916.1	918.9	921.5	924.1	926.9	937.6	942.8	950.9
45°	828.1	830.7	833.3	836.0	833.3	838.7	841.4	846.7	854.8	857.4	860.0
47.5°	745.2	747.9	750.5	753.2	753.2	758.6	761.2	766.6	771.9	774.6	777.3
50°	665.1	670.4	673.0	673.0	675.8	681.1	686.5	686.5	691.8	699.8	702.5
52.5°	593.0	593.0	598.3	600.9	603.7	603.7	611.7	614.3	617.0	622.4	627.6
55°	512.9	520.9	523.5	523.5	528.9	534.2	536.8	539.6	539.6	550.2	550.2
57.5°	443.4	446.0	451.4	451.4	451.4	459.4	459.4	464.7	467.5	470.1	475.5
60°	373.9	379.3	379.3	381.9	379.3	384.7	387.3	392.6	395.3	398.0	400.6
62.5°	309.8	309.8	312.6	312.6	312.6	312.6	317.8	317.8	323.2	325.9	328.5
65°	248.3	248.3	248.3	248.3	248.3	248.3	248.3	248.3	251.1	251.1	256.4
67.5°	192.3	189.6	184.3	187.0	184.3	184.3	181.6	181.6	184.3	184.3	189.6
70°	138.8	136.2	130.8	130.8	128.2	125.6	122.9	120.2	117.5	117.5	117.5
72.5°	90.8	85.4	77.5	74.8	74.8	69.5	64.1	61.5	61.5	61.5	61.5
75°	45.4	40.0	34.7	32.1	32.1	26.7	29.4	26.7	26.7	26.7	26.7
77.5°	18.7	13.3	10.7	10.7	10.7	8.0	8.0	8.0	8.0	8.0	8.0
80°	5.4	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	2.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584378

CATALOG NUMBER: HCC8S35D010MW-HM82555827-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5	2000.5
2.5°	1989.9	1989.9	1984.6	1987.2	1987.2	1987.2	1987.2	1987.2
5°	1965.8	1968.6	1965.8	1968.6	1968.6	1965.8	1965.8	1965.8
7.5°	1941.8	1944.5	1941.8	1944.5	1944.5	1944.5	1941.8	1941.8
10°	1912.5	1912.5	1912.5	1912.5	1912.5	1909.7	1912.5	1912.5
12.5°	1872.4	1872.4	1872.4	1875.0	1875.0	1872.4	1872.4	1869.7
15°	1829.6	1824.3	1827.0	1829.6	1827.0	1827.0	1827.0	1827.0
17.5°	1770.9	1773.5	1770.9	1770.9	1770.9	1770.9	1773.5	1770.9
20°	1709.4	1709.4	1712.1	1709.4	1709.4	1709.4	1709.4	1706.8
22.5°	1639.9	1637.3	1637.3	1639.9	1639.9	1637.3	1639.9	1639.9
25°	1562.6	1565.2	1562.6	1562.6	1565.2	1565.2	1565.2	1562.6
27.5°	1479.8	1482.4	1485.0	1482.4	1482.4	1482.4	1485.0	1487.8
30°	1394.2	1399.6	1394.2	1394.2	1399.6	1397.0	1399.6	1399.6
32.5°	1303.4	1311.5	1306.1	1311.5	1311.5	1314.1	1311.5	1314.1
35°	1212.6	1220.6	1220.6	1220.6	1223.3	1226.0	1226.0	1223.3
37.5°	1127.2	1129.8	1129.8	1135.2	1137.9	1140.5	1140.5	1137.9
40°	1039.0	1044.4	1047.1	1047.1	1047.1	1052.3	1057.7	1052.3
42.5°	953.5	956.2	958.9	958.9	964.3	966.9	969.5	969.5
45°	870.7	876.1	878.7	881.5	884.1	889.4	886.8	892.2
47.5°	785.3	793.3	796.0	798.6	804.0	806.6	809.4	812.0
50°	707.8	713.2	713.2	718.4	726.5	726.5	731.9	734.5
52.5°	630.4	633.0	635.7	638.4	643.7	649.1	649.1	654.3
55°	555.5	558.3	558.3	560.9	563.5	574.3	577.0	577.0
57.5°	478.1	478.1	483.4	486.1	488.8	494.2	494.2	494.2
60°	403.4	406.0	406.0	408.6	411.4	416.7	419.3	416.7
62.5°	328.5	331.2	331.2	333.9	339.3	341.9	339.3	339.3
65°	259.1	261.8	261.8	264.4	269.8	269.8	267.2	269.8
67.5°	189.6	189.6	189.6	189.6	189.6	189.6	189.6	189.6
70°	120.2	117.5	114.9	117.5	117.5	117.5	114.9	120.2
72.5°	58.8	61.5	61.5	61.5	61.5	61.5	61.5	58.8
75°	26.7	26.7	24.1	24.1	24.1	26.7	26.7	24.1
77.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
80°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)