

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584239

Luminaire Tested: **HCC8S30D010MB-HM82555827-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584239  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S30D010MB-HM82555827-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3008.6 lumens  
Efficiency: N/A  
Efficacy: 107.4 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584239  
CATALOG NUMBER: HCC8S30D010MB-HM82555827-81NDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584239

CATALOG NUMBER: HCC8S30D010MB-HM82555827-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95																												
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																												
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84																												
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80																												
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75																												
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72																												
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68																												
8	84	76	70	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65																												
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62																												
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	239373
5°	202799
10°	147141
15°	110499
20°	87184
25°	70328
30°	52118
35°	21115
40°	8908
45°	4775
50°	2144
55°	1081
60°	691
65°	489
70°	406
75°	274
80°	408
85°	814



TEST NUMBER: P584239  
 CATALOG NUMBER: HCC8S30D010MB-HM82555827-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	562.5	18.7
10°-20°	972.1	32.3
20°-30°	939.9	31.2
30°-40°	412.8	13.7
40°-50°	89.3	3.0
50°-60°	20.1	0.7
60°-70°	6.9	0.2
70°-80°	2.7	0.1
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2474.6	82.3
0°-40°	2887.4	96.0
0°-60°	2996.8	99.6
0°-90°	3008.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3008.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7763	
5°	6552	563
15°	3461	972
25°	2067	940
35°	561	413
45°	110	89
55°	20	20
65°	7	7
75°	2	3
85°	2	2
90°	0	



TEST NUMBER: P584239  
CATALOG NUMBER: HCC8S30D010MB-HM82555827-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7762.7
1°	7704.6
2°	7546.0
3°	7259.9
4°	6918.1
5°	6551.6
6°	6151.6
7°	5749.4
8°	5371.8
9°	5021.0
10°	4699.2
11°	4395.3
12°	4122.7
13°	3874.7
14°	3655.7
15°	3461.3
17.5°	3025.5
20°	2656.8
22.5°	2332.8
25°	2067.0
27.5°	1796.6
30°	1463.7
32.5°	994.4
35°	560.9
37.5°	330.7
40°	221.3
42.5°	156.5
45°	109.5
47.5°	71.5
50°	44.7
52.5°	26.9
55°	20.1
57.5°	15.7
60°	11.2
62.5°	8.9
65°	6.7
67.5°	4.5
70°	4.5
72.5°	2.3
75°	2.3
77.5°	2.3
80°	2.3
82.5°	2.3

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P584239  
CATALOG NUMBER: HCC8S30D010MB-HM82555827-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°	2.3
87.5°	2.3

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)