

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584404

Luminaire Tested: **HCC8S35D010MW-HM82555830-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584404
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MW-HM82555830-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3692.1 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584404
CATALOG NUMBER: HCC8S35D010MW-HM82555830-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P584404

CATALOG NUMBER: HCC8S35D010MW-HM82555830-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	56606	56606	56606
5°	58680	56417	54482
10°	60338	55930	52253
15°	61681	54938	49945
20°	61781	52793	47917
25°	60594	49859	46222
30°	57473	46235	44195
35°	52220	42113	42207
40°	45660	37790	39779
45°	39571	33662	37072
50°	34651	29897	33778
55°	30838	26499	30563
60°	27814	23799	26858
65°	25115	20926	23400
70°	22576	17626	17401
75°	19885	13975	13046
80°	16675	11578	12502
85°	12914	10119	11074



TEST NUMBER: P584404
 CATALOG NUMBER: HCC8S35D010MW-HM82555830-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.2	4.7
10°-20°	487.8	13.2
20°-30°	697.1	18.9
30°-40°	740.7	20.1
40°-50°	637.7	17.3
50°-60°	476.8	12.9
60°-70°	304.1	8.2
70°-80°	138.4	3.7
80°-90°	36.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1358.0	36.8
0°-40°	2098.7	56.8
0°-60°	3213.2	87.0
0°-90°	3692.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3692.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1836	1836	1836	1836	1836	
5°	1896	1870	1823	1776	1760	182
15°	1932	1867	1721	1604	1564	544
25°	1781	1669	1465	1377	1358	815
35°	1387	1291	1119	1090	1121	864
45°	907	858	772	793	850	705
55°	574	527	493	534	568	516
65°	344	305	287	300	321	343
75°	167	143	117	107	110	177
85°	36	31	29	31	31	44
90°	0	0	0	0	0	



TEST NUMBER: P584404

CATALOG NUMBER: HCC8S35D010MW-HM82555830-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7
2.5°	1869.6	1864.4	1867.0	1864.4	1867.0	1867.0	1861.8	1861.8	1861.8	1861.8	1853.9
5°	1895.7	1893.1	1893.1	1890.4	1887.8	1890.4	1887.8	1885.3	1880.0	1877.4	1869.6
7.5°	1911.3	1911.3	1911.3	1911.3	1908.8	1906.1	1903.5	1898.2	1893.1	1887.8	1882.7
10°	1927.0	1929.6	1927.0	1924.3	1921.7	1916.6	1913.9	1908.8	1900.9	1893.1	1887.8
12.5°	1934.8	1934.8	1932.1	1932.1	1927.0	1924.3	1916.6	1908.8	1900.9	1893.1	1880.0
15°	1932.1	1932.1	1929.6	1927.0	1919.2	1916.6	1911.3	1903.5	1890.4	1880.0	1867.0
17.5°	1916.6	1913.9	1908.8	1908.8	1898.2	1895.7	1890.4	1880.0	1867.0	1851.4	1835.7
20°	1882.7	1882.7	1880.0	1877.4	1867.0	1859.2	1853.9	1841.0	1830.5	1812.2	1796.6
22.5°	1835.7	1841.0	1835.7	1830.5	1817.5	1814.9	1807.1	1791.4	1775.8	1754.8	1736.6
25°	1780.9	1778.3	1775.8	1770.5	1760.1	1754.8	1744.4	1728.8	1713.1	1689.7	1668.8
27.5°	1710.5	1700.1	1700.1	1689.7	1681.9	1674.1	1668.8	1653.2	1632.3	1614.1	1587.9
30°	1614.1	1616.7	1603.6	1601.0	1587.9	1582.8	1572.4	1556.7	1538.5	1517.6	1496.8
32.5°	1509.7	1501.9	1501.9	1491.5	1481.1	1473.3	1470.7	1452.5	1436.8	1415.9	1395.1
35°	1387.2	1387.2	1379.4	1376.7	1366.3	1361.2	1353.3	1342.8	1324.6	1306.4	1290.7
37.5°	1267.2	1262.1	1259.5	1254.2	1246.4	1238.6	1238.6	1220.3	1217.8	1196.8	1176.0
40°	1134.3	1139.5	1134.3	1126.5	1123.8	1118.7	1116.1	1105.6	1097.7	1079.5	1066.5
42.5°	1022.1	1017.0	1017.0	1014.3	1003.9	1003.9	998.7	993.5	980.4	975.2	959.6
45°	907.4	912.6	904.8	907.4	896.9	896.9	896.9	886.5	876.1	868.3	857.9
47.5°	808.3	810.9	810.9	803.1	800.5	800.5	795.4	790.1	782.3	771.9	764.0
50°	722.3	724.9	719.6	717.1	711.9	709.2	709.2	698.8	693.6	683.2	677.9
52.5°	644.0	644.0	641.4	641.4	633.6	633.6	628.5	620.6	615.4	610.1	597.1
55°	573.6	573.6	571.1	568.5	568.5	560.7	558.0	550.2	545.0	534.5	526.8
57.5°	505.9	508.4	505.9	503.3	500.6	498.0	492.9	485.0	479.8	472.0	466.7
60°	451.0	451.0	448.5	445.9	440.6	438.1	435.5	430.2	422.4	417.3	409.4
62.5°	398.9	396.3	393.8	391.1	385.9	385.9	380.7	375.5	367.7	362.4	357.2
65°	344.2	344.2	341.5	341.5	339.0	333.8	331.1	328.5	318.1	315.6	305.1
67.5°	294.7	297.2	292.1	292.1	286.8	286.8	284.2	276.4	273.7	268.6	263.3
70°	250.4	250.4	250.4	247.7	242.5	239.8	237.3	232.1	229.4	224.3	219.0
72.5°	205.9	205.9	203.4	203.4	200.8	198.1	195.5	190.4	190.4	185.1	179.9
75°	166.9	166.9	164.2	161.6	159.1	159.1	156.5	153.8	148.7	146.0	143.4
77.5°	127.8	127.8	127.8	125.2	122.6	122.6	122.6	117.3	112.1	112.1	109.5
80°	93.9	93.9	91.3	91.3	88.7	88.7	88.7	86.0	83.5	80.9	78.2
82.5°	62.5	62.5	62.5	62.5	60.0	60.0	60.0	57.4	54.7	54.7	54.7
85°	36.5	36.5	36.5	36.5	33.9	33.9	33.9	33.9	33.9	31.3	31.3
87.5°	15.7	13.1	15.7	13.1	15.7	13.1	15.7	13.1	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584404

CATALOG NUMBER: HCC8S35D010MW-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7
2.5°	1856.5	1853.9	1851.4	1848.8	1848.8	1846.1	1841.0	1838.3	1835.7	1833.1	1833.1
5°	1867.0	1864.4	1859.2	1853.9	1851.4	1846.1	1841.0	1835.7	1830.5	1822.6	1820.1
7.5°	1874.9	1867.0	1861.8	1851.4	1848.8	1843.5	1835.7	1827.9	1817.5	1807.1	1799.2
10°	1874.9	1864.4	1856.5	1843.5	1838.3	1833.1	1822.6	1809.6	1796.6	1786.2	1773.2
12.5°	1869.6	1856.5	1843.5	1830.5	1822.6	1814.9	1799.2	1786.2	1770.5	1754.8	1744.4
15°	1851.4	1835.7	1820.1	1804.4	1796.6	1786.2	1770.5	1752.3	1736.6	1720.9	1702.7
17.5°	1817.5	1801.8	1783.6	1765.3	1754.8	1747.0	1723.6	1710.5	1687.0	1671.4	1655.8
20°	1773.2	1754.8	1731.3	1713.1	1700.1	1692.3	1674.1	1650.6	1632.3	1608.8	1593.2
22.5°	1715.8	1692.3	1668.8	1650.6	1637.5	1627.1	1603.6	1580.2	1564.5	1543.6	1525.4
25°	1648.0	1624.5	1601.0	1575.0	1562.0	1551.5	1530.7	1509.7	1488.9	1465.4	1449.8
27.5°	1567.1	1541.1	1520.1	1496.8	1483.7	1468.0	1444.5	1423.7	1402.9	1387.2	1366.3
30°	1478.5	1449.8	1429.0	1405.5	1392.4	1379.4	1355.9	1335.1	1316.8	1298.5	1288.1
32.5°	1371.6	1350.7	1329.9	1306.4	1296.0	1288.1	1264.6	1243.8	1222.9	1207.3	1199.4
35°	1269.9	1246.4	1228.2	1207.3	1194.3	1186.4	1165.5	1147.3	1136.9	1118.7	1108.1
37.5°	1163.0	1144.7	1123.8	1103.0	1095.2	1087.3	1071.7	1053.4	1037.8	1024.8	1019.5
40°	1050.9	1035.2	1017.0	1003.9	996.1	988.2	975.2	962.2	951.8	938.8	933.5
42.5°	943.9	933.5	917.9	902.2	894.4	891.8	876.1	865.7	860.5	855.3	850.1
45°	847.5	831.8	821.3	810.9	803.1	797.9	790.1	782.3	777.0	771.9	766.6
47.5°	753.5	740.5	730.1	722.3	714.5	711.9	706.7	698.8	693.6	693.6	693.6
50°	667.5	657.1	646.7	641.4	638.9	633.6	628.5	625.8	623.2	623.2	623.2
52.5°	591.9	581.5	573.6	568.5	568.5	563.2	558.0	555.4	555.4	555.4	555.4
55°	521.5	513.7	508.4	503.3	498.0	495.5	495.5	495.5	492.9	492.9	495.5
57.5°	459.0	453.7	445.9	440.6	438.1	438.1	435.5	432.8	435.5	438.1	440.6
60°	401.6	396.3	393.8	385.9	385.9	385.9	383.4	383.4	383.4	385.9	388.5
62.5°	349.5	346.8	341.5	339.0	336.4	336.4	333.8	333.8	333.8	333.8	336.4
65°	302.5	297.2	292.1	292.1	292.1	289.4	289.4	284.2	286.8	286.8	284.2
67.5°	258.2	252.9	250.4	247.7	245.1	245.1	242.5	239.8	237.3	237.3	237.3
70°	216.5	211.2	211.2	205.9	205.9	203.4	200.8	200.8	198.1	195.5	193.0
72.5°	174.7	172.2	169.5	166.9	166.9	166.9	164.2	161.6	159.1	156.5	151.2
75°	138.2	138.2	133.0	130.3	130.3	127.8	125.2	122.6	119.9	117.3	114.8
77.5°	106.9	104.3	99.1	96.4	96.4	96.4	93.9	91.3	88.7	86.0	83.5
80°	78.2	75.6	73.0	70.4	70.4	70.4	67.8	67.8	65.2	65.2	65.2
82.5°	52.1	52.1	49.6	49.6	49.6	49.6	47.0	47.0	47.0	47.0	47.0
85°	31.3	31.3	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6	28.6
87.5°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584404

CATALOG NUMBER: HCC8S35D010MW-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7
2.5°	1827.9	1827.9	1822.6	1820.1	1817.5	1820.1	1814.9	1812.2	1809.6	1809.6	1807.1
5°	1812.2	1809.6	1799.2	1796.6	1794.0	1791.4	1786.2	1780.9	1775.8	1773.2	1770.5
7.5°	1791.4	1783.6	1773.2	1770.5	1767.9	1760.1	1752.3	1747.0	1739.3	1736.6	1731.3
10°	1762.7	1752.3	1744.4	1736.6	1731.3	1723.6	1715.8	1708.0	1697.6	1694.9	1687.0
12.5°	1728.8	1715.8	1700.1	1697.6	1689.7	1679.2	1668.8	1661.0	1653.2	1648.0	1640.2
15°	1687.0	1674.1	1658.4	1650.6	1642.7	1634.9	1621.9	1611.4	1603.6	1595.9	1587.9
17.5°	1637.5	1621.9	1608.8	1601.0	1595.9	1582.8	1572.4	1559.3	1551.5	1543.6	1535.8
20°	1577.5	1564.5	1546.3	1538.5	1535.8	1525.4	1512.4	1507.2	1496.8	1488.9	1483.7
22.5°	1509.7	1496.8	1481.1	1475.8	1465.4	1460.2	1447.2	1441.9	1436.8	1429.0	1426.3
25°	1434.1	1421.1	1408.1	1405.5	1397.6	1392.4	1384.6	1376.7	1376.7	1369.0	1369.0
27.5°	1355.9	1342.8	1332.4	1327.3	1324.6	1319.4	1311.6	1308.9	1306.4	1303.8	1303.8
30°	1272.5	1256.8	1251.7	1249.0	1246.4	1241.2	1238.6	1233.3	1236.0	1238.6	1236.0
32.5°	1183.9	1178.6	1168.2	1163.0	1165.5	1163.0	1157.7	1163.0	1160.4	1165.5	1168.2
35°	1097.7	1092.6	1087.3	1087.3	1082.2	1082.2	1082.2	1084.8	1089.9	1092.6	1097.7
37.5°	1014.3	1006.6	1003.9	1001.3	1003.9	1003.9	1003.9	1009.1	1014.3	1019.5	1027.4
40°	925.7	920.4	920.4	920.4	920.4	928.3	925.7	930.8	936.1	943.9	951.8
42.5°	842.2	842.2	844.8	844.8	844.8	844.8	850.1	857.9	865.7	873.6	881.4
45°	764.0	764.0	764.0	769.2	769.2	771.9	782.3	787.4	792.7	800.5	808.3
47.5°	691.0	691.0	693.6	696.2	698.8	704.1	709.2	717.1	724.9	730.1	738.0
50°	623.2	625.8	631.0	636.3	636.3	638.9	646.7	651.8	657.1	664.9	667.5
52.5°	558.0	563.2	568.5	571.1	573.6	578.9	581.5	589.3	591.9	599.7	602.4
55°	498.0	500.6	508.4	511.1	511.1	516.3	521.5	526.8	534.5	534.5	539.8
57.5°	443.3	445.9	451.0	453.7	451.0	459.0	461.6	466.7	469.4	474.5	477.2
60°	388.5	393.8	396.3	396.3	398.9	401.6	406.7	406.7	412.0	417.3	417.3
62.5°	336.4	339.0	341.5	344.2	346.8	344.2	352.0	352.0	357.2	359.9	365.0
65°	286.8	289.4	289.4	292.1	292.1	294.7	294.7	297.2	299.9	305.1	307.6
67.5°	237.3	237.3	237.3	239.8	237.3	239.8	239.8	242.5	242.5	247.7	250.4
70°	193.0	190.4	187.7	187.7	187.7	187.7	185.1	187.7	187.7	190.4	190.4
72.5°	148.7	146.0	143.4	140.8	140.8	138.2	135.6	138.2	138.2	140.8	140.8
75°	112.1	106.9	106.9	106.9	104.3	104.3	104.3	106.9	106.9	106.9	109.5
77.5°	83.5	83.5	80.9	80.9	80.9	83.5	83.5	86.0	86.0	86.0	86.0
80°	62.5	65.2	65.2	65.2	65.2	67.8	67.8	67.8	67.8	70.4	70.4
82.5°	47.0	47.0	47.0	47.0	49.6	49.6	49.6	49.6	49.6	49.6	49.6
85°	28.6	31.3	31.3	28.6	31.3	31.3	31.3	31.3	31.3	31.3	31.3
87.5°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584404

CATALOG NUMBER: HCC8S35D010MW-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7	1835.7
2.5°	1804.4	1804.4	1804.4	1804.4	1801.8	1801.8	1801.8	1799.2
5°	1765.3	1765.3	1765.3	1760.1	1762.7	1762.7	1757.5	1760.1
7.5°	1726.2	1723.6	1720.9	1720.9	1718.4	1715.8	1713.1	1715.8
10°	1681.9	1674.1	1674.1	1671.4	1671.4	1666.2	1666.2	1668.8
12.5°	1632.3	1627.1	1627.1	1624.5	1621.9	1619.3	1616.7	1616.7
15°	1582.8	1577.5	1575.0	1572.4	1569.7	1564.5	1567.1	1564.5
17.5°	1533.2	1525.4	1525.4	1522.8	1520.1	1515.0	1515.0	1512.4
20°	1475.8	1473.3	1468.0	1470.7	1468.0	1462.9	1460.2	1460.2
22.5°	1418.6	1418.6	1415.9	1415.9	1413.3	1410.6	1408.1	1408.1
25°	1363.8	1361.2	1363.8	1363.8	1355.9	1355.9	1355.9	1358.5
27.5°	1301.1	1303.8	1301.1	1301.1	1301.1	1301.1	1303.8	1301.1
30°	1238.6	1238.6	1238.6	1241.2	1246.4	1243.8	1243.8	1241.2
32.5°	1170.8	1173.4	1173.4	1176.0	1178.6	1183.9	1183.9	1186.4
35°	1103.0	1108.1	1110.8	1108.1	1116.1	1116.1	1121.2	1121.2
37.5°	1032.6	1035.2	1040.5	1043.0	1048.2	1050.9	1053.4	1053.4
40°	957.0	967.4	970.0	972.7	980.4	980.4	983.1	988.2
42.5°	886.5	896.9	899.6	902.2	907.4	915.3	912.6	917.9
45°	818.7	826.6	829.3	831.8	839.7	842.2	842.2	850.1
47.5°	745.8	751.0	753.5	758.8	764.0	769.2	774.4	771.9
50°	672.8	680.6	685.7	688.4	696.2	698.8	701.4	704.1
52.5°	607.5	612.8	615.4	617.9	625.8	628.5	631.0	636.3
55°	545.0	547.6	552.8	550.2	558.0	560.7	563.2	568.5
57.5°	482.4	485.0	487.6	487.6	492.9	498.0	500.6	503.3
60°	422.4	427.7	430.2	430.2	430.2	435.5	435.5	435.5
62.5°	367.7	367.7	370.3	370.3	375.5	375.5	375.5	375.5
65°	310.3	312.9	315.6	315.6	320.7	318.1	323.3	320.7
67.5°	250.4	250.4	255.5	255.5	252.9	255.5	255.5	255.5
70°	190.4	190.4	193.0	193.0	193.0	193.0	193.0	193.0
72.5°	140.8	140.8	140.8	143.4	140.8	140.8	143.4	140.8
75°	109.5	109.5	109.5	109.5	109.5	109.5	109.5	109.5
77.5°	86.0	86.0	88.7	88.7	88.7	88.7	88.7	88.7
80°	70.4	70.4	70.4	70.4	73.0	70.4	70.4	70.4
82.5°	52.1	49.6	52.1	49.6	52.1	52.1	52.1	52.1
85°	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3
87.5°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)