

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584402

Luminaire Tested: **HCC8W35D010BZ-HM82555830-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010BZ-HM82555830-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3248.8 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584402
CATALOG NUMBER: HCC8W35D010BZ-HM82555830-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584402

CATALOG NUMBER: HCC8W35D010BZ-HM82555830-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	53785	53785	53785
5°	56005	53665	51405
10°	57877	52983	48897
15°	59341	51768	46357
20°	59461	49620	44058
25°	58457	46480	41782
30°	55326	42888	39826
35°	50447	38570	37392
40°	43869	34003	34530
45°	37630	29445	31608
50°	32142	25392	28390
55°	28171	21865	24666
60°	25082	18650	20741
65°	22254	15220	16548
70°	19745	11288	9395
75°	16454	5898	2800
80°	12963	1847	462
85°	9234	920	0



TEST NUMBER: P584402
 CATALOG NUMBER: HCC8W35D010BZ-HM82555830-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.3	5.1
10°-20°	460.6	14.2
20°-30°	652.0	20.1
30°-40°	682.1	21.0
40°-50°	568.9	17.5
50°-60°	403.4	12.4
60°-70°	232.4	7.2
70°-80°	74.8	2.3
80°-90°	10.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1276.9	39.3
0°-40°	1959.0	60.3
0°-60°	2931.4	90.2
0°-90°	3248.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3248.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1744	1744	1744	1744	1744	
5°	1809	1786	1734	1682	1661	174
15°	1859	1783	1622	1494	1452	523
25°	1718	1590	1366	1257	1228	784
35°	1340	1223	1025	970	993	831
45°	863	793	675	683	725	669
55°	524	469	407	428	459	473
65°	305	256	209	209	227	305
75°	138	102	50	24	24	150
85°	26	13	3	0	0	33
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584402

CATALOG NUMBER: HCC8W35D010BZ-HM82555830-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2
2.5°	1780.7	1778.1	1775.4	1778.1	1775.4	1778.1	1775.4	1775.4	1772.8	1770.2	1770.2
5°	1809.3	1806.7	1806.7	1806.7	1804.1	1801.6	1801.6	1798.9	1793.6	1791.1	1785.9
7.5°	1827.5	1830.2	1830.2	1830.2	1824.9	1824.9	1819.8	1814.5	1809.3	1804.1	1796.3
10°	1848.4	1848.4	1845.9	1843.2	1838.0	1835.5	1832.8	1827.5	1819.8	1809.3	1801.6
12.5°	1856.3	1856.3	1853.7	1848.4	1845.9	1843.2	1840.6	1832.8	1822.4	1809.3	1798.9
15°	1858.8	1853.7	1851.0	1848.4	1843.2	1835.5	1835.5	1824.9	1812.0	1796.3	1783.2
17.5°	1838.0	1840.6	1835.5	1830.2	1822.4	1817.1	1809.3	1801.6	1785.9	1767.6	1754.6
20°	1812.0	1809.3	1806.7	1798.9	1788.5	1785.9	1778.1	1765.0	1752.0	1731.1	1712.9
22.5°	1770.2	1767.6	1762.4	1757.2	1746.8	1741.5	1733.7	1718.1	1699.8	1679.0	1658.2
25°	1718.1	1712.9	1705.0	1694.6	1686.8	1681.6	1671.1	1655.5	1634.7	1611.2	1590.3
27.5°	1634.7	1642.5	1637.3	1621.6	1613.8	1603.4	1600.8	1579.9	1561.6	1538.2	1514.8
30°	1553.8	1553.8	1546.0	1538.2	1525.2	1517.4	1506.8	1491.3	1473.1	1444.3	1426.1
32.5°	1452.1	1449.6	1439.2	1436.5	1426.1	1410.4	1407.9	1386.9	1368.7	1347.9	1324.4
35°	1340.1	1334.8	1324.4	1316.6	1311.3	1303.5	1295.8	1277.4	1259.2	1238.4	1222.7
37.5°	1212.3	1212.3	1209.7	1196.7	1191.4	1186.3	1178.4	1160.1	1149.7	1128.9	1113.2
40°	1089.8	1087.2	1079.4	1076.8	1071.5	1063.7	1058.4	1048.0	1032.4	1016.7	1001.2
42.5°	969.8	972.4	962.0	964.6	954.2	948.9	946.4	930.7	922.9	907.2	894.2
45°	862.9	860.3	855.1	852.5	847.3	842.1	836.9	829.0	816.1	800.4	792.6
47.5°	763.8	756.1	756.1	753.4	750.8	740.4	737.8	729.9	722.2	706.6	696.0
50°	670.0	670.0	670.0	667.4	659.6	657.0	651.8	643.9	636.1	625.7	610.0
52.5°	594.4	594.4	594.4	591.8	581.4	578.8	576.1	565.7	555.3	547.5	537.1
55°	524.0	526.6	524.0	518.9	510.9	510.9	503.2	498.0	487.6	479.7	469.3
57.5°	464.1	464.1	458.8	456.2	451.0	448.4	443.3	438.0	424.9	417.1	404.1
60°	406.7	404.1	404.1	398.9	393.7	388.5	385.9	378.1	372.8	359.8	349.3
62.5°	354.6	354.6	349.3	349.3	338.9	338.9	336.3	328.5	320.7	307.6	302.4
65°	305.0	305.0	302.4	299.9	292.0	289.4	286.8	279.0	271.1	263.3	255.5
67.5°	260.7	260.7	255.5	252.9	247.6	245.1	239.8	234.7	226.8	219.0	211.2
70°	219.0	216.4	213.7	211.2	205.9	203.3	198.1	192.9	185.1	179.9	172.0
72.5°	177.3	177.3	174.7	169.5	166.9	164.2	161.6	156.5	148.6	140.8	135.6
75°	138.1	138.1	138.1	133.0	127.7	125.2	125.2	119.9	114.8	106.9	101.7
77.5°	106.9	104.2	101.7	101.7	96.4	93.8	91.3	88.7	80.9	78.2	73.0
80°	73.0	75.6	73.0	70.4	67.8	65.2	65.2	60.0	57.4	52.1	47.0
82.5°	49.5	47.0	47.0	44.3	44.3	41.7	41.7	36.5	33.9	31.3	28.6
85°	26.1	26.1	23.5	23.5	23.5	20.8	20.8	18.2	18.2	15.7	13.1
87.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584402

CATALOG NUMBER: HCC8W35D010BZ-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2
2.5°	1767.6	1762.4	1759.7	1759.7	1757.2	1754.6	1752.0	1749.3	1744.2	1744.2	1738.9
5°	1780.7	1775.4	1772.8	1765.0	1759.7	1759.7	1749.3	1746.8	1738.9	1733.7	1728.5
7.5°	1791.1	1780.7	1772.8	1765.0	1759.7	1754.6	1744.2	1733.7	1723.3	1712.9	1707.6
10°	1791.1	1780.7	1767.6	1754.6	1749.3	1744.2	1731.1	1715.4	1702.5	1692.1	1679.0
12.5°	1785.9	1770.2	1754.6	1744.2	1733.7	1726.0	1710.3	1694.6	1679.0	1658.2	1647.7
15°	1770.2	1749.3	1733.7	1715.4	1707.6	1694.6	1681.6	1658.2	1639.8	1621.6	1608.6
17.5°	1738.9	1712.9	1694.6	1676.4	1663.3	1655.5	1634.7	1613.8	1593.0	1572.1	1556.4
20°	1692.1	1668.6	1647.7	1624.2	1613.8	1603.4	1577.3	1556.4	1535.6	1512.1	1496.4
22.5°	1634.7	1611.2	1582.6	1564.2	1548.7	1535.6	1512.1	1488.6	1467.8	1446.9	1426.1
25°	1564.2	1540.7	1514.8	1486.0	1475.6	1462.6	1436.5	1413.0	1389.6	1366.1	1347.9
27.5°	1488.6	1457.4	1436.5	1405.3	1394.8	1381.8	1353.1	1327.0	1306.2	1287.8	1267.0
30°	1397.3	1374.0	1345.2	1316.6	1306.2	1293.1	1269.6	1246.2	1225.3	1204.5	1183.6
32.5°	1298.4	1274.9	1246.2	1225.3	1209.7	1199.3	1175.8	1155.0	1134.1	1113.2	1095.0
35°	1194.0	1167.9	1147.1	1126.2	1113.2	1100.2	1076.8	1058.4	1042.9	1024.6	1006.3
37.5°	1087.2	1068.9	1048.0	1024.6	1011.6	1001.2	982.8	962.0	948.9	933.4	920.3
40°	982.8	962.0	943.8	922.9	912.5	904.6	886.4	870.8	857.8	844.7	836.9
42.5°	876.0	857.8	839.4	826.5	818.6	810.8	797.7	779.5	771.8	758.7	750.8
45°	776.9	761.3	748.3	729.9	724.8	719.5	703.9	690.9	683.1	675.2	670.0
47.5°	683.1	672.7	657.0	646.6	638.8	633.5	623.1	612.7	604.9	599.6	594.4
50°	602.2	589.2	578.8	568.3	563.2	555.3	544.9	539.7	534.4	529.3	529.3
52.5°	526.6	513.6	503.2	495.4	490.1	485.0	477.0	474.5	469.3	469.3	466.6
55°	456.2	448.4	438.0	427.6	424.9	422.3	417.1	411.9	409.4	406.7	409.4
57.5°	396.3	388.5	378.1	370.2	367.5	365.0	362.4	357.1	354.6	354.6	354.6
60°	341.5	333.8	325.9	318.1	318.1	312.8	310.3	307.6	305.0	302.4	302.4
62.5°	292.0	284.2	276.4	271.1	268.5	266.0	260.7	258.0	255.5	255.5	252.9
65°	247.6	237.2	234.7	226.8	224.3	221.6	219.0	213.7	211.2	208.6	205.9
67.5°	203.3	198.1	190.4	185.1	182.5	179.9	177.3	172.0	169.5	166.9	161.6
70°	164.2	159.0	153.8	148.6	146.0	143.4	138.1	133.0	130.3	125.2	117.3
72.5°	127.7	122.6	117.3	112.1	109.5	106.9	101.7	96.4	91.3	86.0	80.9
75°	96.4	91.3	83.4	78.2	75.6	75.6	67.8	62.5	57.4	49.5	44.3
77.5°	67.8	60.0	57.4	52.1	49.5	44.3	39.1	33.9	28.6	26.1	20.8
80°	44.3	39.1	33.9	31.3	28.6	26.1	23.5	18.2	13.1	10.4	7.8
82.5°	26.1	23.5	20.8	18.2	15.7	13.1	10.4	10.4	7.8	5.3	2.6
85°	13.1	10.4	7.8	7.8	5.3	5.3	5.3	2.6	2.6	2.6	2.6
87.5°	5.3	2.6	2.6	2.6	2.6	2.6	2.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584402

CATALOG NUMBER: HCC8W35D010BZ-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2
2.5°	1736.4	1733.7	1731.1	1728.5	1728.5	1723.3	1723.3	1720.7	1715.4	1712.9	1712.9
5°	1720.7	1712.9	1707.6	1705.0	1702.5	1694.6	1692.1	1686.8	1681.6	1676.4	1673.7
7.5°	1697.2	1684.1	1679.0	1676.4	1668.6	1660.7	1655.5	1647.7	1639.8	1632.0	1629.4
10°	1668.6	1655.5	1642.5	1637.3	1629.4	1624.2	1613.8	1603.4	1595.5	1587.7	1579.9
12.5°	1632.0	1616.3	1603.4	1598.1	1590.3	1579.9	1564.2	1559.1	1546.0	1540.7	1530.3
15°	1590.3	1572.1	1559.1	1551.2	1543.4	1527.8	1517.4	1506.8	1493.9	1488.6	1478.2
17.5°	1538.2	1517.4	1504.3	1496.4	1491.3	1478.2	1462.6	1449.6	1436.5	1431.3	1423.5
20°	1475.6	1462.6	1444.3	1436.5	1431.3	1415.7	1400.0	1394.8	1384.4	1374.0	1366.1
22.5°	1405.3	1392.2	1374.0	1366.1	1363.6	1350.5	1337.4	1329.7	1321.8	1314.0	1306.2
25°	1332.2	1316.6	1300.9	1295.8	1290.5	1280.1	1269.6	1264.5	1256.6	1251.4	1246.2
27.5°	1254.1	1238.4	1225.3	1217.5	1212.3	1204.5	1199.3	1194.0	1188.9	1183.6	1181.0
30°	1170.6	1155.0	1144.6	1139.3	1134.1	1131.5	1123.6	1121.1	1118.5	1113.2	1115.8
32.5°	1087.2	1074.1	1063.7	1055.9	1055.9	1050.6	1048.0	1048.0	1045.5	1045.5	1045.5
35°	995.9	988.1	980.3	977.7	975.1	972.4	969.8	972.4	969.8	972.4	975.1
37.5°	912.5	904.6	899.5	896.8	894.2	896.8	894.2	894.2	896.8	902.1	904.6
40°	826.5	821.2	816.1	818.6	816.1	816.1	816.1	823.9	826.5	829.0	831.7
42.5°	745.6	740.4	737.8	737.8	740.4	737.8	743.0	745.6	750.8	758.7	763.8
45°	667.4	664.8	664.8	667.4	664.8	670.0	670.0	675.2	683.1	688.3	693.5
47.5°	594.4	594.4	594.4	597.1	597.1	599.6	604.9	607.5	612.7	617.9	623.1
50°	526.6	529.3	531.8	531.8	531.8	537.1	542.3	544.9	547.5	550.1	557.9
52.5°	466.6	469.3	469.3	471.9	474.5	477.0	479.7	485.0	487.6	492.7	495.4
55°	409.4	409.4	414.5	417.1	417.1	417.1	422.3	422.3	427.6	430.2	435.4
57.5°	354.6	357.1	357.1	359.8	359.8	362.4	365.0	367.5	370.2	372.8	375.5
60°	302.4	302.4	302.4	305.0	307.6	310.3	307.6	312.8	312.8	318.1	320.7
62.5°	252.9	255.5	255.5	255.5	255.5	255.5	255.5	258.0	260.7	263.3	266.0
65°	205.9	205.9	205.9	203.3	205.9	203.3	205.9	208.6	208.6	211.2	213.7
67.5°	159.0	159.0	153.8	153.8	156.5	156.5	156.5	156.5	153.8	159.0	159.0
70°	114.8	112.1	109.5	106.9	106.9	104.2	104.2	101.7	101.7	101.7	101.7
72.5°	75.6	70.4	65.2	62.5	60.0	60.0	54.7	52.1	54.7	54.7	54.7
75°	39.1	33.9	31.3	28.6	26.1	26.1	23.5	23.5	23.5	23.5	23.5
77.5°	15.7	13.1	10.4	10.4	7.8	7.8	7.8	7.8	7.8	7.8	7.8
80°	5.3	5.3	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
85°	2.6	0.0	0.0	2.6	0.0	2.6	2.6	2.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584402

CATALOG NUMBER: HCC8W35D010BZ-HM82555830-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2	1744.2
2.5°	1710.3	1710.3	1707.6	1710.3	1705.0	1707.6	1705.0	1705.0
5°	1671.1	1665.9	1665.9	1665.9	1663.3	1663.3	1660.7	1660.7
7.5°	1624.2	1621.6	1619.0	1616.3	1613.8	1611.2	1611.2	1611.2
10°	1577.3	1572.1	1572.1	1569.5	1564.2	1561.6	1561.6	1561.6
12.5°	1522.5	1519.9	1517.4	1517.4	1506.8	1509.5	1506.8	1506.8
15°	1470.4	1467.8	1467.8	1460.0	1454.7	1454.7	1454.7	1452.1
17.5°	1415.7	1413.0	1410.4	1405.3	1400.0	1400.0	1397.3	1400.0
20°	1358.3	1355.7	1350.5	1350.5	1347.9	1345.2	1340.1	1342.6
22.5°	1300.9	1295.8	1293.1	1293.1	1290.5	1290.5	1285.3	1285.3
25°	1241.0	1238.4	1235.7	1238.4	1233.1	1233.1	1228.0	1228.0
27.5°	1178.4	1175.8	1175.8	1175.8	1173.2	1175.8	1173.2	1173.2
30°	1115.8	1115.8	1113.2	1113.2	1115.8	1113.2	1115.8	1118.5
32.5°	1048.0	1048.0	1050.6	1050.6	1053.3	1053.3	1053.3	1053.3
35°	977.7	982.8	982.8	985.5	988.1	990.7	990.7	993.3
37.5°	912.5	915.0	917.7	920.3	925.6	925.6	925.6	925.6
40°	842.1	844.7	849.9	847.3	857.8	860.3	857.8	857.8
42.5°	769.1	774.3	776.9	782.2	784.7	790.0	792.6	792.6
45°	701.3	703.9	709.1	714.4	717.0	724.8	724.8	724.8
47.5°	630.9	636.1	638.8	643.9	646.6	654.3	657.0	654.3
50°	563.2	568.3	573.6	573.6	581.4	584.0	589.2	591.8
52.5°	498.0	500.5	505.8	508.4	513.6	518.9	521.4	524.0
55°	435.4	438.0	443.3	443.3	451.0	453.7	458.8	458.8
57.5°	378.1	380.6	385.9	383.2	388.5	393.7	393.7	391.0
60°	323.2	323.2	323.2	328.5	331.1	333.8	336.3	336.3
62.5°	266.0	271.1	273.7	273.7	276.4	279.0	279.0	276.4
65°	213.7	219.0	221.6	221.6	224.3	224.3	224.3	226.8
67.5°	161.6	161.6	161.6	164.2	161.6	161.6	161.6	161.6
70°	101.7	101.7	101.7	101.7	99.1	101.7	101.7	104.2
72.5°	54.7	54.7	54.7	54.7	54.7	54.7	54.7	54.7
75°	23.5	23.5	23.5	26.1	23.5	23.5	23.5	23.5
77.5°	10.4	7.8	10.4	10.4	7.8	7.8	7.8	7.8
80°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
85°	0.0	2.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)