

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584262

Luminaire Tested: **HCC8W30D010MB-HM82555830-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584262  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W30D010MB-HM82555830-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3644.9 lumens  
Efficiency: N/A  
Efficacy: 130.2 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584262  
CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584262

CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	98	97	96	95	94	92	92	92	84																
	1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	90	93	90	88	90	88	86	84																
	2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	81	78	84	81	78	77	77	77	77																
	3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	77	77	77	77	77	77	77	77	77																
	4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70	70	70	70	70	70	70	70																
	5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64	64	64	64	64	64	64	64																
	6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59	59	59	59	59	59	59	59																
	7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54	54	54	54	54	54	54	54																
	8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50	50	50	50	50	50	50	50																
	9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46	46	46	46	46	46	46	46																
	10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43	43	43	43	43	43	43	43																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	87452
5°	85099
10°	84452
15°	83191
20°	80673
25°	77663
30°	72549
35°	60035
40°	36245
45°	24412
50°	17592
55°	10032
60°	4416
65°	1576
70°	586
75°	250
80°	0
85°	0



TEST NUMBER: P584262  
 CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	261.2	7.2
10°-20°	732.4	20.1
20°-30°	1044.7	28.7
30°-40°	951.3	26.1
40°-50°	448.8	12.3
50°-60°	176.5	4.8
60°-70°	28.1	0.8
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2038.3	55.9
0°-40°	2989.6	82.0
0°-60°	3614.9	99.2
0°-90°	3644.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3644.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2836	
5°	2749	261
15°	2606	732
25°	2283	1045
35°	1595	951
45°	560	449
55°	187	176
65°	22	28
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P584262  
CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2836.0
2.5°	2799.1
5°	2749.2
7.5°	2721.0
10°	2697.1
12.5°	2658.0
15°	2605.9
17.5°	2540.9
20°	2458.4
22.5°	2371.6
25°	2282.6
27.5°	2174.2
30°	2037.5
32.5°	1853.1
35°	1594.8
37.5°	1232.5
40°	900.4
42.5°	692.2
45°	559.8
47.5°	460.0
50°	366.7
52.5°	275.6
55°	186.6
57.5°	117.1
60°	71.6
62.5°	43.4
65°	21.6
67.5°	10.8
70°	6.5
72.5°	2.1
75°	2.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)