

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584268

Luminaire Tested: **HCC8S30D010BZ-HM82555830-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010BZ-HM82555830-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3072.2 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584268
CATALOG NUMBER: HCC8S30D010BZ-HM82555830-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584268

CATALOG NUMBER: HCC8S30D010BZ-HM82555830-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	47102	47102	47102
5°	48827	46948	45335
10°	50209	46536	43480
15°	51328	45715	41559
20°	51408	43930	39871
25°	50424	41489	38464
30°	47823	38477	36775
35°	43453	35043	35122
40°	37992	31446	33101
45°	32929	28010	30845
50°	28832	24874	28102
55°	25666	22048	25429
60°	23152	19803	22350
65°	20897	17409	19474
70°	18780	14678	14471
75°	16549	11628	10854
80°	13869	9625	10406
85°	10720	8456	9199



TEST NUMBER: P584268
 CATALOG NUMBER: HCC8S30D010BZ-HM82555830-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.1	4.7
10°-20°	405.9	13.2
20°-30°	580.1	18.9
30°-40°	616.3	20.1
40°-50°	530.7	17.3
50°-60°	396.7	12.9
60°-70°	253.1	8.2
70°-80°	115.2	3.7
80°-90°	30.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1130.0	36.8
0°-40°	1746.4	56.8
0°-60°	2673.8	87.0
0°-90°	3072.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3072.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1528	1528	1528	1528	1528	
5°	1577	1556	1517	1478	1465	151
15°	1608	1554	1432	1334	1302	453
25°	1482	1389	1219	1146	1130	678
35°	1154	1074	931	907	933	719
45°	755	714	642	660	707	587
55°	477	438	410	445	473	429
65°	286	254	239	250	267	286
75°	139	119	98	89	91	148
85°	30	26	24	26	26	37
90°	0	0	0	0	0	



TEST NUMBER: P584268

CATALOG NUMBER: HCC8S30D010BZ-HM82555830-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5
2.5°	1555.7	1551.4	1553.5	1551.4	1553.5	1553.5	1549.3	1549.3	1549.3	1549.3	1542.7
5°	1577.4	1575.3	1575.3	1573.0	1570.9	1573.0	1570.9	1568.8	1564.4	1562.2	1555.7
7.5°	1590.4	1590.4	1590.4	1590.4	1588.3	1586.1	1584.0	1579.6	1575.3	1570.9	1566.6
10°	1603.5	1605.6	1603.5	1601.3	1599.1	1594.8	1592.7	1588.3	1581.7	1575.3	1570.9
12.5°	1610.0	1610.0	1607.8	1607.8	1603.5	1601.3	1594.8	1588.3	1581.7	1575.3	1564.4
15°	1607.8	1607.8	1605.6	1603.5	1596.9	1594.8	1590.4	1584.0	1573.0	1564.4	1553.5
17.5°	1594.8	1592.7	1588.3	1588.3	1579.6	1577.4	1573.0	1564.4	1553.5	1540.6	1527.5
20°	1566.6	1566.6	1564.4	1562.2	1553.5	1547.0	1542.7	1531.9	1523.2	1508.0	1494.9
22.5°	1527.5	1531.9	1527.5	1523.2	1512.3	1510.1	1503.6	1490.6	1477.6	1460.2	1445.1
25°	1482.0	1479.8	1477.6	1473.3	1464.6	1460.2	1451.5	1438.6	1425.5	1406.0	1388.6
27.5°	1423.4	1414.7	1414.7	1406.0	1399.5	1393.0	1388.6	1375.7	1358.3	1343.1	1321.3
30°	1343.1	1345.2	1334.4	1332.3	1321.3	1317.1	1308.4	1295.3	1280.2	1262.8	1245.5
32.5°	1256.3	1249.8	1249.8	1241.1	1232.4	1225.9	1223.7	1208.6	1195.5	1178.2	1160.8
35°	1154.3	1154.3	1147.9	1145.6	1136.9	1132.6	1126.1	1117.4	1102.2	1087.1	1074.0
37.5°	1054.5	1050.1	1048.0	1043.7	1037.2	1030.6	1030.6	1015.4	1013.3	995.9	978.5
40°	943.8	948.2	943.8	937.3	935.1	930.9	928.6	919.9	913.5	898.3	887.5
42.5°	850.5	846.2	846.2	844.1	835.4	835.4	831.0	826.7	815.8	811.5	798.5
45°	755.1	759.4	752.9	755.1	746.5	746.5	746.5	737.8	729.1	722.6	713.9
47.5°	672.6	674.8	674.8	668.3	666.1	666.1	661.8	657.4	651.0	642.3	635.8
50°	601.0	603.2	598.9	596.6	592.4	590.2	590.2	581.5	577.1	568.5	564.2
52.5°	535.9	535.9	533.7	533.7	527.2	527.2	522.9	516.4	512.1	507.7	496.9
55°	477.4	477.4	475.1	473.0	473.0	466.4	464.3	457.8	453.5	444.8	438.3
57.5°	420.9	423.0	420.9	418.8	416.6	414.4	410.1	403.5	399.3	392.7	388.4
60°	375.4	375.4	373.2	371.1	366.7	364.5	362.4	358.0	351.5	347.2	340.6
62.5°	332.0	329.8	327.7	325.4	321.1	321.1	316.7	312.5	305.9	301.6	297.2
65°	286.4	286.4	284.3	284.3	282.0	277.8	275.6	273.4	264.7	262.5	253.9
67.5°	245.2	247.3	243.0	243.0	238.6	238.6	236.5	230.0	227.8	223.5	219.1
70°	208.3	208.3	208.3	206.2	201.8	199.6	197.5	193.1	191.0	186.6	182.3
72.5°	171.5	171.5	169.2	169.2	167.1	164.9	162.8	158.4	158.4	154.1	149.7
75°	138.9	138.9	136.7	134.5	132.3	132.3	130.2	128.1	123.7	121.5	119.4
77.5°	106.3	106.3	106.3	104.2	102.0	102.0	102.0	97.6	93.3	93.3	91.1
80°	78.1	78.1	76.0	76.0	73.7	73.7	73.7	71.6	69.4	67.3	65.0
82.5°	52.1	52.1	52.1	52.1	49.9	49.9	49.9	47.7	45.5	45.5	45.5
85°	30.3	30.3	30.3	30.3	28.2	28.2	28.2	28.2	28.2	26.0	26.0
87.5°	13.0	10.8	13.0	10.8	13.0	10.8	13.0	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584268

CATALOG NUMBER: HCC8S30D010BZ-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5
2.5°	1544.9	1542.7	1540.6	1538.3	1538.3	1536.2	1531.9	1529.6	1527.5	1525.4	1525.4
5°	1553.5	1551.4	1547.0	1542.7	1540.6	1536.2	1531.9	1527.5	1523.2	1516.7	1514.5
7.5°	1560.1	1553.5	1549.3	1540.6	1538.3	1534.0	1527.5	1521.0	1512.3	1503.6	1497.2
10°	1560.1	1551.4	1544.9	1534.0	1529.6	1525.4	1516.7	1505.9	1494.9	1486.2	1475.4
12.5°	1555.7	1544.9	1534.0	1523.2	1516.7	1510.1	1497.2	1486.2	1473.3	1460.2	1451.5
15°	1540.6	1527.5	1514.5	1501.5	1494.9	1486.2	1473.3	1458.1	1445.1	1432.0	1416.8
17.5°	1512.3	1499.3	1484.1	1468.9	1460.2	1453.8	1434.2	1423.4	1403.9	1390.8	1377.8
20°	1475.4	1460.2	1440.7	1425.5	1414.7	1408.1	1393.0	1373.4	1358.3	1338.7	1325.7
22.5°	1427.8	1408.1	1388.6	1373.4	1362.6	1353.9	1334.4	1314.9	1301.8	1284.5	1269.3
25°	1371.3	1351.8	1332.3	1310.5	1299.7	1291.0	1273.7	1256.3	1238.9	1219.4	1206.4
27.5°	1304.0	1282.3	1265.0	1245.5	1234.5	1221.6	1202.1	1184.7	1167.4	1154.3	1136.9
30°	1230.3	1206.4	1189.0	1169.5	1158.7	1147.9	1128.2	1110.9	1095.8	1080.6	1071.9
32.5°	1141.3	1124.0	1106.6	1087.1	1078.4	1071.9	1052.4	1035.0	1017.7	1004.6	998.0
35°	1056.7	1037.2	1021.9	1004.6	993.8	987.2	969.9	954.6	946.0	930.9	922.2
37.5°	967.7	952.5	935.1	917.8	911.2	904.8	891.8	876.5	863.6	852.8	848.4
40°	874.4	861.4	846.2	835.4	828.9	822.3	811.5	800.7	792.0	781.2	776.8
42.5°	785.5	776.8	763.8	750.7	744.2	742.1	729.1	720.4	716.0	711.7	707.3
45°	705.2	692.1	683.4	674.8	668.3	663.9	657.4	651.0	646.6	642.3	637.9
47.5°	627.1	616.3	607.6	601.0	594.5	592.4	588.0	581.5	577.1	577.1	577.1
50°	555.5	546.8	538.1	533.7	531.6	527.2	522.9	520.8	518.5	518.5	518.5
52.5°	492.5	483.8	477.4	473.0	473.0	468.7	464.3	462.2	462.2	462.2	462.2
55°	434.0	427.4	423.0	418.8	414.4	412.2	412.2	412.2	410.1	410.1	412.2
57.5°	381.9	377.5	371.1	366.7	364.5	364.5	362.4	360.1	362.4	364.5	366.7
60°	334.1	329.8	327.7	321.1	321.1	321.1	319.0	319.0	319.0	321.1	323.3
62.5°	290.7	288.6	284.3	282.0	279.9	279.9	277.8	277.8	277.8	277.8	279.9
65°	251.7	247.3	243.0	243.0	243.0	240.9	240.9	236.5	238.6	238.6	236.5
67.5°	214.9	210.5	208.3	206.2	203.9	203.9	201.8	199.6	197.5	197.5	197.5
70°	180.1	175.7	175.7	171.5	171.5	169.2	167.1	167.1	164.9	162.8	160.5
72.5°	145.4	143.2	141.0	138.9	138.9	138.9	136.7	134.5	132.3	130.2	125.8
75°	115.0	115.0	110.7	108.4	108.4	106.3	104.2	102.0	99.8	97.6	95.5
77.5°	88.9	86.8	82.4	80.3	80.3	80.3	78.1	76.0	73.7	71.6	69.4
80°	65.0	62.9	60.8	58.6	58.6	58.6	56.4	56.4	54.2	54.2	54.2
82.5°	43.4	43.4	41.3	41.3	41.3	41.3	39.0	39.0	39.0	39.0	39.0
85°	26.0	26.0	23.9	23.9	23.9	23.9	23.9	23.9	23.9	23.9	23.9
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584268

CATALOG NUMBER: HCC8S30D010BZ-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5
2.5°	1521.0	1521.0	1516.7	1514.5	1512.3	1514.5	1510.1	1508.0	1505.9	1505.9	1503.6
5°	1508.0	1505.9	1497.2	1494.9	1492.8	1490.6	1486.2	1482.0	1477.6	1475.4	1473.3
7.5°	1490.6	1484.1	1475.4	1473.3	1471.1	1464.6	1458.1	1453.8	1447.3	1445.1	1440.7
10°	1466.8	1458.1	1451.5	1445.1	1440.7	1434.2	1427.8	1421.2	1412.5	1410.4	1403.9
12.5°	1438.6	1427.8	1414.7	1412.5	1406.0	1397.3	1388.6	1382.1	1375.7	1371.3	1364.7
15°	1403.9	1393.0	1380.0	1373.4	1367.0	1360.5	1349.6	1341.0	1334.4	1327.9	1321.3
17.5°	1362.6	1349.6	1338.7	1332.3	1327.9	1317.1	1308.4	1297.6	1291.0	1284.5	1277.9
20°	1312.7	1301.8	1286.6	1280.2	1277.9	1269.3	1258.4	1254.2	1245.5	1238.9	1234.5
22.5°	1256.3	1245.5	1232.4	1228.1	1219.4	1215.0	1204.2	1199.9	1195.5	1189.0	1186.9
25°	1193.4	1182.6	1171.6	1169.5	1163.0	1158.7	1152.1	1145.6	1145.6	1139.2	1139.2
27.5°	1128.2	1117.4	1108.7	1104.5	1102.2	1097.9	1091.4	1089.2	1087.1	1084.8	1084.8
30°	1058.8	1045.8	1041.4	1039.3	1037.2	1032.8	1030.6	1026.3	1028.5	1030.6	1028.5
32.5°	985.1	980.7	972.0	967.7	969.9	967.7	963.3	967.7	965.6	969.9	972.0
35°	913.5	909.1	904.8	904.8	900.4	900.4	900.4	902.6	907.0	909.1	913.5
37.5°	844.1	837.5	835.4	833.1	835.4	835.4	835.4	839.7	844.1	848.4	854.9
40°	770.2	766.0	766.0	766.0	766.0	772.5	770.2	774.6	778.9	785.5	792.0
42.5°	700.8	700.8	703.1	703.1	703.1	703.1	707.3	713.9	720.4	726.8	733.4
45°	635.8	635.8	635.8	640.0	640.0	642.3	651.0	655.3	659.7	666.1	672.6
47.5°	575.0	575.0	577.1	579.3	581.5	585.8	590.2	596.6	603.2	607.6	614.0
50°	518.5	520.8	525.1	529.5	529.5	531.6	538.1	542.4	546.8	553.2	555.5
52.5°	464.3	468.7	473.0	475.1	477.4	481.7	483.8	490.3	492.5	499.0	501.2
55°	414.4	416.6	423.0	425.3	425.3	429.6	434.0	438.3	444.8	444.8	449.1
57.5°	368.8	371.1	375.4	377.5	375.4	381.9	384.0	388.4	390.6	394.9	397.1
60°	323.3	327.7	329.8	329.8	332.0	334.1	338.5	338.5	342.8	347.2	347.2
62.5°	279.9	282.0	284.3	286.4	288.6	286.4	293.0	293.0	297.2	299.4	303.8
65°	238.6	240.9	240.9	243.0	243.0	245.2	245.2	247.3	249.6	253.9	256.0
67.5°	197.5	197.5	197.5	199.6	197.5	199.6	199.6	201.8	201.8	206.2	208.3
70°	160.5	158.4	156.2	156.2	156.2	156.2	154.1	156.2	156.2	158.4	158.4
72.5°	123.7	121.5	119.4	117.1	117.1	115.0	112.8	115.0	115.0	117.1	117.1
75°	93.3	88.9	88.9	88.9	86.8	86.8	86.8	88.9	88.9	88.9	91.1
77.5°	69.4	69.4	67.3	67.3	67.3	69.4	69.4	71.6	71.6	71.6	71.6
80°	52.1	54.2	54.2	54.2	54.2	56.4	56.4	56.4	56.4	58.6	58.6
82.5°	39.0	39.0	39.0	39.0	41.3	41.3	41.3	41.3	41.3	41.3	41.3
85°	23.9	26.0	26.0	23.9	26.0	26.0	26.0	26.0	26.0	26.0	26.0
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584268

CATALOG NUMBER: HCC8S30D010BZ-HM82555830-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5	1527.5
2.5°	1501.5	1501.5	1501.5	1501.5	1499.3	1499.3	1499.3	1497.2
5°	1468.9	1468.9	1468.9	1464.6	1466.8	1466.8	1462.5	1464.6
7.5°	1436.4	1434.2	1432.0	1432.0	1429.9	1427.8	1425.5	1427.8
10°	1399.5	1393.0	1393.0	1390.8	1390.8	1386.5	1386.5	1388.6
12.5°	1358.3	1353.9	1353.9	1351.8	1349.6	1347.4	1345.2	1345.2
15°	1317.1	1312.7	1310.5	1308.4	1306.2	1301.8	1304.0	1301.8
17.5°	1275.8	1269.3	1269.3	1267.1	1265.0	1260.6	1260.6	1258.4
20°	1228.1	1225.9	1221.6	1223.7	1221.6	1217.2	1215.0	1215.0
22.5°	1180.3	1180.3	1178.2	1178.2	1176.0	1173.9	1171.6	1171.6
25°	1134.8	1132.6	1134.8	1134.8	1128.2	1128.2	1128.2	1130.5
27.5°	1082.7	1084.8	1082.7	1082.7	1082.7	1082.7	1084.8	1082.7
30°	1030.6	1030.6	1030.6	1032.8	1037.2	1035.0	1035.0	1032.8
32.5°	974.3	976.4	976.4	978.5	980.7	985.1	985.1	987.2
35°	917.8	922.2	924.3	922.2	928.6	928.6	933.0	933.0
37.5°	859.2	861.4	865.7	867.9	872.3	874.4	876.5	876.5
40°	796.3	805.0	807.2	809.4	815.8	815.8	818.0	822.3
42.5°	737.8	746.5	748.6	750.7	755.1	761.6	759.4	763.8
45°	681.3	687.8	690.0	692.1	698.7	700.8	700.8	707.3
47.5°	620.5	624.9	627.1	631.4	635.8	640.0	644.4	642.3
50°	559.8	566.3	570.6	572.9	579.3	581.5	583.7	585.8
52.5°	505.6	509.8	512.1	514.2	520.8	522.9	525.1	529.5
55°	453.5	455.6	460.0	457.8	464.3	466.4	468.7	473.0
57.5°	401.4	403.5	405.7	405.7	410.1	414.4	416.6	418.8
60°	351.5	355.9	358.0	358.0	358.0	362.4	362.4	362.4
62.5°	305.9	305.9	308.1	308.1	312.5	312.5	312.5	312.5
65°	258.3	260.4	262.5	262.5	266.9	264.7	269.1	266.9
67.5°	208.3	208.3	212.6	212.6	210.5	212.6	212.6	212.6
70°	158.4	158.4	160.5	160.5	160.5	160.5	160.5	160.5
72.5°	117.1	117.1	117.1	119.4	117.1	117.1	119.4	117.1
75°	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.1
77.5°	71.6	71.6	73.7	73.7	73.7	73.7	73.7	73.7
80°	58.6	58.6	58.6	58.6	60.8	58.6	58.6	58.6
82.5°	43.4	41.3	43.4	41.3	43.4	43.4	43.4	43.4
85°	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)