

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584267

Luminaire Tested: **HCC8W30D010MB-HM82555830-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MB-HM82555830-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2950.7 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584267
CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584267

CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	49301	49301	49301
5°	51037	49019	47072
10°	52166	48161	44425
15°	52908	46539	41485
20°	52751	44281	38515
25°	51448	41411	35358
30°	48742	38081	32441
35°	44341	34463	29483
40°	38946	30649	26636
45°	33963	26964	23750
50°	29556	23627	20916
55°	26354	20763	18193
60°	23947	18193	15517
65°	21525	15833	14090
70°	19168	13497	12712
75°	16799	11378	10854
80°	14260	9252	9625
85°	10720	6899	7642



TEST NUMBER: P584267
 CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.8	5.1
10°-20°	412.6	14.0
20°-30°	572.8	19.4
30°-40°	592.2	20.1
40°-50°	495.8	16.8
50°-60°	359.9	12.2
60°-70°	227.2	7.7
70°-80°	112.5	3.8
80°-90°	28.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1135.1	38.5
0°-40°	1727.3	58.5
0°-60°	2583.1	87.5
0°-90°	2950.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2950.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1599	1599	1599	1599	1599	
5°	1649	1629	1584	1540	1521	158
15°	1657	1594	1458	1341	1300	466
25°	1512	1414	1217	1085	1039	693
35°	1178	1091	916	811	783	734
45°	779	722	618	558	545	602
55°	490	447	386	354	338	442
65°	295	258	217	191	193	294
75°	141	117	96	91	91	151
85°	30	24	20	22	22	37
90°	0	0	0	0	0	



TEST NUMBER: P584267

CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8
2.5°	1624.9	1624.9	1627.0	1624.9	1624.9	1624.9	1622.7	1622.7	1620.5	1620.5	1616.2
5°	1648.8	1644.4	1648.8	1644.4	1644.4	1644.4	1642.2	1637.8	1635.7	1631.4	1629.2
7.5°	1659.6	1657.3	1657.3	1655.2	1655.2	1653.1	1650.9	1648.8	1640.1	1637.8	1631.4
10°	1666.0	1663.9	1663.9	1661.7	1657.3	1657.3	1653.1	1650.9	1640.1	1635.7	1627.0
12.5°	1663.9	1663.9	1663.9	1661.7	1655.2	1653.1	1648.8	1642.2	1633.6	1624.9	1616.2
15°	1657.3	1657.3	1653.1	1650.9	1644.4	1640.1	1637.8	1627.0	1618.3	1607.5	1594.4
17.5°	1635.7	1635.7	1633.6	1629.2	1622.7	1618.3	1614.1	1603.1	1594.4	1577.1	1564.1
20°	1607.5	1605.4	1603.1	1596.7	1590.2	1588.0	1581.5	1566.3	1555.4	1542.4	1525.1
22.5°	1566.3	1564.1	1562.0	1557.6	1546.8	1542.4	1538.1	1527.3	1507.8	1494.7	1473.1
25°	1512.1	1512.1	1507.8	1501.2	1490.4	1486.0	1479.5	1468.7	1451.3	1431.8	1414.4
27.5°	1449.2	1447.0	1440.5	1436.1	1427.4	1421.0	1410.2	1397.1	1379.7	1364.5	1342.9
30°	1368.9	1368.9	1364.5	1358.1	1347.1	1342.9	1334.2	1319.0	1301.6	1282.1	1266.9
32.5°	1277.8	1277.8	1271.3	1266.9	1260.5	1249.5	1247.4	1230.0	1214.8	1199.7	1182.3
35°	1177.9	1180.2	1175.8	1167.1	1156.3	1156.3	1151.9	1136.8	1119.4	1104.2	1091.1
37.5°	1078.2	1071.6	1069.5	1065.1	1058.7	1050.0	1045.6	1039.2	1024.0	1013.1	993.5
40°	967.5	969.7	965.3	961.1	958.8	952.4	950.1	939.3	928.5	915.5	906.9
42.5°	867.7	867.7	867.7	863.5	859.1	852.5	850.4	843.8	830.9	822.2	809.2
45°	778.8	772.3	772.3	770.1	768.0	763.6	757.2	752.8	744.1	737.5	722.4
47.5°	692.0	694.3	692.0	689.9	683.3	681.2	679.0	670.4	661.7	655.1	644.3
50°	616.1	620.4	616.1	616.1	611.7	609.6	605.2	598.8	592.2	581.4	570.6
52.5°	553.2	553.2	551.0	548.8	542.3	538.0	535.9	533.6	522.8	514.1	505.4
55°	490.2	492.5	492.5	485.9	483.8	479.4	477.3	470.7	466.4	453.4	446.9
57.5°	436.0	433.9	436.0	431.7	427.3	423.0	420.9	416.5	410.0	401.3	392.6
60°	388.3	383.9	383.9	381.8	377.5	375.2	371.0	364.4	357.9	349.3	342.8
62.5°	340.6	338.4	336.2	334.1	329.7	327.6	325.4	318.9	312.4	305.9	299.4
65°	295.0	295.0	292.9	288.6	286.3	284.2	282.0	277.6	269.0	264.7	258.1
67.5°	253.9	251.6	251.6	247.3	242.9	240.8	240.8	236.5	230.0	223.4	219.1
70°	212.6	214.7	212.6	210.5	206.1	206.1	201.8	199.6	191.0	188.7	182.3
72.5°	175.7	175.7	173.6	173.6	169.2	167.1	167.1	162.7	158.4	154.0	149.7
75°	141.0	141.0	141.0	138.9	136.6	132.3	132.3	130.2	125.8	121.5	117.1
77.5°	110.7	108.4	108.4	106.3	104.2	102.0	102.0	99.8	95.5	93.3	88.9
80°	80.3	78.1	78.1	78.1	73.7	76.0	73.7	71.6	69.4	67.3	65.0
82.5°	52.1	54.2	54.2	52.1	49.9	49.9	49.9	47.7	47.7	45.5	43.4
85°	30.3	30.3	30.3	30.3	28.2	28.2	28.2	26.0	26.0	26.0	23.9
87.5°	13.0	13.0	13.0	13.0	13.0	13.0	10.8	10.8	10.8	10.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584267

CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8
2.5°	1616.2	1611.8	1609.7	1607.5	1607.5	1605.4	1603.1	1598.8	1598.8	1594.4	1592.3
5°	1624.9	1618.3	1614.1	1609.7	1607.5	1603.1	1598.8	1592.3	1590.2	1583.6	1577.1
7.5°	1627.0	1616.2	1611.8	1603.1	1598.8	1594.4	1585.8	1579.3	1570.7	1564.1	1555.4
10°	1618.3	1609.7	1598.8	1588.0	1585.8	1579.3	1566.3	1557.6	1546.8	1538.1	1525.1
12.5°	1605.4	1592.3	1581.5	1568.4	1562.0	1555.4	1542.4	1529.4	1514.2	1499.1	1486.0
15°	1583.6	1568.4	1553.3	1538.1	1529.4	1522.9	1507.8	1492.6	1477.3	1457.8	1444.8
17.5°	1551.1	1533.8	1518.6	1499.1	1490.4	1483.9	1464.4	1447.0	1427.4	1407.9	1394.9
20°	1509.9	1488.2	1470.8	1449.2	1442.6	1431.8	1412.3	1392.8	1371.0	1349.4	1334.2
22.5°	1455.7	1433.9	1414.4	1392.8	1381.9	1371.0	1351.5	1327.6	1306.0	1288.6	1273.4
25°	1392.8	1373.2	1349.4	1329.8	1316.8	1303.7	1282.1	1262.6	1243.1	1217.1	1201.8
27.5°	1323.4	1299.5	1282.1	1256.1	1243.1	1234.4	1210.5	1184.5	1167.1	1143.2	1125.9
30°	1245.2	1223.5	1204.0	1177.9	1165.0	1156.3	1134.5	1110.8	1093.4	1069.5	1052.1
32.5°	1162.8	1138.9	1115.0	1097.7	1082.5	1073.8	1050.0	1034.8	1013.1	993.5	974.0
35°	1073.8	1050.0	1032.6	1008.7	1000.1	991.4	971.9	952.4	932.9	915.5	900.3
37.5°	978.4	961.1	941.6	924.2	917.7	909.0	885.1	867.7	852.5	835.2	822.2
40°	885.1	869.9	856.9	839.6	828.7	822.2	804.8	789.6	772.3	761.4	748.5
42.5°	800.6	783.2	770.1	757.2	746.2	739.8	724.6	713.8	700.7	689.9	674.6
45°	711.5	702.9	687.7	676.9	670.4	661.7	650.9	637.8	627.0	618.3	607.5
47.5°	633.5	624.8	613.9	600.9	596.5	590.1	579.3	570.6	561.9	553.2	542.3
50°	561.9	551.0	542.3	533.6	529.3	522.8	512.0	507.6	501.2	492.5	485.9
52.5°	496.8	488.1	479.4	468.6	466.4	462.0	455.6	446.9	440.4	436.0	431.7
55°	438.3	429.6	423.0	414.4	412.2	407.8	399.1	394.9	390.5	386.2	381.8
57.5°	386.2	377.5	368.8	364.4	360.1	355.7	353.6	347.1	342.8	340.6	336.2
60°	338.4	329.7	323.3	316.7	314.6	312.4	308.1	303.7	299.4	295.0	292.9
62.5°	292.9	284.2	279.9	275.5	271.2	271.2	266.8	262.5	258.1	256.0	251.6
65°	251.6	247.3	240.8	234.4	232.1	232.1	225.7	223.4	221.3	217.0	212.6
67.5°	212.6	208.3	201.8	199.6	197.4	195.2	193.1	188.7	184.4	182.3	177.9
70°	177.9	173.6	169.2	167.1	164.9	162.7	158.4	156.2	151.8	149.7	147.6
72.5°	143.2	141.0	136.6	134.5	132.3	130.2	127.9	125.8	121.5	119.3	117.1
75°	115.0	112.8	108.4	106.3	104.2	104.2	102.0	97.6	95.5	95.5	93.3
77.5°	86.8	84.7	82.4	80.3	78.1	78.1	76.0	73.7	71.6	71.6	69.4
80°	62.9	60.8	58.6	58.6	58.6	56.4	54.2	54.2	52.1	52.1	49.9
82.5°	41.3	41.3	39.0	39.0	39.0	36.9	36.9	34.7	34.7	34.7	34.7
85°	23.9	23.9	23.9	21.6	21.6	21.6	21.6	21.6	21.6	19.5	21.6
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	8.7	8.7	8.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584267

CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8
2.5°	1590.2	1588.0	1583.6	1583.6	1579.3	1579.3	1577.1	1574.9	1572.8	1570.7	1568.4
5°	1574.9	1566.3	1562.0	1559.7	1555.4	1553.3	1546.8	1542.4	1540.2	1536.0	1531.6
7.5°	1546.8	1538.1	1529.4	1527.3	1525.1	1516.5	1509.9	1503.4	1499.1	1494.7	1490.4
10°	1514.2	1505.5	1494.7	1490.4	1486.0	1475.2	1466.5	1460.0	1451.3	1442.6	1440.5
12.5°	1475.2	1462.1	1449.2	1444.8	1438.3	1427.4	1418.8	1407.9	1401.5	1390.5	1388.4
15°	1429.7	1414.4	1403.6	1392.8	1388.4	1377.6	1362.4	1353.7	1340.7	1336.3	1325.5
17.5°	1375.4	1360.2	1345.0	1340.7	1334.2	1319.0	1303.7	1292.9	1280.0	1273.4	1266.9
20°	1319.0	1299.5	1284.2	1280.0	1271.3	1258.2	1243.1	1232.2	1221.3	1208.4	1201.8
22.5°	1253.9	1232.2	1219.2	1208.4	1206.1	1191.0	1173.7	1165.0	1156.3	1145.5	1136.8
25°	1182.3	1162.8	1147.6	1138.9	1134.5	1121.6	1108.5	1097.7	1084.7	1078.2	1067.4
27.5°	1108.5	1095.5	1076.0	1067.4	1060.8	1050.0	1034.8	1028.2	1015.3	1006.6	1000.1
30°	1036.9	1017.4	1006.6	995.8	989.2	978.4	965.3	958.8	948.0	939.3	932.9
32.5°	958.8	945.8	930.6	926.3	917.7	906.9	898.2	887.2	878.6	869.9	867.7
35°	887.2	869.9	854.8	850.4	843.8	833.0	828.7	822.2	811.4	809.2	800.6
37.5°	809.2	800.6	783.2	776.7	774.5	765.8	757.2	752.8	746.2	739.8	737.5
40°	735.4	724.6	715.9	709.4	705.1	698.5	689.9	687.7	683.3	674.6	672.5
42.5°	666.0	655.1	646.5	644.3	637.8	631.2	627.0	620.4	618.3	616.1	611.7
45°	598.8	592.2	583.6	581.4	579.3	570.6	566.2	561.9	557.5	555.4	551.0
47.5°	538.0	531.5	524.9	522.8	518.5	516.3	509.8	507.6	501.2	498.9	496.8
50°	479.4	475.1	470.7	468.6	464.3	462.0	457.8	453.4	449.1	446.9	444.7
52.5°	427.3	423.0	418.6	416.5	414.4	410.0	405.7	401.3	399.1	397.0	394.9
55°	377.5	373.1	371.0	368.8	366.6	364.4	357.9	355.7	353.6	351.5	347.1
57.5°	332.0	327.6	323.3	323.3	321.0	318.9	314.6	310.2	310.2	305.9	301.5
60°	290.7	286.3	282.0	279.9	277.6	273.4	271.2	269.0	266.8	264.7	260.3
62.5°	247.3	245.2	240.8	240.8	236.5	234.4	232.1	230.0	227.8	223.4	221.3
65°	210.5	208.3	203.9	201.8	201.8	199.6	195.2	193.1	191.0	191.0	188.7
67.5°	175.7	173.6	169.2	167.1	167.1	164.9	162.7	162.7	160.5	158.4	160.5
70°	145.3	141.0	141.0	138.9	138.9	136.6	134.5	134.5	134.5	136.6	136.6
72.5°	115.0	112.8	110.7	110.7	110.7	110.7	108.4	108.4	110.7	112.8	112.8
75°	91.1	88.9	88.9	88.9	86.8	86.8	88.9	88.9	91.1	91.1	91.1
77.5°	67.3	67.3	67.3	67.3	67.3	67.3	69.4	69.4	71.6	71.6	71.6
80°	49.9	49.9	49.9	49.9	49.9	52.1	52.1	52.1	52.1	52.1	54.2
82.5°	34.7	34.7	34.7	34.7	34.7	34.7	34.7	36.9	36.9	36.9	36.9
85°	19.5	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6
87.5°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584267

CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8	1598.8
2.5°	1566.3	1566.3	1566.3	1568.4	1564.1	1564.1	1564.1	1564.1
5°	1529.4	1527.3	1525.1	1527.3	1522.9	1522.9	1520.7	1520.7
7.5°	1483.9	1481.7	1479.5	1479.5	1475.2	1475.2	1473.1	1470.8
10°	1433.9	1429.7	1431.8	1427.4	1425.3	1423.1	1421.0	1418.8
12.5°	1379.7	1375.4	1373.2	1368.9	1364.5	1362.4	1364.5	1360.2
15°	1321.1	1314.7	1312.4	1308.1	1303.7	1301.6	1301.6	1299.5
17.5°	1256.1	1251.8	1249.5	1245.2	1243.1	1238.7	1236.6	1234.4
20°	1195.3	1184.5	1186.6	1182.3	1180.2	1171.5	1171.5	1173.7
22.5°	1128.1	1121.6	1117.2	1112.9	1110.8	1106.4	1106.4	1104.2
25°	1060.8	1054.3	1052.1	1047.9	1045.6	1041.3	1039.2	1039.2
27.5°	995.8	987.1	987.1	982.7	978.4	976.2	974.0	971.9
30°	926.3	919.8	917.7	917.7	915.5	915.5	909.0	911.1
32.5°	861.2	856.9	854.8	850.4	850.4	848.2	848.2	841.7
35°	796.2	789.6	791.9	787.5	785.3	783.2	785.3	783.2
37.5°	733.3	728.9	728.9	724.6	724.6	722.4	720.2	724.6
40°	670.4	668.2	666.0	663.8	666.0	663.8	659.5	661.7
42.5°	607.5	607.5	605.2	605.2	603.1	603.1	603.1	603.1
45°	551.0	548.8	548.8	546.7	546.7	546.7	546.7	544.6
47.5°	494.6	492.5	492.5	492.5	490.2	490.2	488.1	490.2
50°	440.4	440.4	438.3	438.3	440.4	438.3	436.0	436.0
52.5°	390.5	390.5	388.3	388.3	386.2	383.9	386.2	386.2
55°	344.9	342.8	340.6	340.6	338.4	336.2	336.2	338.4
57.5°	301.5	299.4	297.2	297.2	292.9	290.7	290.7	290.7
60°	260.3	256.0	256.0	253.9	253.9	251.6	251.6	251.6
62.5°	221.3	219.1	219.1	219.1	219.1	217.0	217.0	217.0
65°	188.7	188.7	188.7	191.0	191.0	193.1	193.1	193.1
67.5°	162.7	164.9	164.9	164.9	167.1	167.1	167.1	164.9
70°	138.9	138.9	138.9	141.0	141.0	141.0	141.0	141.0
72.5°	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0
75°	91.1	93.3	93.3	93.3	91.1	93.3	93.3	91.1
77.5°	71.6	71.6	71.6	71.6	71.6	71.6	71.6	71.6
80°	54.2	54.2	54.2	54.2	54.2	54.2	54.2	54.2
82.5°	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9
85°	21.6	21.6	21.6	21.6	21.6	21.6	21.6	21.6
87.5°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)