

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584278

Luminaire Tested: **HCC8W30D010MW-HM82555835-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
 Report Number: P584278
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 10/21/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO COMMERCIAL
 Catalog Number: HCC8W30D010MW-HM82555835-81WDBB
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
 Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 3445.2 lumens
 Efficiency: N/A
 Efficacy: 123.0 lumens/watt
 Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
 Luminous Opening: Circular (Dia: 0.67' x H: 0')
 CIE Type: Direct

Input Watts (W): 28
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



TEST NUMBER: P584278
CATALOG NUMBER: HCC8W30D010MW-HM82555835-81WDBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584278

CATALOG NUMBER: HCC8W30D010MW-HM82555835-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68				68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62				62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47				47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40				40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64553
5°	64013
10°	63169
15°	63890
20°	68994
25°	75448
30°	74539
35°	61831
40°	36390
45°	23776
50°	18431
55°	12241
60°	5964
65°	1846
70°	622
75°	548
80°	408
85°	814



TEST NUMBER: P584278
 CATALOG NUMBER: HCC8W30D010MW-HM82555835-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.8	5.7
10°-20°	575.0	16.7
20°-30°	1005.3	29.2
30°-40°	977.9	28.4
40°-50°	444.7	12.9
50°-60°	206.2	6.0
60°-70°	34.6	1.0
70°-80°	4.2	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1776.1	51.6
0°-40°	2753.9	79.9
0°-60°	3404.8	98.8
0°-90°	3445.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3445.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2093	
5°	2068	196
15°	2001	575
25°	2218	1005
35°	1642	978
45°	545	445
55°	228	206
65°	25	35
75°	5	4
85°	2	2
90°	0	



TEST NUMBER: P584278
CATALOG NUMBER: HCC8W30D010MW-HM82555835-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2093.4
2.5°	2088.7
5°	2068.0
7.5°	2045.0
10°	2017.4
12.5°	1996.7
15°	2001.3
17.5°	2038.1
20°	2102.5
22.5°	2176.1
25°	2217.5
27.5°	2194.5
30°	2093.4
32.5°	1916.2
35°	1642.5
37.5°	1265.2
40°	904.0
42.5°	674.0
45°	545.2
47.5°	460.0
50°	384.2
52.5°	305.9
55°	227.7
57.5°	156.5
60°	96.7
62.5°	52.9
65°	25.3
67.5°	11.5
70°	6.9
72.5°	4.6
75°	4.6
77.5°	2.3
80°	2.3
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)