

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584446

Luminaire Tested: **HCC8S35D010MW-HM82555927-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MW-HM82555927-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3065.7 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584446
CATALOG NUMBER: HCC8S35D010MW-HM82555927-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584446

CATALOG NUMBER: HCC8S35D010MW-HM82555927-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	49742	49742	49742
5°	50396	49533	49065
10°	50910	49025	48280
15°	51430	47992	47027
20°	51166	46220	45157
25°	49971	43452	42864
30°	47467	40335	40182
35°	43212	36805	37128
40°	37883	32944	34155
45°	32685	29305	31368
50°	28621	25723	28414
55°	25359	22117	25010
60°	22844	18594	20716
65°	20583	14929	15877
70°	18059	10873	8736
75°	15405	5635	2311
80°	11845	1527	391
85°	7642	0	0



TEST NUMBER: P584446
 CATALOG NUMBER: HCC8S35D010MW-HM82555927-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	5.0
10°-20°	427.8	14.0
20°-30°	607.3	19.8
30°-40°	639.2	20.9
40°-50°	543.8	17.7
50°-60°	393.0	12.8
60°-70°	223.5	7.3
70°-80°	70.4	2.3
80°-90°	8.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1187.3	38.7
0°-40°	1826.5	59.6
0°-60°	2763.2	90.1
0°-90°	3065.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3065.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1613	1613	1613	1613	1613	
5°	1628	1620	1600	1589	1585	155
15°	1611	1570	1503	1475	1473	454
25°	1469	1396	1277	1256	1260	673
35°	1148	1081	978	971	986	714
45°	750	721	672	689	719	583
55°	472	437	411	435	465	425
65°	282	243	205	202	218	280
75°	129	99	47	22	19	139
85°	22	13	0	0	0	28
90°	0	0	0	0	0	



TEST NUMBER: P584446

CATALOG NUMBER: HCC8S35D010MW-HM82555927-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1
2.5°	1621.6	1623.8	1619.5	1619.5	1623.8	1619.5	1621.6	1621.6	1619.5	1619.5	1617.3
5°	1628.1	1625.9	1625.9	1625.9	1628.1	1623.8	1621.6	1623.8	1619.5	1619.5	1619.5
7.5°	1630.2	1630.2	1628.1	1625.9	1625.9	1625.9	1623.8	1621.6	1619.5	1615.1	1613.1
10°	1625.9	1625.9	1628.1	1623.8	1623.8	1619.5	1619.5	1615.1	1615.1	1611.0	1604.5
12.5°	1621.6	1619.5	1619.5	1615.1	1615.1	1611.0	1611.0	1604.5	1602.3	1595.9	1589.4
15°	1611.0	1608.8	1604.5	1602.3	1600.2	1598.0	1593.7	1591.5	1585.1	1576.4	1570.0
17.5°	1589.4	1587.2	1585.1	1580.8	1576.4	1574.3	1572.1	1565.7	1557.0	1550.6	1539.8
20°	1559.2	1557.0	1557.0	1550.6	1548.4	1541.9	1539.8	1531.2	1524.7	1511.9	1503.3
22.5°	1518.3	1520.5	1516.2	1511.9	1507.6	1501.1	1496.8	1488.2	1477.4	1464.4	1453.7
25°	1468.7	1470.9	1466.6	1462.3	1455.8	1451.5	1447.2	1434.2	1423.6	1408.5	1395.6
27.5°	1406.3	1406.3	1406.3	1402.0	1391.2	1389.1	1384.8	1371.8	1356.7	1343.8	1331.0
30°	1333.1	1331.0	1331.0	1324.5	1320.2	1311.6	1305.1	1294.3	1283.5	1268.4	1253.3
32.5°	1244.8	1246.9	1240.5	1236.2	1229.7	1229.7	1221.1	1212.5	1199.6	1184.5	1169.4
35°	1147.9	1150.1	1145.8	1143.6	1132.8	1130.7	1128.5	1117.7	1109.1	1098.3	1081.1
37.5°	1048.8	1046.7	1044.5	1044.5	1038.1	1033.8	1029.4	1023.0	1010.0	1001.4	992.8
40°	941.1	941.1	941.1	939.0	936.8	932.5	930.4	926.1	917.4	908.8	902.3
42.5°	844.2	844.2	842.1	839.9	835.6	837.8	833.4	829.1	820.5	814.0	809.7
45°	749.5	749.5	749.5	751.6	747.3	740.8	740.8	736.5	732.2	727.9	721.4
47.5°	665.5	672.0	667.6	665.5	667.6	659.0	659.0	654.7	650.4	646.1	637.5
50°	596.6	596.6	596.6	592.3	590.1	590.1	583.7	579.4	577.2	572.9	564.3
52.5°	534.1	529.8	529.8	527.6	525.4	521.1	521.1	516.8	508.2	504.0	497.5
55°	471.7	471.7	469.5	467.3	465.2	463.0	460.9	454.4	450.1	443.6	437.2
57.5°	415.6	419.9	417.7	413.5	409.2	409.2	404.9	400.6	394.1	387.7	381.2
60°	370.4	368.3	368.3	366.1	361.8	359.6	357.5	351.0	344.5	338.1	331.6
62.5°	323.0	323.0	323.0	318.8	314.5	312.3	310.2	305.8	297.2	290.8	286.4
65°	282.1	280.0	277.8	275.7	273.5	269.2	267.0	262.7	256.3	249.8	243.3
67.5°	241.2	239.0	239.0	236.8	230.5	228.3	228.3	221.9	215.4	208.9	202.5
70°	200.3	200.3	200.3	196.0	193.8	191.7	189.5	185.2	178.7	172.3	165.8
72.5°	165.8	163.6	163.6	161.5	155.0	152.9	150.7	146.4	139.9	135.7	131.4
75°	129.3	129.3	127.1	125.0	122.8	120.6	118.5	114.2	107.7	101.2	99.1
77.5°	99.1	96.9	96.9	94.8	90.4	88.3	88.3	84.0	77.5	73.2	68.9
80°	66.7	68.9	66.7	64.6	62.4	60.3	58.1	55.9	51.6	47.3	43.1
82.5°	41.0	43.1	41.0	41.0	38.8	36.7	36.7	32.3	30.2	28.0	25.9
85°	21.6	21.6	21.6	21.6	19.4	19.4	19.4	17.3	15.1	12.9	12.9
87.5°	6.5	8.6	6.5	6.5	6.5	6.5	6.5	6.5	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584446

CATALOG NUMBER: HCC8S35D010MW-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1
2.5°	1619.5	1617.3	1615.1	1615.1	1615.1	1615.1	1615.1	1613.1	1611.0	1611.0	1611.0
5°	1615.1	1615.1	1615.1	1613.1	1611.0	1611.0	1606.6	1604.5	1602.3	1600.2	1598.0
7.5°	1611.0	1606.6	1604.5	1602.3	1600.2	1600.2	1595.9	1591.5	1591.5	1587.2	1582.9
10°	1598.0	1595.9	1591.5	1587.2	1585.1	1582.9	1578.6	1572.1	1570.0	1565.7	1561.4
12.5°	1582.9	1578.6	1574.3	1565.7	1563.5	1561.4	1552.7	1546.3	1541.9	1539.8	1529.0
15°	1563.5	1554.9	1548.4	1537.6	1535.5	1531.2	1524.7	1518.3	1509.7	1503.3	1498.9
17.5°	1529.0	1520.5	1509.7	1498.9	1494.6	1494.6	1483.8	1475.2	1464.4	1460.1	1451.5
20°	1488.2	1477.4	1468.7	1455.8	1449.3	1442.9	1436.4	1423.6	1415.0	1408.5	1397.7
22.5°	1440.7	1425.7	1415.0	1402.0	1391.2	1384.8	1374.0	1363.2	1352.4	1346.0	1337.4
25°	1380.5	1367.5	1350.3	1337.4	1331.0	1322.4	1309.4	1298.6	1287.8	1277.1	1272.8
27.5°	1313.7	1296.5	1281.4	1266.3	1259.8	1253.3	1238.4	1225.4	1216.8	1206.0	1201.7
30°	1240.5	1223.3	1206.0	1193.1	1186.6	1175.8	1167.2	1152.2	1141.5	1132.8	1122.0
32.5°	1156.4	1143.6	1128.5	1109.1	1104.8	1096.2	1083.2	1076.8	1063.8	1057.5	1048.8
35°	1066.0	1057.5	1042.4	1027.3	1020.8	1016.5	1005.7	992.8	984.2	977.7	973.4
37.5°	979.8	969.1	954.1	943.3	939.0	932.5	919.6	913.1	904.5	900.2	891.6
40°	887.2	876.5	865.8	859.3	852.9	848.5	839.9	833.4	824.8	818.4	816.2
42.5°	796.8	790.3	781.8	773.2	771.0	764.6	760.3	753.8	747.3	745.2	738.7
45°	715.0	708.5	699.9	691.4	689.2	684.9	682.7	676.3	672.0	672.0	672.0
47.5°	633.1	626.7	618.0	613.7	615.9	607.3	607.3	605.1	600.8	600.8	603.0
50°	559.9	551.3	549.2	544.9	540.5	536.2	538.4	531.9	531.9	536.2	534.1
52.5°	491.1	482.4	480.3	476.0	473.8	473.8	471.7	471.7	469.5	471.7	471.7
55°	428.5	422.1	417.7	413.5	411.4	411.4	411.4	409.2	407.1	411.4	413.5
57.5°	372.6	370.4	366.1	359.6	357.5	355.3	353.2	353.2	353.2	353.2	355.3
60°	323.0	318.8	314.5	308.0	308.0	305.8	303.7	301.5	301.5	301.5	301.5
62.5°	280.0	273.5	267.0	262.7	260.6	258.4	256.3	251.9	251.9	251.9	251.9
65°	236.8	230.5	226.2	221.9	217.6	217.6	213.2	211.1	206.8	204.6	200.3
67.5°	196.0	191.7	187.4	180.9	178.7	176.6	172.3	170.1	163.6	161.5	159.3
70°	159.3	152.9	148.6	144.2	142.1	137.9	133.6	129.3	125.0	120.6	116.3
72.5°	125.0	118.5	114.2	109.9	105.5	105.5	99.1	94.8	88.3	84.0	77.5
75°	92.6	86.1	81.8	75.4	73.2	71.0	64.6	60.3	53.8	47.3	43.1
77.5°	62.4	58.1	53.8	47.3	43.1	43.1	36.7	32.3	28.0	21.6	19.4
80°	38.8	34.5	30.2	25.9	25.9	21.6	19.4	15.1	10.8	8.6	6.5
82.5°	21.6	19.4	17.3	12.9	12.9	10.8	8.6	6.5	4.3	2.2	2.2
85°	10.8	8.6	6.5	6.5	4.3	4.3	4.3	2.2	2.2	0.0	0.0
87.5°	4.3	2.2	2.2	2.2	2.2	2.2	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584446

CATALOG NUMBER: HCC8S35D010MW-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1
2.5°	1608.8	1608.8	1606.6	1606.6	1606.6	1604.5	1606.6	1604.5	1604.5	1604.5	1606.6
5°	1600.2	1595.9	1595.9	1593.7	1593.7	1591.5	1593.7	1591.5	1589.4	1587.2	1589.4
7.5°	1582.9	1578.6	1576.4	1574.3	1574.3	1574.3	1572.1	1570.0	1572.1	1565.7	1570.0
10°	1559.2	1557.0	1552.7	1550.6	1548.4	1550.6	1548.4	1544.1	1544.1	1544.1	1541.9
12.5°	1529.0	1524.7	1522.5	1520.5	1516.2	1516.2	1518.3	1514.0	1514.0	1509.7	1509.7
15°	1492.5	1488.2	1483.8	1483.8	1479.5	1479.5	1477.4	1477.4	1475.2	1473.1	1473.1
17.5°	1447.2	1440.7	1436.4	1438.6	1436.4	1434.2	1434.2	1429.9	1427.9	1429.9	1429.9
20°	1393.4	1389.1	1384.8	1386.9	1382.6	1380.5	1382.6	1376.1	1378.3	1378.3	1378.3
22.5°	1333.1	1331.0	1324.5	1324.5	1320.2	1318.0	1320.2	1320.2	1322.4	1320.2	1320.2
25°	1266.3	1262.0	1257.7	1257.7	1255.5	1253.3	1255.5	1257.7	1255.5	1257.7	1257.7
27.5°	1195.2	1188.8	1188.8	1184.5	1184.5	1186.6	1184.5	1186.6	1188.8	1188.8	1193.1
30°	1117.7	1115.6	1113.4	1111.3	1111.3	1113.4	1113.4	1113.4	1115.6	1119.9	1119.9
32.5°	1044.5	1040.2	1035.9	1035.9	1040.2	1038.1	1040.2	1040.2	1044.5	1044.5	1048.8
35°	964.9	964.9	960.6	962.7	962.7	962.7	962.7	967.0	971.2	973.4	977.7
37.5°	891.6	885.1	887.2	887.2	889.4	887.2	893.7	893.7	898.0	898.0	902.3
40°	811.9	811.9	814.0	811.9	814.0	814.0	818.4	822.7	824.8	829.1	831.3
42.5°	736.5	740.8	736.5	738.7	740.8	743.0	745.2	747.3	755.9	760.3	766.7
45°	667.6	669.8	672.0	674.1	672.0	676.3	678.4	682.7	689.2	691.4	693.4
47.5°	600.8	603.0	605.1	607.3	607.3	611.6	613.7	618.0	622.4	624.5	626.7
50°	536.2	540.5	542.7	542.7	544.9	549.2	553.5	553.5	557.8	564.3	566.4
52.5°	478.1	478.1	482.4	484.6	486.7	486.7	493.2	495.4	497.5	501.8	506.2
55°	413.5	419.9	422.1	422.1	426.4	430.7	432.8	435.0	435.0	443.6	443.6
57.5°	357.5	359.6	364.0	364.0	364.0	370.4	370.4	374.7	376.9	379.0	383.4
60°	301.5	305.8	305.8	308.0	305.8	310.2	312.3	316.6	318.8	320.9	323.0
62.5°	249.8	249.8	251.9	251.9	251.9	251.9	256.3	256.3	260.6	262.7	264.9
65°	200.3	200.3	200.3	200.3	200.3	200.3	200.3	200.3	202.5	202.5	206.8
67.5°	155.0	152.9	148.6	150.7	148.6	148.6	146.4	146.4	148.6	148.6	152.9
70°	112.0	109.9	105.5	105.5	103.4	101.2	99.1	96.9	94.8	94.8	94.8
72.5°	73.2	68.9	62.4	60.3	60.3	55.9	51.6	49.5	49.5	49.5	49.5
75°	36.7	32.3	28.0	25.9	25.9	21.6	23.7	21.6	21.6	21.6	21.6
77.5°	15.1	10.8	8.6	8.6	8.6	6.5	6.5	6.5	6.5	6.5	6.5
80°	4.3	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	2.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584446

CATALOG NUMBER: HCC8S35D010MW-HM82555927-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1	1613.1
2.5°	1604.5	1604.5	1600.2	1602.3	1602.3	1602.3	1602.3	1602.3
5°	1585.1	1587.2	1585.1	1587.2	1587.2	1585.1	1585.1	1585.1
7.5°	1565.7	1567.8	1565.7	1567.8	1567.8	1567.8	1565.7	1565.7
10°	1541.9	1541.9	1541.9	1541.9	1541.9	1539.8	1541.9	1541.9
12.5°	1509.7	1509.7	1509.7	1511.9	1511.9	1509.7	1509.7	1507.6
15°	1475.2	1470.9	1473.1	1475.2	1473.1	1473.1	1473.1	1473.1
17.5°	1427.9	1429.9	1427.9	1427.9	1427.9	1427.9	1429.9	1427.9
20°	1378.3	1378.3	1380.5	1378.3	1378.3	1378.3	1378.3	1376.1
22.5°	1322.4	1320.2	1320.2	1322.4	1322.4	1320.2	1322.4	1322.4
25°	1259.8	1262.0	1259.8	1259.8	1262.0	1262.0	1262.0	1259.8
27.5°	1193.1	1195.2	1197.4	1195.2	1195.2	1195.2	1197.4	1199.6
30°	1124.2	1128.5	1124.2	1124.2	1128.5	1126.4	1128.5	1128.5
32.5°	1051.0	1057.5	1053.2	1057.5	1057.5	1059.6	1057.5	1059.6
35°	977.7	984.2	984.2	984.2	986.3	988.5	988.5	986.3
37.5°	908.8	911.0	911.0	915.3	917.4	919.6	919.6	917.4
40°	837.8	842.1	844.2	844.2	844.2	848.5	852.9	848.5
42.5°	768.9	771.0	773.2	773.2	777.5	779.7	781.8	781.8
45°	702.0	706.3	708.5	710.7	712.8	717.1	715.0	719.3
47.5°	633.1	639.6	641.8	643.9	648.2	650.4	652.6	654.7
50°	570.7	575.0	575.0	579.4	585.8	585.8	590.1	592.3
52.5°	508.2	510.3	512.5	514.7	519.0	523.3	523.3	527.6
55°	447.9	450.1	450.1	452.2	454.4	463.0	465.2	465.2
57.5°	385.5	385.5	389.8	392.0	394.1	398.5	398.5	398.5
60°	325.1	327.3	327.3	329.4	331.6	335.9	338.1	335.9
62.5°	264.9	267.0	267.0	269.2	273.5	275.7	273.5	273.5
65°	208.9	211.1	211.1	213.2	217.6	217.6	215.4	217.6
67.5°	152.9	152.9	152.9	152.9	152.9	152.9	152.9	152.9
70°	96.9	94.8	92.6	94.8	94.8	94.8	92.6	96.9
72.5°	47.3	49.5	49.5	49.5	49.5	49.5	49.5	47.3
75°	21.6	21.6	19.4	19.4	19.4	21.6	21.6	19.4
77.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
80°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)