

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584285

Luminaire Tested: **HCC8S30D010MB-HM82555835-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010MB-HM82555835-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3256.6 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584285
CATALOG NUMBER: HCC8S30D010MB-HM82555835-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P584285

CATALOG NUMBER: HCC8S30D010MB-HM82555835-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	49930	49930	49930
5°	51758	49762	48056
10°	53221	49332	46091
15°	54408	48461	44055
20°	54493	46568	42266
25°	53448	43980	40771
30°	50693	40784	38982
35°	46061	37147	37230
40°	40274	33330	35089
45°	34905	29689	32698
50°	30563	26371	29791
55°	27203	23370	26956
60°	24533	20993	23682
65°	22152	18460	20642
70°	19907	15552	15336
75°	17538	12319	11497
80°	14704	10211	11028
85°	11393	8951	9765



TEST NUMBER: P584285
 CATALOG NUMBER: HCC8S30D010MB-HM82555835-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.7	4.7
10°-20°	430.2	13.2
20°-30°	614.9	18.9
30°-40°	653.3	20.1
40°-50°	562.5	17.3
50°-60°	420.6	12.9
60°-70°	268.2	8.2
70°-80°	122.1	3.7
80°-90°	32.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1197.9	36.8
0°-40°	1851.2	56.8
0°-60°	2834.2	87.0
0°-90°	3256.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3256.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1619	1619	1619	1619	1619	
5°	1672	1649	1608	1566	1552	160
15°	1704	1647	1518	1415	1380	480
25°	1571	1472	1293	1214	1198	719
35°	1224	1138	987	961	989	762
45°	800	757	681	699	750	622
55°	506	464	435	472	501	455
65°	304	269	253	265	283	303
75°	147	126	103	94	96	156
85°	32	28	25	28	28	39
90°	0	0	0	0	0	



TEST NUMBER: P584285

CATALOG NUMBER: HCC8S30D010MB-HM82555835-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2
2.5°	1649.1	1644.5	1646.8	1644.5	1646.8	1646.8	1642.2	1642.2	1642.2	1642.2	1635.4
5°	1672.1	1669.8	1669.8	1667.5	1665.2	1667.5	1665.2	1662.9	1658.3	1656.0	1649.1
7.5°	1685.9	1685.9	1685.9	1685.9	1683.6	1681.2	1679.0	1674.3	1669.8	1665.2	1660.6
10°	1699.7	1701.9	1699.7	1697.4	1695.0	1690.5	1688.1	1683.6	1676.7	1669.8	1665.2
12.5°	1706.6	1706.6	1704.3	1704.3	1699.7	1697.4	1690.5	1683.6	1676.7	1669.8	1658.3
15°	1704.3	1704.3	1701.9	1699.7	1692.8	1690.5	1685.9	1679.0	1667.5	1658.3	1646.8
17.5°	1690.5	1688.1	1683.6	1683.6	1674.3	1672.1	1667.5	1658.3	1646.8	1633.0	1619.2
20°	1660.6	1660.6	1658.3	1656.0	1646.8	1639.9	1635.4	1623.8	1614.5	1598.5	1584.7
22.5°	1619.2	1623.8	1619.2	1614.5	1603.1	1600.8	1593.9	1580.1	1566.3	1547.8	1531.8
25°	1570.9	1568.6	1566.3	1561.8	1552.5	1547.8	1538.7	1524.9	1511.1	1490.4	1472.0
27.5°	1508.8	1499.6	1499.6	1490.4	1483.5	1476.6	1472.0	1458.2	1439.8	1423.7	1400.6
30°	1423.7	1426.0	1414.6	1412.2	1400.6	1396.1	1386.8	1373.1	1357.0	1338.6	1320.1
32.5°	1331.7	1324.8	1324.8	1315.6	1306.4	1299.5	1297.2	1281.1	1267.2	1248.9	1230.5
35°	1223.6	1223.6	1216.7	1214.4	1205.2	1200.7	1193.6	1184.5	1168.4	1152.3	1138.5
37.5°	1117.8	1113.1	1110.9	1106.2	1099.3	1092.5	1092.5	1076.4	1074.1	1055.7	1037.3
40°	1000.5	1005.1	1000.5	993.6	991.3	986.8	984.4	975.2	968.3	952.2	940.7
42.5°	901.6	897.0	897.0	894.7	885.4	885.4	880.9	876.3	864.8	860.2	846.4
45°	800.4	805.0	798.1	800.4	791.2	791.2	791.2	782.0	772.8	766.0	756.7
47.5°	713.0	715.3	715.3	708.4	706.1	706.1	701.5	696.9	690.0	680.8	673.9
50°	637.1	639.4	634.8	632.5	627.9	625.7	625.7	616.4	611.7	602.6	597.9
52.5°	568.1	568.1	565.8	565.8	558.9	558.9	554.3	547.4	542.8	538.1	526.7
55°	506.0	506.0	503.7	501.4	501.4	494.5	492.2	485.3	480.7	471.6	464.5
57.5°	446.2	448.5	446.2	443.9	441.6	439.3	434.7	427.8	423.2	416.3	411.8
60°	397.8	397.8	395.6	393.3	388.7	386.4	384.0	379.5	372.6	368.0	361.1
62.5°	351.9	349.6	347.3	345.0	340.4	340.4	335.8	331.3	324.2	319.7	315.1
65°	303.6	303.6	301.3	301.3	299.0	294.4	292.1	289.8	280.6	278.3	269.1
67.5°	259.9	262.2	257.7	257.7	253.0	253.0	250.6	243.7	241.5	236.8	232.3
70°	220.8	220.8	220.8	218.5	213.9	211.6	209.3	204.7	202.4	197.8	193.2
72.5°	181.7	181.7	179.4	179.4	177.0	174.8	172.5	167.9	167.9	163.2	158.7
75°	147.2	147.2	144.9	142.6	140.3	140.3	138.0	135.7	131.1	128.8	126.5
77.5°	112.7	112.7	112.7	110.5	108.1	108.1	108.1	103.4	98.9	98.9	96.5
80°	82.8	82.8	80.5	80.5	78.2	78.2	78.2	75.9	73.6	71.3	69.0
82.5°	55.2	55.2	55.2	55.2	52.9	52.9	52.9	50.7	48.3	48.3	48.3
85°	32.2	32.2	32.2	32.2	29.8	29.8	29.8	29.8	29.8	27.6	27.6
87.5°	13.8	11.5	13.8	11.5	13.8	11.5	13.8	11.5	11.5	11.5	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584285

CATALOG NUMBER: HCC8S30D010MB-HM82555835-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2
2.5°	1637.6	1635.4	1633.0	1630.7	1630.7	1628.3	1623.8	1621.4	1619.2	1616.9	1616.9
5°	1646.8	1644.5	1639.9	1635.4	1633.0	1628.3	1623.8	1619.2	1614.5	1607.6	1605.4
7.5°	1653.7	1646.8	1642.2	1633.0	1630.7	1626.1	1619.2	1612.3	1603.1	1593.9	1587.0
10°	1653.7	1644.5	1637.6	1626.1	1621.4	1616.9	1607.6	1596.2	1584.7	1575.5	1564.0
12.5°	1649.1	1637.6	1626.1	1614.5	1607.6	1600.8	1587.0	1575.5	1561.8	1547.8	1538.7
15°	1633.0	1619.2	1605.4	1591.6	1584.7	1575.5	1561.8	1545.6	1531.8	1518.0	1501.9
17.5°	1603.1	1589.3	1573.2	1557.1	1547.8	1540.9	1520.3	1508.8	1488.2	1474.2	1460.4
20°	1564.0	1547.8	1527.2	1511.1	1499.6	1492.7	1476.6	1455.9	1439.8	1419.1	1405.3
22.5°	1513.4	1492.7	1472.0	1455.9	1444.4	1435.2	1414.6	1393.7	1380.0	1361.6	1345.5
25°	1453.6	1432.9	1412.2	1389.2	1377.7	1368.5	1350.1	1331.7	1313.3	1292.6	1278.8
27.5°	1382.3	1359.3	1340.8	1320.1	1308.7	1294.9	1274.3	1255.8	1237.4	1223.6	1205.2
30°	1304.1	1278.8	1260.3	1239.7	1228.2	1216.7	1196.0	1177.6	1161.5	1145.4	1136.2
32.5°	1209.8	1191.4	1172.9	1152.3	1143.1	1136.2	1115.5	1097.1	1078.7	1064.9	1058.0
35°	1120.0	1099.3	1083.3	1064.9	1053.5	1046.4	1028.1	1012.0	1002.8	986.8	977.5
37.5°	1025.8	1009.7	991.3	972.8	965.9	959.0	945.3	929.2	915.4	903.9	899.2
40°	926.9	913.2	897.0	885.4	878.6	871.7	860.2	848.7	839.6	828.0	823.4
42.5°	832.5	823.4	809.6	795.8	788.9	786.6	772.8	763.6	758.9	754.4	749.8
45°	747.5	733.7	724.5	715.3	708.4	703.8	696.9	690.0	685.3	680.8	676.2
47.5°	664.7	653.2	644.0	637.1	630.2	627.9	623.3	616.4	611.7	611.7	611.7
50°	588.8	579.6	570.4	565.8	563.5	558.9	554.3	552.1	549.7	549.7	549.7
52.5°	522.1	512.9	506.0	501.4	501.4	496.8	492.2	489.9	489.9	489.9	489.9
55°	460.0	453.1	448.5	443.9	439.3	437.0	437.0	437.0	434.7	434.7	437.0
57.5°	404.9	400.2	393.3	388.7	386.4	386.4	384.0	381.8	384.0	386.4	388.7
60°	354.2	349.6	347.3	340.4	340.4	340.4	338.2	338.2	338.2	340.4	342.7
62.5°	308.2	305.9	301.3	299.0	296.7	296.7	294.4	294.4	294.4	294.4	296.7
65°	266.8	262.2	257.7	257.7	257.7	255.3	255.3	250.6	253.0	253.0	250.6
67.5°	227.7	223.1	220.8	218.5	216.2	216.2	213.9	211.6	209.3	209.3	209.3
70°	191.0	186.3	186.3	181.7	181.7	179.4	177.0	177.0	174.8	172.5	170.1
72.5°	154.1	151.8	149.5	147.2	147.2	147.2	144.9	142.6	140.3	138.0	133.4
75°	121.9	121.9	117.4	115.0	115.0	112.7	110.5	108.1	105.8	103.4	101.2
77.5°	94.3	92.0	87.4	85.1	85.1	85.1	82.8	80.5	78.2	75.9	73.6
80°	69.0	66.7	64.4	62.1	62.1	62.1	59.8	59.8	57.5	57.5	57.5
82.5°	46.0	46.0	43.8	43.8	43.8	43.8	41.4	41.4	41.4	41.4	41.4
85°	27.6	27.6	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3
87.5°	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584285

CATALOG NUMBER: HCC8S30D010MB-HM82555835-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2
2.5°	1612.3	1612.3	1607.6	1605.4	1603.1	1605.4	1600.8	1598.5	1596.2	1596.2	1593.9
5°	1598.5	1596.2	1587.0	1584.7	1582.4	1580.1	1575.5	1570.9	1566.3	1564.0	1561.8
7.5°	1580.1	1573.2	1564.0	1561.8	1559.4	1552.5	1545.6	1540.9	1534.0	1531.8	1527.2
10°	1554.7	1545.6	1538.7	1531.8	1527.2	1520.3	1513.4	1506.5	1497.3	1495.0	1488.2
12.5°	1524.9	1513.4	1499.6	1497.3	1490.4	1481.1	1472.0	1465.1	1458.2	1453.6	1446.7
15°	1488.2	1476.6	1462.8	1455.9	1449.0	1442.1	1430.6	1421.4	1414.6	1407.5	1400.6
17.5°	1444.4	1430.6	1419.1	1412.2	1407.5	1396.1	1386.8	1375.4	1368.5	1361.6	1354.7
20°	1391.5	1380.0	1363.9	1357.0	1354.7	1345.5	1333.9	1329.4	1320.1	1313.3	1308.7
22.5°	1331.7	1320.1	1306.4	1301.8	1292.6	1288.0	1276.5	1271.9	1267.2	1260.3	1258.1
25°	1265.0	1253.4	1242.0	1239.7	1232.8	1228.2	1221.3	1214.4	1214.4	1207.5	1207.5
27.5°	1196.0	1184.5	1175.3	1170.7	1168.4	1163.8	1156.9	1154.6	1152.3	1150.0	1150.0
30°	1122.4	1108.6	1104.0	1101.7	1099.3	1094.8	1092.5	1087.9	1090.2	1092.5	1090.2
32.5°	1044.2	1039.5	1030.4	1025.8	1028.1	1025.8	1021.2	1025.8	1023.5	1028.1	1030.4
35°	968.3	963.7	959.0	959.0	954.5	954.5	954.5	956.8	961.4	963.7	968.3
37.5°	894.7	887.8	885.4	883.2	885.4	885.4	885.4	890.1	894.7	899.2	906.1
40°	816.5	811.8	811.8	811.8	811.8	818.7	816.5	821.1	825.6	832.5	839.6
42.5°	742.9	742.9	745.1	745.1	745.1	745.1	749.8	756.7	763.6	770.5	777.4
45°	673.9	673.9	673.9	678.4	678.4	680.8	690.0	694.6	699.3	706.1	713.0
47.5°	609.5	609.5	611.7	614.1	616.4	621.0	625.7	632.5	639.4	644.0	650.9
50°	549.7	552.1	556.6	561.2	561.2	563.5	570.4	575.0	579.6	586.5	588.8
52.5°	492.2	496.8	501.4	503.7	506.0	510.6	512.9	519.8	522.1	529.0	531.2
55°	439.3	441.6	448.5	450.7	450.7	455.4	460.0	464.5	471.6	471.6	476.1
57.5°	390.9	393.3	397.8	400.2	397.8	404.9	407.1	411.8	414.0	418.6	420.9
60°	342.7	347.3	349.6	349.6	351.9	354.2	358.8	358.8	363.4	368.0	368.0
62.5°	296.7	299.0	301.3	303.6	305.9	303.6	310.4	310.4	315.1	317.3	322.0
65°	253.0	255.3	255.3	257.7	257.7	259.9	259.9	262.2	264.6	269.1	271.4
67.5°	209.3	209.3	209.3	211.6	209.3	211.6	211.6	213.9	213.9	218.5	220.8
70°	170.1	167.9	165.6	165.6	165.6	165.6	163.2	165.6	165.6	167.9	167.9
72.5°	131.1	128.8	126.5	124.3	124.3	121.9	119.6	121.9	121.9	124.3	124.3
75°	98.9	94.3	94.3	94.3	92.0	92.0	92.0	94.3	94.3	94.3	96.5
77.5°	73.6	73.6	71.3	71.3	71.3	73.6	73.6	75.9	75.9	75.9	75.9
80°	55.2	57.5	57.5	57.5	57.5	59.8	59.8	59.8	59.8	62.1	62.1
82.5°	41.4	41.4	41.4	41.4	43.8	43.8	43.8	43.8	43.8	43.8	43.8
85°	25.3	27.6	27.6	25.3	27.6	27.6	27.6	27.6	27.6	27.6	27.6
87.5°	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584285

CATALOG NUMBER: HCC8S30D010MB-HM82555835-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2	1619.2
2.5°	1591.6	1591.6	1591.6	1591.6	1589.3	1589.3	1589.3	1587.0
5°	1557.1	1557.1	1557.1	1552.5	1554.7	1554.7	1550.2	1552.5
7.5°	1522.6	1520.3	1518.0	1518.0	1515.7	1513.4	1511.1	1513.4
10°	1483.5	1476.6	1476.6	1474.2	1474.2	1469.7	1469.7	1472.0
12.5°	1439.8	1435.2	1435.2	1432.9	1430.6	1428.3	1426.0	1426.0
15°	1396.1	1391.5	1389.2	1386.8	1384.6	1380.0	1382.3	1380.0
17.5°	1352.4	1345.5	1345.5	1343.2	1340.8	1336.3	1336.3	1333.9
20°	1301.8	1299.5	1294.9	1297.2	1294.9	1290.3	1288.0	1288.0
22.5°	1251.2	1251.2	1248.9	1248.9	1246.5	1244.3	1242.0	1242.0
25°	1202.9	1200.7	1202.9	1202.9	1196.0	1196.0	1196.0	1198.3
27.5°	1147.7	1150.0	1147.7	1147.7	1147.7	1147.7	1150.0	1147.7
30°	1092.5	1092.5	1092.5	1094.8	1099.3	1097.1	1097.1	1094.8
32.5°	1032.6	1035.0	1035.0	1037.3	1039.5	1044.2	1044.2	1046.4
35°	972.8	977.5	979.9	977.5	984.4	984.4	989.0	989.0
37.5°	910.8	913.2	917.7	920.0	924.6	926.9	929.2	929.2
40°	844.1	853.3	855.6	857.9	864.8	864.8	867.1	871.7
42.5°	782.0	791.2	793.5	795.8	800.4	807.3	805.0	809.6
45°	722.2	729.1	731.4	733.7	740.6	742.9	742.9	749.8
47.5°	657.8	662.4	664.7	669.3	673.9	678.4	683.1	680.8
50°	593.4	600.3	604.8	607.2	614.1	616.4	618.8	621.0
52.5°	535.9	540.5	542.8	545.2	552.1	554.3	556.6	561.2
55°	480.7	483.0	487.6	485.3	492.2	494.5	496.8	501.4
57.5°	425.5	427.8	430.1	430.1	434.7	439.3	441.6	443.9
60°	372.6	377.2	379.5	379.5	379.5	384.0	384.0	384.0
62.5°	324.2	324.2	326.6	326.6	331.3	331.3	331.3	331.3
65°	273.7	276.0	278.3	278.3	282.9	280.6	285.2	282.9
67.5°	220.8	220.8	225.4	225.4	223.1	225.4	225.4	225.4
70°	167.9	167.9	170.1	170.1	170.1	170.1	170.1	170.1
72.5°	124.3	124.3	124.3	126.5	124.3	124.3	126.5	124.3
75°	96.5	96.5	96.5	96.5	96.5	96.5	96.5	96.5
77.5°	75.9	75.9	78.2	78.2	78.2	78.2	78.2	78.2
80°	62.1	62.1	62.1	62.1	64.4	62.1	62.1	62.1
82.5°	46.0	43.8	46.0	43.8	46.0	46.0	46.0	46.0
85°	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6
87.5°	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)