

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584288

Luminaire Tested: **HCC8S30D010MW-HM82555840-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584288  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S30D010MW-HM82555840-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3689.0 lumens  
Efficiency: N/A  
Efficacy: 131.8 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584288  
CATALOG NUMBER: HCC8S30D010MW-HM82555840-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584288  
 CATALOG NUMBER: HCC8S30D010MW-HM82555840-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																											
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80																											
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72																											
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65																											
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59																											
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54																											
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50																											
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																											
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																											
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	94325
5°	91757
10°	86343
15°	81748
20°	78635
25°	75602
30°	67147
35°	42760
40°	23863
45°	19990
50°	18047
55°	17010
60°	15517
65°	13995
70°	12352
75°	10973
80°	9731
85°	8845



TEST NUMBER: P584288  
 CATALOG NUMBER: HCC8S30D010MW-HM82555840-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.4	7.5
10°-20°	722.2	19.6
20°-30°	1007.5	27.3
30°-40°	725.0	19.7
40°-50°	359.3	9.7
50°-60°	281.1	7.6
60°-70°	190.3	5.2
70°-80°	98.8	2.7
80°-90°	28.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2006.0	54.4
0°-40°	2731.0	74.0
0°-60°	3371.4	91.4
0°-90°	3689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3689.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3059	
5°	2964	276
15°	2561	722
25°	2222	1008
35°	1136	725
45°	458	359
55°	316	281
65°	192	190
75°	92	99
85°	25	28
90°	0	



TEST NUMBER: P584288  
CATALOG NUMBER: HCC8S30D010MW-HM82555840-81MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3058.9
2.5°	3031.6
5°	2964.3
7.5°	2869.7
10°	2757.5
12.5°	2652.9
15°	2560.7
17.5°	2473.6
20°	2396.3
22.5°	2319.1
25°	2222.0
27.5°	2082.5
30°	1885.8
32.5°	1576.9
35°	1135.9
37.5°	774.8
40°	592.8
42.5°	510.7
45°	458.4
47.5°	413.5
50°	376.2
52.5°	343.7
55°	316.4
57.5°	283.9
60°	251.6
62.5°	219.3
65°	191.8
67.5°	164.4
70°	137.0
72.5°	114.6
75°	92.1
77.5°	72.3
80°	54.8
82.5°	39.8
85°	25.0
87.5°	12.5
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)