

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584471

Luminaire Tested: **HCC8S35D010MW-HM82555930-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MW-HM82555930-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3486.6 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584471
CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584471

CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	58256	58256	58256
5°	60305	57924	55621
10°	61644	56906	52495
15°	62520	54992	49019
20°	62329	52321	45508
25°	60791	48930	41775
30°	57590	45000	38334
35°	52401	40723	34832
40°	46022	36216	31471
45°	40133	31856	28058
50°	34924	27915	24720
55°	31149	24531	21499
60°	28295	21499	18335
65°	25436	18708	16643
70°	22648	15940	15021
75°	19849	13427	12832
80°	16852	10939	11383
85°	12702	8173	9057



TEST NUMBER: P584471
 CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.0	5.1
10°-20°	487.6	14.0
20°-30°	676.8	19.4
30°-40°	699.7	20.1
40°-50°	585.9	16.8
50°-60°	425.3	12.2
60°-70°	268.4	7.7
70°-80°	133.0	3.8
80°-90°	33.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1341.3	38.5
0°-40°	2041.0	58.5
0°-60°	3052.2	87.5
0°-90°	3486.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3486.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1889	1889	1889	1889	1889	
5°	1948	1925	1871	1820	1797	186
15°	1958	1884	1723	1584	1536	551
25°	1787	1671	1438	1282	1228	819
35°	1392	1289	1082	959	925	867
45°	920	854	730	659	643	712
55°	579	528	456	418	400	523
65°	349	305	256	226	228	348
75°	167	138	113	108	108	179
85°	36	28	23	26	26	44
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584471

CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2
2.5°	1919.9	1919.9	1922.6	1919.9	1919.9	1919.9	1917.4	1917.4	1914.9	1914.9	1909.7
5°	1948.2	1943.0	1948.2	1943.0	1943.0	1943.0	1940.5	1935.4	1932.7	1927.7	1925.1
7.5°	1961.0	1958.4	1958.4	1955.9	1955.9	1953.3	1950.7	1948.2	1937.9	1935.4	1927.7
10°	1968.7	1966.0	1966.0	1963.5	1958.4	1958.4	1953.3	1950.7	1937.9	1932.7	1922.6
12.5°	1966.0	1966.0	1966.0	1963.5	1955.9	1953.3	1948.2	1940.5	1930.2	1919.9	1909.7
15°	1958.4	1958.4	1953.3	1950.7	1943.0	1937.9	1935.4	1922.6	1912.2	1899.4	1884.1
17.5°	1932.7	1932.7	1930.2	1925.1	1917.4	1912.2	1907.1	1894.3	1884.1	1863.6	1848.2
20°	1899.4	1896.9	1894.3	1886.6	1878.9	1876.4	1868.6	1850.8	1838.0	1822.5	1802.0
22.5°	1850.8	1848.2	1845.6	1840.5	1827.7	1822.5	1817.4	1804.5	1781.5	1766.2	1740.6
25°	1786.7	1786.7	1781.5	1773.9	1761.1	1755.9	1748.2	1735.4	1714.9	1691.8	1671.3
27.5°	1712.3	1709.8	1702.1	1697.0	1686.7	1679.0	1666.2	1650.8	1630.2	1612.4	1586.8
30°	1617.4	1617.4	1612.4	1604.7	1591.9	1586.8	1576.4	1558.5	1538.0	1515.0	1497.0
32.5°	1509.8	1509.8	1502.2	1497.0	1489.4	1476.5	1473.9	1453.4	1435.4	1417.6	1397.0
35°	1392.0	1394.5	1389.3	1379.1	1366.3	1366.3	1361.2	1343.2	1322.7	1304.7	1289.4
37.5°	1274.0	1266.3	1263.8	1258.6	1251.0	1240.6	1235.5	1227.8	1209.9	1197.0	1174.0
40°	1143.3	1145.8	1140.7	1135.6	1132.9	1125.3	1122.8	1109.9	1097.1	1081.8	1071.5
42.5°	1025.4	1025.4	1025.4	1020.2	1015.1	1007.4	1004.9	997.1	981.8	971.5	956.1
45°	920.3	912.5	912.5	910.0	907.5	902.3	894.7	889.5	879.2	871.5	853.6
47.5°	817.8	820.3	817.8	815.1	807.5	804.9	802.3	792.1	781.8	774.1	761.3
50°	728.0	733.2	728.0	728.0	722.9	720.4	715.2	707.5	699.8	686.9	674.1
52.5°	653.6	653.6	651.1	648.5	640.8	635.7	633.1	630.6	617.8	607.5	597.2
55°	579.4	581.9	581.9	574.2	571.7	566.5	563.9	556.2	551.1	535.7	528.1
57.5°	515.3	512.6	515.3	510.1	505.0	499.8	497.3	492.1	484.5	474.2	464.0
60°	458.8	453.7	453.7	451.2	446.0	443.5	438.3	430.7	423.0	412.7	405.0
62.5°	402.4	399.9	397.4	394.7	389.6	387.1	384.6	376.8	369.1	361.4	353.8
65°	348.6	348.6	346.1	341.0	338.3	335.8	333.3	328.1	317.8	312.7	305.0
67.5°	299.9	297.3	297.3	292.2	287.0	284.5	284.5	279.4	271.7	264.0	258.9
70°	251.2	253.7	251.2	248.7	243.6	243.6	238.4	235.9	225.6	223.1	215.3
72.5°	207.6	207.6	205.1	205.1	199.9	197.4	197.4	192.3	187.1	182.0	176.8
75°	166.6	166.6	166.6	164.0	161.5	156.3	156.3	153.8	148.7	143.5	138.4
77.5°	130.7	128.2	128.2	125.6	123.0	120.5	120.5	117.9	112.7	110.2	105.1
80°	94.9	92.2	92.2	92.2	87.1	89.7	87.1	84.6	82.1	79.4	76.9
82.5°	61.6	64.1	64.1	61.6	58.9	58.9	58.9	56.4	56.4	53.8	51.3
85°	35.9	35.9	35.9	35.9	33.3	33.3	33.3	30.8	30.8	30.8	28.2
87.5°	15.3	15.3	15.3	15.3	15.3	15.3	12.8	12.8	12.8	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584471

CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2
2.5°	1909.7	1904.6	1902.1	1899.4	1899.4	1896.9	1894.3	1889.2	1889.2	1884.1	1881.5
5°	1919.9	1912.2	1907.1	1902.1	1899.4	1894.3	1889.2	1881.5	1878.9	1871.3	1863.6
7.5°	1922.6	1909.7	1904.6	1894.3	1889.2	1884.1	1873.8	1866.1	1855.8	1848.2	1838.0
10°	1912.2	1902.1	1889.2	1876.4	1873.8	1866.1	1850.8	1840.5	1827.7	1817.4	1802.0
12.5°	1896.9	1881.5	1868.6	1853.3	1845.6	1838.0	1822.5	1807.2	1789.2	1771.2	1755.9
15°	1871.3	1853.3	1835.3	1817.4	1807.2	1799.5	1781.5	1763.6	1745.6	1722.6	1707.2
17.5°	1832.8	1812.3	1794.4	1771.2	1761.1	1753.4	1730.3	1709.8	1686.7	1663.7	1648.2
20°	1784.1	1758.4	1737.9	1712.3	1704.6	1691.8	1668.7	1645.7	1620.1	1594.4	1576.4
22.5°	1720.0	1694.3	1671.3	1645.7	1632.9	1620.1	1596.9	1568.8	1543.1	1522.7	1504.7
25°	1645.7	1622.6	1594.4	1571.3	1556.0	1540.6	1515.0	1491.9	1468.7	1438.1	1420.1
27.5°	1563.6	1535.5	1515.0	1484.2	1468.7	1458.6	1430.4	1399.6	1379.1	1350.9	1330.4
30°	1471.4	1445.7	1422.6	1392.0	1376.5	1366.3	1340.7	1312.4	1291.9	1263.8	1243.3
32.5°	1374.0	1345.7	1317.6	1297.1	1279.1	1268.9	1240.6	1222.7	1197.0	1174.0	1150.9
35°	1268.9	1240.6	1220.2	1192.0	1181.7	1171.4	1148.4	1125.3	1102.3	1081.8	1063.8
37.5°	1156.1	1135.6	1112.5	1092.0	1084.3	1074.0	1045.9	1025.4	1007.4	986.9	971.5
40°	1045.9	1027.9	1012.5	992.1	979.2	971.5	951.0	933.1	912.5	899.7	884.4
42.5°	945.8	925.3	910.0	894.7	881.8	874.1	856.2	843.4	827.9	815.1	797.1
45°	840.8	830.6	812.6	799.8	792.1	781.8	769.0	753.7	740.8	730.5	717.7
47.5°	748.5	738.2	725.4	710.1	704.9	697.2	684.4	674.1	663.9	653.6	640.8
50°	663.9	651.1	640.8	630.6	625.5	617.8	605.0	599.8	592.2	581.9	574.2
52.5°	587.0	576.7	566.5	553.7	551.1	546.0	538.3	528.1	520.4	515.3	510.1
55°	517.8	507.6	499.8	489.6	487.0	482.0	471.7	466.5	461.3	456.3	451.2
57.5°	456.3	446.0	435.7	430.7	425.5	420.4	417.9	410.2	405.0	402.4	397.4
60°	399.9	389.6	381.9	374.3	371.7	369.1	364.0	358.9	353.8	348.6	346.1
62.5°	346.1	335.8	330.6	325.5	320.5	320.5	315.3	310.2	305.0	302.5	297.3
65°	297.3	292.2	284.5	276.9	274.2	274.2	266.6	264.0	261.4	256.4	251.2
67.5°	251.2	246.1	238.4	235.9	233.3	230.7	228.1	223.1	217.9	215.3	210.2
70°	210.2	205.1	199.9	197.4	194.8	192.3	187.1	184.6	179.5	176.8	174.3
72.5°	169.2	166.6	161.5	159.0	156.3	153.8	151.2	148.7	143.5	141.0	138.4
75°	135.9	133.3	128.2	125.6	123.0	123.0	120.5	115.4	112.7	112.7	110.2
77.5°	102.5	99.9	97.4	94.9	92.2	92.2	89.7	87.1	84.6	84.6	82.1
80°	74.4	71.8	69.2	69.2	69.2	66.6	64.1	64.1	61.6	61.6	58.9
82.5°	48.8	48.8	46.1	46.1	46.1	43.6	43.6	41.0	41.0	41.0	41.0
85°	28.2	28.2	28.2	25.6	25.6	25.6	25.6	25.6	25.6	23.1	25.6
87.5°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584471

CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2
2.5°	1878.9	1876.4	1871.3	1871.3	1866.1	1866.1	1863.6	1861.0	1858.5	1855.8	1853.3
5°	1861.0	1850.8	1845.6	1843.0	1838.0	1835.3	1827.7	1822.5	1820.0	1814.9	1809.7
7.5°	1827.7	1817.4	1807.2	1804.5	1802.0	1791.7	1784.1	1776.4	1771.2	1766.2	1761.1
10°	1789.2	1779.0	1766.2	1761.1	1755.9	1743.1	1732.8	1725.1	1714.9	1704.6	1702.1
12.5°	1743.1	1727.8	1712.3	1707.2	1699.5	1686.7	1676.5	1663.7	1655.9	1643.1	1640.5
15°	1689.3	1671.3	1658.5	1645.7	1640.5	1627.7	1609.8	1599.6	1584.1	1579.1	1566.3
17.5°	1625.2	1607.2	1589.3	1584.1	1576.4	1558.5	1540.6	1527.8	1512.4	1504.7	1497.0
20°	1558.5	1535.5	1517.5	1512.4	1502.2	1486.7	1468.7	1455.9	1443.2	1427.8	1420.1
22.5°	1481.6	1455.9	1440.6	1427.8	1425.3	1407.3	1386.8	1376.5	1366.3	1353.5	1343.2
25°	1397.0	1374.0	1356.0	1345.7	1340.7	1325.2	1309.9	1297.1	1281.6	1274.0	1261.1
27.5°	1309.9	1294.4	1271.4	1261.1	1253.5	1240.6	1222.7	1215.0	1199.7	1189.4	1181.7
30°	1225.3	1202.2	1189.4	1176.6	1168.9	1156.1	1140.7	1132.9	1120.1	1109.9	1102.3
32.5°	1132.9	1117.6	1099.6	1094.6	1084.3	1071.5	1061.2	1048.4	1038.2	1027.9	1025.4
35°	1048.4	1027.9	1009.9	1004.9	997.1	984.3	979.2	971.5	958.6	956.1	945.8
37.5°	956.1	945.8	925.3	917.7	915.2	904.8	894.7	889.5	881.8	874.1	871.5
40°	869.0	856.2	845.9	838.2	833.1	825.4	815.1	812.6	807.5	797.1	794.6
42.5°	787.0	774.1	763.8	761.3	753.7	746.0	740.8	733.2	730.5	728.0	722.9
45°	707.5	699.8	689.6	686.9	684.4	674.1	669.1	663.9	658.8	656.3	651.1
47.5°	635.7	628.0	620.3	617.8	612.7	610.0	602.4	599.8	592.2	589.5	587.0
50°	566.5	561.4	556.2	553.7	548.6	546.0	540.9	535.7	530.6	528.1	525.4
52.5°	505.0	499.8	494.8	492.1	489.6	484.5	479.3	474.2	471.7	469.1	466.5
55°	446.0	440.9	438.3	435.7	433.2	430.7	423.0	420.4	417.9	415.2	410.2
57.5°	392.2	387.1	381.9	381.9	379.4	376.8	371.7	366.6	366.6	361.4	356.3
60°	343.5	338.3	333.3	330.6	328.1	323.0	320.5	317.8	315.3	312.7	307.6
62.5°	292.2	289.7	284.5	284.5	279.4	276.9	274.2	271.7	269.2	264.0	261.4
65°	248.7	246.1	240.9	238.4	238.4	235.9	230.7	228.1	225.6	225.6	223.1
67.5°	207.6	205.1	199.9	197.4	197.4	194.8	192.3	192.3	189.6	187.1	189.6
70°	171.8	166.6	166.6	164.0	164.0	161.5	159.0	159.0	159.0	161.5	161.5
72.5°	135.9	133.3	130.7	130.7	130.7	130.7	128.2	128.2	130.7	133.3	133.3
75°	107.7	105.1	105.1	105.1	102.5	102.5	105.1	105.1	107.7	107.7	107.7
77.5°	79.4	79.4	79.4	79.4	79.4	79.4	82.1	82.1	84.6	84.6	84.6
80°	58.9	58.9	58.9	58.9	58.9	61.6	61.6	61.6	61.6	61.6	64.1
82.5°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	43.6	43.6	43.6	43.6
85°	23.1	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584471

CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2
2.5°	1850.8	1850.8	1850.8	1853.3	1848.2	1848.2	1848.2	1848.2
5°	1807.2	1804.5	1802.0	1804.5	1799.5	1799.5	1796.9	1796.9
7.5°	1753.4	1750.8	1748.2	1748.2	1743.1	1743.1	1740.6	1737.9
10°	1694.3	1689.3	1691.8	1686.7	1684.1	1681.5	1679.0	1676.5
12.5°	1630.2	1625.2	1622.6	1617.4	1612.4	1609.8	1612.4	1607.2
15°	1561.1	1553.4	1550.8	1545.7	1540.6	1538.0	1538.0	1535.5
17.5°	1484.2	1479.1	1476.5	1471.4	1468.7	1463.7	1461.1	1458.6
20°	1412.4	1399.6	1402.1	1397.0	1394.5	1384.2	1384.2	1386.8
22.5°	1332.9	1325.2	1320.1	1315.0	1312.4	1307.3	1307.3	1304.7
25°	1253.5	1245.8	1243.3	1238.1	1235.5	1230.5	1227.8	1227.8
27.5°	1176.6	1166.4	1166.4	1161.2	1156.1	1153.6	1150.9	1148.4
30°	1094.6	1086.8	1084.3	1084.3	1081.8	1081.8	1074.0	1076.6
32.5°	1017.7	1012.5	1009.9	1004.9	1004.9	1002.2	1002.2	994.6
35°	940.8	933.1	935.6	930.5	928.0	925.3	928.0	925.3
37.5°	866.4	861.2	861.2	856.2	856.2	853.6	851.1	856.2
40°	792.1	789.5	787.0	784.3	787.0	784.3	779.3	781.8
42.5°	717.7	717.7	715.2	715.2	712.6	712.6	712.6	712.6
45°	651.1	648.5	648.5	646.0	646.0	646.0	646.0	643.4
47.5°	584.5	581.9	581.9	581.9	579.4	579.4	576.7	579.4
50°	520.4	520.4	517.8	517.8	520.4	517.8	515.3	515.3
52.5°	461.3	461.3	458.8	458.8	456.3	453.7	456.3	456.3
55°	407.6	405.0	402.4	402.4	399.9	397.4	397.4	399.9
57.5°	356.3	353.8	351.1	351.1	346.1	343.5	343.5	343.5
60°	307.6	302.5	302.5	299.9	299.9	297.3	297.3	297.3
62.5°	261.4	258.9	258.9	258.9	258.9	256.4	256.4	256.4
65°	223.1	223.1	223.1	225.6	225.6	228.1	228.1	228.1
67.5°	192.3	194.8	194.8	194.8	197.4	197.4	197.4	194.8
70°	164.0	164.0	164.0	166.6	166.6	166.6	166.6	166.6
72.5°	135.9	135.9	135.9	135.9	135.9	135.9	135.9	135.9
75°	107.7	110.2	110.2	110.2	107.7	110.2	110.2	107.7
77.5°	84.6	84.6	84.6	84.6	84.6	84.6	84.6	84.6
80°	64.1	64.1	64.1	64.1	64.1	64.1	64.1	64.1
82.5°	43.6	43.6	43.6	43.6	43.6	43.6	43.6	43.6
85°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)