

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584468

Luminaire Tested: **HCC8S35D010MW-HM82555930-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MW-HM82555930-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3937.8 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584468
CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584468

CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89					89			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79					79			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70					70			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63					63			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57					57			
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52					52			
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44					44			
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40					40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37					37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78722
5°	78630
10°	77851
15°	76918
20°	76207
25°	75350
30°	71099
35°	57897
40°	31986
45°	21351
50°	18935
55°	17774
60°	17546
65°	17395
70°	15715
75°	14047
80°	12288
85°	10897



TEST NUMBER: P584468
 CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.7	6.1
10°-20°	680.3	17.3
20°-30°	1010.9	25.7
30°-40°	910.4	23.1
40°-50°	403.6	10.2
50°-60°	298.9	7.6
60°-70°	232.4	5.9
70°-80°	126.0	3.2
80°-90°	34.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1932.0	49.1
0°-40°	2842.3	72.2
0°-60°	3544.8	90.0
0°-90°	3937.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3937.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2553	
5°	2540	241
15°	2409	680
25°	2215	1011
35°	1538	910
45°	490	404
55°	331	299
65°	238	232
75°	118	126
85°	31	35
90°	0	



TEST NUMBER: P584468
CATALOG NUMBER: HCC8S35D010MW-HM82555930-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2552.9
2.5°	2547.9
5°	2540.2
7.5°	2519.6
10°	2486.3
12.5°	2447.9
15°	2409.4
17.5°	2371.0
20°	2322.3
22.5°	2273.6
25°	2214.6
27.5°	2124.9
30°	1996.8
32.5°	1812.2
35°	1538.0
37.5°	1148.3
40°	794.6
42.5°	587.0
45°	489.6
47.5°	433.2
50°	394.7
52.5°	358.8
55°	330.6
57.5°	307.6
60°	284.5
62.5°	264.0
65°	238.4
67.5°	207.6
70°	174.3
72.5°	146.2
75°	117.9
77.5°	92.2
80°	69.2
82.5°	48.8
85°	30.8
87.5°	12.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)