

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584313

Luminaire Tested: **HCC8S30D010MW-HM82555927-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010MW-HM82555927-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3009.7 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584313
CATALOG NUMBER: HCC8S30D010MW-HM82555927-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P584313

CATALOG NUMBER: HCC8S30D010MW-HM82555927-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92											92																	
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84											84																	
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77											77																	
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70											70																	
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64											64																	
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59											59																	
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54											54																	
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50											50																	
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46											46																	
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43											43																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72206
5°	70263
10°	69732
15°	68691
20°	66612
25°	64129
30°	59901
35°	49570
40°	29929
45°	20161
50°	14526
55°	8285
60°	3645
65°	1313
70°	487
75°	214
80°	0
85°	0



TEST NUMBER: P584313
 CATALOG NUMBER: HCC8S30D010MW-HM82555927-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.7	7.2
10°-20°	604.7	20.1
20°-30°	862.6	28.7
30°-40°	785.5	26.1
40°-50°	370.6	12.3
50°-60°	145.8	4.8
60°-70°	23.2	0.8
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1683.0	55.9
0°-40°	2468.5	82.0
0°-60°	2984.8	99.2
0°-90°	3009.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3009.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2342	
5°	2270	216
15°	2152	605
25°	1885	863
35°	1317	786
45°	462	371
55°	154	146
65°	18	23
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P584313
CATALOG NUMBER: HCC8S30D010MW-HM82555927-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2341.6
2.5°	2311.2
5°	2269.9
7.5°	2246.6
10°	2227.0
12.5°	2194.7
15°	2151.7
17.5°	2098.0
20°	2029.9
22.5°	1958.2
25°	1884.8
27.5°	1795.2
30°	1682.3
32.5°	1530.0
35°	1316.8
37.5°	1017.7
40°	743.5
42.5°	571.6
45°	462.3
47.5°	379.8
50°	302.8
52.5°	227.6
55°	154.1
57.5°	96.8
60°	59.1
62.5°	35.8
65°	18.0
67.5°	8.9
70°	5.4
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)