

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584482

Luminaire Tested: **HCC8W35D010BZ-HM82555935-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584482
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010BZ-HM82555935-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3861.2 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584482
CATALOG NUMBER: HCC8W35D010BZ-HM82555935-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584482
 CATALOG NUMBER: HCC8W35D010BZ-HM82555935-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																																				
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																																				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																																				
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																																				
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62																																				
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56																																				
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																																				
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																																				
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																																				
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72342
5°	71742
10°	70796
15°	71603
20°	77323
25°	84560
30°	83533
35°	69292
40°	40781
45°	26645
50°	20657
55°	13720
60°	6679
65°	2072
70°	703
75°	620
80°	462
85°	920



TEST NUMBER: P584482
 CATALOG NUMBER: HCC8W35D010BZ-HM82555935-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.5	5.7
10°-20°	644.4	16.7
20°-30°	1126.6	29.2
30°-40°	1095.9	28.4
40°-50°	498.4	12.9
50°-60°	231.1	6.0
60°-70°	38.7	1.0
70°-80°	4.8	0.1
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1990.5	51.6
0°-40°	3086.4	79.9
0°-60°	3815.8	98.8
0°-90°	3861.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3861.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2346	
5°	2318	219
15°	2243	644
25°	2485	1127
35°	1841	1096
45°	611	498
55°	255	231
65°	28	39
75°	5	5
85°	3	2
90°	0	



TEST NUMBER: P584482
CATALOG NUMBER: HCC8W35D010BZ-HM82555935-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2346.0
2.5°	2340.9
5°	2317.7
7.5°	2291.9
10°	2261.0
12.5°	2237.7
15°	2242.9
17.5°	2284.1
20°	2356.3
22.5°	2438.8
25°	2485.3
27.5°	2459.5
30°	2346.0
32.5°	2147.5
35°	1840.7
37.5°	1418.0
40°	1013.1
42.5°	755.3
45°	611.0
47.5°	515.6
50°	430.6
52.5°	342.9
55°	255.2
57.5°	175.3
60°	108.3
62.5°	59.3
65°	28.4
67.5°	12.9
70°	7.8
72.5°	5.2
75°	5.2
77.5°	2.6
80°	2.6
82.5°	2.6
85°	2.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)