

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584473

Luminaire Tested: **HCC8S35D010MW-HM82555935-81MDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584473  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S35D010MW-HM82555935-81MDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4165.2 lumens  
Efficiency: N/A  
Efficacy: 123.6 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584473  
CATALOG NUMBER: HCC8S35D010MW-HM82555935-81MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584473

CATALOG NUMBER: HCC8S35D010MW-HM82555935-81MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	73	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	248868
5°	237449
10°	205006
15°	156760
20°	119943
25°	94890
30°	71680
35°	38134
40°	14524
45°	6969
50°	2965
55°	1247
60°	481
65°	379
70°	234
75°	0
80°	0
85°	0



TEST NUMBER: P584473  
 CATALOG NUMBER: HCC8S35D010MW-HM82555935-81MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	696.3	16.7
10°-20°	1370.8	32.9
20°-30°	1276.7	30.7
30°-40°	658.8	15.8
40°-50°	134.2	3.2
50°-60°	23.0	0.6
60°-70°	4.5	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3343.8	80.3
0°-40°	4002.6	96.1
0°-60°	4159.7	99.9
0°-90°	4165.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4165.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8071	
5°	7671	696
15°	4910	1371
25°	2789	1277
35°	1013	659
45°	160	134
55°	23	23
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P584473  
CATALOG NUMBER: HCC8S35D010MW-HM82555935-81MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8070.6
2.5°	7962.3
5°	7671.0
7.5°	7191.6
10°	6547.2
12.5°	5701.6
15°	4910.4
17.5°	4224.7
20°	3655.1
22.5°	3191.1
25°	2788.9
27.5°	2407.5
30°	2013.1
32.5°	1544.0
35°	1013.0
37.5°	587.7
40°	360.8
42.5°	237.1
45°	159.8
47.5°	100.5
50°	61.8
52.5°	36.1
55°	23.2
57.5°	10.3
60°	7.8
62.5°	5.2
65°	5.2
67.5°	2.6
70°	2.6
72.5°	2.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)