

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584308

Luminaire Tested: **HCC8W30D010BZ-HM82555927-81NDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584308  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W30D010BZ-HM82555927-81NDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2398.7 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584308  
CATALOG NUMBER: HCC8W30D010BZ-HM82555927-81NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584308

CATALOG NUMBER: HCC8W30D010BZ-HM82555927-81NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81	81	81	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73	73	73	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67	67	67	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61	61	61	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56	56	56	56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45	45	45	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	59789
5°	59630
10°	58638
15°	57779
20°	56396
25°	53534
30°	44152
35°	22733
40°	15220
45°	13052
50°	11259
55°	9822
60°	8733
65°	7844
70°	7105
75°	6398
80°	5718
85°	5732



TEST NUMBER: P584308  
 CATALOG NUMBER: HCC8W30D010BZ-HM82555927-81NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.1	7.6
10°-20°	509.2	21.2
20°-30°	705.6	29.4
30°-40°	423.8	17.7
40°-50°	232.0	9.7
50°-60°	164.8	6.9
60°-70°	107.0	4.5
70°-80°	57.2	2.4
80°-90°	17.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1396.9	58.2
0°-40°	1820.7	75.9
0°-60°	2217.5	92.4
0°-90°	2398.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2398.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1939	
5°	1926	182
15°	1810	509
25°	1573	706
35°	604	424
45°	299	232
55°	183	165
65°	108	107
75°	54	57
85°	16	17
90°	0	



TEST NUMBER: P584308  
CATALOG NUMBER: HCC8W30D010BZ-HM82555927-81NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1938.9
2.5°	1935.3
5°	1926.4
7.5°	1904.9
10°	1872.7
12.5°	1842.2
15°	1809.9
17.5°	1768.8
20°	1718.6
22.5°	1657.6
25°	1573.4
27.5°	1440.8
30°	1240.0
32.5°	908.5
35°	603.9
37.5°	446.2
40°	378.1
42.5°	335.1
45°	299.3
47.5°	265.3
50°	234.7
52.5°	206.1
55°	182.7
57.5°	161.2
60°	141.6
62.5°	123.7
65°	107.5
67.5°	91.4
70°	78.8
72.5°	64.6
75°	53.7
77.5°	43.0
80°	32.2
82.5°	23.3
85°	16.2
87.5°	7.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)