

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584476

Luminaire Tested: **HCC8S35D010SL-HM82555935-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
 Report Number: P584476
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 10/21/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO COMMERCIAL
 Catalog Number: HCC8S35D010SL-HM82555935-81NDC
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
 Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 3827.6 lumens
 Efficiency: N/A
 Efficacy: 113.6 lumens/watt
 Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
 Luminous Opening: Circular (Dia: 0.67' x H: 0')
 CIE Type: Direct

Input Watts (W): 33.7
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



TEST NUMBER: P584476
CATALOG NUMBER: HCC8S35D010SL-HM82555935-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584476
 CATALOG NUMBER: HCC8S35D010SL-HM82555935-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96			96																
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			91																
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87			87																
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83			83																
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80			80																
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76			76																
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73			73																
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71			71																
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68			68																
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66			66																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	720423
5°	462095
10°	208745
15°	125953
20°	95978
25°	77507
30°	56796
35°	20565
40°	7676
45°	3484
50°	1113
55°	280
60°	160
65°	190
70°	0
75°	0
80°	462
85°	920



TEST NUMBER: P584476
 CATALOG NUMBER: HCC8S35D010SL-HM82555935-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1138.6	29.7
10°-20°	1156.4	30.2
20°-30°	1035.2	27.0
30°-40°	417.0	10.9
40°-50°	68.4	1.8
50°-60°	6.2	0.2
60°-70°	2.2	0.1
70°-80°	1.7	0.0
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3330.2	87.0
0°-40°	3747.2	97.9
0°-60°	3821.9	99.8
0°-90°	3828.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3827.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23363	
5°	14928	###
15°	3945	1156
25°	2278	1035
35°	546	417
45°	80	68
55°	5	6
65°	3	2
75°	0	2
85°	3	2
90°	0	



TEST NUMBER: P584476
CATALOG NUMBER: HCC8S35D010SL-HM82555935-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	23362.8
0.5°	23290.6
1°	22989.1
1.5°	22504.7
2°	21770.2
2.5°	20901.7
3°	19814.3
3.5°	18621.1
4°	17440.8
4.5°	16118.9
5°	14928.4
5.5°	13632.2
6°	12580.7
6.5°	11485.5
7°	10624.8
7.5°	9715.2
8°	8983.3
8.5°	8248.8
9°	7697.4
9.5°	7089.2
10°	6666.6
12.5°	4916.8
15°	3945.4
17.5°	3370.7
20°	2924.8
22.5°	2569.2
25°	2278.0
27.5°	1986.9
30°	1595.1
32.5°	1025.6
35°	546.3
37.5°	301.5
40°	190.7
42.5°	126.3
45°	79.9
47.5°	49.0
50°	23.2
52.5°	7.8
55°	5.2
57.5°	2.6
60°	2.6
62.5°	2.6
65°	2.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P584476
CATALOG NUMBER: HCC8S35D010SL-HM82555935-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	2.6
80°	2.6
82.5°	2.6
85°	2.6
87.5°	2.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.6
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)