

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584487

Luminaire Tested: **HCC8W35D010SL-HM82555935-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010SL-HM82555935-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3211.6 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584487
CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584487

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	53168	53168	53168
5°	55365	53052	50814
10°	57213	52372	48336
15°	58661	51174	45824
20°	58776	49049	43556
25°	57787	45946	41298
30°	54692	42397	39367
35°	49863	38126	36963
40°	43362	33612	34131
45°	37203	29109	31242
50°	31777	25099	28064
55°	27848	21612	24386
60°	24792	18434	20500
65°	21999	15045	16366
70°	19519	11162	9286
75°	16275	5838	2764
80°	12803	1829	462
85°	9128	920	0



TEST NUMBER: P584487
 CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	5.1
10°-20°	455.3	14.2
20°-30°	644.5	20.1
30°-40°	674.3	21.0
40°-50°	562.4	17.5
50°-60°	398.8	12.4
60°-70°	229.7	7.2
70°-80°	73.9	2.3
80°-90°	10.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1262.3	39.3
0°-40°	1936.6	60.3
0°-60°	2897.8	90.2
0°-90°	3211.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3211.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1724	1724	1724	1724	1724	
5°	1789	1765	1714	1662	1642	172
15°	1838	1763	1603	1477	1435	517
25°	1698	1572	1350	1242	1214	775
35°	1325	1209	1013	959	982	821
45°	853	784	668	675	716	661
55°	518	464	402	423	454	468
65°	302	252	206	206	224	301
75°	137	100	49	23	23	148
85°	26	13	3	0	0	32
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584487

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2
2.5°	1760.2	1757.6	1755.1	1757.6	1755.1	1757.6	1755.1	1755.1	1752.4	1749.9	1749.9
5°	1788.6	1786.0	1786.0	1786.0	1783.5	1780.8	1780.8	1778.3	1773.2	1770.5	1765.4
7.5°	1806.6	1809.2	1809.2	1809.2	1804.1	1804.1	1798.9	1793.8	1788.6	1783.5	1775.7
10°	1827.2	1827.2	1824.7	1822.0	1816.9	1814.4	1811.7	1806.6	1798.9	1788.6	1780.8
12.5°	1835.0	1835.0	1832.3	1827.2	1824.7	1822.0	1819.5	1811.7	1801.4	1788.6	1778.3
15°	1837.5	1832.3	1829.8	1827.2	1822.0	1814.4	1814.4	1804.1	1791.1	1775.7	1762.7
17.5°	1816.9	1819.5	1814.4	1809.2	1801.4	1796.3	1788.6	1780.8	1765.4	1747.3	1734.5
20°	1791.1	1788.6	1786.0	1778.3	1768.0	1765.4	1757.6	1744.8	1731.8	1711.2	1693.3
22.5°	1749.9	1747.3	1742.1	1737.0	1726.7	1721.5	1713.9	1698.4	1680.3	1659.7	1639.1
25°	1698.4	1693.3	1685.5	1675.2	1667.5	1662.2	1651.9	1636.5	1615.9	1592.7	1572.1
27.5°	1615.9	1623.6	1618.5	1603.0	1595.3	1585.0	1582.4	1561.8	1543.7	1520.5	1497.4
30°	1536.0	1536.0	1528.3	1520.5	1507.7	1499.9	1489.6	1474.1	1456.2	1427.8	1409.7
32.5°	1435.4	1432.9	1422.6	1420.0	1409.7	1394.2	1391.7	1371.1	1353.0	1332.4	1309.2
35°	1324.6	1319.5	1309.2	1301.5	1296.4	1288.6	1280.9	1262.8	1244.7	1224.1	1208.7
37.5°	1198.4	1198.4	1195.8	1182.9	1177.8	1172.6	1164.9	1146.8	1136.5	1115.9	1100.5
40°	1077.2	1074.7	1066.9	1064.4	1059.3	1051.5	1046.3	1036.0	1020.6	1005.1	989.7
42.5°	958.8	961.3	951.0	953.6	943.3	938.2	935.5	920.1	912.3	896.8	884.0
45°	853.1	850.5	845.3	842.8	837.6	832.5	827.2	819.6	806.6	791.2	783.5
47.5°	755.1	747.4	747.4	744.8	742.3	732.0	729.3	721.6	713.9	698.4	688.1
50°	662.4	662.4	662.4	659.7	652.1	649.4	644.3	636.6	628.8	618.5	603.1
52.5°	587.6	587.6	587.6	585.0	574.7	572.2	569.5	559.2	548.9	541.3	531.0
55°	518.0	520.7	518.0	512.9	505.1	505.1	497.4	492.3	482.0	474.2	463.9
57.5°	458.7	458.7	453.6	451.0	445.9	443.3	438.1	433.0	420.1	412.4	399.4
60°	402.0	399.4	399.4	394.3	389.1	384.0	381.4	373.7	368.5	355.7	345.4
62.5°	350.5	350.5	345.4	345.4	335.1	335.1	332.4	324.8	317.0	304.1	298.9
65°	301.5	301.5	298.9	296.4	288.6	286.1	283.4	275.8	268.0	260.3	252.5
67.5°	257.7	257.7	252.5	250.0	244.9	242.2	237.1	231.9	224.3	216.5	208.8
70°	216.5	214.0	211.3	208.8	203.5	201.0	195.9	190.7	182.9	177.8	170.1
72.5°	175.3	175.3	172.6	167.5	165.0	162.3	159.8	154.7	146.9	139.2	134.1
75°	136.6	136.6	136.6	131.4	126.3	123.8	123.8	118.6	113.5	105.7	100.5
77.5°	105.7	103.0	100.5	100.5	95.4	92.7	90.2	87.6	79.9	77.3	72.1
80°	72.1	74.8	72.1	69.6	67.0	64.5	64.5	59.3	56.7	51.5	46.4
82.5°	49.0	46.4	46.4	43.8	43.8	41.2	41.2	36.1	33.5	30.9	28.4
85°	25.8	25.8	23.2	23.2	23.2	20.6	20.6	18.1	18.1	15.5	12.9
87.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	5.2	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584487

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2
2.5°	1747.3	1742.1	1739.6	1739.6	1737.0	1734.5	1731.8	1729.3	1724.2	1724.2	1719.0
5°	1760.2	1755.1	1752.4	1744.8	1739.6	1739.6	1729.3	1726.7	1719.0	1713.9	1708.7
7.5°	1770.5	1760.2	1752.4	1744.8	1739.6	1734.5	1724.2	1713.9	1703.6	1693.3	1688.1
10°	1770.5	1760.2	1747.3	1734.5	1729.3	1724.2	1711.2	1695.8	1683.0	1672.6	1659.7
12.5°	1765.4	1749.9	1734.5	1724.2	1713.9	1706.1	1690.6	1675.2	1659.7	1639.1	1628.8
15°	1749.9	1729.3	1713.9	1695.8	1688.1	1675.2	1662.2	1639.1	1621.0	1603.0	1590.1
17.5°	1719.0	1693.3	1675.2	1657.1	1644.3	1636.5	1615.9	1595.3	1574.7	1554.0	1538.6
20°	1672.6	1649.4	1628.8	1605.6	1595.3	1585.0	1559.2	1538.6	1518.0	1494.7	1479.3
22.5°	1615.9	1592.7	1564.3	1546.3	1530.8	1518.0	1494.7	1471.6	1450.9	1430.3	1409.7
25°	1546.3	1523.1	1497.4	1469.0	1458.7	1445.7	1420.0	1396.9	1373.6	1350.4	1332.4
27.5°	1471.6	1440.6	1420.0	1389.1	1378.8	1366.0	1337.6	1311.8	1291.2	1273.1	1252.5
30°	1381.4	1358.2	1329.8	1301.5	1291.2	1278.3	1255.1	1231.9	1211.3	1190.7	1170.1
32.5°	1283.4	1260.3	1231.9	1211.3	1195.8	1185.5	1162.3	1141.7	1121.1	1100.5	1082.4
35°	1180.4	1154.6	1133.9	1113.3	1100.5	1087.5	1064.4	1046.3	1030.9	1012.8	994.8
37.5°	1074.7	1056.6	1036.0	1012.8	1000.0	989.7	971.6	951.0	938.2	922.6	909.8
40°	971.6	951.0	932.9	912.3	902.0	894.3	876.2	860.8	847.9	835.0	827.2
42.5°	865.9	847.9	829.9	816.9	809.2	801.5	788.6	770.6	762.9	749.9	742.3
45°	768.0	752.6	739.6	721.6	716.4	711.3	695.8	683.0	675.2	667.5	662.4
47.5°	675.2	664.9	649.4	639.1	631.5	626.3	615.9	605.6	597.9	592.8	587.6
50°	595.3	582.5	572.2	561.9	556.7	548.9	538.6	533.5	528.3	523.2	523.2
52.5°	520.7	507.7	497.4	489.6	484.5	479.3	471.7	469.0	463.9	463.9	461.3
55°	451.0	443.3	433.0	422.7	420.1	417.5	412.4	407.2	404.6	402.0	404.6
57.5°	391.7	384.0	373.7	366.0	363.4	360.8	358.2	353.1	350.5	350.5	350.5
60°	337.6	329.9	322.1	314.5	314.5	309.2	306.7	304.1	301.5	298.9	298.9
62.5°	288.6	280.9	273.1	268.0	265.5	262.8	257.7	255.2	252.5	252.5	250.0
65°	244.9	234.6	231.9	224.3	221.6	219.1	216.5	211.3	208.8	206.2	203.5
67.5°	201.0	195.9	188.1	182.9	180.4	177.8	175.3	170.1	167.5	165.0	159.8
70°	162.3	157.2	152.0	146.9	144.4	141.7	136.6	131.4	128.9	123.8	116.0
72.5°	126.3	121.1	116.0	110.8	108.3	105.7	100.5	95.4	90.2	85.1	79.9
75°	95.4	90.2	82.4	77.3	74.8	74.8	67.0	61.8	56.7	49.0	43.8
77.5°	67.0	59.3	56.7	51.5	49.0	43.8	38.7	33.5	28.4	25.8	20.6
80°	43.8	38.7	33.5	30.9	28.4	25.8	23.2	18.1	12.9	10.3	7.8
82.5°	25.8	23.2	20.6	18.1	15.5	12.9	10.3	10.3	7.8	5.2	2.6
85°	12.9	10.3	7.8	7.8	5.2	5.2	5.2	2.6	2.6	2.6	2.6
87.5°	5.2	2.6	2.6	2.6	2.6	2.6	2.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584487

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2
2.5°	1716.4	1713.9	1711.2	1708.7	1708.7	1703.6	1703.6	1700.9	1695.8	1693.3	1693.3
5°	1700.9	1693.3	1688.1	1685.5	1683.0	1675.2	1672.6	1667.5	1662.2	1657.1	1654.6
7.5°	1677.8	1664.9	1659.7	1657.1	1649.4	1641.6	1636.5	1628.8	1621.0	1613.3	1610.7
10°	1649.4	1636.5	1623.6	1618.5	1610.7	1605.6	1595.3	1585.0	1577.3	1569.5	1561.8
12.5°	1613.3	1597.9	1585.0	1579.8	1572.1	1561.8	1546.3	1541.1	1528.3	1523.1	1512.8
15°	1572.1	1554.0	1541.1	1533.4	1525.7	1510.2	1499.9	1489.6	1476.8	1471.6	1461.3
17.5°	1520.5	1499.9	1487.1	1479.3	1474.1	1461.3	1445.7	1432.9	1420.0	1414.8	1407.2
20°	1458.7	1445.7	1427.8	1420.0	1414.8	1399.4	1383.9	1378.8	1368.5	1358.2	1350.4
22.5°	1389.1	1376.3	1358.2	1350.4	1347.9	1334.9	1322.1	1314.3	1306.7	1298.9	1291.2
25°	1317.0	1301.5	1286.1	1280.9	1275.8	1265.4	1255.1	1250.0	1242.2	1237.1	1231.9
27.5°	1239.6	1224.1	1211.3	1203.5	1198.4	1190.7	1185.5	1180.4	1175.2	1170.1	1167.5
30°	1157.1	1141.7	1131.4	1126.2	1121.1	1118.5	1110.8	1108.1	1105.6	1100.5	1103.0
32.5°	1074.7	1061.8	1051.5	1043.8	1043.8	1038.5	1036.0	1036.0	1033.4	1033.4	1033.4
35°	984.5	976.7	969.1	966.4	963.9	961.3	958.8	961.3	958.8	961.3	963.9
37.5°	902.0	894.3	889.2	886.5	884.0	886.5	884.0	884.0	886.5	891.7	894.3
40°	816.9	811.8	806.6	809.2	806.6	806.6	806.6	814.4	816.9	819.6	822.1
42.5°	737.1	732.0	729.3	729.3	732.0	729.3	734.5	737.1	742.3	749.9	755.1
45°	659.7	657.2	657.2	659.7	657.2	662.4	662.4	667.5	675.2	680.3	685.5
47.5°	587.6	587.6	587.6	590.1	590.1	592.8	597.9	600.4	605.6	610.7	615.9
50°	520.7	523.2	525.8	525.8	525.8	531.0	536.1	538.6	541.3	543.8	551.6
52.5°	461.3	463.9	463.9	466.5	469.0	471.7	474.2	479.3	482.0	487.1	489.6
55°	404.6	404.6	409.7	412.4	412.4	412.4	417.5	417.5	422.7	425.3	430.4
57.5°	350.5	353.1	353.1	355.7	355.7	358.2	360.8	363.4	366.0	368.5	371.1
60°	298.9	298.9	298.9	301.5	304.1	306.7	304.1	309.2	309.2	314.5	317.0
62.5°	250.0	252.5	252.5	252.5	252.5	252.5	252.5	255.2	257.7	260.3	262.8
65°	203.5	203.5	203.5	201.0	203.5	201.0	203.5	206.2	206.2	208.8	211.3
67.5°	157.2	157.2	152.0	152.0	154.7	154.7	154.7	154.7	152.0	157.2	157.2
70°	113.5	110.8	108.3	105.7	105.7	103.0	103.0	100.5	100.5	100.5	100.5
72.5°	74.8	69.6	64.5	61.8	59.3	59.3	54.1	51.5	54.1	54.1	54.1
75°	38.7	33.5	30.9	28.4	25.8	25.8	23.2	23.2	23.2	23.2	23.2
77.5°	15.5	12.9	10.3	10.3	7.8	7.8	7.8	7.8	7.8	7.8	7.8
80°	5.2	5.2	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
85°	2.6	0.0	0.0	2.6	0.0	2.6	2.6	2.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584487

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2	1724.2
2.5°	1690.6	1690.6	1688.1	1690.6	1685.5	1688.1	1685.5	1685.5
5°	1651.9	1646.8	1646.8	1646.8	1644.3	1644.3	1641.6	1641.6
7.5°	1605.6	1603.0	1600.4	1597.9	1595.3	1592.7	1592.7	1592.7
10°	1559.2	1554.0	1554.0	1551.4	1546.3	1543.7	1543.7	1543.7
12.5°	1505.0	1502.5	1499.9	1499.9	1489.6	1492.2	1489.6	1489.6
15°	1453.5	1450.9	1450.9	1443.2	1438.1	1438.1	1438.1	1435.4
17.5°	1399.4	1396.9	1394.2	1389.1	1383.9	1383.9	1381.4	1383.9
20°	1342.7	1340.1	1334.9	1334.9	1332.4	1329.8	1324.6	1327.3
22.5°	1286.1	1280.9	1278.3	1278.3	1275.8	1275.8	1270.6	1270.6
25°	1226.8	1224.1	1221.6	1224.1	1219.0	1219.0	1213.8	1213.8
27.5°	1164.9	1162.3	1162.3	1162.3	1159.8	1162.3	1159.8	1159.8
30°	1103.0	1103.0	1100.5	1100.5	1103.0	1100.5	1103.0	1105.6
32.5°	1036.0	1036.0	1038.5	1038.5	1041.2	1041.2	1041.2	1041.2
35°	966.4	971.6	971.6	974.2	976.7	979.4	979.4	981.9
37.5°	902.0	904.6	907.1	909.8	914.9	914.9	914.9	914.9
40°	832.5	835.0	840.2	837.6	847.9	850.5	847.9	847.9
42.5°	760.3	765.4	768.0	773.2	775.7	780.9	783.5	783.5
45°	693.3	695.8	700.9	706.1	708.7	716.4	716.4	716.4
47.5°	623.7	628.8	631.5	636.6	639.1	646.9	649.4	646.9
50°	556.7	561.9	567.0	567.0	574.7	577.3	582.5	585.0
52.5°	492.3	494.8	499.9	502.6	507.7	512.9	515.4	518.0
55°	430.4	433.0	438.1	438.1	445.9	448.4	453.6	453.6
57.5°	373.7	376.3	381.4	378.8	384.0	389.1	389.1	386.6
60°	319.6	319.6	319.6	324.8	327.3	329.9	332.4	332.4
62.5°	262.8	268.0	270.6	270.6	273.1	275.8	275.8	273.1
65°	211.3	216.5	219.1	219.1	221.6	221.6	221.6	224.3
67.5°	159.8	159.8	159.8	162.3	159.8	159.8	159.8	159.8
70°	100.5	100.5	100.5	100.5	97.9	100.5	100.5	103.0
72.5°	54.1	54.1	54.1	54.1	54.1	54.1	54.1	54.1
75°	23.2	23.2	23.2	25.8	23.2	23.2	23.2	23.2
77.5°	10.3	7.8	10.3	10.3	7.8	7.8	7.8	7.8
80°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
85°	0.0	2.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)