

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584327

Luminaire Tested: **HCC8S30D010MW-HM82555930-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010MW-HM82555930-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3037.8 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584327
CATALOG NUMBER: HCC8S30D010MW-HM82555930-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P584327

CATALOG NUMBER: HCC8S30D010MW-HM82555930-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	49289	49289	49289
5°	49935	49078	48617
10°	50447	48577	47842
15°	50957	47551	46596
20°	50700	45797	44750
25°	49515	43058	42472
30°	47036	39965	39819
35°	42817	36470	36793
40°	37537	32642	33841
45°	32384	29035	31085
50°	28357	25493	28155
55°	25128	21913	24784
60°	22634	18428	20531
65°	20394	14790	15731
70°	17888	10774	8664
75°	15262	5600	2299
80°	11738	1527	373
85°	7536	0	0



TEST NUMBER: P584327
 CATALOG NUMBER: HCC8S30D010MW-HM82555930-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	5.0
10°-20°	423.9	14.0
20°-30°	601.7	19.8
30°-40°	633.4	20.9
40°-50°	538.8	17.7
50°-60°	389.4	12.8
60°-70°	221.5	7.3
70°-80°	69.8	2.3
80°-90°	8.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1176.4	38.7
0°-40°	1809.8	59.6
0°-60°	2738.0	90.1
0°-90°	3037.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3037.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1598	1598	1598	1598	1598	
5°	1613	1605	1586	1575	1571	154
15°	1596	1556	1490	1462	1460	449
25°	1455	1383	1266	1244	1248	667
35°	1137	1071	969	962	977	708
45°	743	715	666	683	713	577
55°	467	433	408	431	461	421
65°	280	241	203	201	216	277
75°	128	98	47	21	19	138
85°	21	13	0	0	0	28
90°	0	0	0	0	0	



TEST NUMBER: P584327

CATALOG NUMBER: HCC8S30D010MW-HM82555930-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4
2.5°	1606.9	1609.1	1604.8	1604.8	1609.1	1604.8	1606.9	1606.9	1604.8	1604.8	1602.7
5°	1613.2	1611.1	1611.1	1611.1	1613.2	1609.1	1606.9	1609.1	1604.8	1604.8	1604.8
7.5°	1615.4	1615.4	1613.2	1611.1	1611.1	1611.1	1609.1	1606.9	1604.8	1600.5	1598.4
10°	1611.1	1611.1	1613.2	1609.1	1609.1	1604.8	1604.8	1600.5	1600.5	1596.2	1589.8
12.5°	1606.9	1604.8	1604.8	1600.5	1600.5	1596.2	1596.2	1589.8	1587.7	1581.3	1574.8
15°	1596.2	1594.1	1589.8	1587.7	1585.5	1583.4	1579.1	1577.0	1570.6	1562.1	1555.7
17.5°	1574.8	1572.7	1570.6	1566.4	1562.1	1560.0	1557.8	1551.4	1542.8	1536.4	1525.8
20°	1545.0	1542.8	1542.8	1536.4	1534.3	1527.9	1525.8	1517.3	1510.9	1498.0	1489.5
22.5°	1504.4	1506.6	1502.3	1498.0	1493.7	1487.3	1483.2	1474.6	1463.9	1451.1	1440.5
25°	1455.3	1457.5	1453.2	1448.9	1442.6	1438.3	1434.1	1421.2	1410.5	1395.6	1382.8
27.5°	1393.5	1393.5	1393.5	1389.2	1378.5	1376.4	1372.1	1359.4	1344.4	1331.6	1318.8
30°	1321.0	1318.8	1318.8	1312.4	1308.1	1299.6	1293.2	1282.6	1271.9	1256.9	1242.0
32.5°	1233.5	1235.6	1229.2	1224.9	1218.5	1218.5	1209.9	1201.5	1188.6	1173.7	1158.8
35°	1137.4	1139.5	1135.3	1133.1	1122.4	1120.3	1118.3	1107.6	1099.0	1088.3	1071.3
37.5°	1039.2	1037.2	1035.0	1035.0	1028.6	1024.3	1020.0	1013.6	1000.8	992.3	983.8
40°	932.5	932.5	932.5	930.4	928.3	924.0	921.8	917.6	909.1	900.5	894.1
42.5°	836.5	836.5	834.4	832.3	828.0	830.2	825.9	821.6	813.0	806.6	802.3
45°	742.6	742.6	742.6	744.8	740.5	734.1	734.1	729.8	725.5	721.2	714.8
47.5°	659.4	665.8	661.6	659.4	661.6	653.0	653.0	648.7	644.4	640.2	631.6
50°	591.1	591.1	591.1	586.9	584.8	584.8	578.3	574.0	571.9	567.6	559.1
52.5°	529.2	524.9	524.9	522.8	520.7	516.4	516.4	512.1	503.7	499.4	493.0
55°	467.4	467.4	465.3	463.1	461.0	458.8	456.7	450.3	446.0	439.6	433.2
57.5°	411.9	416.2	414.0	409.7	405.4	405.4	401.2	396.9	390.5	384.2	377.7
60°	367.0	364.9	364.9	362.8	358.5	356.3	354.2	347.8	341.5	335.1	328.6
62.5°	320.1	320.1	320.1	315.8	311.5	309.4	307.2	303.1	294.5	288.1	283.8
65°	279.5	277.4	275.3	273.1	271.0	266.7	264.7	260.4	254.0	247.5	241.1
67.5°	239.0	236.8	236.8	234.7	228.3	226.1	226.1	219.8	213.4	207.0	200.6
70°	198.4	198.4	198.4	194.2	192.0	189.9	187.7	183.5	177.2	170.7	164.3
72.5°	164.3	162.2	162.2	160.0	153.6	151.5	149.3	145.1	138.8	134.5	130.2
75°	128.1	128.1	125.9	123.8	121.6	119.5	117.4	113.1	106.7	100.4	98.2
77.5°	98.2	96.1	96.1	93.9	89.7	87.5	87.5	83.2	76.8	72.5	68.2
80°	66.1	68.2	66.1	64.0	61.8	59.8	57.7	55.5	51.2	47.0	42.7
82.5°	40.5	42.7	40.5	40.5	38.4	36.3	36.3	32.0	29.8	27.7	25.6
85°	21.3	21.3	21.3	21.3	19.3	19.3	19.3	17.1	15.0	12.8	12.8
87.5°	6.4	8.6	6.4	6.4	6.4	6.4	6.4	6.4	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584327

CATALOG NUMBER: HCC8S30D010MW-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4
2.5°	1604.8	1602.7	1600.5	1600.5	1600.5	1600.5	1600.5	1598.4	1596.2	1596.2	1596.2
5°	1600.5	1600.5	1600.5	1598.4	1596.2	1596.2	1592.0	1589.8	1587.7	1585.5	1583.4
7.5°	1596.2	1592.0	1589.8	1587.7	1585.5	1585.5	1581.3	1577.0	1577.0	1572.7	1568.4
10°	1583.4	1581.3	1577.0	1572.7	1570.6	1568.4	1564.2	1557.8	1555.7	1551.4	1547.1
12.5°	1568.4	1564.2	1560.0	1551.4	1549.3	1547.1	1538.6	1532.1	1527.9	1525.8	1515.1
15°	1549.3	1540.7	1534.3	1523.7	1521.6	1517.3	1510.9	1504.4	1495.9	1489.5	1485.3
17.5°	1515.1	1506.6	1495.9	1485.3	1481.0	1481.0	1470.3	1461.8	1451.1	1446.8	1438.3
20°	1474.6	1463.9	1455.3	1442.6	1436.2	1429.8	1423.4	1410.5	1402.1	1395.6	1384.9
22.5°	1427.6	1412.7	1402.1	1389.2	1378.5	1372.1	1361.5	1350.8	1340.1	1333.7	1325.1
25°	1367.8	1355.1	1338.0	1325.1	1318.8	1310.3	1297.4	1286.7	1276.2	1265.5	1261.2
27.5°	1301.7	1284.6	1269.7	1254.8	1248.3	1242.0	1227.0	1214.2	1205.6	1195.1	1190.8
30°	1229.2	1212.1	1195.1	1182.2	1175.8	1165.1	1156.7	1141.7	1131.0	1122.4	1111.8
32.5°	1146.0	1133.1	1118.3	1099.0	1094.7	1086.2	1073.4	1067.0	1054.2	1047.7	1039.2
35°	1056.3	1047.7	1032.9	1017.9	1011.5	1007.2	996.6	983.8	975.2	968.8	964.5
37.5°	970.9	960.2	945.4	934.7	930.4	924.0	911.2	904.8	896.3	892.0	883.4
40°	879.1	868.6	857.9	851.4	845.0	840.7	832.3	825.9	817.3	810.9	808.8
42.5°	789.6	783.2	774.6	766.1	763.9	757.5	753.4	746.9	740.5	738.4	731.9
45°	708.5	702.1	693.5	685.0	682.8	678.6	676.4	670.1	665.8	665.8	665.8
47.5°	627.4	621.0	612.5	608.2	610.3	601.8	601.8	599.6	595.3	595.3	597.5
50°	554.8	546.3	544.2	539.9	535.6	531.4	533.5	527.1	527.1	531.4	529.2
52.5°	486.5	478.0	475.8	471.6	469.4	469.4	467.4	467.4	465.3	467.4	467.4
55°	424.7	418.3	414.0	409.7	407.6	407.6	407.6	405.4	403.3	407.6	409.7
57.5°	369.2	367.0	362.8	356.3	354.2	352.1	349.9	349.9	349.9	349.9	352.1
60°	320.1	315.8	311.5	305.2	305.2	303.1	300.9	298.8	298.8	298.8	298.8
62.5°	277.4	271.0	264.7	260.4	258.3	256.1	254.0	249.7	249.7	249.7	249.7
65°	234.7	228.3	224.0	219.8	215.6	215.6	211.3	209.1	204.9	202.7	198.4
67.5°	194.2	189.9	185.6	179.3	177.2	175.0	170.7	168.6	162.2	160.0	157.9
70°	157.9	151.5	147.2	142.9	140.9	136.6	132.3	128.1	123.8	119.5	115.2
72.5°	123.8	117.4	113.1	108.8	104.5	104.5	98.2	93.9	87.5	83.2	76.8
75°	91.8	85.4	81.1	74.7	72.5	70.4	64.0	59.8	53.4	47.0	42.7
77.5°	61.8	57.7	53.4	47.0	42.7	42.7	36.3	32.0	27.7	21.3	19.3
80°	38.4	34.1	29.8	25.6	25.6	21.3	19.3	15.0	10.7	8.6	6.4
82.5°	21.3	19.3	17.1	12.8	12.8	10.7	8.6	6.4	4.3	2.1	2.1
85°	10.7	8.6	6.4	6.4	4.3	4.3	4.3	2.1	2.1	0.0	0.0
87.5°	4.3	2.1	2.1	2.1	2.1	2.1	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584327

CATALOG NUMBER: HCC8S30D010MW-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4
2.5°	1594.1	1594.1	1592.0	1592.0	1592.0	1589.8	1592.0	1589.8	1589.8	1589.8	1592.0
5°	1585.5	1581.3	1581.3	1579.1	1579.1	1577.0	1579.1	1577.0	1574.8	1572.7	1574.8
7.5°	1568.4	1564.2	1562.1	1560.0	1560.0	1560.0	1557.8	1555.7	1557.8	1551.4	1555.7
10°	1545.0	1542.8	1538.6	1536.4	1534.3	1536.4	1534.3	1530.0	1530.0	1530.0	1527.9
12.5°	1515.1	1510.9	1508.7	1506.6	1502.3	1502.3	1504.4	1500.2	1500.2	1495.9	1495.9
15°	1478.9	1474.6	1470.3	1470.3	1466.0	1466.0	1463.9	1463.9	1461.8	1459.6	1459.6
17.5°	1434.1	1427.6	1423.4	1425.5	1423.4	1421.2	1421.2	1416.9	1414.8	1416.9	1416.9
20°	1380.7	1376.4	1372.1	1374.2	1370.0	1367.8	1370.0	1363.7	1365.7	1365.7	1365.7
22.5°	1321.0	1318.8	1312.4	1312.4	1308.1	1306.0	1308.1	1308.1	1310.3	1308.1	1308.1
25°	1254.8	1250.5	1246.2	1246.2	1244.1	1242.0	1244.1	1246.2	1244.1	1246.2	1246.2
27.5°	1184.4	1177.9	1177.9	1173.7	1173.7	1175.8	1173.7	1175.8	1177.9	1177.9	1182.2
30°	1107.6	1105.4	1103.3	1101.1	1101.1	1103.3	1103.3	1103.3	1105.4	1109.7	1109.7
32.5°	1035.0	1030.7	1026.5	1026.5	1030.7	1028.6	1030.7	1030.7	1035.0	1035.0	1039.2
35°	956.1	956.1	951.8	953.9	953.9	953.9	953.9	958.1	962.4	964.5	968.8
37.5°	883.4	877.0	879.1	879.1	881.3	879.1	885.6	885.6	889.8	889.8	894.1
40°	804.5	804.5	806.6	804.5	806.6	806.6	810.9	815.2	817.3	821.6	823.7
42.5°	729.8	734.1	729.8	731.9	734.1	736.2	738.4	740.5	749.1	753.4	759.7
45°	661.6	663.7	665.8	668.0	665.8	670.1	672.1	676.4	682.8	685.0	687.1
47.5°	595.3	597.5	599.6	601.8	601.8	606.0	608.2	612.5	616.7	618.9	621.0
50°	531.4	535.6	537.8	537.8	539.9	544.2	548.5	548.5	552.6	559.1	561.2
52.5°	473.7	473.7	478.0	480.1	482.3	482.3	488.7	490.8	493.0	497.2	501.5
55°	409.7	416.2	418.3	418.3	422.6	426.9	428.9	431.0	431.0	439.6	439.6
57.5°	354.2	356.3	360.6	360.6	360.6	367.0	367.0	371.3	373.5	375.6	379.9
60°	298.8	303.1	303.1	305.2	303.1	307.2	309.4	313.7	315.8	317.9	320.1
62.5°	247.5	247.5	249.7	249.7	249.7	249.7	254.0	254.0	258.3	260.4	262.5
65°	198.4	198.4	198.4	198.4	198.4	198.4	198.4	198.4	200.6	200.6	204.9
67.5°	153.6	151.5	147.2	149.3	147.2	147.2	145.1	145.1	147.2	147.2	151.5
70°	110.9	108.8	104.5	104.5	102.4	100.4	98.2	96.1	93.9	93.9	93.9
72.5°	72.5	68.2	61.8	59.8	59.8	55.5	51.2	49.1	49.1	49.1	49.1
75°	36.3	32.0	27.7	25.6	25.6	21.3	23.4	21.3	21.3	21.3	21.3
77.5°	15.0	10.7	8.6	8.6	8.6	6.4	6.4	6.4	6.4	6.4	6.4
80°	4.3	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584327

CATALOG NUMBER: HCC8S30D010MW-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4	1598.4
2.5°	1589.8	1589.8	1585.5	1587.7	1587.7	1587.7	1587.7	1587.7
5°	1570.6	1572.7	1570.6	1572.7	1572.7	1570.6	1570.6	1570.6
7.5°	1551.4	1553.5	1551.4	1553.5	1553.5	1553.5	1551.4	1551.4
10°	1527.9	1527.9	1527.9	1527.9	1527.9	1525.8	1527.9	1527.9
12.5°	1495.9	1495.9	1495.9	1498.0	1498.0	1495.9	1495.9	1493.7
15°	1461.8	1457.5	1459.6	1461.8	1459.6	1459.6	1459.6	1459.6
17.5°	1414.8	1416.9	1414.8	1414.8	1414.8	1414.8	1416.9	1414.8
20°	1365.7	1365.7	1367.8	1365.7	1365.7	1365.7	1365.7	1363.7
22.5°	1310.3	1308.1	1308.1	1310.3	1310.3	1308.1	1310.3	1310.3
25°	1248.3	1250.5	1248.3	1248.3	1250.5	1250.5	1250.5	1248.3
27.5°	1182.2	1184.4	1186.5	1184.4	1184.4	1184.4	1186.5	1188.6
30°	1114.0	1118.3	1114.0	1114.0	1118.3	1116.1	1118.3	1118.3
32.5°	1041.3	1047.7	1043.5	1047.7	1047.7	1049.9	1047.7	1049.9
35°	968.8	975.2	975.2	975.2	977.4	979.5	979.5	977.4
37.5°	900.5	902.7	902.7	907.0	909.1	911.2	911.2	909.1
40°	830.2	834.4	836.5	836.5	836.5	840.7	845.0	840.7
42.5°	761.8	763.9	766.1	766.1	770.4	772.5	774.6	774.6
45°	695.7	700.0	702.1	704.2	706.4	710.7	708.5	712.8
47.5°	627.4	633.7	635.9	638.0	642.3	644.4	646.6	648.7
50°	565.5	569.8	569.8	574.0	580.5	580.5	584.8	586.9
52.5°	503.7	505.8	507.9	510.0	514.2	518.5	518.5	522.8
55°	443.9	446.0	446.0	448.1	450.3	458.8	461.0	461.0
57.5°	382.0	382.0	386.3	388.3	390.5	394.7	394.7	394.7
60°	322.2	324.4	324.4	326.5	328.6	332.9	335.1	332.9
62.5°	262.5	264.7	264.7	266.7	271.0	273.1	271.0	271.0
65°	207.0	209.1	209.1	211.3	215.6	215.6	213.4	215.6
67.5°	151.5	151.5	151.5	151.5	151.5	151.5	151.5	151.5
70°	96.1	93.9	91.8	93.9	93.9	93.9	91.8	96.1
72.5°	47.0	49.1	49.1	49.1	49.1	49.1	49.1	47.0
75°	21.3	21.3	19.3	19.3	19.3	21.3	21.3	19.3
77.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)