

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584488

Luminaire Tested: **HCC8W35D010SL-HM82555935-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010SL-HM82555935-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3505.4 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584488
CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584488

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	58570	58570	58570
5°	60627	58234	55922
10°	61973	57213	52776
15°	62855	55286	49281
20°	62667	52603	45751
25°	61118	49189	41999
30°	57904	45242	38541
35°	52679	40938	35024
40°	46268	36414	31640
45°	40347	32031	28211
50°	35111	28064	24850
55°	31316	24660	21612
60°	28450	21616	18434
65°	25574	18803	16738
70°	22765	16030	15102
75°	19956	13523	12903
80°	16941	10974	11454
85°	12772	8208	9128



TEST NUMBER: P584488
 CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	5.1
10°-20°	490.2	14.0
20°-30°	680.4	19.4
30°-40°	703.5	20.1
40°-50°	589.0	16.8
50°-60°	427.6	12.2
60°-70°	269.8	7.7
70°-80°	133.7	3.8
80°-90°	33.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1348.5	38.5
0°-40°	2052.0	58.5
0°-60°	3068.6	87.5
0°-90°	3505.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3505.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1899	1899	1899	1899	1899	
5°	1959	1936	1881	1830	1807	187
15°	1969	1894	1732	1593	1544	554
25°	1796	1680	1446	1289	1234	823
35°	1399	1296	1088	964	930	871
45°	925	858	734	662	647	716
55°	582	531	459	420	402	526
65°	350	307	258	227	229	349
75°	168	139	114	108	108	180
85°	36	28	23	26	26	44
90°	0	0	0	0	0	



TEST NUMBER: P584488

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4
2.5°	1930.3	1930.3	1932.9	1930.3	1930.3	1930.3	1927.7	1927.7	1925.2	1925.2	1920.0
5°	1958.6	1953.5	1958.6	1953.5	1953.5	1953.5	1950.9	1945.8	1943.2	1938.0	1935.5
7.5°	1971.5	1968.9	1968.9	1966.4	1966.4	1963.8	1961.2	1958.6	1948.3	1945.8	1938.0
10°	1979.2	1976.7	1976.7	1974.1	1968.9	1968.9	1963.8	1961.2	1948.3	1943.2	1932.9
12.5°	1976.7	1976.7	1976.7	1974.1	1966.4	1963.8	1958.6	1950.9	1940.6	1930.3	1920.0
15°	1968.9	1968.9	1963.8	1961.2	1953.5	1948.3	1945.8	1932.9	1922.6	1909.7	1894.2
17.5°	1943.2	1943.2	1940.6	1935.5	1927.7	1922.6	1917.4	1904.6	1894.2	1873.6	1858.1
20°	1909.7	1907.1	1904.6	1896.8	1889.0	1886.5	1878.7	1860.7	1847.8	1832.3	1811.7
22.5°	1860.7	1858.1	1855.6	1850.4	1837.5	1832.3	1827.2	1814.4	1791.1	1775.7	1749.9
25°	1796.3	1796.3	1791.1	1783.3	1770.5	1765.4	1757.6	1744.8	1724.2	1700.9	1680.3
27.5°	1721.5	1719.0	1711.2	1706.1	1695.8	1688.1	1675.2	1659.7	1639.1	1621.0	1595.3
30°	1626.2	1626.2	1621.0	1613.3	1600.4	1595.3	1585.0	1566.9	1546.3	1523.1	1505.0
32.5°	1518.0	1518.0	1510.2	1505.0	1497.4	1484.4	1481.9	1461.2	1443.2	1425.1	1404.5
35°	1399.4	1402.0	1396.9	1386.6	1373.6	1373.6	1368.5	1350.4	1329.8	1311.8	1296.4
37.5°	1280.9	1273.1	1270.6	1265.4	1257.7	1247.4	1242.2	1234.4	1216.4	1203.5	1180.4
40°	1149.4	1152.0	1146.8	1141.7	1139.1	1131.4	1128.8	1115.9	1103.0	1087.5	1077.2
42.5°	1030.9	1030.9	1030.9	1025.7	1020.6	1012.8	1010.3	1002.5	987.0	976.7	961.3
45°	925.2	917.4	917.4	914.9	912.3	907.1	899.5	894.3	884.0	876.2	858.2
47.5°	822.1	824.7	822.1	819.6	811.8	809.2	806.6	796.3	786.0	778.3	765.4
50°	731.9	737.0	731.9	731.9	726.7	724.2	719.0	711.3	703.6	690.6	677.8
52.5°	657.2	657.2	654.6	652.1	644.3	639.1	636.6	634.0	621.0	610.7	600.4
55°	582.5	585.0	585.0	577.3	574.7	569.5	567.0	559.2	554.1	538.6	531.0
57.5°	518.0	515.4	518.0	512.9	507.7	502.6	499.9	494.8	487.1	476.8	466.5
60°	461.3	456.2	456.2	453.6	448.4	445.9	440.7	433.0	425.3	414.9	407.2
62.5°	404.6	402.0	399.4	396.9	391.7	389.1	386.6	378.8	371.1	363.4	355.7
65°	350.5	350.5	347.9	342.7	340.2	337.6	335.1	329.9	319.6	314.4	306.7
67.5°	301.5	298.9	298.9	293.7	288.6	286.1	286.1	280.9	273.1	265.5	260.3
70°	252.5	255.2	252.5	250.0	244.9	244.9	239.7	237.1	226.8	224.3	216.5
72.5°	208.7	208.7	206.2	206.2	201.0	198.4	198.4	193.2	188.1	182.9	177.8
75°	167.5	167.5	167.5	165.0	162.3	157.2	157.2	154.7	149.5	144.4	139.2
77.5°	131.4	128.9	128.9	126.3	123.8	121.1	121.1	118.6	113.5	110.8	105.7
80°	95.4	92.7	92.7	92.7	87.6	90.2	87.6	85.1	82.4	79.9	77.3
82.5°	61.8	64.5	64.5	61.8	59.3	59.3	59.3	56.7	56.7	54.1	51.5
85°	36.1	36.1	36.1	36.1	33.5	33.5	33.5	30.9	30.9	30.9	28.4
87.5°	15.5	15.5	15.5	15.5	15.5	15.5	12.9	12.9	12.9	12.9	12.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584488

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4
2.5°	1920.0	1914.9	1912.2	1909.7	1909.7	1907.1	1904.6	1899.4	1899.4	1894.2	1891.6
5°	1930.3	1922.6	1917.4	1912.2	1909.7	1904.6	1899.4	1891.6	1889.0	1881.3	1873.6
7.5°	1932.9	1920.0	1914.9	1904.6	1899.4	1894.2	1883.9	1876.2	1865.9	1858.1	1847.8
10°	1922.6	1912.2	1899.4	1886.5	1883.9	1876.2	1860.7	1850.4	1837.5	1827.2	1811.7
12.5°	1907.1	1891.6	1878.7	1863.2	1855.6	1847.8	1832.3	1816.9	1798.9	1780.8	1765.4
15°	1881.3	1863.2	1845.3	1827.2	1816.9	1809.2	1791.1	1773.0	1755.1	1731.8	1716.4
17.5°	1842.6	1822.0	1804.1	1780.8	1770.5	1762.7	1739.6	1719.0	1695.8	1672.5	1657.1
20°	1793.8	1767.9	1747.3	1721.5	1713.9	1700.9	1677.7	1654.6	1628.8	1603.0	1585.0
22.5°	1729.3	1703.6	1680.3	1654.6	1641.6	1628.8	1605.6	1577.2	1551.4	1530.8	1512.8
25°	1654.6	1631.3	1603.0	1579.8	1564.3	1548.9	1523.1	1499.9	1476.8	1445.7	1427.8
27.5°	1572.0	1543.7	1523.1	1492.2	1476.8	1466.4	1438.1	1407.2	1386.6	1358.2	1337.6
30°	1479.3	1453.5	1430.3	1399.4	1383.9	1373.6	1347.9	1319.5	1298.9	1270.6	1249.9
32.5°	1381.4	1353.0	1324.6	1304.0	1286.1	1275.8	1247.4	1229.3	1203.5	1180.4	1157.1
35°	1275.8	1247.4	1226.8	1198.4	1188.1	1177.8	1154.5	1131.4	1108.1	1087.5	1069.6
37.5°	1162.3	1141.7	1118.5	1097.8	1090.2	1079.9	1051.5	1030.9	1012.8	992.2	976.7
40°	1051.5	1033.4	1017.9	997.3	984.5	976.7	956.1	938.0	917.4	904.6	889.2
42.5°	951.0	930.4	914.9	899.5	886.5	878.9	860.8	847.9	832.4	819.6	801.5
45°	845.3	835.0	816.9	804.1	796.3	786.0	773.2	757.7	744.8	734.5	721.6
47.5°	752.6	742.3	729.3	713.9	708.7	700.9	688.1	677.8	667.5	657.2	644.3
50°	667.5	654.6	644.3	634.0	628.8	621.0	608.2	603.1	595.3	585.0	577.3
52.5°	590.1	579.8	569.5	556.7	554.1	548.9	541.3	531.0	523.2	518.0	512.9
55°	520.5	510.2	502.6	492.3	489.6	484.5	474.2	469.0	463.9	458.7	453.6
57.5°	458.7	448.4	438.1	433.0	427.8	422.7	420.0	412.4	407.2	404.6	399.4
60°	402.0	391.7	384.0	376.3	373.7	371.1	366.0	360.8	355.7	350.5	347.9
62.5°	347.9	337.6	332.4	327.3	322.1	322.1	317.0	311.8	306.7	304.1	298.9
65°	298.9	293.7	286.1	278.3	275.8	275.8	268.0	265.5	262.8	257.7	252.5
67.5°	252.5	247.4	239.7	237.1	234.6	231.9	229.4	224.3	219.1	216.5	211.3
70°	211.3	206.2	201.0	198.4	195.9	193.2	188.1	185.6	180.4	177.8	175.3
72.5°	170.1	167.5	162.3	159.8	157.2	154.7	152.0	149.5	144.4	141.7	139.2
75°	136.6	134.1	128.9	126.3	123.8	123.8	121.1	116.0	113.5	113.5	110.8
77.5°	103.0	100.5	97.9	95.4	92.7	92.7	90.2	87.6	85.1	85.1	82.4
80°	74.8	72.1	69.6	69.6	69.6	67.0	64.5	64.5	61.8	61.8	59.3
82.5°	49.0	49.0	46.4	46.4	46.4	43.8	43.8	41.2	41.2	41.2	41.2
85°	28.4	28.4	28.4	25.8	25.8	25.8	25.8	25.8	25.8	23.2	25.8
87.5°	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584488

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4
2.5°	1889.0	1886.5	1881.3	1881.3	1876.2	1876.2	1873.6	1871.0	1868.4	1865.9	1863.2
5°	1871.0	1860.7	1855.6	1852.9	1847.8	1845.3	1837.5	1832.3	1829.8	1824.7	1819.5
7.5°	1837.5	1827.2	1816.9	1814.4	1811.7	1801.4	1793.8	1786.0	1780.8	1775.7	1770.5
10°	1798.9	1788.5	1775.7	1770.5	1765.4	1752.4	1742.1	1734.5	1724.2	1713.9	1711.2
12.5°	1752.4	1737.0	1721.5	1716.4	1708.7	1695.8	1685.5	1672.5	1664.9	1651.9	1649.4
15°	1698.4	1680.3	1667.4	1654.6	1649.4	1636.5	1618.5	1608.2	1592.7	1587.6	1574.7
17.5°	1634.0	1615.9	1597.9	1592.7	1585.0	1566.9	1548.9	1536.0	1520.5	1512.8	1505.0
20°	1566.9	1543.7	1525.7	1520.5	1510.2	1494.7	1476.8	1463.8	1450.9	1435.4	1427.8
22.5°	1489.6	1463.8	1448.4	1435.4	1432.9	1414.8	1394.2	1383.9	1373.6	1360.7	1350.4
25°	1404.5	1381.4	1363.3	1353.0	1347.9	1332.4	1317.0	1304.0	1288.6	1280.9	1268.0
27.5°	1317.0	1301.5	1278.3	1268.0	1260.2	1247.4	1229.3	1221.6	1206.1	1195.8	1188.1
30°	1231.9	1208.7	1195.8	1182.9	1175.2	1162.3	1146.8	1139.1	1126.2	1115.9	1108.1
32.5°	1139.1	1123.6	1105.6	1100.5	1090.2	1077.2	1066.9	1054.1	1043.7	1033.4	1030.9
35°	1054.1	1033.4	1015.4	1010.3	1002.5	989.7	984.5	976.7	963.9	961.3	951.0
37.5°	961.3	951.0	930.4	922.6	920.1	909.8	899.5	894.3	886.5	878.9	876.2
40°	873.7	860.8	850.5	842.7	837.5	829.9	819.6	816.9	811.8	801.5	798.9
42.5°	791.2	778.3	768.0	765.4	757.7	749.9	744.8	737.0	734.5	731.9	726.7
45°	711.3	703.6	693.3	690.6	688.1	677.8	672.7	667.5	662.4	659.7	654.6
47.5°	639.1	631.3	623.7	621.0	615.9	613.4	605.6	603.1	595.3	592.8	590.1
50°	569.5	564.4	559.2	556.7	551.6	548.9	543.8	538.6	533.5	531.0	528.3
52.5°	507.7	502.6	497.4	494.8	492.3	487.1	482.0	476.8	474.2	471.7	469.0
55°	448.4	443.3	440.7	438.1	435.6	433.0	425.3	422.7	420.0	417.5	412.4
57.5°	394.3	389.1	384.0	384.0	381.4	378.8	373.7	368.5	368.5	363.4	358.2
60°	345.4	340.2	335.1	332.4	329.9	324.8	322.1	319.6	317.0	314.4	309.2
62.5°	293.7	291.2	286.1	286.1	280.9	278.3	275.8	273.1	270.6	265.5	262.8
65°	250.0	247.4	242.2	239.7	239.7	237.1	231.9	229.4	226.8	226.8	224.3
67.5°	208.7	206.2	201.0	198.4	198.4	195.9	193.2	193.2	190.7	188.1	190.7
70°	172.6	167.5	167.5	165.0	165.0	162.3	159.8	159.8	159.8	162.3	162.3
72.5°	136.6	134.1	131.4	131.4	131.4	131.4	128.9	128.9	131.4	134.1	134.1
75°	108.3	105.7	105.7	105.7	103.0	103.0	105.7	105.7	108.3	108.3	108.3
77.5°	79.9	79.9	79.9	79.9	79.9	79.9	82.4	82.4	85.1	85.1	85.1
80°	59.3	59.3	59.3	59.3	59.3	61.8	61.8	61.8	61.8	61.8	64.5
82.5°	41.2	41.2	41.2	41.2	41.2	41.2	41.2	43.8	43.8	43.8	43.8
85°	23.2	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584488

CATALOG NUMBER: HCC8W35D010SL-HM82555935-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4	1899.4
2.5°	1860.7	1860.7	1860.7	1863.2	1858.1	1858.1	1858.1	1858.1
5°	1816.9	1814.4	1811.7	1814.4	1809.2	1809.2	1806.6	1806.6
7.5°	1762.7	1760.2	1757.6	1757.6	1752.4	1752.4	1749.9	1747.3
10°	1703.6	1698.4	1700.9	1695.8	1693.3	1690.6	1688.1	1685.5
12.5°	1639.1	1634.0	1631.3	1626.2	1621.0	1618.5	1621.0	1615.9
15°	1569.5	1561.7	1559.2	1554.0	1548.9	1546.3	1546.3	1543.7
17.5°	1492.2	1487.1	1484.4	1479.3	1476.8	1471.5	1469.0	1466.4
20°	1420.0	1407.2	1409.7	1404.5	1402.0	1391.7	1391.7	1394.2
22.5°	1340.1	1332.4	1327.3	1322.1	1319.5	1314.3	1314.3	1311.8
25°	1260.2	1252.5	1249.9	1244.7	1242.2	1237.1	1234.4	1234.4
27.5°	1182.9	1172.6	1172.6	1167.5	1162.3	1159.8	1157.1	1154.5
30°	1100.5	1092.7	1090.2	1090.2	1087.5	1087.5	1079.9	1082.4
32.5°	1023.1	1017.9	1015.4	1010.3	1010.3	1007.6	1007.6	1000.0
35°	945.8	938.0	940.7	935.5	932.9	930.4	932.9	930.4
37.5°	871.1	865.9	865.9	860.8	860.8	858.2	855.6	860.8
40°	796.3	793.8	791.2	788.6	791.2	788.6	783.5	786.0
42.5°	721.6	721.6	719.0	719.0	716.4	716.4	716.4	716.4
45°	654.6	652.1	652.1	649.4	649.4	649.4	649.4	646.9
47.5°	587.6	585.0	585.0	585.0	582.5	582.5	579.8	582.5
50°	523.2	523.2	520.5	520.5	523.2	520.5	518.0	518.0
52.5°	463.9	463.9	461.3	461.3	458.7	456.2	458.7	458.7
55°	409.7	407.2	404.6	404.6	402.0	399.4	399.4	402.0
57.5°	358.2	355.7	353.1	353.1	347.9	345.4	345.4	345.4
60°	309.2	304.1	304.1	301.5	301.5	298.9	298.9	298.9
62.5°	262.8	260.3	260.3	260.3	260.3	257.7	257.7	257.7
65°	224.3	224.3	224.3	226.8	226.8	229.4	229.4	229.4
67.5°	193.2	195.9	195.9	195.9	198.4	198.4	198.4	195.9
70°	165.0	165.0	165.0	167.5	167.5	167.5	167.5	167.5
72.5°	136.6	136.6	136.6	136.6	136.6	136.6	136.6	136.6
75°	108.3	110.8	110.8	110.8	108.3	110.8	110.8	108.3
77.5°	85.1	85.1	85.1	85.1	85.1	85.1	85.1	85.1
80°	64.5	64.5	64.5	64.5	64.5	64.5	64.5	64.5
82.5°	43.8	43.8	43.8	43.8	43.8	43.8	43.8	43.8
85°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)