

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584485

Luminaire Tested: **HCC8S35D010MW-HM82555935-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MW-HM82555935-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3959.1 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584485
CATALOG NUMBER: HCC8S35D010MW-HM82555935-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584485
 CATALOG NUMBER: HCC8S35D010MW-HM82555935-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																			
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52																			
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48																			
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44																			
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40																			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79148
5°	79054
10°	78271
15°	77336
20°	76617
25°	75758
30°	71480
35°	58209
40°	32159
45°	21469
50°	19040
55°	17870
60°	17645
65°	17490
70°	15805
75°	14130
80°	12360
85°	10933



TEST NUMBER: P584485
 CATALOG NUMBER: HCC8S35D010MW-HM82555935-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.0	6.1
10°-20°	684.0	17.3
20°-30°	1016.3	25.7
30°-40°	915.3	23.1
40°-50°	405.8	10.2
50°-60°	300.5	7.6
60°-70°	233.7	5.9
70°-80°	126.7	3.2
80°-90°	34.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1942.4	49.1
0°-40°	2857.7	72.2
0°-60°	3563.9	90.0
0°-90°	3959.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3959.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2567	
5°	2554	242
15°	2422	684
25°	2227	1016
35°	1546	915
45°	492	406
55°	332	300
65°	240	234
75°	119	127
85°	31	35
90°	0	



TEST NUMBER: P584485
CATALOG NUMBER: HCC8S35D010MW-HM82555935-81WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2566.7
2.5°	2561.6
5°	2553.9
7.5°	2533.3
10°	2499.7
12.5°	2461.1
15°	2422.5
17.5°	2383.8
20°	2334.8
22.5°	2285.9
25°	2226.6
27.5°	2136.4
30°	2007.5
32.5°	1821.9
35°	1546.3
37.5°	1154.5
40°	798.9
42.5°	590.1
45°	492.3
47.5°	435.5
50°	396.9
52.5°	360.8
55°	332.4
57.5°	309.2
60°	286.1
62.5°	265.5
65°	239.7
67.5°	208.7
70°	175.3
72.5°	146.9
75°	118.6
77.5°	92.7
80°	69.6
82.5°	49.0
85°	30.9
87.5°	12.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)