

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584336

Luminaire Tested: **HCC8W30D010BZ-HM82555930-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010BZ-HM82555930-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3020.7 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584336
CATALOG NUMBER: HCC8W30D010BZ-HM82555930-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584336

CATALOG NUMBER: HCC8W30D010BZ-HM82555930-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	46313	46313	46313
5°	48007	46159	44574
10°	49367	45759	42750
15°	50466	44949	40866
20°	50545	43195	39204
25°	49577	40795	37818
30°	47019	37829	36159
35°	42722	34452	34531
40°	37356	30915	32545
45°	32375	27539	30326
50°	28347	24457	27637
55°	25230	21677	24999
60°	22763	19476	21968
65°	20547	17125	19146
70°	18456	14425	14236
75°	16263	11438	10687
80°	13638	9483	10211
85°	10543	8279	9057



TEST NUMBER: P584336
 CATALOG NUMBER: HCC8W30D010BZ-HM82555930-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.7	4.7
10°-20°	399.1	13.2
20°-30°	570.3	18.9
30°-40°	606.0	20.1
40°-50°	521.8	17.3
50°-60°	390.1	12.9
60°-70°	248.8	8.2
70°-80°	113.2	3.7
80°-90°	29.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1111.1	36.8
0°-40°	1717.1	56.8
0°-60°	2628.9	87.0
0°-90°	3020.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3020.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1502	1502	1502	1502	1502	
5°	1551	1530	1491	1453	1440	149
15°	1581	1528	1408	1312	1280	445
25°	1457	1365	1199	1126	1112	667
35°	1135	1056	915	892	917	707
45°	742	702	632	649	695	577
55°	469	431	403	437	465	422
65°	282	250	235	245	262	281
75°	136	117	96	88	90	145
85°	30	26	23	26	26	36
90°	0	0	0	0	0	



TEST NUMBER: P584336

CATALOG NUMBER: HCC8W30D010BZ-HM82555930-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9
2.5°	1529.6	1525.4	1527.5	1525.4	1527.5	1527.5	1523.2	1523.2	1523.2	1523.2	1516.8
5°	1550.9	1548.8	1548.8	1546.7	1544.5	1546.7	1544.5	1542.5	1538.2	1536.1	1529.6
7.5°	1563.8	1563.8	1563.8	1563.8	1561.6	1559.5	1557.4	1553.1	1548.8	1544.5	1540.3
10°	1576.6	1578.8	1576.6	1574.5	1572.3	1568.1	1565.9	1561.6	1555.2	1548.8	1544.5
12.5°	1582.9	1582.9	1580.8	1580.8	1576.6	1574.5	1568.1	1561.6	1555.2	1548.8	1538.2
15°	1580.8	1580.8	1578.8	1576.6	1570.2	1568.1	1563.8	1557.4	1546.7	1538.2	1527.5
17.5°	1568.1	1565.9	1561.6	1561.6	1553.1	1550.9	1546.7	1538.2	1527.5	1514.7	1501.9
20°	1540.3	1540.3	1538.2	1536.1	1527.5	1521.1	1516.8	1506.2	1497.7	1482.7	1469.8
22.5°	1501.9	1506.2	1501.9	1497.7	1487.0	1484.8	1478.4	1465.7	1452.8	1435.7	1420.9
25°	1457.1	1455.0	1452.8	1448.6	1440.0	1435.7	1427.3	1414.4	1401.6	1382.5	1365.3
27.5°	1399.5	1391.0	1391.0	1382.5	1376.0	1369.6	1365.3	1352.6	1335.5	1320.5	1299.2
30°	1320.5	1322.6	1312.1	1309.9	1299.2	1294.9	1286.4	1273.7	1258.7	1241.7	1224.6
32.5°	1235.3	1228.8	1228.8	1220.3	1211.7	1205.4	1203.3	1188.3	1175.4	1158.4	1141.3
35°	1134.9	1134.9	1128.6	1126.5	1117.9	1113.6	1107.2	1098.6	1083.8	1068.8	1056.1
37.5°	1036.8	1032.5	1030.4	1026.1	1019.8	1013.4	1013.4	998.4	996.3	979.3	962.1
40°	928.0	932.3	928.0	921.6	919.5	915.2	913.0	904.6	898.2	883.2	872.6
42.5°	836.3	832.1	832.1	829.9	821.4	821.4	817.1	812.8	802.1	797.9	785.1
45°	742.4	746.7	740.3	742.4	733.9	733.9	733.9	725.3	716.8	710.4	701.9
47.5°	661.3	663.5	663.5	657.0	654.9	654.9	650.7	646.5	640.0	631.5	625.1
50°	590.9	593.1	588.8	586.7	582.4	580.2	580.2	571.8	567.5	558.9	554.7
52.5°	527.0	527.0	524.8	524.8	518.4	518.4	514.1	507.7	503.4	499.3	488.6
55°	469.3	469.3	467.2	465.0	465.0	458.7	456.6	450.2	445.9	437.3	430.9
57.5°	413.9	416.0	413.9	411.8	409.6	407.5	403.2	396.8	392.5	386.2	381.9
60°	369.1	369.1	366.9	364.8	360.5	358.4	356.2	352.1	345.6	341.4	334.9
62.5°	326.4	324.2	322.1	320.0	315.8	315.8	311.5	307.2	300.8	296.5	292.3
65°	281.6	281.6	279.4	279.4	277.4	273.1	271.0	268.8	260.3	258.1	249.6
67.5°	241.1	243.2	239.0	239.0	234.7	234.7	232.6	226.1	224.0	219.7	215.4
70°	204.7	204.7	204.7	202.7	198.4	196.3	194.2	189.9	187.7	183.5	179.2
72.5°	168.5	168.5	166.5	166.5	164.3	162.2	160.0	155.8	155.8	151.5	147.2
75°	136.5	136.5	134.4	132.2	130.2	130.2	128.1	125.9	121.6	119.5	117.4
77.5°	104.5	104.5	104.5	102.4	100.2	100.2	100.2	96.0	91.8	91.8	89.7
80°	76.8	76.8	74.7	74.7	72.5	72.5	72.5	70.4	68.2	66.1	64.0
82.5°	51.2	51.2	51.2	51.2	49.1	49.1	49.1	47.0	44.8	44.8	44.8
85°	29.8	29.8	29.8	29.8	27.7	27.7	27.7	27.7	27.7	25.6	25.6
87.5°	12.8	10.7	12.8	10.7	12.8	10.7	12.8	10.7	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584336

CATALOG NUMBER: HCC8W30D010BZ-HM82555930-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9
2.5°	1518.9	1516.8	1514.7	1512.5	1512.5	1510.4	1506.2	1504.1	1501.9	1499.8	1499.8
5°	1527.5	1525.4	1521.1	1516.8	1514.7	1510.4	1506.2	1501.9	1497.7	1491.2	1489.1
7.5°	1533.9	1527.5	1523.2	1514.7	1512.5	1508.2	1501.9	1495.5	1487.0	1478.4	1472.0
10°	1533.9	1525.4	1518.9	1508.2	1504.1	1499.8	1491.2	1480.5	1469.8	1461.4	1450.7
12.5°	1529.6	1518.9	1508.2	1497.7	1491.2	1484.8	1472.0	1461.4	1448.6	1435.7	1427.3
15°	1514.7	1501.9	1489.1	1476.3	1469.8	1461.4	1448.6	1433.6	1420.9	1408.0	1393.2
17.5°	1487.0	1474.1	1459.3	1444.3	1435.7	1429.4	1410.2	1399.5	1380.3	1367.5	1354.7
20°	1450.7	1435.7	1416.6	1401.6	1391.0	1384.6	1369.6	1350.5	1335.5	1316.3	1303.5
22.5°	1403.7	1384.6	1365.3	1350.5	1339.8	1331.2	1312.1	1292.8	1280.1	1263.0	1248.0
25°	1348.3	1329.1	1309.9	1288.5	1277.9	1269.4	1252.3	1235.3	1218.1	1199.0	1186.1
27.5°	1282.2	1260.8	1243.8	1224.6	1213.9	1201.1	1181.9	1164.9	1147.7	1134.9	1117.9
30°	1209.6	1186.1	1169.1	1149.9	1139.2	1128.6	1109.3	1092.3	1077.4	1062.4	1053.9
32.5°	1122.2	1105.1	1088.1	1068.8	1060.2	1053.9	1034.7	1017.7	1000.5	987.7	981.4
35°	1038.9	1019.8	1004.8	987.7	977.1	970.7	953.6	938.7	930.2	915.2	906.7
37.5°	951.4	936.6	919.5	902.5	896.0	889.6	876.8	861.9	849.1	838.4	834.2
40°	859.8	846.9	832.1	821.4	814.9	808.5	797.9	787.2	778.7	768.0	763.7
42.5°	772.3	763.7	751.0	738.1	731.7	729.6	716.8	708.3	704.0	699.7	695.4
45°	693.3	680.6	672.0	663.5	657.0	652.8	646.5	640.0	635.8	631.5	627.2
47.5°	616.5	605.9	597.4	590.9	584.5	582.4	578.1	571.8	567.5	567.5	567.5
50°	546.1	537.7	529.1	524.8	522.7	518.4	514.1	512.0	509.8	509.8	509.8
52.5°	484.3	475.7	469.3	465.0	465.0	460.9	456.6	454.4	454.4	454.4	454.4
55°	426.7	420.3	416.0	411.8	407.5	405.3	405.3	405.3	403.2	403.2	405.3
57.5°	375.5	371.2	364.8	360.5	358.4	358.4	356.2	354.1	356.2	358.4	360.5
60°	328.5	324.2	322.1	315.8	315.8	315.8	313.7	313.7	313.7	315.8	317.8
62.5°	285.8	283.7	279.4	277.4	275.3	275.3	273.1	273.1	273.1	273.1	275.3
65°	247.4	243.2	239.0	239.0	239.0	236.8	236.8	232.6	234.7	234.7	232.6
67.5°	211.2	206.9	204.7	202.7	200.6	200.6	198.4	196.3	194.2	194.2	194.2
70°	177.0	172.8	172.8	168.5	168.5	166.5	164.3	164.3	162.2	160.0	157.9
72.5°	142.9	140.8	138.6	136.5	136.5	136.5	134.4	132.2	130.2	128.1	123.8
75°	113.1	113.1	108.8	106.7	106.7	104.5	102.4	100.2	98.1	96.0	93.8
77.5°	87.5	85.4	81.1	78.9	78.9	78.9	76.8	74.7	72.5	70.4	68.2
80°	64.0	61.8	59.7	57.5	57.5	57.5	55.5	55.5	53.4	53.4	53.4
82.5°	42.7	42.7	40.5	40.5	40.5	40.5	38.4	38.4	38.4	38.4	38.4
85°	25.6	25.6	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4
87.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584336

CATALOG NUMBER: HCC8W30D010BZ-HM82555930-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9
2.5°	1495.5	1495.5	1491.2	1489.1	1487.0	1489.1	1484.8	1482.7	1480.5	1480.5	1478.4
5°	1482.7	1480.5	1472.0	1469.8	1467.8	1465.7	1461.4	1457.1	1452.8	1450.7	1448.6
7.5°	1465.7	1459.3	1450.7	1448.6	1446.4	1440.0	1433.6	1429.4	1423.0	1420.9	1416.6
10°	1442.1	1433.6	1427.3	1420.9	1416.6	1410.2	1403.7	1397.3	1388.9	1386.7	1380.3
12.5°	1414.4	1403.7	1391.0	1388.9	1382.5	1373.9	1365.3	1358.9	1352.6	1348.3	1341.9
15°	1380.3	1369.6	1356.9	1350.5	1344.0	1337.6	1326.9	1318.5	1312.1	1305.6	1299.2
17.5°	1339.8	1326.9	1316.3	1309.9	1305.6	1294.9	1286.4	1275.8	1269.4	1263.0	1256.5
20°	1290.7	1280.1	1265.1	1258.7	1256.5	1248.0	1237.4	1233.1	1224.6	1218.1	1213.9
22.5°	1235.3	1224.6	1211.7	1207.5	1199.0	1194.7	1184.0	1179.7	1175.4	1169.1	1167.0
25°	1173.3	1162.7	1152.0	1149.9	1143.5	1139.2	1132.9	1126.5	1126.5	1120.0	1120.0
27.5°	1109.3	1098.6	1090.2	1085.9	1083.8	1079.5	1073.1	1070.9	1068.8	1066.7	1066.7
30°	1041.1	1028.2	1024.0	1021.9	1019.8	1015.5	1013.4	1009.1	1011.2	1013.4	1011.2
32.5°	968.6	964.3	955.7	951.4	953.6	951.4	947.3	951.4	949.3	953.6	955.7
35°	898.2	893.9	889.6	889.6	885.3	885.3	885.3	887.5	891.8	893.9	898.2
37.5°	829.9	823.5	821.4	819.2	821.4	821.4	821.4	825.6	829.9	834.2	840.5
40°	757.4	753.1	753.1	753.1	753.1	759.5	757.4	761.7	765.8	772.3	778.7
42.5°	689.0	689.0	691.2	691.2	691.2	691.2	695.4	701.9	708.3	714.7	721.1
45°	625.1	625.1	625.1	629.3	629.3	631.5	640.0	644.3	648.6	654.9	661.3
47.5°	565.4	565.4	567.5	569.6	571.8	576.1	580.2	586.7	593.1	597.4	603.8
50°	509.8	512.0	516.3	520.5	520.5	522.7	529.1	533.4	537.7	544.0	546.1
52.5°	456.6	460.9	465.0	467.2	469.3	473.6	475.7	482.1	484.3	490.7	492.8
55°	407.5	409.6	416.0	418.2	418.2	422.5	426.7	430.9	437.3	437.3	441.6
57.5°	362.6	364.8	369.1	371.2	369.1	375.5	377.6	381.9	384.0	388.3	390.5
60°	317.8	322.1	324.2	324.2	326.4	328.5	332.8	332.8	337.1	341.4	341.4
62.5°	275.3	277.4	279.4	281.6	283.7	281.6	288.0	288.0	292.3	294.4	298.7
65°	234.7	236.8	236.8	239.0	239.0	241.1	241.1	243.2	245.3	249.6	251.7
67.5°	194.2	194.2	194.2	196.3	194.2	196.3	196.3	198.4	198.4	202.7	204.7
70°	157.9	155.8	153.6	153.6	153.6	153.6	151.5	153.6	153.6	155.8	155.8
72.5°	121.6	119.5	117.4	115.2	115.2	113.1	110.9	113.1	113.1	115.2	115.2
75°	91.8	87.5	87.5	87.5	85.4	85.4	85.4	87.5	87.5	87.5	89.7
77.5°	68.2	68.2	66.1	66.1	66.1	68.2	68.2	70.4	70.4	70.4	70.4
80°	51.2	53.4	53.4	53.4	53.4	55.5	55.5	55.5	55.5	57.5	57.5
82.5°	38.4	38.4	38.4	38.4	40.5	40.5	40.5	40.5	40.5	40.5	40.5
85°	23.4	25.6	25.6	23.4	25.6	25.6	25.6	25.6	25.6	25.6	25.6
87.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584336

CATALOG NUMBER: HCC8W30D010BZ-HM82555930-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9	1501.9
2.5°	1476.3	1476.3	1476.3	1476.3	1474.1	1474.1	1474.1	1472.0
5°	1444.3	1444.3	1444.3	1440.0	1442.1	1442.1	1437.9	1440.0
7.5°	1412.3	1410.2	1408.0	1408.0	1405.9	1403.7	1401.6	1403.7
10°	1376.0	1369.6	1369.6	1367.5	1367.5	1363.2	1363.2	1365.3
12.5°	1335.5	1331.2	1331.2	1329.1	1326.9	1324.8	1322.6	1322.6
15°	1294.9	1290.7	1288.5	1286.4	1284.2	1280.1	1282.2	1280.1
17.5°	1254.4	1248.0	1248.0	1246.0	1243.8	1239.5	1239.5	1237.4
20°	1207.5	1205.4	1201.1	1203.3	1201.1	1196.8	1194.7	1194.7
22.5°	1160.6	1160.6	1158.4	1158.4	1156.3	1154.2	1152.0	1152.0
25°	1115.8	1113.6	1115.8	1115.8	1109.3	1109.3	1109.3	1111.5
27.5°	1064.5	1066.7	1064.5	1064.5	1064.5	1064.5	1066.7	1064.5
30°	1013.4	1013.4	1013.4	1015.5	1019.8	1017.7	1017.7	1015.5
32.5°	957.9	960.0	960.0	962.1	964.3	968.6	968.6	970.7
35°	902.5	906.7	908.9	906.7	913.0	913.0	917.3	917.3
37.5°	844.8	846.9	851.2	853.3	857.6	859.8	861.9	861.9
40°	783.0	791.5	793.7	795.8	802.1	802.1	804.2	808.5
42.5°	725.3	733.9	736.0	738.1	742.4	748.8	746.7	751.0
45°	669.9	676.3	678.4	680.6	687.0	689.0	689.0	695.4
47.5°	610.2	614.4	616.5	620.8	625.1	629.3	633.6	631.5
50°	550.4	556.8	561.1	563.2	569.6	571.8	573.9	576.1
52.5°	497.1	501.4	503.4	505.6	512.0	514.1	516.3	520.5
55°	445.9	448.0	452.3	450.2	456.6	458.7	460.9	465.0
57.5°	394.6	396.8	398.9	398.9	403.2	407.5	409.6	411.8
60°	345.6	349.9	352.1	352.1	352.1	356.2	356.2	356.2
62.5°	300.8	300.8	303.0	303.0	307.2	307.2	307.2	307.2
65°	253.9	256.0	258.1	258.1	262.4	260.3	264.6	262.4
67.5°	204.7	204.7	209.0	209.0	206.9	209.0	209.0	209.0
70°	155.8	155.8	157.9	157.9	157.9	157.9	157.9	157.9
72.5°	115.2	115.2	115.2	117.4	115.2	115.2	117.4	115.2
75°	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.7
77.5°	70.4	70.4	72.5	72.5	72.5	72.5	72.5	72.5
80°	57.5	57.5	57.5	57.5	59.7	57.5	57.5	57.5
82.5°	42.7	40.5	42.7	40.5	42.7	42.7	42.7	42.7
85°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6
87.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)