

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584352

Luminaire Tested: **HCC8S30D010MW-HM82555935-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S30D010MW-HM82555935-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2916.9 lumens  
Efficiency: N/A  
Efficacy: 104.2 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584352  
CATALOG NUMBER: HCC8S30D010MW-HM82555935-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584352

CATALOG NUMBER: HCC8S30D010MW-HM82555935-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	48737	48737	48737
5°	50449	48456	46533
10°	51571	47610	43915
15°	52304	46006	41010
20°	52147	43769	38072
25°	50856	40931	34950
30°	48183	37647	32071
35°	43837	34064	29144
40°	38499	30303	26330
45°	33575	26650	23475
50°	29215	23353	20676
55°	26053	20521	17989
60°	23670	17990	15338
65°	21284	15651	13922
70°	18951	13335	12568
75°	16608	11247	10735
80°	14082	9145	9518
85°	10650	6828	7571



TEST NUMBER: P584352  
 CATALOG NUMBER: HCC8S30D010MW-HM82555935-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.0	5.1
10°-20°	407.9	14.0
20°-30°	566.2	19.4
30°-40°	585.4	20.1
40°-50°	490.1	16.8
50°-60°	355.8	12.2
60°-70°	224.5	7.7
70°-80°	111.2	3.8
80°-90°	27.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1122.1	38.5
0°-40°	1707.5	58.5
0°-60°	2553.4	87.5
0°-90°	2916.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2916.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1580	1580	1580	1580	1580	
5°	1630	1610	1565	1523	1503	156
15°	1638	1576	1441	1325	1285	461
25°	1495	1398	1203	1072	1027	685
35°	1164	1079	905	802	774	725
45°	770	714	611	551	538	595
55°	485	442	382	350	335	437
65°	292	255	214	189	191	291
75°	139	116	94	90	90	150
85°	30	24	19	21	21	36
90°	0	0	0	0	0	



TEST NUMBER: P584352

CATALOG NUMBER: HCC8S30D010MW-HM82555935-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5
2.5°	1606.2	1606.2	1608.4	1606.2	1606.2	1606.2	1604.1	1604.1	1601.9	1601.9	1597.7
5°	1629.8	1625.5	1629.8	1625.5	1625.5	1625.5	1623.3	1619.1	1616.9	1612.6	1610.5
7.5°	1640.6	1638.4	1638.4	1636.3	1636.3	1634.0	1631.9	1629.8	1621.2	1619.1	1612.6
10°	1647.0	1644.9	1644.9	1642.7	1638.4	1638.4	1634.0	1631.9	1621.2	1616.9	1608.4
12.5°	1644.9	1644.9	1644.9	1642.7	1636.3	1634.0	1629.8	1623.3	1614.8	1606.2	1597.7
15°	1638.4	1638.4	1634.0	1631.9	1625.5	1621.2	1619.1	1608.4	1599.8	1589.1	1576.3
17.5°	1616.9	1616.9	1614.8	1610.5	1604.1	1599.8	1595.5	1584.8	1576.3	1559.0	1546.2
20°	1589.1	1587.0	1584.8	1578.4	1571.9	1569.7	1563.3	1548.3	1537.6	1524.8	1507.5
22.5°	1548.3	1546.2	1544.0	1539.8	1529.1	1524.8	1520.5	1509.7	1490.4	1477.6	1456.0
25°	1494.7	1494.7	1490.4	1484.0	1473.3	1469.0	1462.6	1451.8	1434.6	1415.4	1398.3
27.5°	1432.5	1430.4	1423.9	1419.7	1411.1	1404.7	1393.9	1381.0	1363.9	1348.9	1327.4
30°	1353.2	1353.2	1348.9	1342.5	1331.7	1327.4	1318.8	1303.9	1286.7	1267.4	1252.4
32.5°	1263.1	1263.1	1256.7	1252.4	1246.0	1235.3	1233.1	1215.9	1200.9	1185.9	1168.8
35°	1164.5	1166.6	1162.4	1153.7	1143.0	1143.0	1138.7	1123.7	1106.6	1091.5	1078.7
37.5°	1065.8	1059.4	1057.3	1053.0	1046.6	1037.9	1033.6	1027.2	1012.2	1001.5	982.2
40°	956.4	958.6	954.3	950.0	947.9	941.5	939.3	928.6	917.8	904.9	896.4
42.5°	857.7	857.7	857.7	853.5	849.2	842.8	840.6	834.2	821.4	812.8	799.8
45°	769.9	763.5	763.5	761.3	759.2	754.9	748.5	744.2	735.5	729.1	714.1
47.5°	684.2	686.3	684.2	681.9	675.5	673.3	671.2	662.6	654.1	647.6	636.9
50°	609.0	613.3	609.0	609.0	604.7	602.6	598.3	591.9	585.5	574.8	563.9
52.5°	546.8	546.8	544.7	542.5	536.1	531.8	529.7	527.6	516.9	508.3	499.6
55°	484.6	486.8	486.8	480.4	478.2	473.9	471.8	465.4	461.1	448.3	441.7
57.5°	431.0	428.9	431.0	426.7	422.5	418.2	416.0	411.8	405.3	396.8	388.2
60°	383.8	379.5	379.5	377.4	373.1	371.0	366.7	360.3	353.8	345.3	338.9
62.5°	336.7	334.6	332.4	330.3	325.9	323.8	321.6	315.2	308.8	302.4	295.9
65°	291.7	291.7	289.5	285.2	283.1	281.0	278.8	274.5	265.9	261.6	255.2
67.5°	250.9	248.7	248.7	244.5	240.2	238.0	238.0	233.8	227.3	220.9	216.6
70°	210.2	212.4	210.2	208.0	203.7	203.7	199.4	197.3	188.7	186.6	180.1
72.5°	173.7	173.7	171.6	171.6	167.3	165.2	165.2	160.9	156.6	152.3	147.9
75°	139.4	139.4	139.4	137.2	135.1	130.8	130.8	128.6	124.4	120.1	115.8
77.5°	109.4	107.2	107.2	105.1	103.0	100.8	100.8	98.7	94.4	92.3	87.9
80°	79.3	77.2	77.2	77.2	72.9	75.0	72.9	70.7	68.6	66.5	64.3
82.5°	51.5	53.6	53.6	51.5	49.3	49.3	49.3	47.2	47.2	45.1	42.9
85°	30.1	30.1	30.1	30.1	27.8	27.8	27.8	25.7	25.7	25.7	23.5
87.5°	12.8	12.8	12.8	12.8	12.8	12.8	10.7	10.7	10.7	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584352

CATALOG NUMBER: HCC8S30D010MW-HM82555935-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5
2.5°	1597.7	1593.4	1591.2	1589.1	1589.1	1587.0	1584.8	1580.5	1580.5	1576.3	1574.0
5°	1606.2	1599.8	1595.5	1591.2	1589.1	1584.8	1580.5	1574.0	1571.9	1565.4	1559.0
7.5°	1608.4	1597.7	1593.4	1584.8	1580.5	1576.3	1567.6	1561.2	1552.6	1546.2	1537.6
10°	1599.8	1591.2	1580.5	1569.7	1567.6	1561.2	1548.3	1539.8	1529.1	1520.5	1507.5
12.5°	1587.0	1574.0	1563.3	1550.5	1544.0	1537.6	1524.8	1511.8	1496.8	1481.9	1469.0
15°	1565.4	1550.5	1535.5	1520.5	1511.8	1505.4	1490.4	1475.4	1460.4	1441.1	1428.2
17.5°	1533.3	1516.2	1501.1	1481.9	1473.3	1466.9	1447.5	1430.4	1411.1	1391.7	1378.9
20°	1492.6	1471.1	1453.9	1432.5	1426.1	1415.4	1396.0	1376.7	1355.3	1333.8	1318.8
22.5°	1438.9	1417.5	1398.3	1376.7	1366.0	1355.3	1336.0	1312.4	1291.0	1273.8	1258.8
25°	1376.7	1357.5	1333.8	1314.6	1301.7	1288.9	1267.4	1248.1	1228.8	1203.0	1188.0
27.5°	1308.1	1284.6	1267.4	1241.7	1228.8	1220.3	1196.6	1170.9	1153.7	1130.1	1113.0
30°	1231.0	1209.5	1190.2	1164.5	1151.5	1143.0	1121.6	1097.9	1080.8	1057.3	1040.0
32.5°	1149.4	1125.9	1102.3	1085.1	1070.1	1061.5	1037.9	1022.9	1001.5	982.2	962.9
35°	1061.5	1037.9	1020.8	997.2	988.7	980.0	960.7	941.5	922.2	904.9	890.0
37.5°	967.1	950.0	930.7	913.5	907.1	898.5	875.0	857.7	842.8	825.6	812.8
40°	875.0	859.9	847.0	829.9	819.2	812.8	795.6	780.6	763.5	752.8	739.8
42.5°	791.3	774.2	761.3	748.5	737.7	731.2	716.3	705.6	692.7	681.9	666.9
45°	703.4	694.9	679.8	669.1	662.6	654.1	643.4	630.5	619.7	611.1	600.4
47.5°	626.2	617.6	606.9	594.0	589.7	583.3	572.6	563.9	555.4	546.8	536.1
50°	555.4	544.7	536.1	527.6	523.3	516.9	506.2	501.8	495.3	486.8	480.4
52.5°	491.1	482.5	473.9	463.2	461.1	456.8	450.4	441.7	435.3	431.0	426.7
55°	433.2	424.6	418.2	409.6	407.5	403.2	394.6	390.3	385.9	381.7	377.4
57.5°	381.7	373.1	364.5	360.3	356.0	351.7	349.6	343.1	338.9	336.7	332.4
60°	334.6	325.9	319.5	313.1	310.9	308.8	304.5	300.2	295.9	291.7	289.5
62.5°	289.5	281.0	276.7	272.4	268.1	268.1	263.7	259.4	255.2	253.0	248.7
65°	248.7	244.5	238.0	231.6	229.5	229.5	223.1	220.9	218.8	214.5	210.2
67.5°	210.2	205.8	199.4	197.3	195.1	193.0	190.8	186.6	182.3	180.1	175.9
70°	175.9	171.6	167.3	165.2	163.0	160.9	156.6	154.5	150.2	147.9	145.8
72.5°	141.5	139.4	135.1	132.9	130.8	128.6	126.5	124.4	120.1	117.9	115.8
75°	113.7	111.5	107.2	105.1	103.0	103.0	100.8	96.5	94.4	94.4	92.3
77.5°	85.7	83.6	81.4	79.3	77.2	77.2	75.0	72.9	70.7	70.7	68.6
80°	62.2	60.0	57.9	57.9	57.9	55.8	53.6	53.6	51.5	51.5	49.3
82.5°	40.8	40.8	38.6	38.6	38.6	36.5	36.5	34.4	34.4	34.4	34.4
85°	23.5	23.5	23.5	21.4	21.4	21.4	21.4	21.4	21.4	19.3	21.4
87.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584352

CATALOG NUMBER: HCC8S30D010MW-HM82555935-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5
2.5°	1571.9	1569.7	1565.4	1565.4	1561.2	1561.2	1559.0	1556.9	1554.7	1552.6	1550.5
5°	1556.9	1548.3	1544.0	1541.9	1537.6	1535.5	1529.1	1524.8	1522.6	1518.4	1514.0
7.5°	1529.1	1520.5	1511.8	1509.7	1507.5	1499.0	1492.6	1486.1	1481.9	1477.6	1473.3
10°	1496.8	1488.3	1477.6	1473.3	1469.0	1458.3	1449.6	1443.2	1434.6	1426.1	1423.9
12.5°	1458.3	1445.3	1432.5	1428.2	1421.8	1411.1	1402.5	1391.7	1385.3	1374.6	1372.5
15°	1413.2	1398.3	1387.4	1376.7	1372.5	1361.8	1346.8	1338.2	1325.3	1321.0	1310.3
17.5°	1359.6	1344.6	1329.5	1325.3	1318.8	1303.9	1288.9	1278.1	1265.2	1258.8	1252.4
20°	1303.9	1284.6	1269.5	1265.2	1256.7	1243.8	1228.8	1218.0	1207.3	1194.5	1188.0
22.5°	1239.5	1218.0	1205.2	1194.5	1192.3	1177.3	1160.2	1151.5	1143.0	1132.3	1123.7
25°	1168.8	1149.4	1134.4	1125.9	1121.6	1108.7	1095.8	1085.1	1072.2	1065.8	1055.1
27.5°	1095.8	1082.9	1063.7	1055.1	1048.7	1037.9	1022.9	1016.5	1003.6	995.1	988.7
30°	1025.0	1005.8	995.1	984.4	977.8	967.1	954.3	947.9	937.2	928.6	922.2
32.5°	947.9	935.0	919.9	915.6	907.1	896.4	887.8	877.1	868.6	859.9	857.7
35°	877.1	859.9	844.9	840.6	834.2	823.5	819.2	812.8	802.0	799.8	791.3
37.5°	799.8	791.3	774.2	767.7	765.6	757.0	748.5	744.2	737.7	731.2	729.1
40°	727.0	716.3	707.7	701.3	697.0	690.6	681.9	679.8	675.5	666.9	664.8
42.5°	658.3	647.6	639.1	636.9	630.5	624.0	619.7	613.3	611.1	609.0	604.7
45°	591.9	585.5	576.9	574.8	572.6	563.9	559.7	555.4	551.1	549.0	544.7
47.5°	531.8	525.4	519.0	516.9	512.6	510.4	503.9	501.8	495.3	493.2	491.1
50°	473.9	469.7	465.4	463.2	459.0	456.8	452.5	448.3	443.9	441.7	439.6
52.5°	422.5	418.2	413.9	411.8	409.6	405.3	401.0	396.8	394.6	392.5	390.3
55°	373.1	368.8	366.7	364.5	362.4	360.3	353.8	351.7	349.6	347.4	343.1
57.5°	328.2	323.8	319.5	319.5	317.3	315.2	310.9	306.6	306.6	302.4	298.1
60°	287.4	283.1	278.8	276.7	274.5	270.3	268.1	265.9	263.7	261.6	257.3
62.5°	244.5	242.3	238.0	238.0	233.8	231.6	229.5	227.3	225.2	220.9	218.8
65°	208.0	205.8	201.5	199.4	199.4	197.3	193.0	190.8	188.7	188.7	186.6
67.5°	173.7	171.6	167.3	165.2	165.2	163.0	160.9	160.9	158.7	156.6	158.7
70°	143.6	139.4	139.4	137.2	137.2	135.1	132.9	132.9	132.9	135.1	135.1
72.5°	113.7	111.5	109.4	109.4	109.4	109.4	107.2	107.2	109.4	111.5	111.5
75°	90.1	87.9	87.9	87.9	85.7	85.7	87.9	87.9	90.1	90.1	90.1
77.5°	66.5	66.5	66.5	66.5	66.5	66.5	68.6	68.6	70.7	70.7	70.7
80°	49.3	49.3	49.3	49.3	49.3	51.5	51.5	51.5	51.5	51.5	53.6
82.5°	34.4	34.4	34.4	34.4	34.4	34.4	34.4	36.5	36.5	36.5	36.5
85°	19.3	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584352

CATALOG NUMBER: HCC8S30D010MW-HM82555935-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5
2.5°	1548.3	1548.3	1548.3	1550.5	1546.2	1546.2	1546.2	1546.2
5°	1511.8	1509.7	1507.5	1509.7	1505.4	1505.4	1503.3	1503.3
7.5°	1466.9	1464.7	1462.6	1462.6	1458.3	1458.3	1456.0	1453.9
10°	1417.5	1413.2	1415.4	1411.1	1409.0	1406.8	1404.7	1402.5
12.5°	1363.9	1359.6	1357.5	1353.2	1348.9	1346.8	1348.9	1344.6
15°	1306.0	1299.6	1297.4	1293.2	1288.9	1286.7	1286.7	1284.6
17.5°	1241.7	1237.4	1235.3	1231.0	1228.8	1224.6	1222.4	1220.3
20°	1181.6	1170.9	1173.1	1168.8	1166.6	1158.0	1158.0	1160.2
22.5°	1115.2	1108.7	1104.5	1100.2	1097.9	1093.6	1093.6	1091.5
25°	1048.7	1042.3	1040.0	1035.7	1033.6	1029.3	1027.2	1027.2
27.5°	984.4	975.7	975.7	971.4	967.1	965.0	962.9	960.7
30°	915.6	909.2	907.1	907.1	904.9	904.9	898.5	900.7
32.5°	851.3	847.0	844.9	840.6	840.6	838.5	838.5	832.1
35°	787.0	780.6	782.7	778.4	776.3	774.2	776.3	774.2
37.5°	724.8	720.5	720.5	716.3	716.3	714.1	712.0	716.3
40°	662.6	660.5	658.3	656.2	658.3	656.2	651.9	654.1
42.5°	600.4	600.4	598.3	598.3	596.2	596.2	596.2	596.2
45°	544.7	542.5	542.5	540.4	540.4	540.4	540.4	538.3
47.5°	488.9	486.8	486.8	486.8	484.6	484.6	482.5	484.6
50°	435.3	435.3	433.2	433.2	435.3	433.2	431.0	431.0
52.5°	385.9	385.9	383.8	383.8	381.7	379.5	381.7	381.7
55°	341.0	338.9	336.7	336.7	334.6	332.4	332.4	334.6
57.5°	298.1	295.9	293.8	293.8	289.5	287.4	287.4	287.4
60°	257.3	253.0	253.0	250.9	250.9	248.7	248.7	248.7
62.5°	218.8	216.6	216.6	216.6	216.6	214.5	214.5	214.5
65°	186.6	186.6	186.6	188.7	188.7	190.8	190.8	190.8
67.5°	160.9	163.0	163.0	163.0	165.2	165.2	165.2	163.0
70°	137.2	137.2	137.2	139.4	139.4	139.4	139.4	139.4
72.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.7	113.7
75°	90.1	92.3	92.3	92.3	90.1	92.3	92.3	90.1
77.5°	70.7	70.7	70.7	70.7	70.7	70.7	70.7	70.7
80°	53.6	53.6	53.6	53.6	53.6	53.6	53.6	53.6
82.5°	36.5	36.5	36.5	36.5	36.5	36.5	36.5	36.5
85°	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4
87.5°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)