

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593707

Luminaire Tested: **HCC8S35D010MB-HM82555950-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593707  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S35D010MB-HM82555950-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4532.8 lumens  
Efficiency: N/A  
Efficacy: 134.5 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593707  
CATALOG NUMBER: HCC8S35D010MB-HM82555950-81WDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593707

CATALOG NUMBER: HCC8S35D010MB-HM82555950-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68				68
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62				62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57				57
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52				52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41				41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	103773
5°	101437
10°	98326
15°	96334
20°	95470
25°	94043
30°	89084
35°	74016
40°	43591
45°	28830
50°	22691
55°	16698
60°	11601
65°	7070
70°	3074
75°	1358
80°	1030
85°	0



TEST NUMBER: P593707  
 CATALOG NUMBER: HCC8S35D010MB-HM82555950-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	308.6	6.8
10°-20°	853.1	18.8
20°-30°	1264.0	27.9
30°-40°	1168.0	25.8
40°-50°	538.5	11.9
50°-60°	283.3	6.2
60°-70°	100.1	2.2
70°-80°	15.7	0.3
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2425.7	53.5
0°-40°	3593.6	79.3
0°-60°	4415.4	97.4
0°-90°	4532.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4532.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3365	
5°	3277	309
15°	3018	853
25°	2764	1264
35°	1966	1168
45°	661	539
55°	311	283
65°	97	100
75°	11	16
85°	0	2
90°	0	



TEST NUMBER: P593707

CATALOG NUMBER: HCC8S35D010MB-HM82555950-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3365.3
2.5°	3336.8
5°	3277.0
7.5°	3211.5
10°	3140.2
12.5°	3071.8
15°	3017.6
17.5°	2969.2
20°	2909.3
22.5°	2843.8
25°	2764.0
27.5°	2655.7
30°	2501.9
32.5°	2282.4
35°	1966.2
37.5°	1510.2
40°	1082.9
42.5°	812.1
45°	661.1
47.5°	561.4
50°	473.0
52.5°	387.6
55°	310.6
57.5°	245.1
60°	188.1
62.5°	142.4
65°	96.9
67.5°	57.0
70°	34.1
72.5°	20.0
75°	11.4
77.5°	8.5
80°	5.8
82.5°	2.9
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)