

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584351

Luminaire Tested: **HCC8W30D010SL-HM82555935-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584351
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010SL-HM82555935-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2672.3 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584351
CATALOG NUMBER: HCC8W30D010SL-HM82555935-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P584351

CATALOG NUMBER: HCC8W30D010SL-HM82555935-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	44238	44238	44238
5°	46069	44144	42283
10°	47610	43577	40223
15°	48815	42584	38133
20°	48908	40816	36245
25°	48083	38233	34368
30°	45512	35279	32758
35°	41495	31727	30759
40°	36084	27972	28403
45°	30954	24221	26000
50°	26438	20883	23353
55°	23171	17989	20290
60°	20636	15338	17065
65°	18307	12521	13615
70°	16238	9286	7727
75°	13546	4861	2299
80°	10655	1527	373
85°	7571	743	0



TEST NUMBER: P584351
 CATALOG NUMBER: HCC8W30D010SL-HM82555935-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.2	5.1
10°-20°	378.9	14.2
20°-30°	536.3	20.1
30°-40°	561.1	21.0
40°-50°	468.0	17.5
50°-60°	331.8	12.4
60°-70°	191.1	7.2
70°-80°	61.5	2.3
80°-90°	8.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1050.4	39.3
0°-40°	1611.4	60.3
0°-60°	2411.2	90.2
0°-90°	2672.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2672.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1435	1435	1435	1435	1435	
5°	1488	1469	1426	1383	1366	143
15°	1529	1467	1334	1229	1194	430
25°	1413	1308	1124	1034	1010	645
35°	1102	1006	843	798	817	683
45°	710	652	555	562	596	550
55°	431	386	335	352	377	389
65°	251	210	172	172	187	251
75°	114	84	41	19	19	123
85°	21	11	2	0	0	27
90°	0	0	0	0	0	



TEST NUMBER: P584351

CATALOG NUMBER: HCC8W30D010SL-HM82555935-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6
2.5°	1464.7	1462.6	1460.4	1462.6	1460.4	1462.6	1460.4	1460.4	1458.3	1456.2	1456.2
5°	1488.3	1486.1	1486.1	1486.1	1484.0	1481.9	1481.9	1479.7	1475.4	1473.3	1469.0
7.5°	1503.3	1505.4	1505.4	1505.4	1501.1	1501.1	1496.8	1492.6	1488.3	1484.0	1477.6
10°	1520.5	1520.5	1518.4	1516.2	1511.9	1509.7	1507.5	1503.3	1496.8	1488.3	1481.9
12.5°	1526.9	1526.9	1524.8	1520.5	1518.4	1516.2	1514.1	1507.5	1499.0	1488.3	1479.7
15°	1529.1	1524.8	1522.6	1520.5	1516.2	1509.7	1509.7	1501.1	1490.4	1477.6	1466.9
17.5°	1511.9	1514.1	1509.7	1505.4	1499.0	1494.7	1488.3	1481.9	1469.0	1454.0	1443.2
20°	1490.4	1488.3	1486.1	1479.7	1471.1	1469.0	1462.6	1451.9	1441.1	1423.9	1409.0
22.5°	1456.2	1454.0	1449.6	1445.3	1436.8	1432.5	1426.1	1413.2	1398.3	1381.0	1363.9
25°	1413.2	1409.0	1402.5	1394.0	1387.4	1383.2	1374.6	1361.8	1344.6	1325.3	1308.1
27.5°	1344.6	1351.1	1346.8	1333.9	1327.4	1318.8	1316.7	1299.6	1284.6	1265.2	1246.0
30°	1278.2	1278.2	1271.6	1265.2	1254.5	1248.1	1239.5	1226.7	1211.6	1188.0	1173.1
32.5°	1194.5	1192.3	1183.8	1181.6	1173.1	1160.2	1158.1	1140.8	1125.9	1108.7	1089.4
35°	1102.3	1098.0	1089.4	1082.9	1078.7	1072.2	1065.8	1050.8	1035.7	1018.6	1005.8
37.5°	997.2	997.2	995.1	984.4	980.1	975.7	969.3	954.3	945.7	928.6	915.6
40°	896.4	894.2	887.8	885.7	881.4	875.0	870.7	862.1	849.2	836.3	823.5
42.5°	797.7	800.0	791.3	793.4	784.9	780.6	778.4	765.6	759.2	746.3	735.5
45°	709.8	707.7	703.4	701.3	697.0	692.7	688.4	682.0	671.2	658.3	651.9
47.5°	628.4	622.0	622.0	619.7	617.6	609.0	606.9	600.4	594.0	581.2	572.6
50°	551.1	551.1	551.1	549.0	542.5	540.4	536.1	529.7	523.3	514.7	501.8
52.5°	488.9	488.9	488.9	486.8	478.2	476.1	473.9	465.4	456.8	450.4	441.7
55°	431.0	433.2	431.0	426.7	420.3	420.3	413.9	409.6	401.0	394.6	386.1
57.5°	381.7	381.7	377.4	375.2	371.0	368.8	364.5	360.3	349.6	343.1	332.4
60°	334.6	332.4	332.4	328.2	323.8	319.5	317.3	310.9	306.6	295.9	287.4
62.5°	291.7	291.7	287.4	287.4	278.8	278.8	276.7	270.3	263.7	253.0	248.7
65°	250.9	250.9	248.7	246.6	240.2	238.0	235.9	229.5	223.1	216.6	210.2
67.5°	214.5	214.5	210.2	208.1	203.7	201.5	197.3	193.0	186.6	180.1	173.7
70°	180.1	178.0	175.9	173.7	169.4	167.3	163.0	158.7	152.3	147.9	141.5
72.5°	145.8	145.8	143.6	139.4	137.2	135.1	132.9	128.6	122.2	115.8	111.5
75°	113.7	113.7	113.7	109.4	105.1	103.0	103.0	98.7	94.4	87.9	83.6
77.5°	87.9	85.7	83.6	83.6	79.3	77.2	75.0	72.9	66.5	64.3	60.0
80°	60.0	62.2	60.0	57.9	55.8	53.6	53.6	49.3	47.2	42.9	38.6
82.5°	40.8	38.6	38.6	36.5	36.5	34.4	34.4	30.1	27.8	25.7	23.5
85°	21.4	21.4	19.3	19.3	19.3	17.1	17.1	15.0	15.0	12.8	10.7
87.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584351

CATALOG NUMBER: HCC8W30D010SL-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6
2.5°	1454.0	1449.6	1447.5	1447.5	1445.3	1443.2	1441.1	1438.9	1434.6	1434.6	1430.4
5°	1464.7	1460.4	1458.3	1451.9	1447.5	1447.5	1438.9	1436.8	1430.4	1426.1	1421.8
7.5°	1473.3	1464.7	1458.3	1451.9	1447.5	1443.2	1434.6	1426.1	1417.5	1409.0	1404.7
10°	1473.3	1464.7	1454.0	1443.2	1438.9	1434.6	1423.9	1411.1	1400.4	1391.7	1381.0
12.5°	1469.0	1456.2	1443.2	1434.6	1426.1	1419.7	1406.8	1394.0	1381.0	1363.9	1355.3
15°	1456.2	1438.9	1426.1	1411.1	1404.7	1394.0	1383.2	1363.9	1348.9	1333.9	1323.1
17.5°	1430.4	1409.0	1394.0	1378.9	1368.2	1361.8	1344.6	1327.4	1310.3	1293.2	1280.3
20°	1391.7	1372.5	1355.3	1336.1	1327.4	1318.8	1297.4	1280.3	1263.1	1243.8	1231.0
22.5°	1344.6	1325.3	1301.7	1286.7	1273.9	1263.1	1243.8	1224.6	1207.3	1190.2	1173.1
25°	1286.7	1267.4	1246.0	1222.4	1213.7	1203.0	1181.6	1162.4	1143.0	1123.7	1108.7
27.5°	1224.6	1198.7	1181.6	1155.9	1147.3	1136.6	1113.0	1091.5	1074.4	1059.4	1042.3
30°	1149.4	1130.1	1106.6	1082.9	1074.4	1063.7	1044.4	1025.0	1007.9	990.8	973.6
32.5°	1068.0	1048.7	1025.0	1007.9	995.1	986.5	967.1	950.0	932.9	915.6	900.7
35°	982.2	960.7	943.6	926.5	915.6	904.9	885.7	870.7	857.7	842.8	827.8
37.5°	894.2	879.3	862.1	842.8	832.1	823.5	808.5	791.3	780.6	767.7	757.0
40°	808.5	791.3	776.3	759.2	750.6	744.2	729.1	716.3	705.6	694.9	688.4
42.5°	720.5	705.6	690.6	679.8	673.3	666.9	656.2	641.2	634.8	624.1	617.6
45°	639.1	626.2	615.4	600.4	596.2	591.9	579.0	568.3	561.8	555.4	551.1
47.5°	561.8	553.2	540.4	531.8	525.4	521.1	512.6	504.0	497.5	493.2	488.9
50°	495.3	484.6	476.1	467.5	463.2	456.8	448.3	443.9	439.6	435.3	435.3
52.5°	433.2	422.5	413.9	407.5	403.2	398.9	392.5	390.3	386.1	386.1	383.8
55°	375.2	368.8	360.3	351.7	349.6	347.4	343.1	338.9	336.7	334.6	336.7
57.5°	326.0	319.5	310.9	304.5	302.4	300.2	298.1	293.8	291.7	291.7	291.7
60°	281.0	274.5	268.1	261.6	261.6	257.3	255.2	253.0	250.9	248.7	248.7
62.5°	240.2	233.8	227.3	223.1	220.9	218.8	214.5	212.4	210.2	210.2	208.1
65°	203.7	195.1	193.0	186.6	184.4	182.3	180.1	175.9	173.7	171.6	169.4
67.5°	167.3	163.0	156.6	152.3	150.2	147.9	145.8	141.5	139.4	137.2	132.9
70°	135.1	130.8	126.5	122.2	120.1	117.9	113.7	109.4	107.2	103.0	96.5
72.5°	105.1	100.8	96.5	92.3	90.1	87.9	83.6	79.3	75.0	70.7	66.5
75°	79.3	75.0	68.6	64.3	62.2	62.2	55.8	51.5	47.2	40.8	36.5
77.5°	55.8	49.3	47.2	42.9	40.8	36.5	32.2	27.8	23.5	21.4	17.1
80°	36.5	32.2	27.8	25.7	23.5	21.4	19.3	15.0	10.7	8.6	6.4
82.5°	21.4	19.3	17.1	15.0	12.8	10.7	8.6	8.6	6.4	4.3	2.1
85°	10.7	8.6	6.4	6.4	4.3	4.3	4.3	2.1	2.1	2.1	2.1
87.5°	4.3	2.1	2.1	2.1	2.1	2.1	2.1	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584351

CATALOG NUMBER: HCC8W30D010SL-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6
2.5°	1428.2	1426.1	1423.9	1421.8	1421.8	1417.5	1417.5	1415.4	1411.1	1409.0	1409.0
5°	1415.4	1409.0	1404.7	1402.5	1400.4	1394.0	1391.7	1387.4	1383.2	1378.9	1376.7
7.5°	1396.1	1385.3	1381.0	1378.9	1372.5	1366.0	1361.8	1355.3	1348.9	1342.5	1340.4
10°	1372.5	1361.8	1351.1	1346.8	1340.4	1336.1	1327.4	1318.8	1312.4	1306.0	1299.6
12.5°	1342.5	1329.5	1318.8	1314.6	1308.1	1299.6	1286.7	1282.5	1271.6	1267.4	1258.8
15°	1308.1	1293.2	1282.5	1276.0	1269.5	1256.7	1248.1	1239.5	1228.8	1224.6	1216.0
17.5°	1265.2	1248.1	1237.4	1231.0	1226.7	1216.0	1203.0	1192.3	1181.6	1177.3	1170.9
20°	1213.7	1203.0	1188.0	1181.6	1177.3	1164.5	1151.5	1147.3	1138.7	1130.1	1123.7
22.5°	1155.9	1145.1	1130.1	1123.7	1121.6	1110.9	1100.2	1093.6	1087.2	1080.8	1074.4
25°	1095.9	1082.9	1070.1	1065.8	1061.5	1053.0	1044.4	1040.1	1033.6	1029.3	1025.0
27.5°	1031.5	1018.6	1007.9	1001.5	997.2	990.8	986.5	982.2	978.0	973.6	971.4
30°	962.9	950.0	941.5	937.2	932.9	930.7	924.3	922.2	920.0	915.6	917.8
32.5°	894.2	883.5	875.0	868.6	868.6	864.3	862.1	862.1	860.0	860.0	860.0
35°	819.2	812.8	806.4	804.2	802.1	800.0	797.7	800.0	797.7	800.0	802.1
37.5°	750.6	744.2	739.8	737.7	735.5	737.7	735.5	735.5	737.7	742.1	744.2
40°	679.8	675.5	671.2	673.3	671.2	671.2	671.2	677.6	679.8	682.0	684.2
42.5°	613.3	609.0	606.9	606.9	609.0	606.9	611.1	613.3	617.6	624.1	628.4
45°	549.0	546.8	546.8	549.0	546.8	551.1	551.1	555.4	561.8	566.2	570.5
47.5°	488.9	488.9	488.9	491.1	491.1	493.2	497.5	499.6	504.0	508.3	512.6
50°	433.2	435.3	437.4	437.4	437.4	441.7	446.1	448.3	450.4	452.5	459.0
52.5°	383.8	386.1	386.1	388.2	390.3	392.5	394.6	398.9	401.0	405.3	407.5
55°	336.7	336.7	341.0	343.1	343.1	343.1	347.4	347.4	351.7	353.8	358.1
57.5°	291.7	293.8	293.8	295.9	295.9	298.1	300.2	302.4	304.5	306.6	308.8
60°	248.7	248.7	248.7	250.9	253.0	255.2	253.0	257.3	257.3	261.6	263.7
62.5°	208.1	210.2	210.2	210.2	210.2	210.2	210.2	212.4	214.5	216.6	218.8
65°	169.4	169.4	169.4	167.3	169.4	167.3	169.4	171.6	171.6	173.7	175.9
67.5°	130.8	130.8	126.5	126.5	128.6	128.6	128.6	128.6	126.5	130.8	130.8
70°	94.4	92.3	90.1	87.9	87.9	85.7	85.7	83.6	83.6	83.6	83.6
72.5°	62.2	57.9	53.6	51.5	49.3	49.3	45.1	42.9	45.1	45.1	45.1
75°	32.2	27.8	25.7	23.5	21.4	21.4	19.3	19.3	19.3	19.3	19.3
77.5°	12.8	10.7	8.6	8.6	6.4	6.4	6.4	6.4	6.4	6.4	6.4
80°	4.3	4.3	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	2.1	0.0	0.0	2.1	0.0	2.1	2.1	2.1	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584351

CATALOG NUMBER: HCC8W30D010SL-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6	1434.6
2.5°	1406.8	1406.8	1404.7	1406.8	1402.5	1404.7	1402.5	1402.5
5°	1374.6	1370.3	1370.3	1370.3	1368.2	1368.2	1366.0	1366.0
7.5°	1336.1	1333.9	1331.7	1329.5	1327.4	1325.3	1325.3	1325.3
10°	1297.4	1293.2	1293.2	1291.0	1286.7	1284.6	1284.6	1284.6
12.5°	1252.4	1250.2	1248.1	1248.1	1239.5	1241.7	1239.5	1239.5
15°	1209.5	1207.3	1207.3	1200.9	1196.6	1196.6	1196.6	1194.5
17.5°	1164.5	1162.4	1160.2	1155.9	1151.5	1151.5	1149.4	1151.5
20°	1117.3	1115.2	1110.9	1110.9	1108.7	1106.6	1102.3	1104.5
22.5°	1070.1	1065.8	1063.7	1063.7	1061.5	1061.5	1057.3	1057.3
25°	1020.8	1018.6	1016.5	1018.6	1014.3	1014.3	1010.1	1010.1
27.5°	969.3	967.1	967.1	967.1	965.0	967.1	965.0	965.0
30°	917.8	917.8	915.6	915.6	917.8	915.6	917.8	920.0
32.5°	862.1	862.1	864.3	864.3	866.4	866.4	866.4	866.4
35°	804.2	808.5	808.5	810.7	812.8	814.9	814.9	817.1
37.5°	750.6	752.8	754.9	757.0	761.3	761.3	761.3	761.3
40°	692.7	694.9	699.1	697.0	705.6	707.7	705.6	705.6
42.5°	632.7	636.9	639.1	643.4	645.5	649.8	651.9	651.9
45°	576.9	579.0	583.3	587.6	589.7	596.2	596.2	596.2
47.5°	519.0	523.3	525.4	529.7	531.8	538.3	540.4	538.3
50°	463.2	467.5	471.8	471.8	478.2	480.4	484.6	486.8
52.5°	409.6	411.8	416.0	418.2	422.5	426.7	428.9	431.0
55°	358.1	360.3	364.5	364.5	371.0	373.1	377.4	377.4
57.5°	310.9	313.1	317.3	315.2	319.5	323.8	323.8	321.6
60°	265.9	265.9	265.9	270.3	272.4	274.5	276.7	276.7
62.5°	218.8	223.1	225.2	225.2	227.3	229.5	229.5	227.3
65°	175.9	180.1	182.3	182.3	184.4	184.4	184.4	186.6
67.5°	132.9	132.9	132.9	135.1	132.9	132.9	132.9	132.9
70°	83.6	83.6	83.6	83.6	81.4	83.6	83.6	85.7
72.5°	45.1	45.1	45.1	45.1	45.1	45.1	45.1	45.1
75°	19.3	19.3	19.3	21.4	19.3	19.3	19.3	19.3
77.5°	8.6	6.4	8.6	8.6	6.4	6.4	6.4	6.4
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	0.0	2.1	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)