

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584521

Luminaire Tested: **HCC8S40D010MB-HM82555827-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010MB-HM82555827-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3854.7 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584521
CATALOG NUMBER: HCC8S40D010MB-HM82555827-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584521

CATALOG NUMBER: HCC8S40D010MB-HM82555827-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88	
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77	
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			67	
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			59	
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			53	
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			47	
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			43	
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			39	
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			35	
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			32	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63813	63813	63813
5°	66452	63673	60992
10°	68674	62859	58018
15°	70409	61422	55005
20°	70550	58877	52278
25°	69358	55150	49570
30°	65648	50886	47254
35°	59854	45764	44367
40°	52052	40343	40966
45°	44651	34940	37499
50°	38138	30127	33686
55°	33429	25940	29268
60°	29757	22128	24607
65°	26406	18059	19635
70°	23432	13389	11162
75°	19539	7006	3312
80°	15378	2202	550
85°	10933	1097	0



TEST NUMBER: P584521

CATALOG NUMBER: HCC8S40D010MB-HM82555827-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.0	5.1
10°-20°	546.5	14.2
20°-30°	773.6	20.1
30°-40°	809.3	21.0
40°-50°	675.0	17.5
50°-60°	478.7	12.4
60°-70°	275.7	7.2
70°-80°	88.7	2.3
80°-90°	12.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1515.1	39.3
0°-40°	2324.4	60.3
0°-60°	3478.1	90.2
0°-90°	3854.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3854.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2069	2069	2069	2069	2069	
5°	2147	2119	2057	1995	1970	206
15°	2206	2116	1924	1772	1723	620
25°	2038	1887	1621	1491	1457	930
35°	1590	1451	1216	1151	1179	986
45°	1024	940	801	810	860	793
55°	622	557	482	507	544	562
65°	362	303	248	248	269	362
75°	164	121	59	28	28	178
85°	31	16	3	0	0	39
90°	0	0	0	0	0	



TEST NUMBER: P584521

CATALOG NUMBER: HCC8S40D010MB-HM82555827-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4
2.5°	2112.7	2109.6	2106.5	2109.6	2106.5	2109.6	2106.5	2106.5	2103.4	2100.4	2100.4
5°	2146.8	2143.7	2143.7	2143.7	2140.6	2137.5	2137.5	2134.4	2128.2	2125.1	2118.9
7.5°	2168.4	2171.5	2171.5	2171.5	2165.3	2165.3	2159.1	2152.9	2146.8	2140.6	2131.3
10°	2193.2	2193.2	2190.1	2187.0	2180.8	2177.7	2174.6	2168.4	2159.1	2146.8	2137.5
12.5°	2202.5	2202.5	2199.4	2193.2	2190.1	2187.0	2183.9	2174.6	2162.2	2146.8	2134.4
15°	2205.5	2199.4	2196.3	2193.2	2187.0	2177.7	2177.7	2165.3	2149.9	2131.3	2115.8
17.5°	2180.8	2183.9	2177.7	2171.5	2162.2	2156.0	2146.8	2137.5	2118.9	2097.3	2081.8
20°	2149.9	2146.8	2143.7	2134.4	2122.0	2118.9	2109.6	2094.2	2078.7	2053.9	2032.3
22.5°	2100.4	2097.3	2091.1	2084.9	2072.5	2066.3	2057.0	2038.5	2016.8	1992.1	1967.3
25°	2038.5	2032.3	2023.0	2010.6	2001.3	1995.2	1982.8	1964.2	1939.5	1911.6	1886.9
27.5°	1939.5	1948.7	1942.6	1924.0	1914.7	1902.3	1899.2	1874.5	1852.9	1825.1	1797.3
30°	1843.7	1843.7	1834.4	1825.1	1809.6	1800.4	1788.0	1769.4	1747.8	1713.7	1692.1
32.5°	1723.0	1719.9	1707.5	1704.4	1692.1	1673.5	1670.4	1645.7	1624.0	1599.2	1571.4
35°	1590.0	1583.8	1571.4	1562.1	1555.9	1546.6	1537.4	1515.7	1494.0	1469.3	1450.7
37.5°	1438.4	1438.4	1435.3	1419.8	1413.6	1407.4	1398.1	1376.5	1364.1	1339.3	1320.9
40°	1293.1	1290.0	1280.7	1277.6	1271.4	1262.1	1255.9	1243.6	1225.0	1206.4	1187.9
42.5°	1150.7	1153.8	1141.4	1144.5	1132.2	1126.0	1122.9	1104.3	1095.0	1076.5	1061.0
45°	1023.9	1020.8	1014.6	1011.5	1005.3	999.1	992.9	983.7	968.2	949.6	940.3
47.5°	906.3	897.0	897.0	893.9	890.8	878.5	875.4	866.1	856.8	838.2	825.9
50°	795.0	795.0	795.0	791.9	782.7	779.6	773.4	764.1	754.8	742.4	723.9
52.5°	705.3	705.3	705.3	702.2	689.8	686.7	683.7	671.3	658.9	649.6	637.2
55°	621.8	624.9	621.8	615.6	606.3	606.3	597.0	590.8	578.5	569.2	556.8
57.5°	550.6	550.6	544.4	541.3	535.1	532.0	525.9	519.7	504.2	494.9	479.5
60°	482.5	479.5	479.5	473.3	467.1	460.9	457.8	448.5	442.3	426.9	414.5
62.5°	420.7	420.7	414.5	414.5	402.1	402.1	399.0	389.7	380.4	365.0	358.8
65°	361.9	361.9	358.8	355.7	346.4	343.3	340.2	330.9	321.7	312.4	303.1
67.5°	309.3	309.3	303.1	300.0	293.8	290.7	284.5	278.3	269.1	259.9	250.6
70°	259.9	256.8	253.7	250.6	244.4	241.3	235.1	229.0	219.7	213.5	204.2
72.5°	210.4	210.4	207.3	201.1	198.0	194.9	191.8	185.6	176.4	167.1	160.9
75°	164.0	164.0	164.0	157.8	151.6	148.5	148.5	142.3	136.1	126.9	120.7
77.5°	126.9	123.8	120.7	120.7	114.5	111.4	108.3	105.2	95.9	92.8	86.6
80°	86.6	89.7	86.6	83.5	80.4	77.4	77.4	71.2	68.1	61.9	55.7
82.5°	58.8	55.7	55.7	52.6	52.6	49.5	49.5	43.3	40.2	37.1	34.0
85°	30.9	30.9	27.8	27.8	27.8	24.8	24.8	21.7	21.7	18.6	15.5
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	6.2	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584521

CATALOG NUMBER: HCC8S40D010MB-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4
2.5°	2097.3	2091.1	2088.0	2088.0	2084.9	2081.8	2078.7	2075.6	2069.4	2069.4	2063.2
5°	2112.7	2106.5	2103.4	2094.2	2088.0	2088.0	2075.6	2072.5	2063.2	2057.0	2050.8
7.5°	2125.1	2112.7	2103.4	2094.2	2088.0	2081.8	2069.4	2057.0	2044.7	2032.3	2026.1
10°	2125.1	2112.7	2097.3	2081.8	2075.6	2069.4	2053.9	2035.4	2019.9	2007.5	1992.1
12.5°	2118.9	2100.4	2081.8	2069.4	2057.0	2047.8	2029.2	2010.6	1992.1	1967.3	1954.9
15°	2100.4	2075.6	2057.0	2035.4	2026.1	2010.6	1995.2	1967.3	1945.6	1924.0	1908.5
17.5°	2063.2	2032.3	2010.6	1989.0	1973.5	1964.2	1939.5	1914.7	1890.0	1865.3	1846.8
20°	2007.5	1979.7	1954.9	1927.1	1914.7	1902.3	1871.5	1846.8	1822.0	1794.2	1775.6
22.5°	1939.5	1911.6	1877.6	1856.0	1837.5	1822.0	1794.2	1766.3	1741.6	1716.8	1692.1
25°	1856.0	1828.2	1797.3	1763.2	1750.8	1735.4	1704.4	1676.6	1648.7	1620.9	1599.2
27.5°	1766.3	1729.2	1704.4	1667.3	1654.9	1639.5	1605.4	1574.5	1549.7	1528.1	1503.3
30°	1658.0	1630.2	1596.1	1562.1	1549.7	1534.3	1506.4	1478.6	1453.8	1429.1	1404.3
32.5°	1540.5	1512.6	1478.6	1453.8	1435.3	1422.9	1395.0	1370.3	1345.5	1320.9	1299.2
35°	1416.7	1385.8	1361.0	1336.4	1320.9	1305.4	1277.6	1255.9	1237.4	1215.7	1194.0
37.5°	1290.0	1268.3	1243.6	1215.7	1200.2	1187.9	1166.2	1141.4	1126.0	1107.4	1091.9
40°	1166.2	1141.4	1119.8	1095.0	1082.7	1073.4	1051.7	1033.2	1017.7	1002.2	992.9
42.5°	1039.3	1017.7	996.0	980.6	971.3	962.0	946.5	924.9	915.6	900.1	890.8
45°	921.8	903.2	887.7	866.1	859.9	853.7	835.1	819.7	810.4	801.2	795.0
47.5°	810.4	798.1	779.6	767.2	757.9	751.7	739.3	727.0	717.7	711.5	705.3
50°	714.6	699.1	686.7	674.4	668.2	658.9	646.5	640.3	634.2	628.0	628.0
52.5°	624.9	609.4	597.0	587.7	581.6	575.4	566.1	563.0	556.8	556.8	553.7
55°	541.3	532.0	519.7	507.3	504.2	501.1	494.9	488.7	485.6	482.5	485.6
57.5°	470.2	460.9	448.5	439.2	436.1	433.0	429.9	423.8	420.7	420.7	420.7
60°	405.2	395.9	386.6	377.3	377.3	371.2	368.1	365.0	361.9	358.8	358.8
62.5°	346.4	337.1	327.8	321.7	318.6	315.5	309.3	306.2	303.1	303.1	300.0
65°	293.8	281.4	278.3	269.1	266.1	263.0	259.9	253.7	250.6	247.5	244.4
67.5°	241.3	235.1	225.9	219.7	216.6	213.5	210.4	204.2	201.1	198.0	191.8
70°	194.9	188.7	182.5	176.4	173.3	170.2	164.0	157.8	154.7	148.5	139.2
72.5°	151.6	145.4	139.2	133.0	129.9	126.9	120.7	114.5	108.3	102.1	95.9
75°	114.5	108.3	99.0	92.8	89.7	89.7	80.4	74.3	68.1	58.8	52.6
77.5°	80.4	71.2	68.1	61.9	58.8	52.6	46.4	40.2	34.0	30.9	24.8
80°	52.6	46.4	40.2	37.1	34.0	30.9	27.8	21.7	15.5	12.4	9.3
82.5°	30.9	27.8	24.8	21.7	18.6	15.5	12.4	12.4	9.3	6.2	3.1
85°	15.5	12.4	9.3	9.3	6.2	6.2	6.2	3.1	3.1	3.1	3.1
87.5°	6.2	3.1	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584521

CATALOG NUMBER: HCC8S40D010MB-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4
2.5°	2060.1	2057.0	2053.9	2050.8	2050.8	2044.7	2044.7	2041.6	2035.4	2032.3	2032.3
5°	2041.6	2032.3	2026.1	2023.0	2019.9	2010.6	2007.5	2001.3	1995.2	1989.0	1985.9
7.5°	2013.7	1998.2	1992.1	1989.0	1979.7	1970.4	1964.2	1954.9	1945.6	1936.4	1933.3
10°	1979.7	1964.2	1948.7	1942.6	1933.3	1927.1	1914.7	1902.3	1893.1	1883.8	1874.5
12.5°	1936.4	1917.8	1902.3	1896.1	1886.9	1874.5	1856.0	1849.9	1834.4	1828.2	1815.8
15°	1886.9	1865.3	1849.9	1840.6	1831.3	1812.7	1800.4	1788.0	1772.5	1766.3	1753.9
17.5°	1825.1	1800.4	1784.9	1775.6	1769.4	1753.9	1735.4	1719.9	1704.4	1698.2	1689.0
20°	1750.8	1735.4	1713.7	1704.4	1698.2	1679.7	1661.1	1654.9	1642.6	1630.2	1620.9
22.5°	1667.3	1651.8	1630.2	1620.9	1617.8	1602.3	1586.9	1577.6	1568.3	1559.0	1549.7
25°	1580.7	1562.1	1543.5	1537.4	1531.2	1518.8	1506.4	1500.2	1491.0	1484.8	1478.6
27.5°	1487.9	1469.3	1453.8	1444.5	1438.4	1429.1	1422.9	1416.7	1410.5	1404.3	1401.2
30°	1388.8	1370.3	1357.9	1351.7	1345.5	1342.4	1333.3	1330.2	1327.1	1320.9	1324.0
32.5°	1290.0	1274.5	1262.1	1252.8	1252.8	1246.6	1243.6	1243.6	1240.5	1240.5	1240.5
35°	1181.7	1172.4	1163.1	1160.0	1156.9	1153.8	1150.7	1153.8	1150.7	1153.8	1156.9
37.5°	1082.7	1073.4	1067.2	1064.1	1061.0	1064.1	1061.0	1061.0	1064.1	1070.3	1073.4
40°	980.6	974.4	968.2	971.3	968.2	968.2	968.2	977.5	980.6	983.7	986.7
42.5°	884.6	878.5	875.4	875.4	878.5	875.4	881.6	884.6	890.8	900.1	906.3
45°	791.9	788.9	788.9	791.9	788.9	795.0	795.0	801.2	810.4	816.6	822.8
47.5°	705.3	705.3	705.3	708.4	708.4	711.5	717.7	720.8	727.0	733.2	739.3
50°	624.9	628.0	631.1	631.1	631.1	637.2	643.4	646.5	649.6	652.7	662.0
52.5°	553.7	556.8	556.8	559.9	563.0	566.1	569.2	575.4	578.5	584.6	587.7
55°	485.6	485.6	491.8	494.9	494.9	494.9	501.1	501.1	507.3	510.4	516.6
57.5°	420.7	423.8	423.8	426.9	426.9	429.9	433.0	436.1	439.2	442.3	445.4
60°	358.8	358.8	358.8	361.9	365.0	368.1	365.0	371.2	371.2	377.3	380.4
62.5°	300.0	303.1	303.1	303.1	303.1	303.1	303.1	306.2	309.3	312.4	315.5
65°	244.4	244.4	244.4	241.3	244.4	241.3	244.4	247.5	247.5	250.6	253.7
67.5°	188.7	188.7	182.5	182.5	185.6	185.6	185.6	185.6	182.5	188.7	188.7
70°	136.1	133.0	129.9	126.9	126.9	123.8	123.8	120.7	120.7	120.7	120.7
72.5°	89.7	83.5	77.4	74.3	71.2	71.2	65.0	61.9	65.0	65.0	65.0
75°	46.4	40.2	37.1	34.0	30.9	30.9	27.8	27.8	27.8	27.8	27.8
77.5°	18.6	15.5	12.4	12.4	9.3	9.3	9.3	9.3	9.3	9.3	9.3
80°	6.2	6.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
82.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
85°	3.1	0.0	0.0	3.1	0.0	3.1	3.1	3.1	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584521

CATALOG NUMBER: HCC8S40D010MB-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4	2069.4
2.5°	2029.2	2029.2	2026.1	2029.2	2023.0	2026.1	2023.0	2023.0
5°	1982.8	1976.6	1976.6	1976.6	1973.5	1973.5	1970.4	1970.4
7.5°	1927.1	1924.0	1920.9	1917.8	1914.7	1911.6	1911.6	1911.6
10°	1871.5	1865.3	1865.3	1862.2	1856.0	1852.9	1852.9	1852.9
12.5°	1806.5	1803.4	1800.4	1800.4	1788.0	1791.1	1788.0	1788.0
15°	1744.7	1741.6	1741.6	1732.3	1726.1	1726.1	1726.1	1723.0
17.5°	1679.7	1676.6	1673.5	1667.3	1661.1	1661.1	1658.0	1661.1
20°	1611.6	1608.5	1602.3	1602.3	1599.2	1596.1	1590.0	1593.1
22.5°	1543.5	1537.4	1534.3	1534.3	1531.2	1531.2	1525.0	1525.0
25°	1472.4	1469.3	1466.2	1469.3	1463.1	1463.1	1456.9	1456.9
27.5°	1398.1	1395.0	1395.0	1395.0	1391.9	1395.0	1391.9	1391.9
30°	1324.0	1324.0	1320.9	1320.9	1324.0	1320.9	1324.0	1327.1
32.5°	1243.6	1243.6	1246.6	1246.6	1249.7	1249.7	1249.7	1249.7
35°	1160.0	1166.2	1166.2	1169.3	1172.4	1175.5	1175.5	1178.6
37.5°	1082.7	1085.8	1088.8	1091.9	1098.1	1098.1	1098.1	1098.1
40°	999.1	1002.2	1008.4	1005.3	1017.7	1020.8	1017.7	1017.7
42.5°	912.5	918.7	921.8	928.0	931.1	937.2	940.3	940.3
45°	832.0	835.1	841.3	847.5	850.6	859.9	859.9	859.9
47.5°	748.6	754.8	757.9	764.1	767.2	776.5	779.6	776.5
50°	668.2	674.4	680.6	680.6	689.8	692.9	699.1	702.2
52.5°	590.8	593.9	600.1	603.2	609.4	615.6	618.7	621.8
55°	516.6	519.7	525.9	525.9	535.1	538.2	544.4	544.4
57.5°	448.5	451.6	457.8	454.7	460.9	467.1	467.1	464.0
60°	383.5	383.5	383.5	389.7	392.8	395.9	399.0	399.0
62.5°	315.5	321.7	324.8	324.8	327.8	330.9	330.9	327.8
65°	253.7	259.9	263.0	263.0	266.1	266.1	266.1	269.1
67.5°	191.8	191.8	191.8	194.9	191.8	191.8	191.8	191.8
70°	120.7	120.7	120.7	120.7	117.6	120.7	120.7	123.8
72.5°	65.0	65.0	65.0	65.0	65.0	65.0	65.0	65.0
75°	27.8	27.8	27.8	30.9	27.8	27.8	27.8	27.8
77.5°	12.4	9.3	12.4	12.4	9.3	9.3	9.3	9.3
80°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
82.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
85°	0.0	3.1	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)