

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584370

Luminaire Tested: **HCC8W30D010SL-HM82555940-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010SL-HM82555940-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3356.9 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584370
CATALOG NUMBER: HCC8W30D010SL-HM82555940-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P584370

CATALOG NUMBER: HCC8W30D010SL-HM82555940-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	51469	51469	51469
5°	53352	51297	49536
10°	54862	50854	47513
15°	56081	49952	45412
20°	56173	48002	43566
25°	55095	45334	42030
30°	52256	42041	40182
35°	47481	38288	38374
40°	41514	34357	36168
45°	35978	30601	33701
50°	31504	27186	30712
55°	28042	24091	27789
60°	25298	21641	24416
65°	22831	19022	21284
70°	20520	16030	15823
75°	18074	12712	11855
80°	15165	10513	11365
85°	11746	9199	10048



TEST NUMBER: P584370
 CATALOG NUMBER: HCC8W30D010SL-HM82555940-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	4.7
10°-20°	443.5	13.2
20°-30°	633.8	18.9
30°-40°	673.5	20.1
40°-50°	579.8	17.3
50°-60°	433.5	12.9
60°-70°	276.5	8.2
70°-80°	125.8	3.7
80°-90°	33.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1234.8	36.8
0°-40°	1908.2	56.8
0°-60°	2921.6	87.0
0°-90°	3356.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3356.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1669	1669	1669	1669	1669	
5°	1724	1700	1657	1614	1600	165
15°	1757	1698	1565	1458	1422	495
25°	1619	1517	1332	1252	1235	741
35°	1261	1174	1017	991	1019	786
45°	825	780	702	721	773	641
55°	522	479	448	486	517	469
65°	313	277	261	273	292	312
75°	152	130	107	97	100	161
85°	33	28	26	28	28	40
90°	0	0	0	0	0	



TEST NUMBER: P584370

CATALOG NUMBER: HCC8W30D010SL-HM82555940-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1
2.5°	1699.9	1695.2	1697.5	1695.2	1697.5	1697.5	1692.8	1692.8	1692.8	1692.8	1685.6
5°	1723.6	1721.2	1721.2	1718.8	1716.4	1718.8	1716.4	1714.2	1709.4	1707.0	1699.9
7.5°	1737.8	1737.8	1737.8	1737.8	1735.5	1733.1	1730.7	1726.0	1721.2	1716.4	1711.8
10°	1752.1	1754.4	1752.1	1749.7	1747.4	1742.6	1740.2	1735.5	1728.3	1721.2	1716.4
12.5°	1759.1	1759.1	1756.7	1756.7	1752.1	1749.7	1742.6	1735.5	1728.3	1721.2	1709.4
15°	1756.7	1756.7	1754.4	1752.1	1745.0	1742.6	1737.8	1730.7	1718.8	1709.4	1697.5
17.5°	1742.6	1740.2	1735.5	1735.5	1726.0	1723.6	1718.8	1709.4	1697.5	1683.3	1669.1
20°	1711.8	1711.8	1709.4	1707.0	1697.5	1690.4	1685.6	1673.9	1664.4	1647.7	1633.6
22.5°	1669.1	1673.9	1669.1	1664.4	1652.5	1650.1	1643.0	1628.8	1614.5	1595.6	1579.0
25°	1619.3	1616.9	1614.5	1609.8	1600.3	1595.6	1586.1	1571.9	1557.6	1536.3	1517.4
27.5°	1555.3	1545.8	1545.8	1536.3	1529.2	1522.0	1517.4	1503.1	1484.1	1467.6	1443.8
30°	1467.6	1470.0	1458.1	1455.7	1443.8	1439.0	1429.7	1415.4	1398.9	1379.8	1360.8
32.5°	1372.7	1365.6	1365.6	1356.2	1346.7	1339.5	1337.1	1320.5	1306.4	1287.3	1268.4
35°	1261.3	1261.3	1254.2	1251.8	1242.3	1237.6	1230.5	1221.0	1204.3	1187.8	1173.5
37.5°	1152.3	1147.5	1145.1	1140.4	1133.2	1126.1	1126.1	1109.6	1107.2	1088.2	1069.3
40°	1031.3	1036.1	1031.3	1024.2	1021.8	1017.1	1014.7	1005.2	998.2	981.5	969.6
42.5°	929.3	924.7	924.7	922.3	912.8	912.8	908.0	903.3	891.4	886.8	872.5
45°	825.0	829.8	822.7	825.0	815.5	815.5	815.5	806.1	796.6	789.5	780.0
47.5°	734.9	737.3	737.3	730.2	727.9	727.9	723.1	718.4	711.3	701.7	694.6
50°	656.7	659.1	654.3	651.9	647.3	644.9	644.9	635.4	630.6	621.1	616.4
52.5°	585.6	585.6	583.2	583.2	576.1	576.1	571.4	564.3	559.5	554.8	542.9
55°	521.6	521.6	519.2	516.9	516.9	509.7	507.3	500.2	495.5	486.1	478.9
57.5°	459.9	462.3	459.9	457.5	455.1	452.9	448.1	441.0	436.2	429.1	424.4
60°	410.2	410.2	407.8	405.4	400.7	398.3	395.9	391.2	384.0	379.3	372.3
62.5°	362.8	360.4	358.0	355.6	350.9	350.9	346.1	341.4	334.3	329.6	324.8
65°	312.9	312.9	310.6	310.6	308.2	303.4	301.1	298.7	289.3	286.9	277.4
67.5°	267.9	270.3	265.5	265.5	260.7	260.7	258.4	251.4	249.0	244.2	239.5
70°	227.6	227.6	227.6	225.2	220.4	218.1	215.8	211.0	208.7	203.9	199.2
72.5°	187.3	187.3	184.9	184.9	182.5	180.1	177.8	173.1	173.1	168.4	163.6
75°	151.7	151.7	149.3	147.0	144.6	144.6	142.2	139.8	135.2	132.8	130.4
77.5°	116.2	116.2	116.2	113.8	111.4	111.4	111.4	106.7	101.9	101.9	99.5
80°	85.4	85.4	83.0	83.0	80.6	80.6	80.6	78.2	75.9	73.5	71.1
82.5°	57.0	57.0	57.0	57.0	54.6	54.6	54.6	52.2	49.8	49.8	49.8
85°	33.2	33.2	33.2	33.2	30.8	30.8	30.8	30.8	30.8	28.4	28.4
87.5°	14.3	11.9	14.3	11.9	14.3	11.9	14.3	11.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584370

CATALOG NUMBER: HCC8W30D010SL-HM82555940-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1
2.5°	1688.0	1685.6	1683.3	1680.9	1680.9	1678.5	1673.9	1671.5	1669.1	1666.7	1666.7
5°	1697.5	1695.2	1690.4	1685.6	1683.3	1678.5	1673.9	1669.1	1664.4	1657.2	1654.9
7.5°	1704.7	1697.5	1692.8	1683.3	1680.9	1676.1	1669.1	1662.0	1652.5	1643.0	1635.8
10°	1704.7	1695.2	1688.0	1676.1	1671.5	1666.7	1657.2	1645.3	1633.6	1624.1	1612.2
12.5°	1699.9	1688.0	1676.1	1664.4	1657.2	1650.1	1635.8	1624.1	1609.8	1595.6	1586.1
15°	1683.3	1669.1	1654.9	1640.6	1633.6	1624.1	1609.8	1593.3	1579.0	1564.7	1548.2
17.5°	1652.5	1638.2	1621.7	1605.0	1595.6	1588.5	1567.1	1555.3	1533.9	1519.7	1505.5
20°	1612.2	1595.6	1574.2	1557.6	1545.8	1538.7	1522.0	1500.8	1484.1	1462.8	1448.6
22.5°	1560.0	1538.7	1517.4	1500.8	1488.9	1479.4	1458.1	1436.8	1422.5	1403.5	1387.0
25°	1498.4	1477.1	1455.7	1432.0	1420.1	1410.6	1391.7	1372.7	1353.8	1332.4	1318.2
27.5°	1424.9	1401.1	1382.2	1360.8	1349.0	1334.8	1313.5	1294.5	1275.6	1261.3	1242.3
30°	1344.3	1318.2	1299.2	1277.9	1266.0	1254.2	1232.9	1213.9	1197.3	1180.7	1171.2
32.5°	1247.0	1228.1	1209.1	1187.8	1178.3	1171.2	1149.9	1130.9	1112.0	1097.7	1090.6
35°	1154.6	1133.2	1116.7	1097.7	1085.8	1078.8	1059.8	1043.2	1033.7	1017.1	1007.6
37.5°	1057.4	1040.9	1021.8	1002.9	995.8	988.7	974.4	957.9	943.6	931.7	926.9
40°	955.5	941.2	924.7	912.8	905.7	898.5	886.8	874.9	865.4	853.5	848.7
42.5°	858.2	848.7	834.6	820.3	813.2	810.8	796.6	787.1	782.4	777.6	772.8
45°	770.5	756.3	746.8	737.3	730.2	725.5	718.4	711.3	706.5	701.7	697.0
47.5°	685.2	673.3	663.8	656.7	649.7	647.3	642.5	635.4	630.6	630.6	630.6
50°	607.0	597.5	588.0	583.2	580.8	576.1	571.4	569.1	566.7	566.7	566.7
52.5°	538.1	528.7	521.6	516.9	516.9	512.1	507.3	505.0	505.0	505.0	505.0
55°	474.2	467.0	462.3	457.5	452.9	450.5	450.5	450.5	448.1	448.1	450.5
57.5°	417.2	412.6	405.4	400.7	398.3	398.3	395.9	393.6	395.9	398.3	400.7
60°	365.1	360.4	358.0	350.9	350.9	350.9	348.5	348.5	348.5	350.9	353.3
62.5°	317.7	315.3	310.6	308.2	305.8	305.8	303.4	303.4	303.4	303.4	305.8
65°	275.0	270.3	265.5	265.5	265.5	263.1	263.1	258.4	260.7	260.7	258.4
67.5°	234.7	230.0	227.6	225.2	222.8	222.8	220.4	218.1	215.8	215.8	215.8
70°	196.8	192.0	192.0	187.3	187.3	184.9	182.5	182.5	180.1	177.8	175.5
72.5°	158.9	156.5	154.1	151.7	151.7	151.7	149.3	147.0	144.6	142.2	137.6
75°	125.7	125.7	120.9	118.5	118.5	116.2	113.8	111.4	109.0	106.7	104.3
77.5°	97.3	94.9	90.1	87.7	87.7	87.7	85.4	83.0	80.6	78.2	75.9
80°	71.1	68.7	66.3	64.0	64.0	64.0	61.6	61.6	59.2	59.2	59.2
82.5°	47.4	47.4	45.1	45.1	45.1	45.1	42.7	42.7	42.7	42.7	42.7
85°	28.4	28.4	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584370

CATALOG NUMBER: HCC8W30D010SL-HM82555940-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1
2.5°	1662.0	1662.0	1657.2	1654.9	1652.5	1654.9	1650.1	1647.7	1645.3	1645.3	1643.0
5°	1647.7	1645.3	1635.8	1633.6	1631.2	1628.8	1624.1	1619.3	1614.5	1612.2	1609.8
7.5°	1628.8	1621.7	1612.2	1609.8	1607.4	1600.3	1593.3	1588.5	1581.4	1579.0	1574.2
10°	1602.7	1593.3	1586.1	1579.0	1574.2	1567.1	1560.0	1553.0	1543.4	1541.1	1533.9
12.5°	1571.9	1560.0	1545.8	1543.4	1536.3	1526.8	1517.4	1510.3	1503.1	1498.4	1491.2
15°	1533.9	1522.0	1507.9	1500.8	1493.6	1486.5	1474.7	1465.2	1458.1	1450.9	1443.8
17.5°	1488.9	1474.7	1462.8	1455.7	1450.9	1439.0	1429.7	1417.8	1410.6	1403.5	1396.5
20°	1434.4	1422.5	1405.9	1398.9	1396.5	1387.0	1375.1	1370.3	1360.8	1353.8	1349.0
22.5°	1372.7	1360.8	1346.7	1341.9	1332.4	1327.6	1315.9	1311.1	1306.4	1299.2	1296.8
25°	1304.0	1292.1	1280.3	1277.9	1270.8	1266.0	1258.9	1251.8	1251.8	1244.6	1244.6
27.5°	1232.9	1221.0	1211.5	1206.7	1204.3	1199.7	1192.6	1190.2	1187.8	1185.4	1185.4
30°	1157.0	1142.7	1138.0	1135.6	1133.2	1128.5	1126.1	1121.5	1123.7	1126.1	1123.7
32.5°	1076.4	1071.6	1062.1	1057.4	1059.8	1057.4	1052.6	1057.4	1055.0	1059.8	1062.1
35°	998.2	993.4	988.7	988.7	983.9	983.9	983.9	986.3	991.0	993.4	998.2
37.5°	922.3	915.2	912.8	910.4	912.8	912.8	912.8	917.6	922.3	926.9	934.1
40°	841.7	836.9	836.9	836.9	836.9	844.1	841.7	846.4	851.1	858.2	865.4
42.5°	765.8	765.8	768.2	768.2	768.2	768.2	772.8	780.0	787.1	794.3	801.4
45°	694.6	694.6	694.6	699.4	699.4	701.7	711.3	716.0	720.8	727.9	734.9
47.5°	628.3	628.3	630.6	633.0	635.4	640.2	644.9	651.9	659.1	663.8	671.0
50°	566.7	569.1	573.7	578.4	578.4	580.8	588.0	592.7	597.5	604.6	607.0
52.5°	507.3	512.1	516.9	519.2	521.6	526.4	528.7	535.8	538.1	545.3	547.7
55°	452.9	455.1	462.3	464.7	464.7	469.4	474.2	478.9	486.1	486.1	490.8
57.5°	403.1	405.4	410.2	412.6	410.2	417.2	419.6	424.4	426.7	431.5	433.9
60°	353.3	358.0	360.4	360.4	362.8	365.1	369.9	369.9	374.5	379.3	379.3
62.5°	305.8	308.2	310.6	312.9	315.3	312.9	320.1	320.1	324.8	327.2	332.0
65°	260.7	263.1	263.1	265.5	265.5	267.9	267.9	270.3	272.6	277.4	279.8
67.5°	215.8	215.8	215.8	218.1	215.8	218.1	218.1	220.4	220.4	225.2	227.6
70°	175.5	173.1	170.7	170.7	170.7	170.7	168.4	170.7	170.7	173.1	173.1
72.5°	135.2	132.8	130.4	128.1	128.1	125.7	123.3	125.7	125.7	128.1	128.1
75°	101.9	97.3	97.3	97.3	94.9	94.9	94.9	97.3	97.3	97.3	99.5
77.5°	75.9	75.9	73.5	73.5	73.5	75.9	75.9	78.2	78.2	78.2	78.2
80°	57.0	59.2	59.2	59.2	59.2	61.6	61.6	61.6	61.6	64.0	64.0
82.5°	42.7	42.7	42.7	42.7	45.1	45.1	45.1	45.1	45.1	45.1	45.1
85°	26.0	28.4	28.4	26.0	28.4	28.4	28.4	28.4	28.4	28.4	28.4
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584370

CATALOG NUMBER: HCC8W30D010SL-HM82555940-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1	1669.1
2.5°	1640.6	1640.6	1640.6	1640.6	1638.2	1638.2	1638.2	1635.8
5°	1605.0	1605.0	1605.0	1600.3	1602.7	1602.7	1597.9	1600.3
7.5°	1569.5	1567.1	1564.7	1564.7	1562.3	1560.0	1557.6	1560.0
10°	1529.2	1522.0	1522.0	1519.7	1519.7	1515.0	1515.0	1517.4
12.5°	1484.1	1479.4	1479.4	1477.1	1474.7	1472.3	1470.0	1470.0
15°	1439.0	1434.4	1432.0	1429.7	1427.3	1422.5	1424.9	1422.5
17.5°	1394.1	1387.0	1387.0	1384.6	1382.2	1377.5	1377.5	1375.1
20°	1341.9	1339.5	1334.8	1337.1	1334.8	1330.0	1327.6	1327.6
22.5°	1289.7	1289.7	1287.3	1287.3	1285.0	1282.6	1280.3	1280.3
25°	1240.0	1237.6	1240.0	1240.0	1232.9	1232.9	1232.9	1235.3
27.5°	1183.1	1185.4	1183.1	1183.1	1183.1	1183.1	1185.4	1183.1
30°	1126.1	1126.1	1126.1	1128.5	1133.2	1130.9	1130.9	1128.5
32.5°	1064.5	1066.9	1066.9	1069.3	1071.6	1076.4	1076.4	1078.8
35°	1002.9	1007.6	1009.9	1007.6	1014.7	1014.7	1019.4	1019.4
37.5°	938.8	941.2	946.0	948.3	953.1	955.5	957.9	957.9
40°	870.1	879.6	882.0	884.4	891.4	891.4	893.8	898.5
42.5°	806.1	815.5	817.9	820.3	825.0	832.2	829.8	834.6
45°	744.4	751.6	753.9	756.3	763.5	765.8	765.8	772.8
47.5°	678.1	682.8	685.2	689.9	694.6	699.4	704.1	701.7
50°	611.6	618.8	623.5	625.9	633.0	635.4	637.8	640.2
52.5°	552.4	557.2	559.5	561.9	569.1	571.4	573.7	578.4
55°	495.5	497.8	502.6	500.2	507.3	509.7	512.1	516.9
57.5°	438.6	441.0	443.4	443.4	448.1	452.9	455.1	457.5
60°	384.0	388.8	391.2	391.2	391.2	395.9	395.9	395.9
62.5°	334.3	334.3	336.6	336.6	341.4	341.4	341.4	341.4
65°	282.1	284.5	286.9	286.9	291.7	289.3	294.0	291.7
67.5°	227.6	227.6	232.3	232.3	230.0	232.3	232.3	232.3
70°	173.1	173.1	175.5	175.5	175.5	175.5	175.5	175.5
72.5°	128.1	128.1	128.1	130.4	128.1	128.1	130.4	128.1
75°	99.5	99.5	99.5	99.5	99.5	99.5	99.5	99.5
77.5°	78.2	78.2	80.6	80.6	80.6	80.6	80.6	80.6
80°	64.0	64.0	64.0	64.0	66.3	64.0	64.0	64.0
82.5°	47.4	45.1	47.4	45.1	47.4	47.4	47.4	47.4
85°	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)