

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584522

Luminaire Tested: **HCC8S40D010MW-HM82555827-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584522
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010MW-HM82555827-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4207.4 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584522
CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584522

CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	70301	70301	70301
5°	72767	69897	67121
10°	74385	68674	63344
15°	75443	66361	59149
20°	75219	63137	54916
25°	73356	59045	50414
30°	69497	54300	46257
35°	63231	49137	42037
40°	55534	43708	37976
45°	48428	38446	33862
50°	42144	33686	29829
55°	37585	29601	25940
60°	34148	25946	22128
65°	30696	22568	20080
70°	27327	19249	18131
75°	23960	16215	15477
80°	20333	13194	13745
85°	15320	9836	10933



TEST NUMBER: P584522

CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.5	5.1
10°-20°	588.4	14.0
20°-30°	816.7	19.4
30°-40°	844.4	20.1
40°-50°	707.0	16.8
50°-60°	513.2	12.2
60°-70°	323.9	7.7
70°-80°	160.5	3.8
80°-90°	39.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1618.6	38.5
0°-40°	2462.9	58.5
0°-60°	3683.2	87.5
0°-90°	4207.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4207.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2280	2280	2280	2280	2280	
5°	2351	2323	2258	2196	2168	225
15°	2363	2274	2079	1912	1853	665
25°	2156	2017	1735	1547	1482	988
35°	1680	1556	1305	1157	1117	1046
45°	1110	1030	882	795	776	859
55°	699	637	551	504	482	631
65°	421	368	309	272	275	419
75°	201	167	136	130	130	216
85°	43	34	28	31	31	53
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584522

CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8
2.5°	2316.9	2316.9	2320.0	2316.9	2316.9	2316.9	2313.8	2313.8	2310.7	2310.7	2304.6
5°	2350.8	2344.7	2350.8	2344.7	2344.7	2344.7	2341.6	2335.4	2332.3	2326.2	2323.1
7.5°	2366.3	2363.2	2363.2	2360.1	2360.1	2357.0	2353.9	2350.8	2338.5	2335.4	2326.2
10°	2375.6	2372.5	2372.5	2369.4	2363.2	2363.2	2357.0	2353.9	2338.5	2332.3	2320.0
12.5°	2372.5	2372.5	2372.5	2369.4	2360.1	2357.0	2350.8	2341.6	2329.3	2316.9	2304.6
15°	2363.2	2363.2	2357.0	2353.9	2344.7	2338.5	2335.4	2320.0	2307.6	2292.2	2273.6
17.5°	2332.3	2332.3	2329.3	2323.1	2313.8	2307.6	2301.5	2286.0	2273.6	2248.9	2230.3
20°	2292.2	2289.1	2286.0	2276.7	2267.4	2264.3	2255.0	2233.4	2217.9	2199.4	2174.6
22.5°	2233.4	2230.3	2227.2	2221.0	2205.5	2199.4	2193.2	2177.7	2149.9	2131.3	2100.4
25°	2156.0	2156.0	2149.9	2140.6	2125.1	2118.9	2109.6	2094.2	2069.4	2041.6	2016.8
27.5°	2066.3	2063.2	2053.9	2047.8	2035.4	2026.1	2010.6	1992.1	1967.3	1945.6	1914.7
30°	1951.8	1951.8	1945.6	1936.4	1920.9	1914.7	1902.3	1880.7	1855.9	1828.1	1806.5
32.5°	1821.9	1821.9	1812.6	1806.5	1797.3	1781.8	1778.7	1753.9	1732.3	1710.6	1685.9
35°	1679.7	1682.8	1676.6	1664.2	1648.7	1648.7	1642.6	1620.9	1596.1	1574.5	1555.9
37.5°	1537.4	1528.1	1525.0	1518.8	1509.5	1497.1	1491.0	1481.7	1460.0	1444.5	1416.7
40°	1379.6	1382.7	1376.5	1370.3	1367.2	1357.9	1354.8	1339.3	1323.9	1305.3	1293.1
42.5°	1237.4	1237.4	1237.4	1231.2	1225.0	1215.7	1212.6	1203.3	1184.8	1172.4	1153.8
45°	1110.5	1101.2	1101.2	1098.1	1095.0	1088.8	1079.6	1073.4	1061.0	1051.7	1030.1
47.5°	986.7	989.8	986.7	983.7	974.4	971.3	968.2	955.8	943.4	934.2	918.7
50°	878.5	884.6	878.5	878.5	872.3	869.2	863.0	853.7	844.4	829.0	813.5
52.5°	788.7	788.7	785.6	782.5	773.4	767.2	764.1	761.0	745.5	733.2	720.8
55°	699.1	702.2	702.2	692.9	689.8	683.7	680.6	671.3	665.1	646.5	637.2
57.5°	621.8	618.7	621.8	615.6	609.4	603.2	600.1	593.9	584.6	572.3	559.9
60°	553.7	547.5	547.5	544.4	538.2	535.1	529.0	519.7	510.4	498.0	488.7
62.5°	485.6	482.5	479.5	476.4	470.2	467.1	464.0	454.7	445.4	436.1	426.9
65°	420.7	420.7	417.6	411.4	408.3	405.2	402.1	395.9	383.5	377.3	368.1
67.5°	361.9	358.8	358.8	352.6	346.4	343.3	343.3	337.1	327.8	318.6	312.4
70°	303.1	306.2	303.1	300.0	293.8	293.8	287.6	284.5	272.2	269.1	259.8
72.5°	250.6	250.6	247.5	247.5	241.3	238.2	238.2	232.0	225.9	219.7	213.5
75°	201.1	201.1	201.1	198.0	194.9	188.7	188.7	185.6	179.5	173.3	167.1
77.5°	157.8	154.7	154.7	151.6	148.5	145.4	145.4	142.3	136.1	133.0	126.9
80°	114.5	111.4	111.4	111.4	105.2	108.3	105.2	102.1	99.0	95.9	92.8
82.5°	74.3	77.4	77.4	74.3	71.2	71.2	71.2	68.1	68.1	65.0	61.9
85°	43.3	43.3	43.3	43.3	40.2	40.2	40.2	37.1	37.1	37.1	34.0
87.5°	18.6	18.6	18.6	18.6	18.6	18.6	15.5	15.5	15.5	15.5	15.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584522

CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8
2.5°	2304.6	2298.4	2295.3	2292.2	2292.2	2289.1	2286.0	2279.8	2279.8	2273.6	2270.5
5°	2316.9	2307.6	2301.5	2295.3	2292.2	2286.0	2279.8	2270.5	2267.4	2258.1	2248.9
7.5°	2320.0	2304.6	2298.4	2286.0	2279.8	2273.6	2261.2	2252.0	2239.6	2230.3	2217.9
10°	2307.6	2295.3	2279.8	2264.3	2261.2	2252.0	2233.4	2221.0	2205.5	2193.2	2174.6
12.5°	2289.1	2270.5	2255.0	2236.5	2227.2	2217.9	2199.4	2180.8	2159.1	2137.5	2118.9
15°	2258.1	2236.5	2214.8	2193.2	2180.8	2171.5	2149.9	2128.2	2106.5	2078.7	2060.1
17.5°	2211.7	2187.0	2165.3	2137.5	2125.1	2115.8	2088.0	2063.2	2035.4	2007.5	1989.0
20°	2152.9	2122.0	2097.3	2066.3	2057.0	2041.6	2013.7	1985.9	1954.9	1924.0	1902.3
22.5°	2075.6	2044.7	2016.8	1985.9	1970.4	1954.9	1927.1	1893.1	1862.1	1837.4	1815.7
25°	1985.9	1958.0	1924.0	1896.1	1877.6	1859.0	1828.1	1800.4	1772.5	1735.4	1713.7
27.5°	1886.9	1852.8	1828.1	1791.1	1772.5	1760.1	1726.1	1689.0	1664.2	1630.2	1605.4
30°	1775.6	1744.7	1716.8	1679.7	1661.1	1648.7	1617.8	1583.8	1559.0	1525.0	1500.2
32.5°	1658.0	1624.0	1590.0	1565.2	1543.5	1531.2	1497.1	1475.5	1444.5	1416.7	1388.8
35°	1531.2	1497.1	1472.4	1438.4	1426.0	1413.6	1385.8	1357.9	1330.1	1305.3	1283.8
37.5°	1395.0	1370.3	1342.4	1317.7	1308.4	1296.0	1262.1	1237.4	1215.7	1191.0	1172.4
40°	1262.1	1240.5	1221.9	1197.1	1181.7	1172.4	1147.6	1126.0	1101.2	1085.8	1067.2
42.5°	1141.4	1116.7	1098.1	1079.6	1064.1	1054.8	1033.2	1017.7	999.1	983.7	962.0
45°	1014.6	1002.2	980.6	965.1	955.8	943.4	928.0	909.4	893.9	881.6	866.1
47.5°	903.2	890.8	875.4	856.8	850.6	841.3	825.9	813.5	801.1	788.7	773.4
50°	801.1	785.6	773.4	761.0	754.8	745.5	730.1	723.9	714.6	702.2	692.9
52.5°	708.4	696.0	683.7	668.2	665.1	658.9	649.6	637.2	628.0	621.8	615.6
55°	624.9	612.5	603.2	590.8	587.7	581.6	569.2	563.0	556.8	550.6	544.4
57.5°	550.6	538.2	525.9	519.7	513.5	507.3	504.2	494.9	488.7	485.6	479.5
60°	482.5	470.2	460.9	451.6	448.5	445.4	439.2	433.0	426.9	420.7	417.6
62.5°	417.6	405.2	399.0	392.8	386.6	386.6	380.4	374.3	368.1	365.0	358.8
65°	358.8	352.6	343.3	334.0	330.9	330.9	321.7	318.6	315.5	309.3	303.1
67.5°	303.1	296.9	287.6	284.5	281.4	278.3	275.2	269.1	262.9	259.8	253.7
70°	253.7	247.5	241.3	238.2	235.1	232.0	225.9	222.8	216.6	213.5	210.4
72.5°	204.2	201.1	194.9	191.8	188.7	185.6	182.5	179.5	173.3	170.2	167.1
75°	164.0	160.9	154.7	151.6	148.5	148.5	145.4	139.2	136.1	136.1	133.0
77.5°	123.8	120.7	117.6	114.5	111.4	111.4	108.3	105.2	102.1	102.1	99.0
80°	89.7	86.6	83.5	83.5	83.5	80.4	77.4	77.4	74.3	74.3	71.2
82.5°	58.8	58.8	55.7	55.7	55.7	52.6	52.6	49.5	49.5	49.5	49.5
85°	34.0	34.0	34.0	30.9	30.9	30.9	30.9	30.9	30.9	27.8	30.9
87.5°	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	12.4	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584522

CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8
2.5°	2267.4	2264.3	2258.1	2258.1	2252.0	2252.0	2248.9	2245.8	2242.7	2239.6	2236.5
5°	2245.8	2233.4	2227.2	2224.1	2217.9	2214.8	2205.5	2199.4	2196.3	2190.1	2183.9
7.5°	2205.5	2193.2	2180.8	2177.7	2174.6	2162.2	2152.9	2143.7	2137.5	2131.3	2125.1
10°	2159.1	2146.8	2131.3	2125.1	2118.9	2103.4	2091.1	2081.8	2069.4	2057.0	2053.9
12.5°	2103.4	2084.9	2066.3	2060.1	2050.8	2035.4	2023.0	2007.5	1998.2	1982.8	1979.7
15°	2038.5	2016.8	2001.3	1985.9	1979.7	1964.2	1942.6	1930.2	1911.6	1905.4	1890.0
17.5°	1961.1	1939.5	1917.8	1911.6	1902.3	1880.7	1859.0	1843.5	1825.0	1815.7	1806.5
20°	1880.7	1852.8	1831.2	1825.0	1812.6	1794.2	1772.5	1757.0	1741.6	1723.0	1713.7
22.5°	1788.0	1757.0	1738.5	1723.0	1719.9	1698.2	1673.5	1661.1	1648.7	1633.3	1620.9
25°	1685.9	1658.0	1636.4	1624.0	1617.8	1599.2	1580.7	1565.2	1546.6	1537.4	1521.9
27.5°	1580.7	1562.1	1534.3	1521.9	1512.6	1497.1	1475.5	1466.2	1447.6	1435.3	1426.0
30°	1478.6	1450.7	1435.3	1419.8	1410.5	1395.0	1376.5	1367.2	1351.7	1339.3	1330.1
32.5°	1367.2	1348.6	1327.0	1320.8	1308.4	1293.1	1280.7	1265.2	1252.8	1240.5	1237.4
35°	1265.2	1240.5	1218.8	1212.6	1203.3	1187.9	1181.7	1172.4	1156.9	1153.8	1141.4
37.5°	1153.8	1141.4	1116.7	1107.4	1104.3	1091.9	1079.6	1073.4	1064.1	1054.8	1051.7
40°	1048.6	1033.2	1020.8	1011.5	1005.3	996.0	983.7	980.6	974.4	962.0	958.9
42.5°	949.6	934.2	921.8	918.7	909.4	900.1	893.9	884.6	881.6	878.5	872.3
45°	853.7	844.4	832.0	829.0	825.9	813.5	807.3	801.1	794.9	791.8	785.6
47.5°	767.2	757.9	748.6	745.5	739.3	736.3	727.0	723.9	714.6	711.5	708.4
50°	683.7	677.5	671.3	668.2	662.0	658.9	652.7	646.5	640.3	637.2	634.2
52.5°	609.4	603.2	597.0	593.9	590.8	584.6	578.5	572.3	569.2	566.1	563.0
55°	538.2	532.0	529.0	525.9	522.8	519.7	510.4	507.3	504.2	501.1	494.9
57.5°	473.3	467.1	460.9	460.9	457.8	454.7	448.5	442.3	442.3	436.1	429.9
60°	414.5	408.3	402.1	399.0	395.9	389.7	386.6	383.5	380.4	377.3	371.2
62.5°	352.6	349.5	343.3	343.3	337.1	334.0	330.9	327.8	324.8	318.6	315.5
65°	300.0	296.9	290.7	287.6	287.6	284.5	278.3	275.2	272.2	272.2	269.1
67.5°	250.6	247.5	241.3	238.2	238.2	235.1	232.0	232.0	229.0	225.9	229.0
70°	207.3	201.1	201.1	198.0	198.0	194.9	191.8	191.8	191.8	194.9	194.9
72.5°	164.0	160.9	157.8	157.8	157.8	157.8	154.7	154.7	157.8	160.9	160.9
75°	129.9	126.9	126.9	126.9	123.8	123.8	126.9	126.9	129.9	129.9	129.9
77.5°	95.9	95.9	95.9	95.9	95.9	95.9	99.0	99.0	102.1	102.1	102.1
80°	71.2	71.2	71.2	71.2	71.2	74.3	74.3	74.3	74.3	74.3	77.4
82.5°	49.5	49.5	49.5	49.5	49.5	49.5	49.5	52.6	52.6	52.6	52.6
85°	27.8	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9
87.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584522

CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8	2279.8
2.5°	2233.4	2233.4	2233.4	2236.5	2230.3	2230.3	2230.3	2230.3
5°	2180.8	2177.7	2174.6	2177.7	2171.5	2171.5	2168.4	2168.4
7.5°	2115.8	2112.7	2109.6	2109.6	2103.4	2103.4	2100.4	2097.3
10°	2044.7	2038.5	2041.6	2035.4	2032.3	2029.2	2026.1	2023.0
12.5°	1967.3	1961.1	1958.0	1951.8	1945.6	1942.6	1945.6	1939.5
15°	1883.8	1874.5	1871.4	1865.2	1859.0	1855.9	1855.9	1852.8
17.5°	1791.1	1784.9	1781.8	1775.6	1772.5	1766.3	1763.2	1760.1
20°	1704.4	1689.0	1692.1	1685.9	1682.8	1670.4	1670.4	1673.5
22.5°	1608.5	1599.2	1593.1	1586.9	1583.8	1577.6	1577.6	1574.5
25°	1512.6	1503.3	1500.2	1494.0	1491.0	1484.8	1481.7	1481.7
27.5°	1419.8	1407.4	1407.4	1401.2	1395.0	1391.9	1388.8	1385.8
30°	1320.8	1311.5	1308.4	1308.4	1305.3	1305.3	1296.0	1299.1
32.5°	1228.1	1221.9	1218.8	1212.6	1212.6	1209.5	1209.5	1200.2
35°	1135.3	1126.0	1129.1	1122.9	1119.8	1116.7	1119.8	1116.7
37.5°	1045.5	1039.3	1039.3	1033.2	1033.2	1030.1	1027.0	1033.2
40°	955.8	952.7	949.6	946.5	949.6	946.5	940.3	943.4
42.5°	866.1	866.1	863.0	863.0	859.9	859.9	859.9	859.9
45°	785.6	782.5	782.5	779.4	779.4	779.4	779.4	776.5
47.5°	705.3	702.2	702.2	702.2	699.1	699.1	696.0	699.1
50°	628.0	628.0	624.9	624.9	628.0	624.9	621.8	621.8
52.5°	556.8	556.8	553.7	553.7	550.6	547.5	550.6	550.6
55°	491.8	488.7	485.6	485.6	482.5	479.5	479.5	482.5
57.5°	429.9	426.9	423.8	423.8	417.6	414.5	414.5	414.5
60°	371.2	365.0	365.0	361.9	361.9	358.8	358.8	358.8
62.5°	315.5	312.4	312.4	312.4	312.4	309.3	309.3	309.3
65°	269.1	269.1	269.1	272.2	272.2	275.2	275.2	275.2
67.5°	232.0	235.1	235.1	235.1	238.2	238.2	238.2	235.1
70°	198.0	198.0	198.0	201.1	201.1	201.1	201.1	201.1
72.5°	164.0	164.0	164.0	164.0	164.0	164.0	164.0	164.0
75°	129.9	133.0	133.0	133.0	129.9	133.0	133.0	129.9
77.5°	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1
80°	77.4	77.4	77.4	77.4	77.4	77.4	77.4	77.4
82.5°	52.6	52.6	52.6	52.6	52.6	52.6	52.6	52.6
85°	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9
87.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)