

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593683

Luminaire Tested: **HCC8W30D010SL-HM82555950-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010SL-HM82555950-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2953.9 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593683
CATALOG NUMBER: HCC8W30D010SL-HM82555950-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593683

CATALOG NUMBER: HCC8W30D010SL-HM82555950-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			67
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			59
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			47
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			43
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			39
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			35
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	48900	48900	48900
5°	50923	48796	46741
10°	52626	48170	44460
15°	53958	47069	42153
20°	54063	45115	40058
25°	53149	42261	37988
30°	50305	38996	36212
35°	45866	35069	34000
40°	39884	30915	31394
45°	34216	26776	28734
50°	29225	23085	25814
55°	25612	19881	22429
60°	22807	16960	18859
65°	20240	13834	15045
70°	17960	10260	8547
75°	14976	5373	2538
80°	11774	1687	426
85°	8385	849	0



TEST NUMBER: P593683
 CATALOG NUMBER: HCC8W30D010SL-HM82555950-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.4	5.1
10°-20°	418.8	14.2
20°-30°	592.8	20.1
30°-40°	620.2	21.0
40°-50°	517.3	17.5
50°-60°	366.8	12.4
60°-70°	211.3	7.2
70°-80°	68.0	2.3
80°-90°	9.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1161.0	39.3
0°-40°	1781.2	60.3
0°-60°	2665.3	90.2
0°-90°	2953.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2953.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1586	1586	1586	1586	1586	
5°	1645	1624	1576	1529	1510	158
15°	1690	1621	1474	1358	1320	475
25°	1562	1446	1242	1142	1116	713
35°	1218	1112	932	882	903	755
45°	785	721	614	621	659	608
55°	476	427	370	389	417	430
65°	277	232	190	190	206	277
75°	126	92	45	21	21	136
85°	24	12	2	0	0	30
90°	0	0	0	0	0	



TEST NUMBER: P593683

CATALOG NUMBER: HCC8W30D010SL-HM82555950-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8
2.5°	1619.1	1616.7	1614.3	1616.7	1614.3	1616.7	1614.3	1614.3	1611.9	1609.5	1609.5
5°	1645.1	1642.7	1642.7	1642.7	1640.3	1638.0	1638.0	1635.6	1630.8	1628.5	1623.7
7.5°	1661.6	1664.0	1664.0	1664.0	1659.4	1659.4	1654.6	1649.9	1645.1	1640.3	1633.2
10°	1680.7	1680.7	1678.3	1675.9	1671.1	1668.8	1666.4	1661.6	1654.6	1645.1	1638.0
12.5°	1687.8	1687.8	1685.4	1680.7	1678.3	1675.9	1673.5	1666.4	1657.0	1645.1	1635.6
15°	1690.2	1685.4	1683.0	1680.7	1675.9	1668.8	1668.8	1659.4	1647.5	1633.2	1621.4
17.5°	1671.1	1673.5	1668.8	1664.0	1657.0	1652.2	1645.1	1638.0	1623.7	1607.2	1595.3
20°	1647.5	1645.1	1642.7	1635.6	1626.1	1623.7	1616.7	1604.8	1592.9	1574.0	1557.4
22.5°	1609.5	1607.2	1602.4	1597.7	1588.1	1583.5	1576.4	1562.1	1545.6	1526.6	1507.7
25°	1562.1	1557.4	1550.2	1540.8	1533.7	1528.9	1519.4	1505.3	1486.2	1465.0	1445.9
27.5°	1486.2	1493.4	1488.6	1474.4	1467.3	1457.8	1455.5	1436.4	1419.9	1398.6	1377.2
30°	1412.8	1412.8	1405.6	1398.6	1386.7	1379.6	1370.1	1355.9	1339.3	1313.3	1296.6
32.5°	1320.4	1318.0	1308.5	1306.1	1296.6	1282.5	1280.1	1261.1	1244.5	1225.5	1204.2
35°	1218.4	1213.6	1204.2	1197.1	1192.3	1185.2	1178.1	1161.5	1144.9	1126.0	1111.7
37.5°	1102.2	1102.2	1099.9	1088.1	1083.3	1078.5	1071.4	1054.9	1045.4	1026.3	1012.2
40°	990.8	988.4	981.4	979.0	974.3	967.1	962.4	952.9	938.7	924.4	910.3
42.5°	881.8	884.1	874.7	877.0	867.6	862.9	860.5	846.2	839.2	824.9	813.0
45°	784.6	782.2	777.5	775.1	770.4	765.6	761.0	753.8	741.9	727.7	720.7
47.5°	694.5	687.5	687.5	685.1	682.7	673.2	670.8	663.7	656.6	642.4	632.9
50°	609.2	609.2	609.2	606.9	599.7	597.4	592.6	585.5	578.3	568.9	554.7
52.5°	540.5	540.5	540.5	538.1	528.6	526.3	523.9	514.4	504.8	497.8	488.3
55°	476.4	478.8	476.4	471.7	464.7	464.7	457.5	452.8	443.3	436.1	426.7
57.5°	422.0	422.0	417.2	414.8	410.1	407.7	403.0	398.2	386.4	379.3	367.4
60°	369.8	367.4	367.4	362.6	357.9	353.3	350.9	343.7	339.0	327.1	317.6
62.5°	322.3	322.3	317.6	317.6	308.2	308.2	305.8	298.7	291.5	279.8	275.0
65°	277.4	277.4	275.0	272.6	265.5	263.1	260.7	253.6	246.5	239.5	232.3
67.5°	237.1	237.1	232.3	230.0	225.2	222.8	218.1	213.3	206.2	199.2	192.0
70°	199.2	196.8	194.4	192.0	187.3	184.9	180.1	175.4	168.2	163.6	156.5
72.5°	161.2	161.2	158.9	154.1	151.7	149.3	147.0	142.2	135.1	128.1	123.3
75°	125.7	125.7	125.7	120.9	116.2	113.8	113.8	109.0	104.3	97.1	92.5
77.5°	97.1	94.8	92.5	92.5	87.7	85.4	83.0	80.6	73.5	71.1	66.3
80°	66.3	68.7	66.3	64.0	61.6	59.2	59.2	54.6	52.2	47.4	42.7
82.5°	45.1	42.7	42.7	40.3	40.3	37.9	37.9	33.2	30.8	28.4	26.0
85°	23.7	23.7	21.3	21.3	21.3	18.9	18.9	16.6	16.6	14.3	11.9
87.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	4.8	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593683

CATALOG NUMBER: HCC8W30D010SL-HM82555950-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8
2.5°	1607.2	1602.4	1600.0	1600.0	1597.7	1595.3	1592.9	1590.5	1585.8	1585.8	1581.1
5°	1619.1	1614.3	1611.9	1604.8	1600.0	1600.0	1590.5	1588.1	1581.1	1576.4	1571.6
7.5°	1628.5	1619.1	1611.9	1604.8	1600.0	1595.3	1585.8	1576.4	1566.9	1557.4	1552.6
10°	1628.5	1619.1	1607.2	1595.3	1590.5	1585.8	1574.0	1559.7	1548.0	1538.4	1526.6
12.5°	1623.7	1609.5	1595.3	1585.8	1576.4	1569.2	1555.0	1540.8	1526.6	1507.7	1498.1
15°	1609.5	1590.5	1576.4	1559.7	1552.6	1540.8	1528.9	1507.7	1491.0	1474.4	1462.6
17.5°	1581.1	1557.4	1540.8	1524.2	1512.3	1505.3	1486.2	1467.3	1448.3	1429.4	1415.1
20°	1538.4	1517.0	1498.1	1476.7	1467.3	1457.8	1434.2	1415.1	1396.2	1374.8	1360.7
22.5°	1486.2	1465.0	1438.8	1422.3	1408.0	1396.2	1374.8	1353.6	1334.5	1315.6	1296.6
25°	1422.3	1400.9	1377.2	1351.2	1341.7	1329.8	1306.1	1284.8	1263.4	1242.1	1225.5
27.5°	1353.6	1325.0	1306.1	1277.7	1268.2	1256.3	1230.3	1206.6	1187.6	1171.0	1152.0
30°	1270.6	1249.3	1223.1	1197.1	1187.6	1175.7	1154.4	1133.1	1114.1	1095.2	1076.2
32.5°	1180.4	1159.2	1133.1	1114.1	1099.9	1090.4	1069.0	1050.1	1031.1	1012.2	995.5
35°	1085.7	1062.0	1043.0	1024.1	1012.2	1000.3	979.0	962.4	948.2	931.6	914.9
37.5°	988.4	971.9	952.9	931.6	919.7	910.3	893.7	874.7	862.9	848.6	836.8
40°	893.7	874.7	858.1	839.2	829.7	822.6	805.9	791.8	779.9	768.0	761.0
42.5°	796.5	779.9	763.3	751.4	744.3	737.2	725.4	708.8	701.6	689.9	682.7
45°	706.4	692.1	680.3	663.7	658.9	654.2	640.0	628.1	621.0	614.0	609.2
47.5°	621.0	611.6	597.4	587.8	580.7	576.1	566.6	557.0	549.9	545.2	540.5
50°	547.5	535.8	526.3	516.7	512.0	504.8	495.5	490.7	485.9	481.2	481.2
52.5°	478.8	466.9	457.5	450.4	445.6	440.9	433.7	431.4	426.7	426.7	424.4
55°	414.8	407.7	398.2	388.8	386.4	384.0	379.3	374.5	372.2	369.8	372.2
57.5°	360.3	353.3	343.7	336.6	334.2	331.8	329.5	324.7	322.3	322.3	322.3
60°	310.6	303.4	296.3	289.2	289.2	284.4	282.0	279.8	277.4	275.0	275.0
62.5°	265.5	258.4	251.2	246.5	244.1	241.8	237.1	234.7	232.3	232.3	230.0
65°	225.2	215.7	213.3	206.2	203.9	201.5	199.2	194.4	192.0	189.6	187.3
67.5°	184.9	180.1	173.0	168.2	166.0	163.6	161.2	156.5	154.1	151.7	147.0
70°	149.3	144.6	139.8	135.1	132.7	130.4	125.7	120.9	118.5	113.8	106.7
72.5°	116.2	111.4	106.7	101.9	99.5	97.1	92.5	87.7	83.0	78.2	73.5
75°	87.7	83.0	75.9	71.1	68.7	68.7	61.6	56.8	52.2	45.1	40.3
77.5°	61.6	54.6	52.2	47.4	45.1	40.3	35.6	30.8	26.0	23.7	18.9
80°	40.3	35.6	30.8	28.4	26.0	23.7	21.3	16.6	11.9	9.5	7.1
82.5°	23.7	21.3	18.9	16.6	14.3	11.9	9.5	9.5	7.1	4.8	2.4
85°	11.9	9.5	7.1	7.1	4.8	4.8	4.8	2.4	2.4	2.4	2.4
87.5°	4.8	2.4	2.4	2.4	2.4	2.4	2.4	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P593683

CATALOG NUMBER: HCC8W30D010SL-HM82555950-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8
2.5°	1578.8	1576.4	1574.0	1571.6	1571.6	1566.9	1566.9	1564.5	1559.7	1557.4	1557.4
5°	1564.5	1557.4	1552.6	1550.2	1548.0	1540.8	1538.4	1533.7	1528.9	1524.2	1521.8
7.5°	1543.2	1531.3	1526.6	1524.2	1517.0	1510.0	1505.3	1498.1	1491.0	1483.9	1481.5
10°	1517.0	1505.3	1493.4	1488.6	1481.5	1476.7	1467.3	1457.8	1450.7	1443.6	1436.4
12.5°	1483.9	1469.7	1457.8	1453.1	1445.9	1436.4	1422.3	1417.5	1405.6	1400.9	1391.5
15°	1445.9	1429.4	1417.5	1410.4	1403.3	1389.1	1379.6	1370.1	1358.3	1353.6	1344.0
17.5°	1398.6	1379.6	1367.7	1360.7	1355.9	1344.0	1329.8	1318.0	1306.1	1301.4	1294.2
20°	1341.7	1329.8	1313.3	1306.1	1301.4	1287.1	1272.9	1268.2	1258.7	1249.3	1242.1
22.5°	1277.7	1265.8	1249.3	1242.1	1239.8	1227.9	1216.0	1209.0	1201.8	1194.7	1187.6
25°	1211.4	1197.1	1182.8	1178.1	1173.4	1163.9	1154.4	1149.6	1142.5	1137.8	1133.1
27.5°	1140.1	1126.0	1114.1	1107.0	1102.2	1095.2	1090.4	1085.7	1080.9	1076.2	1073.8
30°	1064.3	1050.1	1040.6	1035.9	1031.1	1028.7	1021.7	1019.3	1017.0	1012.2	1014.6
32.5°	988.4	976.6	967.1	960.0	960.0	955.2	952.9	952.9	950.6	950.6	950.6
35°	905.5	898.4	891.3	888.9	886.5	884.1	881.8	884.1	881.8	884.1	886.5
37.5°	829.7	822.6	817.8	815.4	813.0	815.4	813.0	813.0	815.4	820.2	822.6
40°	751.4	746.7	741.9	744.3	741.9	741.9	741.9	749.1	751.4	753.8	756.2
42.5°	678.0	673.2	670.8	670.8	673.2	670.8	675.6	678.0	682.7	689.9	694.5
45°	606.9	604.5	604.5	606.9	604.5	609.2	609.2	614.0	621.0	625.8	630.5
47.5°	540.5	540.5	540.5	542.8	542.8	545.2	549.9	552.3	557.0	561.8	566.6
50°	478.8	481.2	483.6	483.6	483.6	488.3	493.1	495.5	497.8	500.2	507.2
52.5°	424.4	426.7	426.7	429.0	431.4	433.7	436.1	440.9	443.3	448.0	450.4
55°	372.2	372.2	376.9	379.3	379.3	379.3	384.0	384.0	388.8	391.2	395.8
57.5°	322.3	324.7	324.7	327.1	327.1	329.5	331.8	334.2	336.6	339.0	341.4
60°	275.0	275.0	275.0	277.4	279.8	282.0	279.8	284.4	284.4	289.2	291.5
62.5°	230.0	232.3	232.3	232.3	232.3	232.3	232.3	234.7	237.1	239.5	241.8
65°	187.3	187.3	187.3	184.9	187.3	184.9	187.3	189.6	189.6	192.0	194.4
67.5°	144.6	144.6	139.8	139.8	142.2	142.2	142.2	142.2	139.8	144.6	144.6
70°	104.3	101.9	99.5	97.1	97.1	94.8	94.8	92.5	92.5	92.5	92.5
72.5°	68.7	64.0	59.2	56.8	54.6	54.6	49.8	47.4	49.8	49.8	49.8
75°	35.6	30.8	28.4	26.0	23.7	23.7	21.3	21.3	21.3	21.3	21.3
77.5°	14.3	11.9	9.5	9.5	7.1	7.1	7.1	7.1	7.1	7.1	7.1
80°	4.8	4.8	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
85°	2.4	0.0	0.0	2.4	0.0	2.4	2.4	2.4	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593683

CATALOG NUMBER: HCC8W30D010SL-HM82555950-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8	1585.8
2.5°	1555.0	1555.0	1552.6	1555.0	1550.2	1552.6	1550.2	1550.2
5°	1519.4	1514.7	1514.7	1514.7	1512.3	1512.3	1510.0	1510.0
7.5°	1476.7	1474.4	1472.1	1469.7	1467.3	1465.0	1465.0	1465.0
10°	1434.2	1429.4	1429.4	1427.0	1422.3	1419.9	1419.9	1419.9
12.5°	1384.4	1382.0	1379.6	1379.6	1370.1	1372.5	1370.1	1370.1
15°	1336.9	1334.5	1334.5	1327.4	1322.8	1322.8	1322.8	1320.4
17.5°	1287.1	1284.8	1282.5	1277.7	1272.9	1272.9	1270.6	1272.9
20°	1235.0	1232.6	1227.9	1227.9	1225.5	1223.1	1218.4	1220.7
22.5°	1182.8	1178.1	1175.7	1175.7	1173.4	1173.4	1168.7	1168.7
25°	1128.4	1126.0	1123.6	1126.0	1121.2	1121.2	1116.5	1116.5
27.5°	1071.4	1069.0	1069.0	1069.0	1066.7	1069.0	1066.7	1066.7
30°	1014.6	1014.6	1012.2	1012.2	1014.6	1012.2	1014.6	1017.0
32.5°	952.9	952.9	955.2	955.2	957.6	957.6	957.6	957.6
35°	888.9	893.7	893.7	896.0	898.4	900.8	900.8	903.2
37.5°	829.7	832.1	834.4	836.8	841.5	841.5	841.5	841.5
40°	765.6	768.0	772.7	770.4	779.9	782.2	779.9	779.9
42.5°	699.3	704.0	706.4	711.1	713.5	718.3	720.7	720.7
45°	637.7	640.0	644.8	649.6	651.9	658.9	658.9	658.9
47.5°	573.7	578.3	580.7	585.5	587.8	595.0	597.4	595.0
50°	512.0	516.7	521.5	521.5	528.6	531.0	535.8	538.1
52.5°	452.8	455.1	459.9	462.3	466.9	471.7	474.1	476.4
55°	395.8	398.2	403.0	403.0	410.1	412.5	417.2	417.2
57.5°	343.7	346.1	350.9	348.5	353.3	357.9	357.9	355.5
60°	293.9	293.9	293.9	298.7	301.1	303.4	305.8	305.8
62.5°	241.8	246.5	248.9	248.9	251.2	253.6	253.6	251.2
65°	194.4	199.2	201.5	201.5	203.9	203.9	203.9	206.2
67.5°	147.0	147.0	147.0	149.3	147.0	147.0	147.0	147.0
70°	92.5	92.5	92.5	92.5	90.1	92.5	92.5	94.8
72.5°	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8
75°	21.3	21.3	21.3	23.7	21.3	21.3	21.3	21.3
77.5°	9.5	7.1	9.5	9.5	7.1	7.1	7.1	7.1
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
85°	0.0	2.4	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)