

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584527

Luminaire Tested: **HCC8W40D010BZ-HM82555830-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010BZ-HM82555830-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4486.1 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584527
CATALOG NUMBER: HCC8W40D010BZ-HM82555830-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584527
 CATALOG NUMBER: HCC8W40D010BZ-HM82555830-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103		102	101	100		99	98	97	96
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		95	92	90		92	90	89	87
4	102	96	91	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	83	97	91	86	83	89	85	82		87	84	82		86	83	81	80
6	95	88	83	79	93	87	82	79	86	82	79		84	81	78		83	80	78	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		77	74	72	71
9	85	78	73	70	84	77	73	70	76	72	70		76	72	69		75	72	69	68
10	83	75	70	67	82	75	70	67	74	70	67		73	69	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	844391
5°	541610
10°	244666
15°	147623
20°	112497
25°	90844
30°	66570
35°	24104
40°	8997
45°	4086
50°	1300
55°	328
60°	185
65°	219
70°	0
75°	0
80°	533
85°	1061



TEST NUMBER: P584527
 CATALOG NUMBER: HCC8W40D010BZ-HM82555830-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1334.5	29.7
10°-20°	1355.4	30.2
20°-30°	1213.4	27.0
30°-40°	488.8	10.9
40°-50°	80.2	1.8
50°-60°	7.3	0.2
60°-70°	2.6	0.1
70°-80°	2.0	0.0
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3903.3	87.0
0°-40°	4392.0	97.9
0°-60°	4479.4	99.9
0°-90°	4486.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4486.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27383	
5°	17497	###
15°	4624	1355
25°	2670	1213
35°	640	489
45°	94	80
55°	6	7
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584527
CATALOG NUMBER: HCC8W40D010BZ-HM82555830-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	27383.0
0.5°	27298.4
1°	26945.1
1.5°	26377.2
2°	25516.3
2.5°	24498.5
3°	23223.9
3.5°	21825.4
4°	20442.1
4.5°	18892.6
5°	17497.2
5.5°	15977.9
6°	14745.6
6.5°	13461.9
7°	12453.1
7.5°	11386.9
8°	10529.1
8.5°	9668.3
9°	9022.0
9.5°	8309.2
10°	7813.8
12.5°	5762.9
15°	4624.2
17.5°	3950.7
20°	3428.2
22.5°	3011.3
25°	2670.0
27.5°	2328.7
30°	1869.6
32.5°	1202.1
35°	640.3
37.5°	353.4
40°	223.5
42.5°	148.0
45°	93.7
47.5°	57.4
50°	27.1
52.5°	9.0
55°	6.1
57.5°	3.0
60°	3.0
62.5°	3.0
65°	3.0



TEST NUMBER: P584527
CATALOG NUMBER: HCC8W40D010BZ-HM82555830-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.0
80°	3.0
82.5°	3.0
85°	3.0
87.5°	3.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.0
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)