

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584526

Luminaire Tested: **HCC8W40D010MW-HM82555830-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584526  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W40D010MW-HM82555830-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4474.0 lumens  
Efficiency: N/A  
Efficacy: 109.1 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584526  
CATALOG NUMBER: HCC8W40D010MW-HM82555830-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584526

CATALOG NUMBER: HCC8W40D010MW-HM82555830-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90				
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80				
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72				
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65				
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59				
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54				
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50				
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114406
5°	111286
10°	104723
15°	99150
20°	95371
25°	91692
30°	81436
35°	51862
40°	28943
45°	24238
50°	21885
55°	20628
60°	18816
65°	16972
70°	14975
75°	13308
80°	11809
85°	10685



TEST NUMBER: P584526  
 CATALOG NUMBER: HCC8W40D010MW-HM82555830-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	335.2	7.5
10°-20°	875.9	19.6
20°-30°	1221.9	27.3
30°-40°	879.3	19.7
40°-50°	435.7	9.7
50°-60°	340.9	7.6
60°-70°	230.8	5.2
70°-80°	119.8	2.7
80°-90°	34.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2433.0	54.4
0°-40°	3312.3	74.0
0°-60°	4088.9	91.4
0°-90°	4474.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4474.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3710	
5°	3595	335
15°	3106	876
25°	2695	1222
35°	1378	879
45°	556	436
55°	384	341
65°	233	231
75°	112	120
85°	30	35
90°	0	



TEST NUMBER: P584526  
CATALOG NUMBER: HCC8W40D010MW-HM82555830-81MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3710.1
2.5°	3676.7
5°	3595.2
7.5°	3480.4
10°	3344.5
12.5°	3217.5
15°	3105.8
17.5°	3000.0
20°	2906.3
22.5°	2812.7
25°	2694.9
27.5°	2525.7
30°	2287.1
32.5°	1912.4
35°	1377.7
37.5°	939.6
40°	719.0
42.5°	619.4
45°	555.8
47.5°	501.5
50°	456.2
52.5°	417.0
55°	383.7
57.5°	344.4
60°	305.1
62.5°	265.8
65°	232.6
67.5°	199.4
70°	166.1
72.5°	139.0
75°	111.7
77.5°	87.6
80°	66.5
82.5°	48.3
85°	30.2
87.5°	15.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)