

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584383

Luminaire Tested: **HCC8S35D010BZ-HM82555827-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584383  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S35D010BZ-HM82555827-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4101.2 lumens  
Efficiency: N/A  
Efficacy: 121.7 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584383  
CATALOG NUMBER: HCC8S35D010BZ-HM82555827-81WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584383

CATALOG NUMBER: HCC8S35D010BZ-HM82555827-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	81994
5°	81895
10°	81086
15°	80114
20°	79374
25°	78480
30°	74051
35°	60298
40°	33314
45°	22236
50°	19726
55°	18515
60°	18280
65°	18110
70°	16364
75°	14631
80°	12803
85°	11322



TEST NUMBER: P584383  
 CATALOG NUMBER: HCC8S35D010BZ-HM82555827-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	250.7	6.1
10°-20°	708.6	17.3
20°-30°	1052.9	25.7
30°-40°	948.2	23.1
40°-50°	420.3	10.2
50°-60°	311.3	7.6
60°-70°	242.0	5.9
70°-80°	131.2	3.2
80°-90°	35.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2012.2	49.1
0°-40°	2960.4	72.2
0°-60°	3692.0	90.0
0°-90°	4101.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4101.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2659	
5°	2646	251
15°	2510	709
25°	2307	1053
35°	1602	948
45°	510	420
55°	344	311
65°	248	242
75°	123	131
85°	32	36
90°	0	



TEST NUMBER: P584383  
CATALOG NUMBER: HCC8S35D010BZ-HM82555827-81WDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2659.0
2.5°	2653.7
5°	2645.7
7.5°	2624.3
10°	2589.6
12.5°	2549.6
15°	2509.5
17.5°	2469.4
20°	2418.8
22.5°	2368.0
25°	2306.6
27.5°	2213.2
30°	2079.7
32.5°	1887.4
35°	1601.8
37.5°	1196.0
40°	827.6
42.5°	611.3
45°	509.9
47.5°	451.2
50°	411.2
52.5°	373.8
55°	344.4
57.5°	320.3
60°	296.4
62.5°	274.9
65°	248.2
67.5°	216.2
70°	181.5
72.5°	152.1
75°	122.8
77.5°	96.1
80°	72.1
82.5°	50.7
85°	32.0
87.5°	13.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)