

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584567

Luminaire Tested: **HCC8S40D010BZ-HM82555840-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584567  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S40D010BZ-HM82555840-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5195.5 lumens  
Efficiency: N/A  
Efficacy: 126.7 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584567  
CATALOG NUMBER: HCC8S40D010BZ-HM82555840-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P584567  
 CATALOG NUMBER: HCC8S40D010BZ-HM82555840-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68				
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62				
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56				
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47				
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	97344
5°	96533
10°	95264
15°	96350
20°	104044
25°	113780
30°	112403
35°	93241
40°	54882
45°	35855
50°	27791
55°	18462
60°	8986
65°	2787
70°	938
75°	822
80°	622
85°	1238



TEST NUMBER: P584567  
 CATALOG NUMBER: HCC8S40D010BZ-HM82555840-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	295.3	5.7
10°-20°	867.1	16.7
20°-30°	1516.0	29.2
30°-40°	1474.7	28.4
40°-50°	670.6	12.9
50°-60°	310.9	6.0
60°-70°	52.1	1.0
70°-80°	6.4	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2678.4	51.6
0°-40°	4153.0	79.9
0°-60°	5134.6	98.8
0°-90°	5195.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5195.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3157	
5°	3119	295
15°	3018	867
25°	3344	1516
35°	2477	1475
45°	822	671
55°	343	311
65°	38	52
75°	7	6
85°	4	2
90°	0	



TEST NUMBER: P584567  
CATALOG NUMBER: HCC8S40D010BZ-HM82555840-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3156.8
2.5°	3149.9
5°	3118.6
7.5°	3084.0
10°	3042.4
12.5°	3011.2
15°	3018.1
17.5°	3073.5
20°	3170.6
22.5°	3281.7
25°	3344.1
27.5°	3309.5
30°	3156.8
32.5°	2889.7
35°	2476.9
37.5°	1907.9
40°	1363.4
42.5°	1016.4
45°	822.2
47.5°	693.8
50°	579.3
52.5°	461.4
55°	343.4
57.5°	235.9
60°	145.7
62.5°	79.7
65°	38.2
67.5°	17.4
70°	10.4
72.5°	6.9
75°	6.9
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)