

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584408

Luminaire Tested: **HCC8S35D010SL-HM82555835-81NDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584408  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S35D010SL-HM82555835-81NDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4104.5 lumens  
Efficiency: N/A  
Efficacy: 121.8 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584408  
CATALOG NUMBER: HCC8S35D010SL-HM82555835-81NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584408

CATALOG NUMBER: HCC8S35D010SL-HM82555835-81NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96					96			
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91					91			
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87					87			
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83					83			
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80					80			
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76					76			
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73					73			
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71					71			
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68					68			
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66					66			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	772521
5°	495513
10°	223840
15°	135058
20°	102922
25°	83114
30°	60905
35°	22052
40°	8232
45°	3737
50°	1195
55°	296
60°	173
65°	204
70°	0
75°	0
80°	497
85°	991



TEST NUMBER: P584408  
 CATALOG NUMBER: HCC8S35D010SL-HM82555835-81NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1220.9	29.7
10°-20°	1240.1	30.2
20°-30°	1110.1	27.0
30°-40°	447.2	10.9
40°-50°	73.3	1.8
50°-60°	6.7	0.2
60°-70°	2.4	0.1
70°-80°	1.9	0.0
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3571.1	87.0
0°-40°	4018.2	97.9
0°-60°	4098.2	99.8
0°-90°	4105.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4104.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	25052	
5°	16008	###
15°	4231	1240
25°	2443	1110
35°	586	447
45°	86	73
55°	6	7
65°	3	2
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584408  
CATALOG NUMBER: HCC8S35D010SL-HM82555835-81NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	25052.3
0.5°	24974.9
1°	24651.7
1.5°	24132.2
2°	23344.6
2.5°	22413.4
3°	21247.2
3.5°	19967.8
4°	18702.2
4.5°	17284.6
5°	16008.0
5.5°	14618.0
6°	13490.6
6.5°	12316.2
7°	11393.2
7.5°	10417.8
8°	9633.0
8.5°	8845.4
9°	8254.1
9.5°	7601.9
10°	7148.7
12.5°	5272.4
15°	4230.6
17.5°	3614.5
20°	3136.4
22.5°	2755.0
25°	2442.8
27.5°	2130.5
30°	1710.5
32.5°	1099.8
35°	585.8
37.5°	323.3
40°	204.5
42.5°	135.4
45°	85.7
47.5°	52.5
50°	24.9
52.5°	8.3
55°	5.5
57.5°	2.8
60°	2.8
62.5°	2.8
65°	2.8



TEST NUMBER: P584408  
CATALOG NUMBER: HCC8S35D010SL-HM82555835-81NDC

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	2.8
80°	2.8
82.5°	2.8
85°	2.8
87.5°	2.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.8
70°		0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)