

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584420

Luminaire Tested: **HCC8S35D010MB-HM82555835-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MB-HM82555835-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3758.9 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584420
CATALOG NUMBER: HCC8S35D010MB-HM82555835-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P584420

CATALOG NUMBER: HCC8S35D010MB-HM82555835-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62804	62804	62804
5°	65013	62447	59967
10°	66457	61350	56590
15°	67405	59286	52847
20°	67196	56406	49062
25°	65534	52748	45041
30°	62091	48514	41329
35°	56489	43904	37558
40°	49613	39046	33930
45°	43265	34347	30247
50°	37649	30093	26649
55°	33574	26445	23182
60°	30509	23177	19772
65°	27420	20168	17942
70°	24424	17193	16193
75°	21398	14488	13832
80°	18166	11791	12271
85°	13692	8810	9800



TEST NUMBER: P584420
 CATALOG NUMBER: HCC8S35D010MB-HM82555835-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	5.1
10°-20°	525.6	14.0
20°-30°	729.6	19.4
30°-40°	754.4	20.1
40°-50°	631.6	16.8
50°-60°	458.5	12.2
60°-70°	289.4	7.7
70°-80°	143.3	3.8
80°-90°	35.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1446.0	38.5
0°-40°	2200.4	58.5
0°-60°	3290.6	87.5
0°-90°	3758.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3758.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2037	2037	2037	2037	2037	
5°	2100	2075	2017	1962	1937	201
15°	2111	2031	1857	1708	1655	594
25°	1926	1802	1550	1382	1324	883
35°	1501	1390	1166	1034	998	934
45°	992	920	788	710	694	767
55°	624	569	492	450	431	564
65°	376	329	276	243	246	375
75°	180	149	122	116	116	193
85°	39	30	25	28	28	47
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584420

CATALOG NUMBER: HCC8S35D010MB-HM82555835-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7
2.5°	2069.9	2069.9	2072.7	2069.9	2069.9	2069.9	2067.1	2067.1	2064.4	2064.4	2058.9
5°	2100.3	2094.8	2100.3	2094.8	2094.8	2094.8	2091.9	2086.4	2083.7	2078.2	2075.4
7.5°	2114.1	2111.4	2111.4	2108.6	2108.6	2105.8	2103.1	2100.3	2089.2	2086.4	2078.2
10°	2122.4	2119.6	2119.6	2116.9	2111.4	2111.4	2105.8	2103.1	2089.2	2083.7	2072.7
12.5°	2119.6	2119.6	2119.6	2116.9	2108.6	2105.8	2100.3	2091.9	2080.9	2069.9	2058.9
15°	2111.4	2111.4	2105.8	2103.1	2094.8	2089.2	2086.4	2072.7	2061.6	2047.7	2031.2
17.5°	2083.7	2083.7	2080.9	2075.4	2067.1	2061.6	2056.1	2042.2	2031.2	2009.0	1992.5
20°	2047.7	2045.0	2042.2	2034.0	2025.7	2022.9	2014.7	1995.3	1981.5	1964.8	1942.8
22.5°	1995.3	1992.5	1989.8	1984.2	1970.5	1964.8	1959.3	1945.6	1920.6	1904.1	1876.4
25°	1926.1	1926.1	1920.6	1912.4	1898.6	1893.1	1884.7	1870.9	1848.9	1824.0	1801.8
27.5°	1846.0	1843.2	1835.0	1829.5	1818.4	1810.2	1796.3	1779.7	1757.6	1738.3	1710.6
30°	1743.8	1743.8	1738.3	1730.0	1716.1	1710.6	1699.6	1680.2	1658.2	1633.2	1613.9
32.5°	1627.7	1627.7	1619.5	1613.9	1605.7	1591.8	1589.0	1567.0	1547.6	1528.3	1506.1
35°	1500.6	1503.4	1497.9	1486.8	1472.9	1472.9	1467.4	1448.1	1426.0	1406.7	1390.0
37.5°	1373.5	1365.2	1362.5	1356.9	1348.6	1337.6	1332.1	1323.8	1304.4	1290.6	1265.7
40°	1232.5	1235.3	1229.7	1224.2	1221.5	1213.2	1210.5	1196.6	1182.8	1166.3	1155.1
42.5°	1105.4	1105.4	1105.4	1099.9	1094.4	1086.1	1083.4	1075.0	1058.4	1047.4	1030.8
45°	992.1	983.8	983.8	981.0	978.3	972.8	964.5	959.0	947.9	939.6	920.3
47.5°	881.6	884.4	881.6	878.9	870.5	867.7	865.0	853.9	842.9	834.6	820.7
50°	784.8	790.3	784.8	784.8	779.3	776.5	771.0	762.8	754.5	740.6	726.8
52.5°	704.7	704.7	701.9	699.2	690.9	685.4	682.6	679.9	666.0	654.9	643.9
55°	624.5	627.3	627.3	619.0	616.3	610.7	608.0	599.7	594.2	577.6	569.3
57.5°	555.5	552.8	555.5	550.0	544.4	538.9	536.1	530.6	522.3	511.3	500.2
60°	494.7	489.1	489.1	486.4	480.9	478.1	472.6	464.2	456.0	444.9	436.7
62.5°	433.9	431.2	428.4	425.5	420.0	417.3	414.5	406.2	398.0	389.7	381.3
65°	375.8	375.8	373.1	367.5	364.8	362.0	359.3	353.8	342.6	337.1	328.9
67.5°	323.3	320.6	320.6	315.1	309.6	306.8	306.8	301.2	292.9	284.6	279.1
70°	270.9	273.6	270.9	268.1	262.5	262.5	257.0	254.2	243.2	240.4	232.2
72.5°	223.9	223.9	221.0	221.0	215.5	212.8	212.8	207.3	201.7	196.2	190.7
75°	179.6	179.6	179.6	176.8	174.1	168.6	168.6	165.8	160.3	154.8	149.3
77.5°	140.9	138.1	138.1	135.4	132.6	129.9	129.9	127.1	121.6	118.8	113.3
80°	102.3	99.4	99.4	99.4	93.9	96.7	93.9	91.2	88.4	85.7	82.9
82.5°	66.4	69.1	69.1	66.4	63.6	63.6	63.6	60.7	60.7	58.0	55.2
85°	38.7	38.7	38.7	38.7	35.9	35.9	35.9	33.2	33.2	33.2	30.4
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	13.8	13.8	13.8	13.8	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584420

CATALOG NUMBER: HCC8S35D010MB-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7
2.5°	2058.9	2053.4	2050.5	2047.7	2047.7	2045.0	2042.2	2036.7	2036.7	2031.2	2028.5
5°	2069.9	2061.6	2056.1	2050.5	2047.7	2042.2	2036.7	2028.5	2025.7	2017.4	2009.0
7.5°	2072.7	2058.9	2053.4	2042.2	2036.7	2031.2	2020.2	2011.9	2000.8	1992.5	1981.5
10°	2061.6	2050.5	2036.7	2022.9	2020.2	2011.9	1995.3	1984.2	1970.5	1959.3	1942.8
12.5°	2045.0	2028.5	2014.7	1998.0	1989.8	1981.5	1964.8	1948.3	1928.9	1909.6	1893.1
15°	2017.4	1998.0	1978.7	1959.3	1948.3	1940.0	1920.6	1901.3	1881.9	1857.1	1840.5
17.5°	1976.0	1953.8	1934.5	1909.6	1898.6	1890.3	1865.4	1843.2	1818.4	1793.5	1777.0
20°	1923.4	1895.8	1873.7	1846.0	1837.7	1824.0	1799.0	1774.2	1746.6	1718.9	1699.6
22.5°	1854.4	1826.7	1801.8	1774.2	1760.3	1746.6	1721.6	1691.3	1663.7	1641.5	1622.2
25°	1774.2	1749.3	1718.9	1694.1	1677.4	1660.9	1633.2	1608.4	1583.5	1550.3	1531.0
27.5°	1685.7	1655.4	1633.2	1600.0	1583.5	1572.5	1542.1	1508.9	1486.8	1456.4	1434.2
30°	1586.3	1558.6	1533.8	1500.6	1484.1	1472.9	1445.4	1415.0	1392.8	1362.5	1340.3
32.5°	1481.2	1450.9	1420.5	1398.3	1379.0	1368.0	1337.6	1318.2	1290.6	1265.7	1240.9
35°	1368.0	1337.6	1315.4	1285.1	1274.0	1262.9	1238.0	1213.2	1188.3	1166.3	1146.8
37.5°	1246.4	1224.2	1199.4	1177.3	1169.0	1158.0	1127.6	1105.4	1086.1	1063.9	1047.4
40°	1127.6	1108.1	1091.6	1069.5	1055.7	1047.4	1025.2	1006.0	983.8	970.0	953.4
42.5°	1019.7	997.7	981.0	964.5	950.6	942.3	923.1	909.2	892.6	878.9	859.4
45°	906.4	895.4	876.1	862.2	853.9	842.9	829.0	812.5	798.7	787.6	773.8
47.5°	807.0	796.0	782.1	765.5	760.0	751.7	737.8	726.8	715.8	704.7	690.9
50°	715.8	701.9	690.9	679.9	674.4	666.0	652.2	646.7	638.4	627.3	619.0
52.5°	632.9	621.8	610.7	597.0	594.2	588.6	580.3	569.3	561.0	555.5	550.0
55°	558.3	547.1	538.9	527.8	525.1	519.6	508.6	502.9	497.4	491.9	486.4
57.5°	491.9	480.9	469.9	464.2	458.7	453.2	450.4	442.2	436.7	433.9	428.4
60°	431.2	420.0	411.8	403.5	400.7	398.0	392.5	387.0	381.3	375.8	373.1
62.5°	373.1	362.0	356.5	351.0	345.5	345.5	339.9	334.4	328.9	326.1	320.6
65°	320.6	315.1	306.8	298.4	295.7	295.7	287.4	284.6	281.9	276.4	270.9
67.5°	270.9	265.4	257.0	254.2	251.5	248.7	245.9	240.4	234.9	232.2	226.7
70°	226.7	221.0	215.5	212.8	210.0	207.3	201.7	199.0	193.5	190.7	188.0
72.5°	182.3	179.6	174.1	171.3	168.6	165.8	163.0	160.3	154.8	152.0	149.3
75°	146.5	143.8	138.1	135.4	132.6	132.6	129.9	124.4	121.6	121.6	118.8
77.5°	110.6	107.8	105.1	102.3	99.4	99.4	96.7	93.9	91.2	91.2	88.4
80°	80.1	77.4	74.6	74.6	74.6	71.9	69.1	69.1	66.4	66.4	63.6
82.5°	52.5	52.5	49.7	49.7	49.7	47.0	47.0	44.2	44.2	44.2	44.2
85°	30.4	30.4	30.4	27.7	27.7	27.7	27.7	27.7	27.7	24.9	27.7
87.5°	13.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8	11.0	11.0	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584420

CATALOG NUMBER: HCC8S35D010MB-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7
2.5°	2025.7	2022.9	2017.4	2017.4	2011.9	2011.9	2009.0	2006.3	2003.5	2000.8	1998.0
5°	2006.3	1995.3	1989.8	1987.0	1981.5	1978.7	1970.5	1964.8	1962.1	1956.6	1951.1
7.5°	1970.5	1959.3	1948.3	1945.6	1942.8	1931.8	1923.4	1915.1	1909.6	1904.1	1898.6
10°	1928.9	1917.9	1904.1	1898.6	1893.1	1879.2	1868.2	1859.9	1848.9	1837.7	1835.0
12.5°	1879.2	1862.7	1846.0	1840.5	1832.2	1818.4	1807.3	1793.5	1785.3	1771.5	1768.7
15°	1821.2	1801.8	1788.0	1774.2	1768.7	1754.8	1735.5	1724.4	1707.9	1702.4	1688.6
17.5°	1752.1	1732.8	1713.4	1707.9	1699.6	1680.2	1660.9	1647.1	1630.5	1622.2	1613.9
20°	1680.2	1655.4	1636.0	1630.5	1619.5	1602.8	1583.5	1569.7	1555.8	1539.3	1531.0
22.5°	1597.3	1569.7	1553.1	1539.3	1536.6	1517.1	1495.1	1484.1	1472.9	1459.2	1448.1
25°	1506.1	1481.2	1461.9	1450.9	1445.4	1428.7	1412.2	1398.3	1381.8	1373.5	1359.6
27.5°	1412.2	1395.6	1370.8	1359.6	1351.3	1337.6	1318.2	1309.9	1293.4	1282.3	1274.0
30°	1321.0	1296.1	1282.3	1268.4	1260.2	1246.4	1229.7	1221.5	1207.7	1196.6	1188.3
32.5°	1221.5	1204.9	1185.5	1180.0	1169.0	1155.1	1144.1	1130.3	1119.3	1108.1	1105.4
35°	1130.3	1108.1	1088.9	1083.4	1075.0	1061.2	1055.7	1047.4	1033.5	1030.8	1019.7
37.5°	1030.8	1019.7	997.7	989.3	986.6	975.5	964.5	959.0	950.6	942.3	939.6
40°	936.8	923.1	911.9	903.7	898.1	889.9	878.9	876.1	870.5	859.4	856.7
42.5°	848.4	834.6	823.5	820.7	812.5	804.2	798.7	790.3	787.6	784.8	779.3
45°	762.8	754.5	743.4	740.6	737.8	726.8	721.3	715.8	710.2	707.4	701.9
47.5°	685.4	677.1	668.7	666.0	660.5	657.7	649.4	646.7	638.4	635.7	632.9
50°	610.7	605.2	599.7	597.0	591.5	588.6	583.1	577.6	572.0	569.3	566.5
52.5°	544.4	538.9	533.3	530.6	527.8	522.3	516.8	511.3	508.6	505.7	502.9
55°	480.9	475.4	472.6	469.9	467.0	464.2	456.0	453.2	450.4	447.7	442.2
57.5°	422.8	417.3	411.8	411.8	409.0	406.2	400.7	395.2	395.2	389.7	384.1
60°	370.3	364.8	359.3	356.5	353.8	348.3	345.5	342.6	339.9	337.1	331.6
62.5°	315.1	312.3	306.8	306.8	301.2	298.4	295.7	292.9	290.2	284.6	281.9
65°	268.1	265.4	259.7	257.0	257.0	254.2	248.7	245.9	243.2	243.2	240.4
67.5°	223.9	221.0	215.5	212.8	212.8	210.0	207.3	207.3	204.5	201.7	204.5
70°	185.2	179.6	179.6	176.8	176.8	174.1	171.3	171.3	171.3	174.1	174.1
72.5°	146.5	143.8	140.9	140.9	140.9	140.9	138.1	138.1	140.9	143.8	143.8
75°	116.1	113.3	113.3	113.3	110.6	110.6	113.3	113.3	116.1	116.1	116.1
77.5°	85.7	85.7	85.7	85.7	85.7	85.7	88.4	88.4	91.2	91.2	91.2
80°	63.6	63.6	63.6	63.6	63.6	66.4	66.4	66.4	66.4	66.4	69.1
82.5°	44.2	44.2	44.2	44.2	44.2	44.2	44.2	47.0	47.0	47.0	47.0
85°	24.9	27.7	27.7	27.7	27.7	27.7	27.7	27.7	27.7	27.7	27.7
87.5°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584420

CATALOG NUMBER: HCC8S35D010MB-HM82555835-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7	2036.7
2.5°	1995.3	1995.3	1995.3	1998.0	1992.5	1992.5	1992.5	1992.5
5°	1948.3	1945.6	1942.8	1945.6	1940.0	1940.0	1937.3	1937.3
7.5°	1890.3	1887.4	1884.7	1884.7	1879.2	1879.2	1876.4	1873.7
10°	1826.7	1821.2	1824.0	1818.4	1815.7	1812.9	1810.2	1807.3
12.5°	1757.6	1752.1	1749.3	1743.8	1738.3	1735.5	1738.3	1732.8
15°	1683.0	1674.7	1671.9	1666.4	1660.9	1658.2	1658.2	1655.4
17.5°	1600.0	1594.5	1591.8	1586.3	1583.5	1578.0	1575.3	1572.5
20°	1522.7	1508.9	1511.6	1506.1	1503.4	1492.3	1492.3	1495.1
22.5°	1437.0	1428.7	1423.2	1417.7	1415.0	1409.4	1409.4	1406.7
25°	1351.3	1343.1	1340.3	1334.8	1332.1	1326.5	1323.8	1323.8
27.5°	1268.4	1257.4	1257.4	1251.9	1246.4	1243.6	1240.9	1238.0
30°	1180.0	1171.8	1169.0	1169.0	1166.3	1166.3	1158.0	1160.7
32.5°	1097.1	1091.6	1088.9	1083.4	1083.4	1080.6	1080.6	1072.2
35°	1014.2	1006.0	1008.7	1003.2	1000.4	997.7	1000.4	997.7
37.5°	934.1	928.6	928.6	923.1	923.1	920.3	917.5	923.1
40°	853.9	851.2	848.4	845.7	848.4	845.7	840.2	842.9
42.5°	773.8	773.8	771.0	771.0	768.3	768.3	768.3	768.3
45°	701.9	699.2	699.2	696.4	696.4	696.4	696.4	693.6
47.5°	630.1	627.3	627.3	627.3	624.5	624.5	621.8	624.5
50°	561.0	561.0	558.3	558.3	561.0	558.3	555.5	555.5
52.5°	497.4	497.4	494.7	494.7	491.9	489.1	491.9	491.9
55°	439.4	436.7	433.9	433.9	431.2	428.4	428.4	431.2
57.5°	384.1	381.3	378.6	378.6	373.1	370.3	370.3	370.3
60°	331.6	326.1	326.1	323.3	323.3	320.6	320.6	320.6
62.5°	281.9	279.1	279.1	279.1	279.1	276.4	276.4	276.4
65°	240.4	240.4	240.4	243.2	243.2	245.9	245.9	245.9
67.5°	207.3	210.0	210.0	210.0	212.8	212.8	212.8	210.0
70°	176.8	176.8	176.8	179.6	179.6	179.6	179.6	179.6
72.5°	146.5	146.5	146.5	146.5	146.5	146.5	146.5	146.5
75°	116.1	118.8	118.8	118.8	116.1	118.8	118.8	116.1
77.5°	91.2	91.2	91.2	91.2	91.2	91.2	91.2	91.2
80°	69.1	69.1	69.1	69.1	69.1	69.1	69.1	69.1
82.5°	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
85°	27.7	27.7	27.7	27.7	27.7	27.7	27.7	27.7
87.5°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)