

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584589

Luminaire Tested: **HCC8S40D010MB-HM82555927-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010MB-HM82555927-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3108.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584589
CATALOG NUMBER: HCC8S40D010MB-HM82555927-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584589

CATALOG NUMBER: HCC8S40D010MB-HM82555927-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	51453	51453	51453
5°	53578	51340	49180
10°	55369	50682	46777
15°	56771	49524	44349
20°	56882	47471	42151
25°	55922	44466	39972
30°	52929	41030	38096
35°	48260	36899	35770
40°	41969	32529	33028
45°	35999	28167	30239
50°	30746	24289	27162
55°	26951	20919	23601
60°	23997	17842	19846
65°	21291	14564	15826
70°	18897	10792	8989
75°	15751	5647	2681
80°	12413	1776	444
85°	8845	885	0



TEST NUMBER: P584589
 CATALOG NUMBER: HCC8S40D010MB-HM82555927-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.2	5.1
10°-20°	440.7	14.2
20°-30°	623.7	20.1
30°-40°	652.5	21.0
40°-50°	544.3	17.5
50°-60°	385.9	12.4
60°-70°	222.3	7.2
70°-80°	71.5	2.3
80°-90°	9.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1221.6	39.3
0°-40°	1874.1	60.3
0°-60°	2804.3	90.2
0°-90°	3108.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3108.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1669	1669	1669	1669	1669	
5°	1731	1708	1659	1609	1589	166
15°	1778	1706	1551	1429	1389	500
25°	1644	1521	1307	1202	1175	750
35°	1282	1170	980	928	950	795
45°	826	758	646	653	693	640
55°	501	449	389	409	439	453
65°	292	244	200	200	217	292
75°	132	97	47	22	22	143
85°	25	12	2	0	0	31
90°	0	0	0	0	0	



TEST NUMBER: P584589

CATALOG NUMBER: HCC8S40D010MB-HM82555927-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6
2.5°	1703.5	1701.0	1698.5	1701.0	1698.5	1701.0	1698.5	1698.5	1696.0	1693.5	1693.5
5°	1730.9	1728.5	1728.5	1728.5	1726.0	1723.5	1723.5	1721.0	1716.0	1713.5	1708.5
7.5°	1748.3	1750.8	1750.8	1750.8	1745.8	1745.8	1740.9	1735.9	1730.9	1726.0	1718.5
10°	1768.3	1768.3	1765.8	1763.3	1758.3	1755.8	1753.3	1748.3	1740.9	1730.9	1723.5
12.5°	1775.8	1775.8	1773.3	1768.3	1765.8	1763.3	1760.8	1753.3	1743.4	1730.9	1721.0
15°	1778.3	1773.3	1770.8	1768.3	1763.3	1755.8	1755.8	1745.8	1733.4	1718.5	1706.0
17.5°	1758.3	1760.8	1755.8	1750.8	1743.4	1738.4	1730.9	1723.5	1708.5	1691.0	1678.5
20°	1733.4	1730.9	1728.5	1721.0	1711.0	1708.5	1701.0	1688.5	1676.0	1656.1	1638.6
22.5°	1693.5	1691.0	1686.0	1681.0	1671.0	1666.1	1658.6	1643.6	1626.1	1606.3	1586.3
25°	1643.6	1638.6	1631.1	1621.1	1613.6	1608.8	1598.8	1583.8	1563.8	1541.4	1521.4
27.5°	1563.8	1571.3	1566.3	1551.3	1543.9	1533.9	1531.4	1511.4	1493.9	1471.6	1449.1
30°	1486.5	1486.5	1479.1	1471.6	1459.1	1451.6	1441.6	1426.7	1409.2	1381.7	1364.3
32.5°	1389.2	1386.7	1376.7	1374.2	1364.3	1349.3	1346.8	1326.8	1309.4	1289.5	1267.0
35°	1282.0	1277.0	1267.0	1259.5	1254.5	1247.0	1239.6	1222.1	1204.6	1184.6	1169.8
37.5°	1159.8	1159.8	1157.3	1144.8	1139.8	1134.8	1127.3	1109.9	1099.9	1079.9	1064.9
40°	1042.6	1040.1	1032.6	1030.1	1025.1	1017.6	1012.6	1002.6	987.7	972.7	957.7
42.5°	927.8	930.3	920.3	922.8	912.8	907.9	905.4	890.4	882.9	868.0	855.5
45°	825.5	823.0	818.1	815.6	810.6	805.6	800.6	793.1	780.6	765.6	758.3
47.5°	730.8	723.3	723.3	720.8	718.3	708.3	705.8	698.3	690.9	675.9	665.9
50°	640.9	640.9	640.9	638.4	631.1	628.6	623.6	616.1	608.6	598.6	583.6
52.5°	568.7	568.7	568.7	566.2	556.2	553.7	551.2	541.2	531.2	523.7	513.8
55°	501.3	503.8	501.3	496.3	488.9	488.9	481.4	476.4	466.4	458.9	449.0
57.5°	444.0	444.0	439.0	436.5	431.5	429.0	424.0	419.0	406.5	399.0	386.6
60°	389.1	386.6	386.6	381.6	376.6	371.6	369.1	361.6	356.6	344.1	334.2
62.5°	339.2	339.2	334.2	334.2	324.3	324.3	321.8	314.3	306.8	294.3	289.3
65°	291.8	291.8	289.3	286.8	279.3	276.8	274.3	266.9	259.4	251.9	244.4
67.5°	249.4	249.4	244.4	241.9	236.9	234.4	229.4	224.4	216.9	209.6	202.1
70°	209.6	207.1	204.6	202.1	197.1	194.6	189.6	184.6	177.1	172.1	164.6
72.5°	169.6	169.6	167.1	162.1	159.6	157.1	154.6	149.7	142.2	134.7	129.7
75°	132.2	132.2	132.2	127.2	122.2	119.7	119.7	114.7	109.7	102.2	97.2
77.5°	102.2	99.7	97.2	97.2	92.2	89.8	87.3	84.8	77.4	74.9	69.9
80°	69.9	72.4	69.9	67.4	64.9	62.4	62.4	57.4	54.9	49.9	44.9
82.5°	47.4	44.9	44.9	42.4	42.4	39.9	39.9	34.9	32.4	30.0	27.5
85°	25.0	25.0	22.5	22.5	22.5	20.0	20.0	17.5	17.5	15.0	12.5
87.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	5.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584589

CATALOG NUMBER: HCC8S40D010MB-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6
2.5°	1691.0	1686.0	1683.5	1683.5	1681.0	1678.5	1676.0	1673.5	1668.6	1668.6	1663.6
5°	1703.5	1698.5	1696.0	1688.5	1683.5	1683.5	1673.5	1671.0	1663.6	1658.6	1653.6
7.5°	1713.5	1703.5	1696.0	1688.5	1683.5	1678.5	1668.6	1658.6	1648.6	1638.6	1633.6
10°	1713.5	1703.5	1691.0	1678.5	1673.5	1668.6	1656.1	1641.1	1628.6	1618.6	1606.3
12.5°	1708.5	1693.5	1678.5	1668.6	1658.6	1651.1	1636.1	1621.1	1606.3	1586.3	1576.3
15°	1693.5	1673.5	1658.6	1641.1	1633.6	1621.1	1608.8	1586.3	1568.8	1551.3	1538.9
17.5°	1663.6	1638.6	1621.1	1603.8	1591.3	1583.8	1563.8	1543.9	1523.9	1503.9	1488.9
20°	1618.6	1596.3	1576.3	1553.8	1543.9	1533.9	1508.9	1488.9	1469.1	1446.6	1431.6
22.5°	1563.8	1541.4	1513.9	1496.4	1481.6	1469.1	1446.6	1424.2	1404.2	1384.2	1364.3
25°	1496.4	1474.1	1449.1	1421.7	1411.7	1399.2	1374.2	1351.8	1329.3	1306.9	1289.5
27.5°	1424.2	1394.2	1374.2	1344.3	1334.3	1321.9	1294.5	1269.5	1249.5	1232.1	1212.1
30°	1336.8	1314.4	1287.0	1259.5	1249.5	1237.1	1214.6	1192.1	1172.3	1152.3	1132.3
32.5°	1242.1	1219.6	1192.1	1172.3	1157.3	1147.3	1124.8	1104.9	1084.9	1064.9	1047.6
35°	1142.3	1117.4	1097.4	1077.4	1064.9	1052.6	1030.1	1012.6	997.7	980.2	962.7
37.5°	1040.1	1022.6	1002.6	980.2	967.7	957.7	940.3	920.3	907.9	892.9	880.5
40°	940.3	920.3	902.9	882.9	873.0	865.5	848.0	833.0	820.5	808.1	800.6
42.5°	838.0	820.5	803.1	790.6	783.1	775.6	763.1	745.8	738.3	725.8	718.3
45°	743.3	728.3	715.8	698.3	693.4	688.4	673.4	660.9	653.4	645.9	640.9
47.5°	653.4	643.4	628.6	618.6	611.1	606.1	596.1	586.1	578.6	573.7	568.7
50°	576.2	563.7	553.7	543.7	538.7	531.2	521.2	516.2	511.3	506.3	506.3
52.5°	503.8	491.4	481.4	473.9	468.9	463.9	456.4	454.0	449.0	449.0	446.5
55°	436.5	429.0	419.0	409.0	406.5	404.0	399.0	394.1	391.6	389.1	391.6
57.5°	379.1	371.6	361.6	354.1	351.6	349.1	346.6	341.6	339.2	339.2	339.2
60°	326.8	319.3	311.8	304.3	304.3	299.3	296.8	294.3	291.8	289.3	289.3
62.5°	279.3	271.9	264.4	259.4	256.9	254.4	249.4	246.9	244.4	244.4	241.9
65°	236.9	226.9	224.4	216.9	214.4	212.1	209.6	204.6	202.1	199.6	197.1
67.5°	194.6	189.6	182.1	177.1	174.6	172.1	169.6	164.6	162.1	159.6	154.6
70°	157.1	152.1	147.2	142.2	139.7	137.2	132.2	127.2	124.7	119.7	112.2
72.5°	122.2	117.2	112.2	107.2	104.7	102.2	97.2	92.2	87.3	82.3	77.4
75°	92.2	87.3	79.8	74.9	72.4	72.4	64.9	59.9	54.9	47.4	42.4
77.5°	64.9	57.4	54.9	49.9	47.4	42.4	37.4	32.4	27.5	25.0	20.0
80°	42.4	37.4	32.4	30.0	27.5	25.0	22.5	17.5	12.5	10.0	7.5
82.5°	25.0	22.5	20.0	17.5	15.0	12.5	10.0	10.0	7.5	5.0	2.5
85°	12.5	10.0	7.5	7.5	5.0	5.0	5.0	2.5	2.5	2.5	2.5
87.5°	5.0	2.5	2.5	2.5	2.5	2.5	2.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584589

CATALOG NUMBER: HCC8S40D010MB-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6
2.5°	1661.1	1658.6	1656.1	1653.6	1653.6	1648.6	1648.6	1646.1	1641.1	1638.6	1638.6
5°	1646.1	1638.6	1633.6	1631.1	1628.6	1621.1	1618.6	1613.6	1608.8	1603.8	1601.3
7.5°	1623.6	1611.1	1606.3	1603.8	1596.3	1588.8	1583.8	1576.3	1568.8	1561.3	1558.8
10°	1596.3	1583.8	1571.3	1566.3	1558.8	1553.8	1543.9	1533.9	1526.4	1518.9	1511.4
12.5°	1561.3	1546.4	1533.9	1528.9	1521.4	1511.4	1496.4	1491.4	1479.1	1474.1	1464.1
15°	1521.4	1503.9	1491.4	1484.0	1476.6	1461.6	1451.6	1441.6	1429.1	1424.2	1414.2
17.5°	1471.6	1451.6	1439.1	1431.6	1426.7	1414.2	1399.2	1386.7	1374.2	1369.2	1361.8
20°	1411.7	1399.2	1381.7	1374.2	1369.2	1354.3	1339.3	1334.3	1324.4	1314.4	1306.9
22.5°	1344.3	1331.8	1314.4	1306.9	1304.5	1292.0	1279.5	1272.0	1264.5	1257.0	1249.5
25°	1274.5	1259.5	1244.6	1239.6	1234.6	1224.6	1214.6	1209.6	1202.1	1197.1	1192.1
27.5°	1199.6	1184.6	1172.3	1164.8	1159.8	1152.3	1147.3	1142.3	1137.3	1132.3	1129.8
30°	1119.9	1104.9	1094.9	1089.9	1084.9	1082.4	1074.9	1072.4	1069.9	1064.9	1067.4
32.5°	1040.1	1027.6	1017.6	1010.1	1010.1	1005.1	1002.6	1002.6	1000.2	1000.2	1000.2
35°	952.7	945.2	937.8	935.3	932.8	930.3	927.8	930.3	927.8	930.3	932.8
37.5°	873.0	865.5	860.5	858.0	855.5	858.0	855.5	855.5	858.0	863.0	865.5
40°	790.6	785.6	780.6	783.1	780.6	780.6	780.6	788.1	790.6	793.1	795.6
42.5°	713.3	708.3	705.8	705.8	708.3	705.8	710.8	713.3	718.3	725.8	730.8
45°	638.4	636.1	636.1	638.4	636.1	640.9	640.9	645.9	653.4	658.4	663.4
47.5°	568.7	568.7	568.7	571.2	571.2	573.7	578.6	581.1	586.1	591.1	596.1
50°	503.8	506.3	508.8	508.8	508.8	513.8	518.7	521.2	523.7	526.2	533.7
52.5°	446.5	449.0	449.0	451.5	454.0	456.4	458.9	463.9	466.4	471.4	473.9
55°	391.6	391.6	396.5	399.0	399.0	399.0	404.0	404.0	409.0	411.5	416.5
57.5°	339.2	341.6	341.6	344.1	344.1	346.6	349.1	351.6	354.1	356.6	359.1
60°	289.3	289.3	289.3	291.8	294.3	296.8	294.3	299.3	299.3	304.3	306.8
62.5°	241.9	244.4	244.4	244.4	244.4	244.4	244.4	246.9	249.4	251.9	254.4
65°	197.1	197.1	197.1	194.6	197.1	194.6	197.1	199.6	199.6	202.1	204.6
67.5°	152.1	152.1	147.2	147.2	149.7	149.7	149.7	149.7	147.2	152.1	152.1
70°	109.7	107.2	104.7	102.2	102.2	99.7	99.7	97.2	97.2	97.2	97.2
72.5°	72.4	67.4	62.4	59.9	57.4	57.4	52.4	49.9	52.4	52.4	52.4
75°	37.4	32.4	30.0	27.5	25.0	25.0	22.5	22.5	22.5	22.5	22.5
77.5°	15.0	12.5	10.0	10.0	7.5	7.5	7.5	7.5	7.5	7.5	7.5
80°	5.0	5.0	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
85°	2.5	0.0	0.0	2.5	0.0	2.5	2.5	2.5	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584589

CATALOG NUMBER: HCC8S40D010MB-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6
2.5°	1636.1	1636.1	1633.6	1636.1	1631.1	1633.6	1631.1	1631.1
5°	1598.8	1593.8	1593.8	1593.8	1591.3	1591.3	1588.8	1588.8
7.5°	1553.8	1551.3	1548.8	1546.4	1543.9	1541.4	1541.4	1541.4
10°	1508.9	1503.9	1503.9	1501.4	1496.4	1493.9	1493.9	1493.9
12.5°	1456.6	1454.1	1451.6	1451.6	1441.6	1444.1	1441.6	1441.6
15°	1406.7	1404.2	1404.2	1396.7	1391.7	1391.7	1391.7	1389.2
17.5°	1354.3	1351.8	1349.3	1344.3	1339.3	1339.3	1336.8	1339.3
20°	1299.5	1297.0	1292.0	1292.0	1289.5	1287.0	1282.0	1284.5
22.5°	1244.6	1239.6	1237.1	1237.1	1234.6	1234.6	1229.6	1229.6
25°	1187.1	1184.6	1182.3	1184.6	1179.8	1179.8	1174.8	1174.8
27.5°	1127.3	1124.8	1124.8	1124.8	1122.4	1124.8	1122.4	1122.4
30°	1067.4	1067.4	1064.9	1064.9	1067.4	1064.9	1067.4	1069.9
32.5°	1002.6	1002.6	1005.1	1005.1	1007.6	1007.6	1007.6	1007.6
35°	935.3	940.3	940.3	942.7	945.2	947.7	947.7	950.2
37.5°	873.0	875.5	878.0	880.5	885.4	885.4	885.4	885.4
40°	805.6	808.1	813.1	810.6	820.5	823.0	820.5	820.5
42.5°	735.8	740.8	743.3	748.3	750.8	755.8	758.3	758.3
45°	670.9	673.4	678.4	683.4	685.9	693.4	693.4	693.4
47.5°	603.6	608.6	611.1	616.1	618.6	626.1	628.6	626.1
50°	538.7	543.7	548.7	548.7	556.2	558.7	563.7	566.2
52.5°	476.4	478.9	483.9	486.4	491.4	496.3	498.8	501.3
55°	416.5	419.0	424.0	424.0	431.5	434.0	439.0	439.0
57.5°	361.6	364.1	369.1	366.6	371.6	376.6	376.6	374.1
60°	309.3	309.3	309.3	314.3	316.8	319.3	321.8	321.8
62.5°	254.4	259.4	261.9	261.9	264.4	266.9	266.9	264.4
65°	204.6	209.6	212.1	212.1	214.4	214.4	214.4	216.9
67.5°	154.6	154.6	154.6	157.1	154.6	154.6	154.6	154.6
70°	97.2	97.2	97.2	97.2	94.7	97.2	97.2	99.7
72.5°	52.4	52.4	52.4	52.4	52.4	52.4	52.4	52.4
75°	22.5	22.5	22.5	25.0	22.5	22.5	22.5	22.5
77.5°	10.0	7.5	10.0	10.0	7.5	7.5	7.5	7.5
80°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
85°	0.0	2.5	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)