

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584590

Luminaire Tested: **HCC8W40D010MB-HM82555927-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584590  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W40D010MB-HM82555927-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3392.4 lumens  
Efficiency: N/A  
Efficacy: 82.7 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584590  
CATALOG NUMBER: HCC8W40D010MB-HM82555927-81WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P584590

CATALOG NUMBER: HCC8W40D010MB-HM82555927-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87	87	87	87	87	87		
	2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76	76	76		
	3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66	66	66	66	66	66		
	4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58	58	58	58	58	58		
	5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51	51	51	51	51	51		
	6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46	46	46	46	46	46		
	7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41	41	41	41	41	41		
	8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38	38	38	38	38	38		
	9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34	34	34	34	34	34		
	10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32	32	32	32	32	32		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	56683	56683	56683
5°	58677	56358	54117
10°	59975	55369	51073
15°	60828	53505	47691
20°	60646	50906	44278
25°	59148	47607	40645
30°	56038	43782	37302
35°	50982	39624	33895
40°	44778	35242	30617
45°	39048	30997	27304
50°	33979	27162	24049
55°	30305	23870	20919
60°	27537	20919	17842
65°	24750	18197	16191
70°	22035	15516	14615
75°	19313	13070	12474
80°	16373	10637	11081
85°	12348	7961	8845



TEST NUMBER: P584590  
 CATALOG NUMBER: HCC8W40D010MB-HM82555927-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.2	5.1
10°-20°	474.4	14.0
20°-30°	658.5	19.4
30°-40°	680.8	20.1
40°-50°	570.0	16.8
50°-60°	413.8	12.2
60°-70°	261.1	7.7
70°-80°	129.4	3.8
80°-90°	32.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1305.0	38.5
0°-40°	1985.8	58.5
0°-60°	2969.7	87.5
0°-90°	3392.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3392.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1838	1838	1838	1838	1838	
5°	1896	1873	1821	1771	1748	181
15°	1905	1833	1676	1541	1494	536
25°	1738	1626	1399	1247	1195	797
35°	1354	1254	1053	933	900	843
45°	895	830	711	641	626	693
55°	564	514	444	406	389	509
65°	339	297	249	219	222	338
75°	162	135	110	105	105	174
85°	35	28	22	25	25	42
90°	0	0	0	0	0	



TEST NUMBER: P584590

CATALOG NUMBER: HCC8W40D010MB-HM82555927-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2
2.5°	1868.1	1868.1	1870.6	1868.1	1868.1	1868.1	1865.6	1865.6	1863.1	1863.1	1858.1
5°	1895.6	1890.6	1895.6	1890.6	1890.6	1890.6	1888.1	1883.1	1880.6	1875.6	1873.1
7.5°	1907.9	1905.4	1905.4	1903.0	1903.0	1900.5	1898.0	1895.6	1885.6	1883.1	1875.6
10°	1915.4	1912.9	1912.9	1910.4	1905.4	1905.4	1900.5	1898.0	1885.6	1880.6	1870.6
12.5°	1912.9	1912.9	1912.9	1910.4	1903.0	1900.5	1895.6	1888.1	1878.1	1868.1	1858.1
15°	1905.4	1905.4	1900.5	1898.0	1890.6	1885.6	1883.1	1870.6	1860.6	1848.1	1833.2
17.5°	1880.6	1880.6	1878.1	1873.1	1865.6	1860.6	1855.6	1843.2	1833.2	1813.2	1798.2
20°	1848.1	1845.6	1843.2	1835.7	1828.2	1825.7	1818.2	1800.7	1788.2	1773.3	1753.3
22.5°	1800.7	1798.2	1795.7	1790.7	1778.3	1773.3	1768.3	1755.8	1733.4	1718.5	1693.5
25°	1738.4	1738.4	1733.4	1725.9	1713.5	1708.5	1701.0	1688.5	1668.5	1646.1	1626.1
27.5°	1666.0	1663.5	1656.1	1651.1	1641.1	1633.6	1621.1	1606.1	1586.3	1568.8	1543.8
30°	1573.8	1573.8	1568.8	1561.3	1548.8	1543.8	1533.9	1516.4	1496.4	1474.1	1456.6
32.5°	1469.1	1469.1	1461.6	1456.6	1449.1	1436.6	1434.1	1414.2	1396.7	1379.2	1359.3
35°	1354.3	1356.8	1351.8	1341.8	1329.3	1329.3	1324.4	1306.9	1287.0	1269.5	1254.5
37.5°	1239.6	1232.1	1229.6	1224.6	1217.1	1207.1	1202.1	1194.6	1177.3	1164.8	1142.3
40°	1112.4	1114.9	1109.9	1104.9	1102.4	1094.9	1092.4	1079.9	1067.4	1052.6	1042.6
42.5°	997.7	997.7	997.7	992.7	987.7	980.2	977.7	970.2	955.2	945.2	930.3
45°	895.4	887.9	887.9	885.4	882.9	877.9	870.5	865.5	855.5	848.0	830.5
47.5°	795.6	798.1	795.6	793.1	785.6	783.1	780.6	770.6	760.6	753.3	740.8
50°	708.3	713.3	708.3	708.3	703.3	700.8	695.8	688.4	680.9	668.4	655.9
52.5°	635.9	635.9	633.6	631.1	623.6	618.6	616.1	613.6	601.1	591.1	581.1
55°	563.7	566.2	566.2	558.7	556.2	551.2	548.7	541.2	536.2	521.2	513.8
57.5°	501.3	498.8	501.3	496.3	491.4	486.4	483.9	478.9	471.4	461.4	451.5
60°	446.5	441.5	441.5	439.0	434.0	431.5	426.5	419.0	411.5	401.5	394.0
62.5°	391.6	389.1	386.6	384.1	379.1	376.6	374.1	366.6	359.1	351.6	344.1
65°	339.2	339.2	336.7	331.8	329.3	326.8	324.3	319.3	309.3	304.3	296.8
67.5°	291.8	289.3	289.3	284.3	279.3	276.8	276.8	271.9	264.4	256.9	251.9
70°	244.4	246.9	244.4	241.9	236.9	236.9	231.9	229.4	219.4	216.9	209.6
72.5°	202.1	202.1	199.6	199.6	194.6	192.1	192.1	187.1	182.1	177.1	172.1
75°	162.1	162.1	162.1	159.6	157.1	152.1	152.1	149.7	144.7	139.7	134.7
77.5°	127.2	124.7	124.7	122.2	119.7	117.2	117.2	114.7	109.7	107.2	102.2
80°	92.2	89.8	89.8	89.8	84.8	87.3	84.8	82.3	79.8	77.4	74.9
82.5°	59.9	62.4	62.4	59.9	57.4	57.4	57.4	54.9	54.9	52.4	49.9
85°	34.9	34.9	34.9	34.9	32.4	32.4	32.4	30.0	30.0	30.0	27.5
87.5°	15.0	15.0	15.0	15.0	15.0	15.0	12.5	12.5	12.5	12.5	12.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584590

CATALOG NUMBER: HCC8W40D010MB-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2
2.5°	1858.1	1853.1	1850.6	1848.1	1848.1	1845.6	1843.2	1838.2	1838.2	1833.2	1830.7
5°	1868.1	1860.6	1855.6	1850.6	1848.1	1843.2	1838.2	1830.7	1828.2	1820.7	1813.2
7.5°	1870.6	1858.1	1853.1	1843.2	1838.2	1833.2	1823.2	1815.7	1805.7	1798.2	1788.2
10°	1860.6	1850.6	1838.2	1825.7	1823.2	1815.7	1800.7	1790.7	1778.3	1768.3	1753.3
12.5°	1845.6	1830.7	1818.2	1803.2	1795.7	1788.2	1773.3	1758.3	1740.9	1723.5	1708.5
15°	1820.7	1803.2	1785.7	1768.3	1758.3	1750.8	1733.4	1716.0	1698.5	1676.0	1661.1
17.5°	1783.3	1763.3	1745.8	1723.5	1713.5	1706.0	1683.5	1663.5	1641.1	1618.6	1603.6
20°	1735.9	1711.0	1691.0	1666.0	1658.6	1646.1	1623.6	1601.3	1576.3	1551.3	1533.9
22.5°	1673.5	1648.6	1626.1	1601.3	1588.8	1576.3	1553.8	1526.4	1501.4	1481.6	1464.1
25°	1601.3	1578.8	1551.3	1528.9	1513.9	1498.9	1474.1	1451.6	1429.1	1399.2	1381.7
27.5°	1521.4	1493.9	1474.1	1444.1	1429.1	1419.2	1391.7	1361.7	1341.8	1314.4	1294.5
30°	1431.6	1406.7	1384.2	1354.3	1339.3	1329.3	1304.4	1277.0	1257.0	1229.6	1209.6
32.5°	1336.8	1309.4	1282.0	1262.0	1244.5	1234.6	1207.1	1189.6	1164.8	1142.3	1119.8
35°	1234.6	1207.1	1187.1	1159.8	1149.8	1139.8	1117.4	1094.9	1072.4	1052.6	1035.1
37.5°	1124.8	1104.9	1082.4	1062.4	1055.1	1045.1	1017.6	997.7	980.2	960.2	945.2
40°	1017.6	1000.1	985.2	965.2	952.7	945.2	925.3	907.9	887.9	875.5	860.5
42.5°	920.3	900.4	885.4	870.5	858.0	850.5	833.0	820.5	805.6	793.1	775.6
45°	818.0	808.1	790.6	778.1	770.6	760.6	748.3	733.3	720.8	710.8	698.3
47.5°	728.3	718.3	705.8	690.9	685.9	678.4	665.9	655.9	645.9	635.9	623.6
50°	645.9	633.6	623.6	613.6	608.6	601.1	588.6	583.6	576.1	566.2	558.7
52.5°	571.2	561.2	551.2	538.7	536.2	531.2	523.7	513.8	506.3	501.3	496.3
55°	503.8	493.8	486.4	476.4	473.9	468.9	458.9	453.9	449.0	444.0	439.0
57.5°	444.0	434.0	424.0	419.0	414.0	409.0	406.5	399.0	394.0	391.6	386.6
60°	389.1	379.1	371.6	364.1	361.6	359.1	354.1	349.1	344.1	339.2	336.7
62.5°	336.7	326.8	321.8	316.8	311.8	311.8	306.8	301.8	296.8	294.3	289.3
65°	289.3	284.3	276.8	269.4	266.9	266.9	259.4	256.9	254.4	249.4	244.4
67.5°	244.4	239.4	231.9	229.4	226.9	224.4	221.9	216.9	211.9	209.6	204.6
70°	204.6	199.6	194.6	192.1	189.6	187.1	182.1	179.6	174.6	172.1	169.6
72.5°	164.6	162.1	157.1	154.6	152.1	149.7	147.2	144.7	139.7	137.2	134.7
75°	132.2	129.7	124.7	122.2	119.7	119.7	117.2	112.2	109.7	109.7	107.2
77.5°	99.7	97.2	94.7	92.2	89.8	89.8	87.3	84.8	82.3	82.3	79.8
80°	72.4	69.9	67.4	67.4	67.4	64.9	62.4	62.4	59.9	59.9	57.4
82.5°	47.4	47.4	44.9	44.9	44.9	42.4	42.4	39.9	39.9	39.9	39.9
85°	27.5	27.5	27.5	25.0	25.0	25.0	25.0	25.0	25.0	22.5	25.0
87.5°	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5	10.0	10.0	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584590

CATALOG NUMBER: HCC8W40D010MB-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2
2.5°	1828.2	1825.7	1820.7	1820.7	1815.7	1815.7	1813.2	1810.7	1808.2	1805.7	1803.2
5°	1810.7	1800.7	1795.7	1793.2	1788.2	1785.7	1778.3	1773.3	1770.8	1765.8	1760.8
7.5°	1778.3	1768.3	1758.3	1755.8	1753.3	1743.4	1735.9	1728.4	1723.5	1718.5	1713.5
10°	1740.9	1730.9	1718.5	1713.5	1708.5	1696.0	1686.0	1678.5	1668.5	1658.6	1656.1
12.5°	1696.0	1681.0	1666.0	1661.1	1653.6	1641.1	1631.1	1618.6	1611.1	1598.8	1596.3
15°	1643.6	1626.1	1613.6	1601.3	1596.3	1583.8	1566.3	1556.3	1541.4	1536.4	1523.9
17.5°	1581.3	1563.8	1546.3	1541.4	1533.9	1516.4	1498.9	1486.4	1471.6	1464.1	1456.6
20°	1516.4	1493.9	1476.6	1471.6	1461.6	1446.6	1429.1	1416.7	1404.2	1389.2	1381.7
22.5°	1441.6	1416.7	1401.7	1389.2	1386.7	1369.2	1349.3	1339.3	1329.3	1316.9	1306.9
25°	1359.3	1336.8	1319.4	1309.4	1304.4	1289.5	1274.5	1262.0	1247.0	1239.6	1227.1
27.5°	1274.5	1259.5	1237.1	1227.1	1219.6	1207.1	1189.6	1182.1	1167.3	1157.3	1149.8
30°	1192.1	1169.8	1157.3	1144.8	1137.3	1124.8	1109.9	1102.4	1089.9	1079.9	1072.4
32.5°	1102.4	1087.4	1069.9	1064.9	1055.1	1042.6	1032.6	1020.1	1010.1	1000.1	997.7
35°	1020.1	1000.1	982.7	977.7	970.2	957.7	952.7	945.2	932.8	930.3	920.3
37.5°	930.3	920.3	900.4	892.9	890.4	880.4	870.5	865.5	858.0	850.5	848.0
40°	845.5	833.0	823.0	815.6	810.6	803.1	793.1	790.6	785.6	775.6	773.1
42.5°	765.6	753.3	743.3	740.8	733.3	725.8	720.8	713.3	710.8	708.3	703.3
45°	688.4	680.9	670.9	668.4	665.9	655.9	650.9	645.9	640.9	638.4	633.6
47.5°	618.6	611.1	603.6	601.1	596.1	593.6	586.1	583.6	576.1	573.7	571.2
50°	551.2	546.2	541.2	538.7	533.7	531.2	526.2	521.2	516.2	513.8	511.3
52.5°	491.4	486.4	481.4	478.9	476.4	471.4	466.4	461.4	458.9	456.4	453.9
55°	434.0	429.0	426.5	424.0	421.5	419.0	411.5	409.0	406.5	404.0	399.0
57.5°	381.6	376.6	371.6	371.6	369.1	366.6	361.6	356.6	356.6	351.6	346.6
60°	334.2	329.3	324.3	321.8	319.3	314.3	311.8	309.3	306.8	304.3	299.3
62.5°	284.3	281.8	276.8	276.8	271.9	269.4	266.9	264.4	261.9	256.9	254.4
65°	241.9	239.4	234.4	231.9	231.9	229.4	224.4	221.9	219.4	219.4	216.9
67.5°	202.1	199.6	194.6	192.1	192.1	189.6	187.1	187.1	184.6	182.1	184.6
70°	167.1	162.1	162.1	159.6	159.6	157.1	154.6	154.6	154.6	157.1	157.1
72.5°	132.2	129.7	127.2	127.2	127.2	127.2	124.7	124.7	127.2	129.7	129.7
75°	104.7	102.2	102.2	102.2	99.7	99.7	102.2	102.2	104.7	104.7	104.7
77.5°	77.4	77.4	77.4	77.4	77.4	77.4	79.8	79.8	82.3	82.3	82.3
80°	57.4	57.4	57.4	57.4	57.4	59.9	59.9	59.9	59.9	59.9	62.4
82.5°	39.9	39.9	39.9	39.9	39.9	39.9	39.9	42.4	42.4	42.4	42.4
85°	22.5	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0
87.5°	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584590

CATALOG NUMBER: HCC8W40D010MB-HM82555927-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2	1838.2
2.5°	1800.7	1800.7	1800.7	1803.2	1798.2	1798.2	1798.2	1798.2
5°	1758.3	1755.8	1753.3	1755.8	1750.8	1750.8	1748.3	1748.3
7.5°	1706.0	1703.5	1701.0	1701.0	1696.0	1696.0	1693.5	1691.0
10°	1648.6	1643.6	1646.1	1641.1	1638.6	1636.1	1633.6	1631.1
12.5°	1586.3	1581.3	1578.8	1573.8	1568.8	1566.3	1568.8	1563.8
15°	1518.9	1511.4	1508.9	1503.9	1498.9	1496.4	1496.4	1493.9
17.5°	1444.1	1439.1	1436.6	1431.6	1429.1	1424.1	1421.6	1419.2
20°	1374.2	1361.7	1364.2	1359.3	1356.8	1346.8	1346.8	1349.3
22.5°	1297.0	1289.5	1284.5	1279.5	1277.0	1272.0	1272.0	1269.5
25°	1219.6	1212.1	1209.6	1204.6	1202.1	1197.1	1194.6	1194.6
27.5°	1144.8	1134.8	1134.8	1129.8	1124.8	1122.3	1119.8	1117.4
30°	1064.9	1057.6	1055.1	1055.1	1052.6	1052.6	1045.1	1047.6
32.5°	990.2	985.2	982.7	977.7	977.7	975.2	975.2	967.7
35°	915.3	907.9	910.4	905.4	902.9	900.4	902.9	900.4
37.5°	843.0	838.0	838.0	833.0	833.0	830.5	828.0	833.0
40°	770.6	768.1	765.6	763.1	765.6	763.1	758.1	760.6
42.5°	698.3	698.3	695.8	695.8	693.4	693.4	693.4	693.4
45°	633.6	631.1	631.1	628.6	628.6	628.6	628.6	626.1
47.5°	568.7	566.2	566.2	566.2	563.7	563.7	561.2	563.7
50°	506.3	506.3	503.8	503.8	506.3	503.8	501.3	501.3
52.5°	449.0	449.0	446.5	446.5	444.0	441.5	444.0	444.0
55°	396.5	394.0	391.6	391.6	389.1	386.6	386.6	389.1
57.5°	346.6	344.1	341.6	341.6	336.7	334.2	334.2	334.2
60°	299.3	294.3	294.3	291.8	291.8	289.3	289.3	289.3
62.5°	254.4	251.9	251.9	251.9	251.9	249.4	249.4	249.4
65°	216.9	216.9	216.9	219.4	219.4	221.9	221.9	221.9
67.5°	187.1	189.6	189.6	189.6	192.1	192.1	192.1	189.6
70°	159.6	159.6	159.6	162.1	162.1	162.1	162.1	162.1
72.5°	132.2	132.2	132.2	132.2	132.2	132.2	132.2	132.2
75°	104.7	107.2	107.2	107.2	104.7	107.2	107.2	104.7
77.5°	82.3	82.3	82.3	82.3	82.3	82.3	82.3	82.3
80°	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4
82.5°	42.4	42.4	42.4	42.4	42.4	42.4	42.4	42.4
85°	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0
87.5°	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)