

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584412

Luminaire Tested: **HCC8W35D010BZ-HM82555835-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584412
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010BZ-HM82555835-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3935.8 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584412
CATALOG NUMBER: HCC8W35D010BZ-HM82555835-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P584412

CATALOG NUMBER: HCC8W35D010BZ-HM82555835-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63859	63859	63859
5°	64700	63586	62989
10°	65361	62937	61985
15°	66022	61610	60375
20°	65686	59333	57975
25°	64159	55786	55031
30°	60941	51783	51583
35°	55476	47255	47669
40°	48635	42291	43849
45°	41956	37622	40269
50°	36742	33029	36479
55°	32553	28391	32106
60°	29332	23873	26599
65°	26428	19161	20379
70°	23180	13957	11225
75°	19766	7256	2967
80°	15219	1953	497
85°	9800	0	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584412

CATALOG NUMBER: HCC8W35D010BZ-HM82555835-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.4	5.0
10°-20°	549.3	14.0
20°-30°	779.6	19.8
30°-40°	820.6	20.9
40°-50°	698.1	17.7
50°-60°	504.5	12.8
60°-70°	286.9	7.3
70°-80°	90.4	2.3
80°-90°	11.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1524.2	38.7
0°-40°	2344.9	59.6
0°-60°	3547.4	90.1
0°-90°	3935.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3935.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2071	2071	2071	2071	2071	
5°	2090	2079	2054	2040	2035	199
15°	2068	2016	1930	1894	1891	582
25°	1886	1792	1640	1612	1617	864
35°	1474	1388	1255	1247	1266	917
45°	962	926	863	885	923	748
55°	606	561	528	558	597	546
65°	362	312	263	260	279	359
75°	166	127	61	28	25	178
85°	28	16	0	0	0	36
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584412

CATALOG NUMBER: HCC8W35D010BZ-HM82555835-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9
2.5°	2081.9	2084.6	2079.1	2079.1	2084.6	2079.1	2081.9	2081.9	2079.1	2079.1	2076.4
5°	2090.2	2087.4	2087.4	2087.4	2090.2	2084.6	2081.9	2084.6	2079.1	2079.1	2079.1
7.5°	2092.9	2092.9	2090.2	2087.4	2087.4	2087.4	2084.6	2081.9	2079.1	2073.6	2070.9
10°	2087.4	2087.4	2090.2	2084.6	2084.6	2079.1	2079.1	2073.6	2073.6	2068.1	2059.8
12.5°	2081.9	2079.1	2079.1	2073.6	2073.6	2068.1	2068.1	2059.8	2057.0	2048.7	2040.4
15°	2068.1	2065.4	2059.8	2057.0	2054.2	2051.5	2045.9	2043.2	2034.9	2023.8	2015.5
17.5°	2040.4	2037.7	2034.9	2029.4	2023.8	2021.0	2018.3	2010.0	1999.0	1990.7	1976.8
20°	2001.7	1999.0	1999.0	1990.7	1987.8	1979.6	1976.8	1965.8	1957.5	1940.9	1929.9
22.5°	1949.1	1951.9	1946.4	1940.9	1935.4	1927.1	1921.6	1910.5	1896.7	1880.0	1866.2
25°	1885.7	1888.4	1882.8	1877.3	1869.0	1863.5	1858.0	1841.3	1827.5	1808.1	1791.6
27.5°	1805.4	1805.4	1805.4	1799.9	1786.1	1783.3	1777.7	1761.2	1741.8	1725.2	1708.7
30°	1711.5	1708.7	1708.7	1700.3	1694.8	1683.8	1675.5	1661.6	1647.8	1628.4	1609.2
32.5°	1598.0	1600.8	1592.5	1587.0	1578.7	1578.7	1567.7	1556.6	1540.0	1520.6	1501.3
35°	1473.7	1476.4	1470.9	1468.1	1454.3	1451.5	1448.7	1435.0	1423.8	1410.0	1387.9
37.5°	1346.4	1343.7	1340.9	1340.9	1332.7	1327.1	1321.6	1313.2	1296.7	1285.7	1274.6
40°	1208.2	1208.2	1208.2	1205.4	1202.7	1197.2	1194.4	1188.9	1177.8	1166.7	1158.5
42.5°	1083.8	1083.8	1081.1	1078.3	1072.7	1075.6	1069.9	1064.4	1053.4	1045.1	1039.6
45°	962.1	962.1	962.1	964.9	959.4	951.1	951.1	945.6	940.1	934.6	926.2
47.5°	854.3	862.7	857.0	854.3	857.0	846.0	846.0	840.5	835.0	829.5	818.4
50°	765.9	765.9	765.9	760.4	757.6	757.6	749.2	743.7	741.0	735.5	724.4
52.5°	685.6	680.1	680.1	677.3	674.6	669.1	669.1	663.6	652.6	646.9	638.7
55°	605.5	605.5	602.7	600.0	597.2	594.4	591.7	583.4	577.8	569.5	561.3
57.5°	533.6	539.1	536.3	530.8	525.3	525.3	519.8	514.3	505.9	497.6	489.4
60°	475.6	472.7	472.7	470.0	464.5	461.7	459.0	450.7	442.4	434.0	425.8
62.5°	414.7	414.7	414.7	409.2	403.6	400.9	398.1	392.6	381.6	373.3	367.7
65°	362.2	359.4	356.6	353.9	351.1	345.6	342.9	337.4	329.0	320.7	312.4
67.5°	309.7	306.9	306.9	304.2	295.8	293.0	293.0	284.8	276.5	268.2	259.8
70°	257.1	257.1	257.1	251.6	248.8	246.1	243.3	237.8	229.5	221.2	212.9
72.5°	212.9	210.1	210.1	207.4	199.1	196.4	193.5	188.0	179.7	174.2	168.7
75°	165.9	165.9	163.2	160.4	157.5	154.8	152.0	146.5	138.2	130.0	127.2
77.5°	127.2	124.5	124.5	121.6	116.1	113.3	113.3	107.8	99.6	94.0	88.5
80°	85.7	88.5	85.7	82.9	80.1	77.4	74.6	71.9	66.4	60.9	55.3
82.5°	52.5	55.3	52.5	52.5	49.7	47.0	47.0	41.5	38.7	35.9	33.2
85°	27.7	27.7	27.7	27.7	24.9	24.9	24.9	22.2	19.4	16.5	16.5
87.5°	8.3	11.0	8.3	8.3	8.3	8.3	8.3	8.3	5.5	5.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584412

CATALOG NUMBER: HCC8W35D010BZ-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9
2.5°	2079.1	2076.4	2073.6	2073.6	2073.6	2073.6	2073.6	2070.9	2068.1	2068.1	2068.1
5°	2073.6	2073.6	2073.6	2070.9	2068.1	2068.1	2062.6	2059.8	2057.0	2054.2	2051.5
7.5°	2068.1	2062.6	2059.8	2057.0	2054.2	2054.2	2048.7	2043.2	2043.2	2037.7	2032.2
10°	2051.5	2048.7	2043.2	2037.7	2034.9	2032.2	2026.7	2018.3	2015.5	2010.0	2004.5
12.5°	2032.2	2026.7	2021.0	2010.0	2007.2	2004.5	1993.5	1985.1	1979.6	1976.8	1963.0
15°	2007.2	1996.2	1987.8	1974.1	1971.3	1965.8	1957.5	1949.1	1938.1	1929.9	1924.3
17.5°	1963.0	1951.9	1938.1	1924.3	1918.7	1918.7	1904.9	1893.9	1880.0	1874.5	1863.5
20°	1910.5	1896.7	1885.7	1869.0	1860.7	1852.5	1844.1	1827.5	1816.5	1808.1	1794.4
22.5°	1849.7	1830.3	1816.5	1799.9	1786.1	1777.7	1763.9	1750.2	1736.3	1728.0	1717.0
25°	1772.2	1755.7	1733.5	1717.0	1708.7	1697.6	1681.0	1667.1	1653.4	1639.6	1634.0
27.5°	1686.5	1664.4	1645.1	1625.7	1617.4	1609.2	1589.7	1573.2	1562.1	1548.3	1542.8
30°	1592.5	1570.5	1548.3	1531.8	1523.4	1509.6	1498.6	1479.2	1465.4	1454.3	1440.5
32.5°	1484.7	1468.1	1448.7	1423.8	1418.3	1407.3	1390.6	1382.4	1365.8	1357.6	1346.4
35°	1368.6	1357.6	1338.2	1318.8	1310.5	1305.0	1291.2	1274.6	1263.5	1255.3	1249.6
37.5°	1258.0	1244.1	1224.8	1210.9	1205.4	1197.2	1180.6	1172.2	1161.2	1155.7	1144.7
40°	1139.1	1125.3	1111.5	1103.1	1094.9	1089.3	1078.3	1069.9	1058.9	1050.6	1047.9
42.5°	1023.0	1014.7	1003.7	992.5	989.8	981.5	976.0	967.6	959.4	956.6	948.3
45°	917.9	909.6	898.6	887.5	884.7	879.2	876.5	868.2	862.7	862.7	862.7
47.5°	812.8	804.6	793.6	787.9	790.7	779.7	779.7	776.9	771.4	771.4	774.1
50°	718.8	707.8	705.0	699.5	694.0	688.5	691.2	682.9	682.9	688.5	685.6
52.5°	630.4	619.4	616.6	611.0	608.2	608.2	605.5	605.5	602.7	605.5	605.5
55°	550.2	541.9	536.3	530.8	528.1	528.1	528.1	525.3	522.6	528.1	530.8
57.5°	478.4	475.6	470.0	461.7	459.0	456.2	453.4	453.4	453.4	453.4	456.2
60°	414.7	409.2	403.6	395.3	395.3	392.6	389.8	387.1	387.1	387.1	387.1
62.5°	359.4	351.1	342.9	337.4	334.6	331.7	329.0	323.5	323.5	323.5	323.5
65°	304.2	295.8	290.3	284.8	279.3	279.3	273.7	271.0	265.5	262.6	257.1
67.5°	251.6	246.1	240.6	232.3	229.5	226.7	221.2	218.4	210.1	207.4	204.6
70°	204.6	196.4	190.7	185.2	182.5	176.9	171.4	165.9	160.4	154.8	149.3
72.5°	160.4	152.0	146.5	141.0	135.5	135.5	127.2	121.6	113.3	107.8	99.6
75°	118.8	110.6	105.1	96.8	94.0	91.3	82.9	77.4	69.1	60.9	55.3
77.5°	80.1	74.6	69.1	60.9	55.3	55.3	47.0	41.5	35.9	27.7	24.9
80°	49.7	44.2	38.7	33.2	33.2	27.7	24.9	19.4	13.8	11.0	8.3
82.5°	27.7	24.9	22.2	16.5	16.5	13.8	11.0	8.3	5.5	2.8	2.8
85°	13.8	11.0	8.3	8.3	5.5	5.5	5.5	2.8	2.8	0.0	0.0
87.5°	5.5	2.8	2.8	2.8	2.8	2.8	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584412

CATALOG NUMBER: HCC8W35D010BZ-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9
2.5°	2065.4	2065.4	2062.6	2062.6	2062.6	2059.8	2062.6	2059.8	2059.8	2059.8	2062.6
5°	2054.2	2048.7	2048.7	2045.9	2045.9	2043.2	2045.9	2043.2	2040.4	2037.7	2040.4
7.5°	2032.2	2026.7	2023.8	2021.0	2021.0	2021.0	2018.3	2015.5	2018.3	2010.0	2015.5
10°	2001.7	1999.0	1993.5	1990.7	1987.8	1990.7	1987.8	1982.3	1982.3	1982.3	1979.6
12.5°	1963.0	1957.5	1954.8	1951.9	1946.4	1946.4	1949.1	1943.6	1943.6	1938.1	1938.1
15°	1916.0	1910.5	1904.9	1904.9	1899.4	1899.4	1896.7	1896.7	1893.9	1891.2	1891.2
17.5°	1858.0	1849.7	1844.1	1846.8	1844.1	1841.3	1841.3	1835.8	1833.1	1835.8	1835.8
20°	1788.9	1783.3	1777.7	1780.6	1775.0	1772.2	1775.0	1766.7	1769.4	1769.4	1769.4
22.5°	1711.5	1708.7	1700.3	1700.3	1694.8	1692.1	1694.8	1694.8	1697.6	1694.8	1694.8
25°	1625.7	1620.2	1614.7	1614.7	1611.9	1609.2	1611.9	1614.7	1611.9	1614.7	1614.7
27.5°	1534.5	1526.1	1526.1	1520.6	1520.6	1523.4	1520.6	1523.4	1526.1	1526.1	1531.8
30°	1435.0	1432.2	1429.5	1426.7	1426.7	1429.5	1429.5	1429.5	1432.2	1437.7	1437.7
32.5°	1340.9	1335.4	1329.9	1329.9	1335.4	1332.7	1335.4	1335.4	1340.9	1340.9	1346.4
35°	1238.6	1238.6	1233.1	1235.9	1235.9	1235.9	1235.9	1241.4	1246.9	1249.6	1255.3
37.5°	1144.7	1136.3	1139.1	1139.1	1141.8	1139.1	1147.4	1147.4	1153.0	1153.0	1158.5
40°	1042.4	1042.4	1045.1	1042.4	1045.1	1045.1	1050.6	1056.2	1058.9	1064.4	1067.2
42.5°	945.6	951.1	945.6	948.3	951.1	953.8	956.6	959.4	970.5	976.0	984.3
45°	857.0	859.8	862.7	865.4	862.7	868.2	870.9	876.5	884.7	887.5	890.2
47.5°	771.4	774.1	776.9	779.7	779.7	785.2	787.9	793.6	799.1	801.8	804.6
50°	688.5	694.0	696.8	696.8	699.5	705.0	710.5	710.5	716.0	724.4	727.2
52.5°	613.7	613.7	619.4	622.1	624.9	624.9	633.1	635.9	638.7	644.2	649.7
55°	530.8	539.1	541.9	541.9	547.5	553.0	555.8	558.5	558.5	569.5	569.5
57.5°	459.0	461.7	467.2	467.2	467.2	475.6	475.6	481.1	483.9	486.6	492.1
60°	387.1	392.6	392.6	395.3	392.6	398.1	400.9	406.5	409.2	412.0	414.7
62.5°	320.7	320.7	323.5	323.5	323.5	323.5	329.0	329.0	334.6	337.4	340.1
65°	257.1	257.1	257.1	257.1	257.1	257.1	257.1	257.1	259.8	259.8	265.5
67.5°	199.1	196.4	190.7	193.5	190.7	190.7	188.0	188.0	190.7	190.7	196.4
70°	143.8	141.0	135.5	135.5	132.7	130.0	127.2	124.5	121.6	121.6	121.6
72.5°	94.0	88.5	80.1	77.4	77.4	71.9	66.4	63.6	63.6	63.6	63.6
75°	47.0	41.5	35.9	33.2	33.2	27.7	30.4	27.7	27.7	27.7	27.7
77.5°	19.4	13.8	11.0	11.0	11.0	8.3	8.3	8.3	8.3	8.3	8.3
80°	5.5	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584412

CATALOG NUMBER: HCC8W35D010BZ-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9	2070.9
2.5°	2059.8	2059.8	2054.2	2057.0	2057.0	2057.0	2057.0	2057.0
5°	2034.9	2037.7	2034.9	2037.7	2037.7	2034.9	2034.9	2034.9
7.5°	2010.0	2012.8	2010.0	2012.8	2012.8	2012.8	2010.0	2010.0
10°	1979.6	1979.6	1979.6	1979.6	1979.6	1976.8	1979.6	1979.6
12.5°	1938.1	1938.1	1938.1	1940.9	1940.9	1938.1	1938.1	1935.4
15°	1893.9	1888.4	1891.2	1893.9	1891.2	1891.2	1891.2	1891.2
17.5°	1833.1	1835.8	1833.1	1833.1	1833.1	1833.1	1835.8	1833.1
20°	1769.4	1769.4	1772.2	1769.4	1769.4	1769.4	1769.4	1766.7
22.5°	1697.6	1694.8	1694.8	1697.6	1697.6	1694.8	1697.6	1697.6
25°	1617.4	1620.2	1617.4	1617.4	1620.2	1620.2	1620.2	1617.4
27.5°	1531.8	1534.5	1537.3	1534.5	1534.5	1534.5	1537.3	1540.0
30°	1443.2	1448.7	1443.2	1443.2	1448.7	1446.0	1448.7	1448.7
32.5°	1349.2	1357.6	1351.9	1357.6	1357.6	1360.3	1357.6	1360.3
35°	1255.3	1263.5	1263.5	1263.5	1266.3	1269.0	1269.0	1266.3
37.5°	1166.7	1169.5	1169.5	1175.0	1177.8	1180.6	1180.6	1177.8
40°	1075.6	1081.1	1083.8	1083.8	1083.8	1089.3	1094.9	1089.3
42.5°	987.0	989.8	992.5	992.5	998.1	1000.8	1003.7	1003.7
45°	901.4	906.9	909.6	912.4	915.2	920.7	917.9	923.4
47.5°	812.8	821.1	823.9	826.6	832.3	835.0	837.8	840.5
50°	732.7	738.2	738.2	743.7	752.0	752.0	757.6	760.4
52.5°	652.6	655.3	658.1	660.8	666.3	671.8	671.8	677.3
55°	575.0	577.8	577.8	580.6	583.4	594.4	597.2	597.2
57.5°	494.9	494.9	500.4	503.2	505.9	511.5	511.5	511.5
60°	417.5	420.3	420.3	423.0	425.8	431.3	434.0	431.3
62.5°	340.1	342.9	342.9	345.6	351.1	353.9	351.1	351.1
65°	268.2	271.0	271.0	273.7	279.3	279.3	276.5	279.3
67.5°	196.4	196.4	196.4	196.4	196.4	196.4	196.4	196.4
70°	124.5	121.6	118.8	121.6	121.6	121.6	118.8	124.5
72.5°	60.9	63.6	63.6	63.6	63.6	63.6	63.6	60.9
75°	27.7	27.7	24.9	24.9	24.9	27.7	27.7	24.9
77.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3
80°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)