

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584588

Luminaire Tested: **HCC8W40D010BZ-HM82555927-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584588  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W40D010BZ-HM82555927-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4108.3 lumens  
Efficiency: N/A  
Efficacy: 100.2 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584588  
CATALOG NUMBER: HCC8W40D010BZ-HM82555927-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P584588  
 CATALOG NUMBER: HCC8W40D010BZ-HM82555927-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72151
5°	71656
10°	71467
15°	73342
20°	79400
25°	85128
30°	83224
35°	69299
40°	42577
45°	29480
50°	22499
55°	14752
60°	9232
65°	6917
70°	6978
75°	8030
80°	8861
85°	7961



TEST NUMBER: P584588  
 CATALOG NUMBER: HCC8W40D010BZ-HM82555927-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.9	5.4
10°-20°	659.5	16.1
20°-30°	1135.3	27.6
30°-40°	1100.0	26.8
40°-50°	541.8	13.2
50°-60°	255.7	6.2
60°-70°	100.8	2.5
70°-80°	69.5	1.7
80°-90°	25.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2014.8	49.0
0°-40°	3114.7	75.8
0°-60°	3912.2	95.2
0°-90°	4108.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4108.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2340	
5°	2315	220
15°	2297	659
25°	2502	1135
35°	1841	1100
45°	676	542
55°	274	256
65°	95	101
75°	67	70
85°	22	26
90°	0	



TEST NUMBER: P584588  
CATALOG NUMBER: HCC8W40D010BZ-HM82555927-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2339.8
2.5°	2332.3
5°	2314.9
7.5°	2297.4
10°	2282.4
12.5°	2279.9
15°	2297.4
17.5°	2349.8
20°	2419.6
22.5°	2482.0
25°	2502.0
27.5°	2457.0
30°	2337.3
32.5°	2140.2
35°	1840.9
37.5°	1429.3
40°	1057.7
42.5°	820.6
45°	676.0
47.5°	568.7
50°	469.0
52.5°	369.1
55°	274.4
57.5°	199.6
60°	149.7
62.5°	117.2
65°	94.8
67.5°	82.3
70°	77.4
72.5°	72.4
75°	67.4
77.5°	59.9
80°	49.9
82.5°	37.4
85°	22.5
87.5°	10.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)