

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593700

Luminaire Tested: **HCC8S35D010BZ-HM82555850-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010BZ-HM82555850-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3729.9 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593700
CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593700

CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61744	61744	61744
5°	64298	61611	59017
10°	66447	60827	56139
15°	68129	59433	53221
20°	68262	56967	50585
25°	67113	53363	47967
30°	63519	49241	45719
35°	57916	44281	42929
40°	50362	39038	39642
45°	43204	33806	36287
50°	36901	29148	32593
55°	32343	25107	28322
60°	28801	21413	23812
65°	25552	17475	19000
70°	22675	12947	10792
75°	18896	6779	3217
80°	14899	2131	533
85°	10614	1061	0



TEST NUMBER: P593700
 CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.7	5.1
10°-20°	528.8	14.2
20°-30°	748.5	20.1
30°-40°	783.1	21.0
40°-50°	653.1	17.5
50°-60°	463.2	12.4
60°-70°	266.8	7.2
70°-80°	85.9	2.3
80°-90°	11.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1466.0	39.3
0°-40°	2249.1	60.3
0°-60°	3365.4	90.2
0°-90°	3729.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3729.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2002	2002	2002	2002	2002	
5°	2077	2050	1990	1931	1907	199
15°	2134	2047	1862	1715	1667	600
25°	1972	1826	1568	1443	1410	900
35°	1538	1404	1176	1113	1140	954
45°	991	910	775	784	832	768
55°	602	539	467	491	527	544
65°	350	293	240	240	260	350
75°	159	117	57	27	27	172
85°	30	15	3	0	0	37
90°	0	0	0	0	0	



TEST NUMBER: P593700

CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3
2.5°	2044.3	2041.3	2038.3	2041.3	2038.3	2041.3	2038.3	2038.3	2035.3	2032.3	2032.3
5°	2077.2	2074.2	2074.2	2074.2	2071.2	2068.2	2068.2	2065.2	2059.2	2056.2	2050.3
7.5°	2098.2	2101.2	2101.2	2101.2	2095.2	2095.2	2089.2	2083.2	2077.2	2071.2	2062.2
10°	2122.1	2122.1	2119.1	2116.1	2110.2	2107.2	2104.2	2098.2	2089.2	2077.2	2068.2
12.5°	2131.1	2131.1	2128.1	2122.1	2119.1	2116.1	2113.2	2104.2	2092.2	2077.2	2065.2
15°	2134.1	2128.1	2125.1	2122.1	2116.1	2107.2	2107.2	2095.2	2080.2	2062.2	2047.3
17.5°	2110.2	2113.2	2107.2	2101.2	2092.2	2086.2	2077.2	2068.2	2050.3	2029.3	2014.3
20°	2080.2	2077.2	2074.2	2065.2	2053.3	2050.3	2041.3	2026.3	2011.3	1987.4	1966.5
22.5°	2032.3	2029.3	2023.3	2017.3	2005.3	1999.3	1990.4	1972.5	1951.5	1927.6	1903.6
25°	1972.5	1966.5	1957.5	1945.6	1936.6	1930.6	1918.6	1900.6	1876.7	1849.7	1825.8
27.5°	1876.7	1885.7	1879.7	1861.7	1852.7	1840.7	1837.7	1813.8	1792.9	1766.0	1739.0
30°	1783.9	1783.9	1775.0	1766.0	1751.0	1742.0	1730.0	1712.1	1691.1	1658.2	1637.2
32.5°	1667.1	1664.1	1652.2	1649.2	1637.2	1619.2	1616.2	1592.4	1571.4	1547.5	1520.5
35°	1538.5	1532.5	1520.5	1511.5	1505.5	1496.5	1487.6	1466.6	1445.6	1421.7	1403.8
37.5°	1391.8	1391.8	1388.8	1373.9	1367.9	1361.9	1352.9	1331.9	1320.0	1296.0	1278.0
40°	1251.1	1248.1	1239.1	1236.1	1230.1	1221.2	1215.3	1203.3	1185.3	1167.3	1149.4
42.5°	1113.4	1116.4	1104.4	1107.4	1095.5	1089.5	1086.5	1068.5	1059.5	1041.5	1026.7
45°	990.7	987.8	981.8	978.8	972.8	966.8	960.8	951.8	936.8	918.9	909.9
47.5°	876.9	868.0	868.0	865.0	862.0	850.0	847.1	838.1	829.1	811.2	799.2
50°	769.2	769.2	769.2	766.2	757.3	754.3	748.3	739.3	730.3	718.3	700.4
52.5°	682.4	682.4	682.4	679.4	667.4	664.4	661.4	649.6	637.6	628.6	616.6
55°	601.6	604.6	601.6	595.6	586.7	586.7	577.7	571.7	559.7	550.7	538.7
57.5°	532.8	532.8	526.8	523.8	517.8	514.8	508.8	502.8	487.8	478.8	464.0
60°	467.0	464.0	464.0	458.0	452.0	446.0	443.0	434.0	428.0	413.1	401.1
62.5°	407.1	407.1	401.1	401.1	389.1	389.1	386.1	377.1	368.1	353.2	347.2
65°	350.2	350.2	347.2	344.2	335.2	332.2	329.2	320.2	311.2	302.3	293.3
67.5°	299.3	299.3	293.3	290.3	284.3	281.4	275.4	269.4	260.4	251.5	242.5
70°	251.5	248.5	245.5	242.5	236.5	233.5	227.5	221.5	212.5	206.5	197.6
72.5°	203.5	203.5	200.5	194.6	191.6	188.6	185.6	179.6	170.6	161.6	155.6
75°	158.6	158.6	158.6	152.6	146.6	143.6	143.6	137.7	131.7	122.7	116.7
77.5°	122.7	119.7	116.7	116.7	110.7	107.7	104.7	101.7	92.8	89.8	83.9
80°	83.9	86.9	83.9	80.9	77.9	74.9	74.9	68.9	65.9	59.9	53.9
82.5°	56.9	53.9	53.9	50.9	50.9	47.9	47.9	41.9	38.9	35.9	32.9
85°	30.0	30.0	27.0	27.0	27.0	24.0	24.0	21.0	21.0	18.0	15.0
87.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	6.0	6.0	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593700

CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3
2.5°	2029.3	2023.3	2020.3	2020.3	2017.3	2014.3	2011.3	2008.3	2002.3	2002.3	1996.3
5°	2044.3	2038.3	2035.3	2026.3	2020.3	2020.3	2008.3	2005.3	1996.3	1990.4	1984.4
7.5°	2056.2	2044.3	2035.3	2026.3	2020.3	2014.3	2002.3	1990.4	1978.5	1966.5	1960.5
10°	2056.2	2044.3	2029.3	2014.3	2008.3	2002.3	1987.4	1969.5	1954.5	1942.6	1927.6
12.5°	2050.3	2032.3	2014.3	2002.3	1990.4	1981.5	1963.5	1945.6	1927.6	1903.6	1891.6
15°	2032.3	2008.3	1990.4	1969.5	1960.5	1945.6	1930.6	1903.6	1882.7	1861.7	1846.7
17.5°	1996.3	1966.5	1945.6	1924.6	1909.6	1900.6	1876.7	1852.7	1828.7	1804.8	1786.9
20°	1942.6	1915.6	1891.6	1864.7	1852.7	1840.7	1810.8	1786.9	1763.0	1736.0	1718.1
22.5°	1876.7	1849.7	1816.8	1795.8	1778.0	1763.0	1736.0	1709.1	1685.1	1661.1	1637.2
25°	1795.8	1769.0	1739.0	1706.1	1694.1	1679.1	1649.2	1622.2	1595.4	1568.4	1547.5
27.5°	1709.1	1673.1	1649.2	1613.2	1601.4	1586.4	1553.4	1523.5	1499.5	1478.6	1454.6
30°	1604.4	1577.4	1544.5	1511.5	1499.5	1484.6	1457.6	1430.7	1406.8	1382.9	1358.9
32.5°	1490.6	1463.6	1430.7	1406.8	1388.8	1376.9	1349.9	1325.9	1302.0	1278.0	1257.1
35°	1370.9	1340.9	1317.0	1293.0	1278.0	1263.1	1236.1	1215.3	1197.3	1176.3	1155.4
37.5°	1248.1	1227.2	1203.3	1176.3	1161.3	1149.4	1128.4	1104.4	1089.5	1071.5	1056.5
40°	1128.4	1104.4	1083.5	1059.5	1047.5	1038.5	1017.7	999.7	984.8	969.8	960.8
42.5°	1005.7	984.8	963.8	948.8	939.8	930.8	915.9	894.9	885.9	870.9	862.0
45°	891.9	873.9	859.0	838.1	832.1	826.1	808.2	793.2	784.2	775.2	769.2
47.5°	784.2	772.2	754.3	742.3	733.3	727.3	715.3	703.3	694.4	688.4	682.4
50°	691.4	676.4	664.4	652.6	646.6	637.6	625.6	619.6	613.6	607.6	607.6
52.5°	604.6	589.7	577.7	568.7	562.7	556.7	547.7	544.7	538.7	538.7	535.7
55°	523.8	514.8	502.8	490.8	487.8	484.8	478.8	472.9	470.0	467.0	470.0
57.5°	455.0	446.0	434.0	425.1	422.1	419.1	416.1	410.1	407.1	407.1	407.1
60°	392.1	383.1	374.1	365.2	365.2	359.2	356.2	353.2	350.2	347.2	347.2
62.5°	335.2	326.2	317.2	311.2	308.2	305.3	299.3	296.3	293.3	293.3	290.3
65°	284.3	272.4	269.4	260.4	257.5	254.5	251.5	245.5	242.5	239.5	236.5
67.5°	233.5	227.5	218.5	212.5	209.5	206.5	203.5	197.6	194.6	191.6	185.6
70°	188.6	182.6	176.6	170.6	167.6	164.6	158.6	152.6	149.6	143.6	134.7
72.5°	146.6	140.6	134.7	128.7	125.7	122.7	116.7	110.7	104.7	98.7	92.8
75°	110.7	104.7	95.7	89.8	86.9	86.9	77.9	71.9	65.9	56.9	50.9
77.5°	77.9	68.9	65.9	59.9	56.9	50.9	44.9	38.9	32.9	30.0	24.0
80°	50.9	44.9	38.9	35.9	32.9	30.0	27.0	21.0	15.0	12.0	9.0
82.5°	30.0	27.0	24.0	21.0	18.0	15.0	12.0	12.0	9.0	6.0	3.0
85°	15.0	12.0	9.0	9.0	6.0	6.0	6.0	3.0	3.0	3.0	3.0
87.5°	6.0	3.0	3.0	3.0	3.0	3.0	3.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593700

CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3
2.5°	1993.4	1990.4	1987.4	1984.4	1984.4	1978.5	1978.5	1975.5	1969.5	1966.5	1966.5
5°	1975.5	1966.5	1960.5	1957.5	1954.5	1945.6	1942.6	1936.6	1930.6	1924.6	1921.6
7.5°	1948.5	1933.6	1927.6	1924.6	1915.6	1906.6	1900.6	1891.6	1882.7	1873.7	1870.7
10°	1915.6	1900.6	1885.7	1879.7	1870.7	1864.7	1852.7	1840.7	1831.7	1822.8	1813.8
12.5°	1873.7	1855.7	1840.7	1834.7	1825.8	1813.8	1795.8	1789.9	1775.0	1769.0	1757.0
15°	1825.8	1804.8	1789.9	1780.9	1772.0	1754.0	1742.0	1730.0	1715.1	1709.1	1697.1
17.5°	1766.0	1742.0	1727.0	1718.1	1712.1	1697.1	1679.1	1664.1	1649.2	1643.2	1634.2
20°	1694.1	1679.1	1658.2	1649.2	1643.2	1625.2	1607.2	1601.4	1589.4	1577.4	1568.4
22.5°	1613.2	1598.4	1577.4	1568.4	1565.4	1550.5	1535.5	1526.5	1517.5	1508.5	1499.5
25°	1529.5	1511.5	1493.5	1487.6	1481.6	1469.6	1457.6	1451.6	1442.6	1436.6	1430.7
27.5°	1439.6	1421.7	1406.8	1397.8	1391.8	1382.9	1376.9	1370.9	1364.9	1358.9	1355.9
30°	1343.9	1325.9	1314.0	1308.0	1302.0	1299.0	1290.0	1287.0	1284.0	1278.0	1281.0
32.5°	1248.1	1233.1	1221.2	1212.3	1212.3	1206.3	1203.3	1203.3	1200.3	1200.3	1200.3
35°	1143.4	1134.4	1125.4	1122.4	1119.4	1116.4	1113.4	1116.4	1113.4	1116.4	1119.4
37.5°	1047.5	1038.5	1032.7	1029.7	1026.7	1029.7	1026.7	1026.7	1029.7	1035.7	1038.5
40°	948.8	942.8	936.8	939.8	936.8	936.8	936.8	945.8	948.8	951.8	954.8
42.5°	856.0	850.0	847.1	847.1	850.0	847.1	853.0	856.0	862.0	870.9	876.9
45°	766.2	763.2	763.2	766.2	763.2	769.2	769.2	775.2	784.2	790.2	796.2
47.5°	682.4	682.4	682.4	685.4	685.4	688.4	694.4	697.4	703.3	709.3	715.3
50°	604.6	607.6	610.6	610.6	610.6	616.6	622.6	625.6	628.6	631.6	640.6
52.5°	535.7	538.7	538.7	541.7	544.7	547.7	550.7	556.7	559.7	565.7	568.7
55°	470.0	470.0	475.8	478.8	478.8	478.8	484.8	484.8	490.8	493.8	499.8
57.5°	407.1	410.1	410.1	413.1	413.1	416.1	419.1	422.1	425.1	428.0	431.0
60°	347.2	347.2	347.2	350.2	353.2	356.2	353.2	359.2	359.2	365.2	368.1
62.5°	290.3	293.3	293.3	293.3	293.3	293.3	293.3	296.3	299.3	302.3	305.3
65°	236.5	236.5	236.5	233.5	236.5	233.5	236.5	239.5	239.5	242.5	245.5
67.5°	182.6	182.6	176.6	176.6	179.6	179.6	179.6	179.6	176.6	182.6	182.6
70°	131.7	128.7	125.7	122.7	122.7	119.7	119.7	116.7	116.7	116.7	116.7
72.5°	86.9	80.9	74.9	71.9	68.9	68.9	62.9	59.9	62.9	62.9	62.9
75°	44.9	38.9	35.9	32.9	30.0	30.0	27.0	27.0	27.0	27.0	27.0
77.5°	18.0	15.0	12.0	12.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
80°	6.0	6.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
85°	3.0	0.0	0.0	3.0	0.0	3.0	3.0	3.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P593700

CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3	2002.3
2.5°	1963.5	1963.5	1960.5	1963.5	1957.5	1960.5	1957.5	1957.5
5°	1918.6	1912.6	1912.6	1912.6	1909.6	1909.6	1906.6	1906.6
7.5°	1864.7	1861.7	1858.7	1855.7	1852.7	1849.7	1849.7	1849.7
10°	1810.8	1804.8	1804.8	1801.8	1795.8	1792.9	1792.9	1792.9
12.5°	1748.0	1745.0	1742.0	1742.0	1730.0	1733.0	1730.0	1730.0
15°	1688.1	1685.1	1685.1	1676.1	1670.1	1670.1	1670.1	1667.1
17.5°	1625.2	1622.2	1619.2	1613.2	1607.2	1607.2	1604.4	1607.2
20°	1559.4	1556.4	1550.5	1550.5	1547.5	1544.5	1538.5	1541.5
22.5°	1493.5	1487.6	1484.6	1484.6	1481.6	1481.6	1475.6	1475.6
25°	1424.7	1421.7	1418.7	1421.7	1415.8	1415.8	1409.8	1409.8
27.5°	1352.9	1349.9	1349.9	1349.9	1346.9	1349.9	1346.9	1346.9
30°	1281.0	1281.0	1278.0	1278.0	1281.0	1278.0	1281.0	1284.0
32.5°	1203.3	1203.3	1206.3	1206.3	1209.3	1209.3	1209.3	1209.3
35°	1122.4	1128.4	1128.4	1131.4	1134.4	1137.4	1137.4	1140.4
37.5°	1047.5	1050.5	1053.5	1056.5	1062.5	1062.5	1062.5	1062.5
40°	966.8	969.8	975.8	972.8	984.8	987.8	984.8	984.8
42.5°	882.9	888.9	891.9	897.9	900.9	906.9	909.9	909.9
45°	805.2	808.2	814.2	820.2	823.1	832.1	832.1	832.1
47.5°	724.3	730.3	733.3	739.3	742.3	751.3	754.3	751.3
50°	646.6	652.6	658.5	658.5	667.4	670.4	676.4	679.4
52.5°	571.7	574.7	580.7	583.7	589.7	595.6	598.6	601.6
55°	499.8	502.8	508.8	508.8	517.8	520.8	526.8	526.8
57.5°	434.0	437.0	443.0	440.0	446.0	452.0	452.0	449.0
60°	371.1	371.1	371.1	377.1	380.1	383.1	386.1	386.1
62.5°	305.3	311.2	314.2	314.2	317.2	320.2	320.2	317.2
65°	245.5	251.5	254.5	254.5	257.5	257.5	257.5	260.4
67.5°	185.6	185.6	185.6	188.6	185.6	185.6	185.6	185.6
70°	116.7	116.7	116.7	116.7	113.7	116.7	116.7	119.7
72.5°	62.9	62.9	62.9	62.9	62.9	62.9	62.9	62.9
75°	27.0	27.0	27.0	30.0	27.0	27.0	27.0	27.0
77.5°	12.0	9.0	12.0	12.0	9.0	9.0	9.0	9.0
80°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
85°	0.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)