

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584599

Luminaire Tested: **HCC8S40D010MW-HM82555930-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584599
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010MW-HM82555930-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4229.8 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584599
CATALOG NUMBER: HCC8S40D010MW-HM82555930-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584599

CATALOG NUMBER: HCC8S40D010MW-HM82555930-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	68626	68626	68626
5°	69535	68337	67694
10°	70245	67640	66616
15°	70955	66214	64883
20°	70596	63770	62303
25°	68950	59950	59141
30°	65491	55650	55440
35°	59621	50782	51230
40°	52270	45451	47125
45°	45092	40426	43282
50°	39482	35490	39203
55°	34983	30510	34504
60°	31521	25656	28585
65°	28398	20598	21897
70°	24911	15003	12063
75°	21243	7780	3193
80°	16355	2113	533
85°	10543	0	0



TEST NUMBER: P584599
 CATALOG NUMBER: HCC8S40D010MW-HM82555930-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.0	5.0
10°-20°	590.3	14.0
20°-30°	837.8	19.8
30°-40°	881.9	20.9
40°-50°	750.2	17.7
50°-60°	542.2	12.8
60°-70°	308.4	7.3
70°-80°	97.2	2.3
80°-90°	11.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1638.1	38.7
0°-40°	2520.0	59.6
0°-60°	3812.4	90.1
0°-90°	4229.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4229.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2226	2226	2226	2226	2226	
5°	2246	2234	2208	2193	2187	214
15°	2223	2166	2074	2035	2032	626
25°	2026	1925	1762	1732	1738	928
35°	1584	1492	1349	1340	1361	985
45°	1034	995	927	951	992	804
55°	651	603	568	600	642	587
65°	389	336	282	279	300	386
75°	178	137	65	30	27	192
85°	30	18	0	0	0	38
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584599

CATALOG NUMBER: HCC8S40D010MW-HM82555930-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5
2.5°	2237.4	2240.4	2234.5	2234.5	2240.4	2234.5	2237.4	2237.4	2234.5	2234.5	2231.5
5°	2246.4	2243.4	2243.4	2243.4	2246.4	2240.4	2237.4	2240.4	2234.5	2234.5	2234.5
7.5°	2249.3	2249.3	2246.4	2243.4	2243.4	2243.4	2240.4	2237.4	2234.5	2228.5	2225.5
10°	2243.4	2243.4	2246.4	2240.4	2240.4	2234.5	2234.5	2228.5	2228.5	2222.6	2213.6
12.5°	2237.4	2234.5	2234.5	2228.5	2228.5	2222.6	2222.6	2213.6	2210.7	2201.7	2192.8
15°	2222.6	2219.6	2213.6	2210.7	2207.7	2204.7	2198.8	2195.8	2186.9	2175.0	2166.2
17.5°	2192.8	2189.8	2186.9	2180.9	2175.0	2172.0	2169.1	2160.2	2148.3	2139.4	2124.5
20°	2151.3	2148.3	2148.3	2139.4	2136.4	2127.5	2124.5	2112.6	2103.7	2085.8	2074.1
22.5°	2094.8	2097.7	2091.8	2085.8	2079.9	2071.1	2065.1	2053.2	2038.4	2020.5	2005.6
25°	2026.5	2029.4	2023.5	2017.5	2008.6	2002.7	1996.7	1978.9	1964.1	1943.3	1925.4
27.5°	1940.3	1940.3	1940.3	1934.3	1919.5	1916.5	1910.5	1892.7	1872.0	1854.1	1836.3
30°	1839.3	1836.3	1836.3	1827.4	1821.4	1809.5	1800.6	1785.7	1771.0	1750.1	1729.3
32.5°	1717.4	1720.4	1711.5	1705.5	1696.6	1696.6	1684.8	1672.9	1655.1	1634.2	1613.4
35°	1583.8	1586.7	1580.8	1577.8	1562.9	1560.0	1557.0	1542.1	1530.2	1515.3	1491.7
37.5°	1447.0	1444.1	1441.1	1441.1	1432.2	1426.2	1420.3	1411.3	1393.6	1381.7	1369.8
40°	1298.5	1298.5	1298.5	1295.6	1292.6	1286.6	1283.7	1277.7	1265.8	1253.9	1245.0
42.5°	1164.8	1164.8	1161.8	1158.8	1152.9	1155.8	1149.9	1143.9	1132.0	1123.1	1117.2
45°	1034.0	1034.0	1034.0	1037.0	1031.0	1022.1	1022.1	1016.1	1010.3	1004.4	995.4
47.5°	918.1	927.0	921.1	918.1	921.1	909.3	909.3	903.3	897.4	891.4	879.5
50°	823.0	823.0	823.0	817.2	814.2	814.2	805.3	799.3	796.3	790.4	778.5
52.5°	736.8	730.9	730.9	727.9	724.9	719.1	719.1	713.2	701.3	695.3	686.4
55°	650.7	650.7	647.7	644.7	641.8	638.8	635.8	627.0	621.1	612.1	603.2
57.5°	573.5	579.4	576.4	570.5	564.5	564.5	558.6	552.6	543.7	534.8	526.0
60°	511.1	508.1	508.1	505.2	499.2	496.2	493.3	484.3	475.4	466.5	457.6
62.5°	445.7	445.7	445.7	439.7	433.9	430.9	427.9	422.0	410.1	401.1	395.2
65°	389.2	386.3	383.3	380.3	377.3	371.4	368.4	362.5	353.5	344.6	335.8
67.5°	332.8	329.9	329.9	326.9	318.0	315.0	315.0	306.1	297.1	288.2	279.3
70°	276.3	276.3	276.3	270.4	267.4	264.4	261.4	255.5	246.6	237.8	228.8
72.5°	228.8	225.9	225.9	222.9	214.0	211.0	208.0	202.1	193.1	187.2	181.2
75°	178.3	178.3	175.3	172.3	169.3	166.4	163.4	157.4	148.5	139.7	136.7
77.5°	136.7	133.8	133.8	130.8	124.8	121.9	121.9	115.9	107.0	101.0	95.1
80°	92.1	95.1	92.1	89.1	86.2	83.2	80.2	77.2	71.3	65.3	59.4
82.5°	56.4	59.4	56.4	56.4	53.4	50.5	50.5	44.6	41.6	38.7	35.7
85°	29.8	29.8	29.8	29.8	26.8	26.8	26.8	23.8	20.8	17.8	17.8
87.5°	8.9	11.9	8.9	8.9	8.9	8.9	8.9	8.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584599

CATALOG NUMBER: HCC8S40D010MW-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5
2.5°	2234.5	2231.5	2228.5	2228.5	2228.5	2228.5	2228.5	2225.5	2222.6	2222.6	2222.6
5°	2228.5	2228.5	2228.5	2225.5	2222.6	2222.6	2216.6	2213.6	2210.7	2207.7	2204.7
7.5°	2222.6	2216.6	2213.6	2210.7	2207.7	2207.7	2201.7	2195.8	2195.8	2189.8	2183.9
10°	2204.7	2201.7	2195.8	2189.8	2186.9	2183.9	2177.9	2169.1	2166.2	2160.2	2154.3
12.5°	2183.9	2177.9	2172.0	2160.2	2157.2	2154.3	2142.4	2133.4	2127.5	2124.5	2109.6
15°	2157.2	2145.3	2136.4	2121.5	2118.6	2112.6	2103.7	2094.8	2082.9	2074.1	2068.1
17.5°	2109.6	2097.7	2082.9	2068.1	2062.2	2062.2	2047.3	2035.4	2020.5	2014.6	2002.7
20°	2053.2	2038.4	2026.5	2008.6	1999.7	1990.8	1981.8	1964.1	1952.2	1943.3	1928.4
22.5°	1987.8	1967.1	1952.2	1934.3	1919.5	1910.5	1895.7	1880.9	1866.0	1857.1	1845.2
25°	1904.6	1886.7	1863.1	1845.2	1836.3	1824.4	1806.5	1791.7	1776.9	1762.0	1756.1
27.5°	1812.5	1788.7	1768.0	1747.2	1738.2	1729.3	1708.5	1690.6	1678.9	1664.0	1658.0
30°	1711.5	1687.8	1664.0	1646.1	1637.2	1622.3	1610.4	1589.7	1574.8	1562.9	1548.1
32.5°	1595.6	1577.8	1557.0	1530.2	1524.3	1512.4	1494.6	1485.7	1467.9	1458.9	1447.0
35°	1470.8	1458.9	1438.1	1417.3	1408.4	1402.4	1387.7	1369.8	1357.9	1349.0	1343.0
37.5°	1352.0	1337.1	1316.3	1301.5	1295.6	1286.6	1268.8	1259.9	1248.0	1242.0	1230.1
40°	1224.2	1209.3	1194.5	1185.6	1176.7	1170.7	1158.8	1149.9	1138.0	1129.1	1126.1
42.5°	1099.4	1090.5	1078.6	1066.7	1063.7	1054.8	1048.9	1039.9	1031.0	1028.0	1019.1
45°	986.5	977.6	965.7	953.8	950.8	944.9	941.9	933.0	927.0	927.0	927.0
47.5°	873.6	864.7	852.8	846.8	849.8	837.9	837.9	834.9	829.0	829.0	831.9
50°	772.5	760.6	757.7	751.7	745.8	739.8	742.8	733.9	733.9	739.8	736.8
52.5°	677.5	665.6	662.6	656.6	653.7	653.7	650.7	650.7	647.7	650.7	650.7
55°	591.3	582.4	576.4	570.5	567.5	567.5	567.5	564.5	561.6	567.5	570.5
57.5°	514.1	511.1	505.2	496.2	493.3	490.3	487.3	487.3	487.3	487.3	490.3
60°	445.7	439.7	433.9	424.9	424.9	422.0	419.0	416.0	416.0	416.0	416.0
62.5°	386.3	377.3	368.4	362.5	359.5	356.5	353.5	347.6	347.6	347.6	347.6
65°	326.9	318.0	312.0	306.1	300.1	300.1	294.2	291.2	285.2	282.3	276.3
67.5°	270.4	264.4	258.5	249.5	246.6	243.6	237.8	234.8	225.9	222.9	219.9
70°	219.9	211.0	205.0	199.1	196.1	190.2	184.2	178.3	172.3	166.4	160.4
72.5°	172.3	163.4	157.4	151.5	145.5	145.5	136.7	130.8	121.9	115.9	107.0
75°	127.8	118.9	112.9	104.0	101.0	98.1	89.1	83.2	74.3	65.3	59.4
77.5°	86.2	80.2	74.3	65.3	59.4	59.4	50.5	44.6	38.7	29.8	26.8
80°	53.4	47.6	41.6	35.7	35.7	29.8	26.8	20.8	14.9	11.9	8.9
82.5°	29.8	26.8	23.8	17.8	17.8	14.9	11.9	8.9	5.9	3.0	3.0
85°	14.9	11.9	8.9	8.9	5.9	5.9	5.9	3.0	3.0	0.0	0.0
87.5°	5.9	3.0	3.0	3.0	3.0	3.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584599

CATALOG NUMBER: HCC8S40D010MW-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5
2.5°	2219.6	2219.6	2216.6	2216.6	2216.6	2213.6	2216.6	2213.6	2213.6	2213.6	2216.6
5°	2207.7	2201.7	2201.7	2198.8	2198.8	2195.8	2198.8	2195.8	2192.8	2189.8	2192.8
7.5°	2183.9	2177.9	2175.0	2172.0	2172.0	2172.0	2169.1	2166.2	2169.1	2160.2	2166.2
10°	2151.3	2148.3	2142.4	2139.4	2136.4	2139.4	2136.4	2130.5	2130.5	2130.5	2127.5
12.5°	2109.6	2103.7	2100.7	2097.7	2091.8	2091.8	2094.8	2088.8	2088.8	2082.9	2082.9
15°	2059.2	2053.2	2047.3	2047.3	2041.3	2041.3	2038.4	2038.4	2035.4	2032.4	2032.4
17.5°	1996.7	1987.8	1981.8	1984.8	1981.8	1978.9	1978.9	1973.0	1970.0	1973.0	1973.0
20°	1922.4	1916.5	1910.5	1913.5	1907.6	1904.6	1907.6	1898.6	1901.6	1901.6	1901.6
22.5°	1839.3	1836.3	1827.4	1827.4	1821.4	1818.4	1821.4	1821.4	1824.4	1821.4	1821.4
25°	1747.2	1741.2	1735.3	1735.3	1732.3	1729.3	1732.3	1735.3	1732.3	1735.3	1735.3
27.5°	1649.1	1640.2	1640.2	1634.2	1634.2	1637.2	1634.2	1637.2	1640.2	1640.2	1646.1
30°	1542.1	1539.1	1536.2	1533.2	1533.2	1536.2	1536.2	1536.2	1539.1	1545.1	1545.1
32.5°	1441.1	1435.1	1429.2	1429.2	1435.1	1432.2	1435.1	1435.1	1441.1	1441.1	1447.0
35°	1331.1	1331.1	1325.2	1328.2	1328.2	1328.2	1328.2	1334.1	1340.1	1343.0	1349.0
37.5°	1230.1	1221.2	1224.2	1224.2	1227.1	1224.2	1233.1	1233.1	1239.0	1239.0	1245.0
40°	1120.1	1120.1	1123.1	1120.1	1123.1	1123.1	1129.1	1135.0	1138.0	1143.9	1146.9
42.5°	1016.1	1022.1	1016.1	1019.1	1022.1	1025.1	1028.0	1031.0	1042.9	1048.9	1057.8
45°	921.1	924.0	927.0	930.0	927.0	933.0	935.9	941.9	950.8	953.8	956.8
47.5°	829.0	831.9	834.9	837.9	837.9	843.8	846.8	852.8	858.7	861.7	864.7
50°	739.8	745.8	748.7	748.7	751.7	757.7	763.6	763.6	769.6	778.5	781.5
52.5°	659.6	659.6	665.6	668.5	671.5	671.5	680.4	683.4	686.4	692.3	698.3
55°	570.5	579.4	582.4	582.4	588.3	594.3	597.3	600.2	600.2	612.1	612.1
57.5°	493.3	496.2	502.2	502.2	502.2	511.1	511.1	517.1	520.0	523.0	529.0
60°	416.0	422.0	422.0	424.9	422.0	427.9	430.9	436.7	439.7	442.7	445.7
62.5°	344.6	344.6	347.6	347.6	347.6	347.6	353.5	353.5	359.5	362.5	365.4
65°	276.3	276.3	276.3	276.3	276.3	276.3	276.3	276.3	279.3	279.3	285.2
67.5°	214.0	211.0	205.0	208.0	205.0	205.0	202.1	202.1	205.0	205.0	211.0
70°	154.5	151.5	145.5	145.5	142.7	139.7	136.7	133.8	130.8	130.8	130.8
72.5°	101.0	95.1	86.2	83.2	83.2	77.2	71.3	68.3	68.3	68.3	68.3
75°	50.5	44.6	38.7	35.7	35.7	29.8	32.7	29.8	29.8	29.8	29.8
77.5°	20.8	14.9	11.9	11.9	11.9	8.9	8.9	8.9	8.9	8.9	8.9
80°	5.9	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584599

CATALOG NUMBER: HCC8S40D010MW-HM82555930-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5	2225.5
2.5°	2213.6	2213.6	2207.7	2210.7	2210.7	2210.7	2210.7	2210.7
5°	2186.9	2189.8	2186.9	2189.8	2189.8	2186.9	2186.9	2186.9
7.5°	2160.2	2163.2	2160.2	2163.2	2163.2	2163.2	2160.2	2160.2
10°	2127.5	2127.5	2127.5	2127.5	2127.5	2124.5	2127.5	2127.5
12.5°	2082.9	2082.9	2082.9	2085.8	2085.8	2082.9	2082.9	2079.9
15°	2035.4	2029.4	2032.4	2035.4	2032.4	2032.4	2032.4	2032.4
17.5°	1970.0	1973.0	1970.0	1970.0	1970.0	1970.0	1973.0	1970.0
20°	1901.6	1901.6	1904.6	1901.6	1901.6	1901.6	1901.6	1898.6
22.5°	1824.4	1821.4	1821.4	1824.4	1824.4	1821.4	1824.4	1824.4
25°	1738.2	1741.2	1738.2	1738.2	1741.2	1741.2	1741.2	1738.2
27.5°	1646.1	1649.1	1652.1	1649.1	1649.1	1649.1	1652.1	1655.1
30°	1551.0	1557.0	1551.0	1551.0	1557.0	1554.0	1557.0	1557.0
32.5°	1450.0	1458.9	1453.0	1458.9	1458.9	1461.9	1458.9	1461.9
35°	1349.0	1357.9	1357.9	1357.9	1360.9	1363.9	1363.9	1360.9
37.5°	1253.9	1256.9	1256.9	1262.8	1265.8	1268.8	1268.8	1265.8
40°	1155.8	1161.8	1164.8	1164.8	1164.8	1170.7	1176.7	1170.7
42.5°	1060.8	1063.7	1066.7	1066.7	1072.7	1075.6	1078.6	1078.6
45°	968.7	974.6	977.6	980.6	983.5	989.5	986.5	992.5
47.5°	873.6	882.5	885.5	888.5	894.4	897.4	900.4	903.3
50°	787.4	793.4	793.4	799.3	808.2	808.2	814.2	817.2
52.5°	701.3	704.2	707.2	710.2	716.1	722.1	722.1	727.9
55°	618.1	621.1	621.1	624.0	627.0	638.8	641.8	641.8
57.5°	531.8	531.8	537.8	540.7	543.7	549.7	549.7	549.7
60°	448.6	451.6	451.6	454.6	457.6	463.5	466.5	463.5
62.5°	365.4	368.4	368.4	371.4	377.3	380.3	377.3	377.3
65°	288.2	291.2	291.2	294.2	300.1	300.1	297.1	300.1
67.5°	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0
70°	133.8	130.8	127.8	130.8	130.8	130.8	127.8	133.8
72.5°	65.3	68.3	68.3	68.3	68.3	68.3	68.3	65.3
75°	29.8	29.8	26.8	26.8	26.8	29.8	29.8	26.8
77.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
80°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)