

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584449

Luminaire Tested: **HCC8S35D010MB-HM82555927-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584449  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S35D010MB-HM82555927-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3616.9 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584449  
CATALOG NUMBER: HCC8S35D010MB-HM82555927-81WDC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584449

CATALOG NUMBER: HCC8S35D010MB-HM82555927-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92											92																	
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84											84																	
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77											77																	
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70											70																	
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64											64																	
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59											59																	
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54											54																	
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50											50																	
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46											46																	
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43											43																	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	86776
5°	84443
10°	83800
15°	82553
20°	80053
25°	77068
30°	71986
35°	59576
40°	35967
45°	24225
50°	17453
55°	9957
60°	4379
65°	1576
70°	586
75°	262
80°	0
85°	0



TEST NUMBER: P584449  
 CATALOG NUMBER: HCC8S35D010MB-HM82555927-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	259.2	7.2
10°-20°	726.7	20.1
20°-30°	1036.7	28.7
30°-40°	944.0	26.1
40°-50°	445.3	12.3
50°-60°	175.1	4.8
60°-70°	27.9	0.8
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2022.6	55.9
0°-40°	2966.6	82.0
0°-60°	3587.0	99.2
0°-90°	3616.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3616.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2814	
5°	2728	259
15°	2586	727
25°	2265	1037
35°	1583	944
45°	556	445
55°	185	175
65°	22	28
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P584449  
CATALOG NUMBER: HCC8S35D010MB-HM82555927-81WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2814.1
2.5°	2777.4
5°	2728.0
7.5°	2699.9
10°	2676.3
12.5°	2637.5
15°	2585.9
17.5°	2521.3
20°	2439.5
22.5°	2353.4
25°	2265.1
27.5°	2157.4
30°	2021.7
32.5°	1838.7
35°	1582.6
37.5°	1222.9
40°	893.5
42.5°	686.8
45°	555.5
47.5°	456.4
50°	363.8
52.5°	273.4
55°	185.2
57.5°	116.3
60°	71.0
62.5°	43.0
65°	21.6
67.5°	10.8
70°	6.5
72.5°	2.2
75°	2.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)