

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584453

Luminaire Tested: **HCC8W35D010BZ-HM82555927-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010BZ-HM82555927-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2682.5 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584453
CATALOG NUMBER: HCC8W35D010BZ-HM82555927-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584453

CATALOG NUMBER: HCC8W35D010BZ-HM82555927-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	44407	44407	44407
5°	46242	44311	42444
10°	47792	43746	40374
15°	49000	42743	38280
20°	49095	40973	36379
25°	48267	38379	34497
30°	45680	35411	32883
35°	41653	31847	30876
40°	36221	28077	28512
45°	31076	24312	26096
50°	26539	20964	23444
55°	23263	18053	20365
60°	20710	15400	17126
65°	18373	12565	13659
70°	16301	9313	7763
75°	13582	4873	2311
80°	10708	1527	391
85°	7642	778	0



TEST NUMBER: P584453
 CATALOG NUMBER: HCC8W35D010BZ-HM82555927-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	5.1
10°-20°	380.3	14.2
20°-30°	538.3	20.1
30°-40°	563.2	21.0
40°-50°	469.7	17.5
50°-60°	333.1	12.4
60°-70°	191.9	7.2
70°-80°	61.7	2.3
80°-90°	8.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1054.4	39.3
0°-40°	1617.5	60.3
0°-60°	2420.4	90.2
0°-90°	2682.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2682.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1440	1440	1440	1440	1440	
5°	1494	1474	1432	1388	1371	143
15°	1535	1472	1339	1234	1199	432
25°	1419	1313	1128	1038	1014	647
35°	1106	1010	846	801	820	686
45°	713	654	558	564	598	552
55°	433	387	336	353	379	391
65°	252	211	172	172	187	252
75°	114	84	41	19	19	124
85°	22	11	2	0	0	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584453

CATALOG NUMBER: HCC8W35D010BZ-HM82555927-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1
2.5°	1470.3	1468.1	1466.0	1468.1	1466.0	1468.1	1466.0	1466.0	1463.8	1461.7	1461.7
5°	1493.9	1491.7	1491.7	1491.7	1489.6	1487.4	1487.4	1485.3	1481.0	1478.8	1474.5
7.5°	1509.0	1511.2	1511.2	1511.2	1506.8	1506.8	1502.5	1498.2	1493.9	1489.6	1483.1
10°	1526.3	1526.3	1524.1	1521.9	1517.6	1515.5	1513.3	1509.0	1502.5	1493.9	1487.4
12.5°	1532.7	1532.7	1530.6	1526.3	1524.1	1521.9	1519.8	1513.3	1504.7	1493.9	1485.3
15°	1534.9	1530.6	1528.4	1526.3	1521.9	1515.5	1515.5	1506.8	1496.1	1483.1	1472.5
17.5°	1517.6	1519.8	1515.5	1511.2	1504.7	1500.4	1493.9	1487.4	1474.5	1459.5	1448.7
20°	1496.1	1493.9	1491.7	1485.3	1476.7	1474.5	1468.1	1457.4	1446.6	1429.3	1414.2
22.5°	1461.7	1459.5	1455.2	1450.9	1442.3	1438.0	1431.5	1418.6	1403.6	1386.3	1369.1
25°	1418.6	1414.2	1407.8	1399.3	1392.8	1388.5	1379.9	1366.9	1349.7	1330.4	1313.1
27.5°	1349.7	1356.1	1351.8	1338.9	1332.5	1323.9	1321.8	1304.5	1289.4	1270.0	1250.7
30°	1282.9	1282.9	1276.5	1270.0	1259.3	1252.9	1244.2	1231.3	1216.2	1192.6	1177.5
32.5°	1199.1	1196.9	1188.3	1186.1	1177.5	1164.6	1162.4	1145.2	1130.2	1112.9	1093.5
35°	1106.5	1102.2	1093.5	1087.1	1082.8	1076.3	1069.8	1054.8	1039.7	1022.5	1009.6
37.5°	1000.9	1000.9	998.8	988.1	983.8	979.5	973.0	957.9	949.3	932.0	919.2
40°	899.8	897.7	891.2	889.0	884.7	878.3	873.9	865.3	852.5	839.6	826.6
42.5°	800.7	802.9	794.3	796.4	787.9	783.6	781.5	768.5	762.0	749.1	738.3
45°	712.6	710.4	706.1	703.9	699.6	695.3	691.0	684.5	673.8	660.8	654.3
47.5°	630.7	624.3	624.3	622.1	620.0	611.3	609.2	602.7	596.2	583.3	574.8
50°	553.2	553.2	553.2	551.1	544.6	542.5	538.1	531.7	525.2	516.6	503.8
52.5°	490.8	490.8	490.8	488.7	480.0	477.9	475.7	467.1	458.5	452.0	443.5
55°	432.7	434.9	432.7	428.4	421.9	421.9	415.5	411.2	402.5	396.1	387.4
57.5°	383.1	383.1	378.8	376.8	372.5	370.3	366.0	361.7	350.9	344.4	333.6
60°	335.8	333.6	333.6	329.3	325.0	320.7	318.5	312.1	307.9	297.1	288.5
62.5°	292.8	292.8	288.5	288.5	279.9	279.9	277.7	271.2	264.8	254.0	249.7
65°	251.8	251.8	249.7	247.5	241.0	239.0	236.8	230.4	223.9	217.4	211.0
67.5°	215.3	215.3	211.0	208.8	204.5	202.3	198.0	193.7	187.2	180.8	174.3
70°	180.8	178.6	176.5	174.3	170.1	168.0	163.6	159.3	152.9	148.6	142.1
72.5°	146.4	146.4	144.2	139.9	137.8	135.6	133.5	129.1	122.7	116.2	111.9
75°	114.0	114.0	114.0	109.7	105.4	103.3	103.3	99.1	94.8	88.3	84.0
77.5°	88.3	86.1	84.0	84.0	79.7	77.5	75.4	73.2	66.7	64.6	60.3
80°	60.3	62.4	60.3	58.1	55.9	53.8	53.8	49.5	47.3	43.0	38.7
82.5°	40.9	38.7	38.7	36.5	36.5	34.4	34.4	30.2	28.0	25.9	23.7
85°	21.6	21.6	19.4	19.4	19.4	17.3	17.3	15.1	15.1	12.9	10.8
87.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584453

CATALOG NUMBER: HCC8W35D010BZ-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1
2.5°	1459.5	1455.2	1453.1	1453.1	1450.9	1448.7	1446.6	1444.4	1440.1	1440.1	1435.8
5°	1470.3	1466.0	1463.8	1457.4	1453.1	1453.1	1444.4	1442.3	1435.8	1431.5	1427.2
7.5°	1478.8	1470.3	1463.8	1457.4	1453.1	1448.7	1440.1	1431.5	1422.9	1414.2	1409.9
10°	1478.8	1470.3	1459.5	1448.7	1444.4	1440.1	1429.3	1416.4	1405.7	1397.1	1386.3
12.5°	1474.5	1461.7	1448.7	1440.1	1431.5	1425.0	1412.1	1399.3	1386.3	1369.1	1360.4
15°	1461.7	1444.4	1431.5	1416.4	1409.9	1399.3	1388.5	1369.1	1354.0	1338.9	1328.2
17.5°	1435.8	1414.2	1399.3	1384.2	1373.4	1366.9	1349.7	1332.5	1315.3	1298.0	1285.1
20°	1397.1	1377.7	1360.4	1341.0	1332.5	1323.9	1302.3	1285.1	1268.0	1248.6	1235.6
22.5°	1349.7	1330.4	1306.7	1291.6	1278.6	1268.0	1248.6	1229.1	1211.9	1194.8	1177.5
25°	1291.6	1272.2	1250.7	1227.0	1218.4	1207.6	1186.1	1166.7	1147.3	1128.0	1112.9
27.5°	1229.1	1203.3	1186.1	1160.3	1151.6	1140.9	1117.3	1095.7	1078.4	1063.3	1046.2
30°	1153.8	1134.4	1110.8	1087.1	1078.4	1067.7	1048.4	1029.0	1011.7	994.5	977.3
32.5°	1072.0	1052.7	1029.0	1011.7	998.8	990.3	970.9	953.6	936.4	919.2	904.1
35°	986.0	964.4	947.1	929.9	919.2	908.4	889.0	873.9	861.0	846.0	830.9
37.5°	897.7	882.6	865.3	846.0	835.2	826.6	811.5	794.3	783.6	770.7	759.9
40°	811.5	794.3	779.3	762.0	753.4	747.0	731.9	719.0	708.3	697.5	691.0
42.5°	723.2	708.3	693.2	682.4	675.9	669.4	658.7	643.7	637.2	626.4	620.0
45°	641.5	628.6	617.8	602.7	598.4	594.1	581.3	570.5	564.0	557.5	553.2
47.5°	564.0	555.4	542.5	533.8	527.4	523.0	514.4	505.9	499.4	495.1	490.8
50°	497.3	486.5	477.9	469.3	464.9	458.5	449.8	445.7	441.3	437.0	437.0
52.5°	434.9	424.1	415.5	409.0	404.7	400.4	393.9	391.7	387.4	387.4	385.3
55°	376.8	370.3	361.7	353.1	350.9	348.7	344.4	340.1	338.0	335.8	338.0
57.5°	327.2	320.7	312.1	305.7	303.6	301.4	299.3	294.9	292.8	292.8	292.8
60°	282.0	275.5	269.1	262.6	262.6	258.3	256.1	254.0	251.8	249.7	249.7
62.5°	241.0	234.7	228.2	223.9	221.7	219.6	215.3	213.1	211.0	211.0	208.8
65°	204.5	195.9	193.7	187.2	185.1	182.9	180.8	176.5	174.3	172.2	170.1
67.5°	168.0	163.6	157.2	152.9	150.7	148.6	146.4	142.1	139.9	137.8	133.5
70°	135.6	131.3	127.0	122.7	120.5	118.4	114.0	109.7	107.6	103.3	96.9
72.5°	105.4	101.2	96.9	92.6	90.4	88.3	84.0	79.7	75.4	71.0	66.7
75°	79.7	75.4	68.9	64.6	62.4	62.4	55.9	51.6	47.3	40.9	36.5
77.5°	55.9	49.5	47.3	43.0	40.9	36.5	32.3	28.0	23.7	21.6	17.3
80°	36.5	32.3	28.0	25.9	23.7	21.6	19.4	15.1	10.8	8.6	6.5
82.5°	21.6	19.4	17.3	15.1	12.9	10.8	8.6	8.6	6.5	4.3	2.2
85°	10.8	8.6	6.5	6.5	4.3	4.3	4.3	2.2	2.2	2.2	2.2
87.5°	4.3	2.2	2.2	2.2	2.2	2.2	2.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584453

CATALOG NUMBER: HCC8W35D010BZ-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1
2.5°	1433.6	1431.5	1429.3	1427.2	1427.2	1422.9	1422.9	1420.7	1416.4	1414.2	1414.2
5°	1420.7	1414.2	1409.9	1407.8	1405.7	1399.3	1397.1	1392.8	1388.5	1384.2	1382.0
7.5°	1401.4	1390.6	1386.3	1384.2	1377.7	1371.2	1366.9	1360.4	1354.0	1347.5	1345.4
10°	1377.7	1366.9	1356.1	1351.8	1345.4	1341.0	1332.5	1323.9	1317.4	1311.0	1304.5
12.5°	1347.5	1334.7	1323.9	1319.6	1313.1	1304.5	1291.6	1287.3	1276.5	1272.2	1263.7
15°	1313.1	1298.0	1287.3	1280.8	1274.3	1261.5	1252.9	1244.2	1233.5	1229.1	1220.5
17.5°	1270.0	1252.9	1242.1	1235.6	1231.3	1220.5	1207.6	1196.9	1186.1	1181.8	1175.4
20°	1218.4	1207.6	1192.6	1186.1	1181.8	1168.9	1156.0	1151.6	1143.0	1134.4	1128.0
22.5°	1160.3	1149.5	1134.4	1128.0	1125.9	1115.1	1104.3	1097.8	1091.4	1084.9	1078.4
25°	1100.0	1087.1	1074.1	1069.8	1065.5	1057.0	1048.4	1044.1	1037.6	1033.3	1029.0
27.5°	1035.4	1022.5	1011.7	1005.2	1000.9	994.5	990.3	986.0	981.6	977.3	975.2
30°	966.5	953.6	945.0	940.7	936.4	934.2	927.7	925.7	923.5	919.2	921.4
32.5°	897.7	886.9	878.3	871.8	871.8	867.5	865.3	865.3	863.2	863.2	863.2
35°	822.3	815.8	809.4	807.2	805.1	802.9	800.7	802.9	800.7	802.9	805.1
37.5°	753.4	747.0	742.6	740.5	738.3	740.5	738.3	738.3	740.5	744.8	747.0
40°	682.4	678.1	673.8	675.9	673.8	673.8	673.8	680.2	682.4	684.5	686.7
42.5°	615.7	611.3	609.2	609.2	611.3	609.2	613.5	615.7	620.0	626.4	630.7
45°	551.1	548.9	548.9	551.1	548.9	553.2	553.2	557.5	564.0	568.3	572.6
47.5°	490.8	490.8	490.8	493.0	493.0	495.1	499.4	501.6	505.9	510.2	514.4
50°	434.9	437.0	439.2	439.2	439.2	443.5	447.7	449.8	452.0	454.2	460.6
52.5°	385.3	387.4	387.4	389.6	391.7	393.9	396.1	400.4	402.5	406.8	409.0
55°	338.0	338.0	342.3	344.4	344.4	344.4	348.7	348.7	353.1	355.2	359.5
57.5°	292.8	294.9	294.9	297.1	297.1	299.3	301.4	303.6	305.7	307.9	309.9
60°	249.7	249.7	249.7	251.8	254.0	256.1	254.0	258.3	258.3	262.6	264.8
62.5°	208.8	211.0	211.0	211.0	211.0	211.0	211.0	213.1	215.3	217.4	219.6
65°	170.1	170.1	170.1	168.0	170.1	168.0	170.1	172.2	172.2	174.3	176.5
67.5°	131.3	131.3	127.0	127.0	129.1	129.1	129.1	129.1	127.0	131.3	131.3
70°	94.8	92.6	90.4	88.3	88.3	86.1	86.1	84.0	84.0	84.0	84.0
72.5°	62.4	58.1	53.8	51.6	49.5	49.5	45.2	43.0	45.2	45.2	45.2
75°	32.3	28.0	25.9	23.7	21.6	21.6	19.4	19.4	19.4	19.4	19.4
77.5°	12.9	10.8	8.6	8.6	6.5	6.5	6.5	6.5	6.5	6.5	6.5
80°	4.3	4.3	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
85°	2.2	0.0	0.0	2.2	0.0	2.2	2.2	2.2	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584453

CATALOG NUMBER: HCC8W35D010BZ-HM82555927-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1
2.5°	1412.1	1412.1	1409.9	1412.1	1407.8	1409.9	1407.8	1407.8
5°	1379.9	1375.5	1375.5	1375.5	1373.4	1373.4	1371.2	1371.2
7.5°	1341.0	1338.9	1336.8	1334.7	1332.5	1330.4	1330.4	1330.4
10°	1302.3	1298.0	1298.0	1295.9	1291.6	1289.4	1289.4	1289.4
12.5°	1257.2	1255.0	1252.9	1252.9	1244.2	1246.4	1244.2	1244.2
15°	1214.1	1211.9	1211.9	1205.4	1201.1	1201.1	1201.1	1199.1
17.5°	1168.9	1166.7	1164.6	1160.3	1156.0	1156.0	1153.8	1156.0
20°	1121.6	1119.4	1115.1	1115.1	1112.9	1110.8	1106.5	1108.6
22.5°	1074.1	1069.8	1067.7	1067.7	1065.5	1065.5	1061.3	1061.3
25°	1024.6	1022.5	1020.3	1022.5	1018.2	1018.2	1013.9	1013.9
27.5°	973.0	970.9	970.9	970.9	968.7	970.9	968.7	968.7
30°	921.4	921.4	919.2	919.2	921.4	919.2	921.4	923.5
32.5°	865.3	865.3	867.5	867.5	869.6	869.6	869.6	869.6
35°	807.2	811.5	811.5	813.7	815.8	818.0	818.0	820.2
37.5°	753.4	755.6	757.7	759.9	764.2	764.2	764.2	764.2
40°	695.3	697.5	701.8	699.6	708.3	710.4	708.3	708.3
42.5°	635.1	639.4	641.5	645.8	648.0	652.2	654.3	654.3
45°	579.1	581.3	585.5	589.8	591.9	598.4	598.4	598.4
47.5°	520.9	525.2	527.4	531.7	533.8	540.3	542.5	540.3
50°	464.9	469.3	473.6	473.6	480.0	482.2	486.5	488.7
52.5°	411.2	413.3	417.6	419.8	424.1	428.4	430.6	432.7
55°	359.5	361.7	366.0	366.0	372.5	374.6	378.8	378.8
57.5°	312.1	314.2	318.5	316.4	320.7	325.0	325.0	322.9
60°	266.9	266.9	266.9	271.2	273.4	275.5	277.7	277.7
62.5°	219.6	223.9	226.1	226.1	228.2	230.4	230.4	228.2
65°	176.5	180.8	182.9	182.9	185.1	185.1	185.1	187.2
67.5°	133.5	133.5	133.5	135.6	133.5	133.5	133.5	133.5
70°	84.0	84.0	84.0	84.0	81.8	84.0	84.0	86.1
72.5°	45.2	45.2	45.2	45.2	45.2	45.2	45.2	45.2
75°	19.4	19.4	19.4	21.6	19.4	19.4	19.4	19.4
77.5°	8.6	6.5	8.6	8.6	6.5	6.5	6.5	6.5
80°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
85°	0.0	2.2	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)