

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584617

Luminaire Tested: **HCC8W40D010MB-HM82555935-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010MB-HM82555935-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4133.1 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584617
CATALOG NUMBER: HCC8W40D010MB-HM82555935-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P584617

CATALOG NUMBER: HCC8W40D010MB-HM82555935-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88				
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77				77				
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67				
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59				
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47				
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35				35				
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	67985	67985	67985
5°	69263	67687	66115
10°	70342	66507	63701
15°	71053	64851	60943
20°	70779	62349	58136
25°	68916	58749	54888
30°	65630	54460	51697
35°	59267	49705	48019
40°	52068	44617	44497
45°	44948	39213	40910
50°	39122	34396	36690
55°	34687	29870	31961
60°	30947	25236	26532
65°	27894	20489	20926
70°	24785	15354	12388
75°	21350	8900	5349
80°	16444	3196	1580
85°	10579	1061	1061



TEST NUMBER: P584617
 CATALOG NUMBER: HCC8W40D010MB-HM82555935-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.0	5.0
10°-20°	576.2	13.9
20°-30°	814.9	19.7
30°-40°	858.7	20.8
40°-50°	729.8	17.7
50°-60°	525.5	12.7
60°-70°	303.1	7.3
70°-80°	103.7	2.5
80°-90°	14.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1598.0	38.7
0°-40°	2456.7	59.4
0°-60°	3712.0	89.8
0°-90°	4133.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4133.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2205	2205	2205	2205	2205	
5°	2238	2223	2187	2148	2136	214
15°	2226	2157	2031	1942	1909	627
25°	2026	1921	1727	1637	1613	929
35°	1574	1482	1320	1273	1276	980
45°	1031	983	899	905	938	801
55°	645	594	556	577	594	581
65°	382	329	281	275	287	380
75°	179	134	75	48	45	189
85°	30	18	3	3	3	40
90°	0	0	0	0	0	



TEST NUMBER: P584617

CATALOG NUMBER: HCC8W40D010MB-HM82555935-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7
2.5°	2225.7	2228.6	2225.7	2225.7	2222.6	2219.6	2216.6	2213.6	2207.7	2201.7	2201.7
5°	2237.6	2243.5	2237.6	2237.6	2228.6	2222.6	2216.6	2207.7	2195.8	2186.7	2186.7
7.5°	2246.5	2246.5	2246.5	2237.6	2231.6	2222.6	2207.7	2192.7	2177.8	2162.8	2156.9
10°	2246.5	2246.5	2243.5	2231.6	2225.7	2207.7	2192.7	2171.9	2150.9	2130.0	2124.0
12.5°	2237.6	2240.5	2234.6	2222.6	2207.7	2186.7	2165.9	2139.0	2115.1	2091.2	2079.2
15°	2225.7	2222.6	2216.6	2201.7	2183.8	2156.9	2135.9	2106.1	2073.2	2043.3	2031.4
17.5°	2195.8	2195.8	2186.7	2171.9	2148.0	2118.1	2085.2	2052.4	2016.5	1983.6	1968.7
20°	2156.9	2156.9	2145.0	2127.0	2103.1	2064.3	2028.5	1989.6	1947.8	1914.9	1900.0
22.5°	2100.1	2103.1	2088.2	2067.3	2040.4	1995.6	1959.7	1912.0	1870.1	1831.3	1819.3
25°	2025.5	2031.4	2016.5	1995.6	1959.7	1920.9	1876.0	1831.3	1783.5	1744.7	1726.7
27.5°	1938.9	1941.8	1926.8	1905.9	1870.1	1828.3	1783.5	1735.7	1690.9	1649.0	1631.1
30°	1843.2	1831.3	1825.3	1798.4	1759.5	1723.7	1672.9	1634.1	1586.3	1550.5	1529.5
32.5°	1708.8	1714.8	1696.8	1675.9	1646.0	1604.2	1562.4	1517.6	1472.7	1445.8	1431.0
35°	1574.4	1580.3	1571.4	1550.5	1517.6	1481.8	1439.9	1407.1	1368.3	1335.4	1320.4
37.5°	1434.0	1434.0	1428.0	1416.0	1392.2	1359.2	1317.4	1284.6	1251.8	1224.9	1215.8
40°	1293.5	1287.6	1284.6	1275.6	1254.7	1224.9	1198.0	1171.1	1138.2	1120.3	1108.4
42.5°	1156.1	1156.1	1150.1	1141.2	1120.3	1105.4	1078.5	1048.6	1024.7	1006.7	1006.7
45°	1030.7	1033.6	1024.7	1018.8	1006.7	982.8	958.9	938.1	917.1	905.2	899.2
47.5°	920.1	920.1	911.2	905.2	893.2	872.3	851.4	833.5	818.6	809.6	806.6
50°	815.5	815.5	815.5	800.6	785.6	770.8	755.8	734.9	725.9	719.9	717.0
52.5°	725.9	722.9	722.9	711.0	696.0	678.2	663.2	645.2	636.3	630.3	633.3
55°	645.2	645.2	642.2	627.4	612.4	594.5	579.5	564.7	558.6	552.6	555.6
56°	612.4	612.4	609.4	597.5	579.5	564.7	546.7	531.8	522.8	525.7	525.7
57°	588.6	582.5	582.5	567.6	552.6	531.8	516.8	501.8	495.9	492.9	492.9
58°	558.6	555.6	552.6	537.8	522.8	504.9	489.9	475.0	466.0	466.0	463.0
59°	528.7	528.7	522.8	510.9	495.9	478.0	463.0	448.2	439.1	436.1	436.1
60°	501.8	504.9	495.9	484.0	472.0	451.1	433.2	421.3	412.2	409.2	409.2
61°	478.0	478.0	472.0	457.1	442.1	427.2	409.2	394.4	388.4	382.3	382.3
62°	457.1	451.1	448.2	433.2	418.3	400.3	385.3	370.4	361.5	355.5	358.4
63°	430.2	427.2	421.3	409.2	394.4	376.4	358.4	346.5	337.6	328.6	331.7
64°	409.2	406.3	397.3	385.3	370.4	352.5	334.6	322.6	316.7	307.7	304.8
65°	382.3	379.4	376.4	361.5	346.5	328.6	313.7	301.8	292.7	286.8	280.8
66°	358.4	361.5	355.5	343.6	325.6	310.7	289.8	277.9	271.8	262.9	256.9
67°	337.6	337.6	331.7	319.6	301.8	286.8	271.8	256.9	248.0	239.0	236.0
67.5°	325.6	325.6	319.6	304.8	292.7	274.9	259.9	248.0	236.0	230.0	224.1
68°	313.7	313.7	310.7	298.7	283.8	265.8	251.0	236.0	224.1	215.0	212.1
69°	292.7	295.7	289.8	277.9	262.9	245.0	230.0	218.1	206.1	197.2	191.2
70°	274.9	271.8	265.8	253.9	239.0	227.1	212.1	197.2	185.2	173.3	170.3
71°	251.0	251.0	245.0	236.0	221.1	206.1	191.2	179.2	167.3	152.3	149.3
72°	233.0	233.0	227.1	215.0	203.1	188.3	173.3	158.4	149.3	134.5	128.4
72.5°	221.1	224.1	218.1	206.1	194.2	176.2	164.3	152.3	137.4	125.4	119.5
73°	215.0	212.1	209.1	197.2	182.2	170.3	155.3	143.4	128.4	116.5	110.6



TEST NUMBER: P584617
 CATALOG NUMBER: HCC8W40D010MB-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	134.5	134.5	131.5	119.5	107.6	95.6	83.7	71.6	59.7	47.8	41.8
80°	92.6	95.6	89.6	83.7	74.7	62.7	50.8	41.8	29.9	23.9	18.0
82.5°	59.7	59.7	56.8	50.8	44.9	35.8	29.9	20.9	15.0	11.9	8.9
85°	29.9	32.8	29.9	26.9	20.9	18.0	15.0	8.9	5.9	3.0	3.0
87.5°	11.9	11.9	11.9	8.9	8.9	5.9	3.0	3.0	3.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584617

CATALOG NUMBER: HCC8W40D010MB-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7	2204.7
2.5°	2195.8	2195.8	2189.7	2186.7	2183.8	2180.8	2177.8	2174.8	2174.8	2177.8
5°	2177.8	2171.9	2159.8	2156.9	2148.0	2145.0	2139.0	2135.9	2139.0	2135.9
7.5°	2150.9	2139.0	2124.0	2118.1	2106.1	2100.1	2091.2	2091.2	2085.2	2088.2
10°	2115.1	2097.1	2079.2	2067.3	2058.3	2049.3	2043.3	2037.4	2034.4	2034.4
12.5°	2070.2	2049.3	2031.4	2013.5	1998.6	1992.5	1980.6	1980.6	1974.7	1971.7
15°	2019.4	1992.5	1971.7	1953.7	1941.8	1929.8	1920.9	1914.9	1909.0	1909.0
17.5°	1953.7	1929.8	1909.0	1888.1	1870.1	1861.2	1852.2	1843.2	1843.2	1837.2
20°	1882.1	1855.2	1837.2	1816.3	1801.4	1786.4	1774.5	1774.5	1768.6	1771.6
22.5°	1801.4	1768.6	1750.6	1735.7	1720.7	1708.8	1696.8	1696.8	1693.8	1690.9
25°	1711.8	1684.9	1664.0	1646.0	1637.1	1625.2	1622.2	1616.1	1613.2	1613.2
27.5°	1616.1	1595.3	1568.4	1559.4	1547.5	1541.5	1541.5	1538.6	1532.5	1535.6
30°	1514.6	1490.7	1475.7	1469.8	1457.9	1457.9	1454.9	1448.9	1448.9	1451.9
32.5°	1416.0	1392.2	1380.2	1377.2	1365.3	1365.3	1362.2	1365.3	1365.3	1368.3
35°	1308.5	1287.6	1284.6	1275.6	1272.6	1272.6	1272.6	1278.7	1284.6	1275.6
37.5°	1206.9	1192.0	1183.0	1180.0	1183.0	1183.0	1186.0	1195.0	1192.0	1188.9
40°	1102.3	1090.4	1084.4	1084.4	1090.4	1096.3	1096.3	1105.4	1108.4	1105.4
42.5°	997.8	988.8	988.8	991.9	997.8	1000.8	1009.7	1018.8	1021.7	1024.7
45°	899.2	899.2	899.2	902.1	905.2	911.2	923.1	932.0	935.1	938.1
47.5°	803.6	800.6	809.6	812.5	821.6	824.6	833.5	845.4	848.5	851.4
50°	714.0	719.9	722.9	732.0	737.9	737.9	749.8	755.8	764.8	764.8
52.5°	630.3	639.3	642.2	651.3	654.3	657.2	663.2	672.1	678.2	678.2
55°	555.6	558.6	564.7	567.6	576.6	579.5	585.5	588.6	597.5	594.5
56°	522.8	528.7	531.8	537.8	543.7	546.7	552.6	555.6	561.7	564.7
57°	492.9	495.9	504.9	507.9	513.8	513.8	516.8	525.7	525.7	528.7
58°	463.0	469.0	472.0	475.0	481.0	484.0	489.9	492.9	495.9	492.9
59°	436.1	439.1	442.1	442.1	448.2	448.2	457.1	463.0	466.0	466.0
60°	409.2	409.2	412.2	415.2	421.3	424.2	424.2	430.2	430.2	430.2
61°	382.3	382.3	385.3	388.4	391.4	391.4	397.3	397.3	400.3	403.3
62°	358.4	355.5	355.5	358.4	358.4	364.5	367.5	370.4	373.4	370.4
63°	331.7	328.6	328.6	328.6	328.6	334.6	334.6	337.6	343.6	340.6
64°	301.8	301.8	301.8	301.8	304.8	304.8	310.7	313.7	316.7	319.6
65°	280.8	274.9	271.8	271.8	274.9	277.9	280.8	283.8	286.8	286.8
66°	256.9	251.0	248.0	248.0	248.0	248.0	253.9	253.9	259.9	259.9
67°	230.0	224.1	221.1	218.1	218.1	218.1	227.1	224.1	224.1	224.1
67.5°	221.1	212.1	209.1	206.1	203.1	209.1	206.1	209.1	209.1	206.1
68°	209.1	203.1	197.2	191.2	191.2	191.2	194.2	197.2	194.2	191.2
69°	185.2	182.2	173.3	167.3	164.3	167.3	164.3	167.3	164.3	167.3
70°	164.3	155.3	146.4	143.4	140.4	140.4	140.4	137.4	140.4	137.4
71°	143.4	134.5	125.4	119.5	116.5	116.5	113.5	116.5	113.5	116.5
72°	122.5	113.5	101.6	95.6	95.6	95.6	95.6	92.6	95.6	92.6
72.5°	113.5	101.6	92.6	86.6	83.7	83.7	83.7	83.7	80.7	83.7
73°	104.6	92.6	80.7	77.7	77.7	77.7	74.7	71.6	74.7	74.7



TEST NUMBER: P584617
CATALOG NUMBER: HCC8W40D010MB-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	35.8	26.9	23.9	23.9	23.9	23.9	23.9	23.9	20.9	20.9
80°	15.0	11.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
82.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
85°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	194.2	194.2	188.3	179.2	164.3	149.3	137.4	125.4	110.6	95.6	89.6
75°	179.2	176.2	170.3	161.4	149.3	134.5	122.5	107.6	95.6	80.7	74.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	86.6	71.6	65.7	59.7	59.7	59.7	56.8	56.8	56.8	59.7
75°	68.7	56.8	50.8	44.9	47.8	44.9	47.8	44.9	44.9	44.9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)