

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584471

Luminaire Tested: **HCC8W35D010MB-HM82555930-81WWW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584471  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W35D010MB-HM82555930-81WWW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3486.6 lumens  
Efficiency: N/A  
Efficacy: 103.5 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584471  
CATALOG NUMBER: HCC8W35D010MB-HM82555930-81WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584471

CATALOG NUMBER: HCC8W35D010MB-HM82555930-81WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	58256	58256	58256
5°	60305	57924	55621
10°	61644	56906	52495
15°	62520	54992	49019
20°	62329	52321	45508
25°	60791	48930	41775
30°	57590	45000	38334
35°	52401	40723	34832
40°	46022	36216	31471
45°	40133	31856	28058
50°	34924	27915	24720
55°	31149	24531	21499
60°	28295	21499	18335
65°	25436	18708	16643
70°	22648	15940	15021
75°	19849	13427	12832
80°	16852	10939	11383
85°	12702	8173	9057



TEST NUMBER: P584471  
 CATALOG NUMBER: HCC8W35D010MB-HM82555930-81WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	177.0	5.1
10°-20°	487.6	14.0
20°-30°	676.8	19.4
30°-40°	699.7	20.1
40°-50°	585.9	16.8
50°-60°	425.3	12.2
60°-70°	268.4	7.7
70°-80°	133.0	3.8
80°-90°	33.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1341.3	38.5
0°-40°	2041.0	58.5
0°-60°	3052.2	87.5
0°-90°	3486.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3486.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1889	1889	1889	1889	1889	
5°	1948	1925	1871	1820	1797	186
15°	1958	1884	1723	1584	1536	551
25°	1787	1671	1438	1282	1228	819
35°	1392	1289	1082	959	925	867
45°	920	854	730	659	643	712
55°	579	528	456	418	400	523
65°	349	305	256	226	228	348
75°	167	138	113	108	108	179
85°	36	28	23	26	26	44
90°	0	0	0	0	0	



TEST NUMBER: P584471

CATALOG NUMBER: HCC8W35D010MB-HM82555930-81WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2
2.5°	1919.9	1919.9	1922.6	1919.9	1919.9	1919.9	1917.4	1917.4	1914.9	1914.9	1909.7
5°	1948.2	1943.0	1948.2	1943.0	1943.0	1943.0	1940.5	1935.4	1932.7	1927.7	1925.1
7.5°	1961.0	1958.4	1958.4	1955.9	1955.9	1953.3	1950.7	1948.2	1937.9	1935.4	1927.7
10°	1968.7	1966.0	1966.0	1963.5	1958.4	1958.4	1953.3	1950.7	1937.9	1932.7	1922.6
12.5°	1966.0	1966.0	1966.0	1963.5	1955.9	1953.3	1948.2	1940.5	1930.2	1919.9	1909.7
15°	1958.4	1958.4	1953.3	1950.7	1943.0	1937.9	1935.4	1922.6	1912.2	1899.4	1884.1
17.5°	1932.7	1932.7	1930.2	1925.1	1917.4	1912.2	1907.1	1894.3	1884.1	1863.6	1848.2
20°	1899.4	1896.9	1894.3	1886.6	1878.9	1876.4	1868.6	1850.8	1838.0	1822.5	1802.0
22.5°	1850.8	1848.2	1845.6	1840.5	1827.7	1822.5	1817.4	1804.5	1781.5	1766.2	1740.6
25°	1786.7	1786.7	1781.5	1773.9	1761.1	1755.9	1748.2	1735.4	1714.9	1691.8	1671.3
27.5°	1712.3	1709.8	1702.1	1697.0	1686.7	1679.0	1666.2	1650.8	1630.2	1612.4	1586.8
30°	1617.4	1617.4	1612.4	1604.7	1591.9	1586.8	1576.4	1558.5	1538.0	1515.0	1497.0
32.5°	1509.8	1509.8	1502.2	1497.0	1489.4	1476.5	1473.9	1453.4	1435.4	1417.6	1397.0
35°	1392.0	1394.5	1389.3	1379.1	1366.3	1366.3	1361.2	1343.2	1322.7	1304.7	1289.4
37.5°	1274.0	1266.3	1263.8	1258.6	1251.0	1240.6	1235.5	1227.8	1209.9	1197.0	1174.0
40°	1143.3	1145.8	1140.7	1135.6	1132.9	1125.3	1122.8	1109.9	1097.1	1081.8	1071.5
42.5°	1025.4	1025.4	1025.4	1020.2	1015.1	1007.4	1004.9	997.1	981.8	971.5	956.1
45°	920.3	912.5	912.5	910.0	907.5	902.3	894.7	889.5	879.2	871.5	853.6
47.5°	817.8	820.3	817.8	815.1	807.5	804.9	802.3	792.1	781.8	774.1	761.3
50°	728.0	733.2	728.0	728.0	722.9	720.4	715.2	707.5	699.8	686.9	674.1
52.5°	653.6	653.6	651.1	648.5	640.8	635.7	633.1	630.6	617.8	607.5	597.2
55°	579.4	581.9	581.9	574.2	571.7	566.5	563.9	556.2	551.1	535.7	528.1
57.5°	515.3	512.6	515.3	510.1	505.0	499.8	497.3	492.1	484.5	474.2	464.0
60°	458.8	453.7	453.7	451.2	446.0	443.5	438.3	430.7	423.0	412.7	405.0
62.5°	402.4	399.9	397.4	394.7	389.6	387.1	384.6	376.8	369.1	361.4	353.8
65°	348.6	348.6	346.1	341.0	338.3	335.8	333.3	328.1	317.8	312.7	305.0
67.5°	299.9	297.3	297.3	292.2	287.0	284.5	284.5	279.4	271.7	264.0	258.9
70°	251.2	253.7	251.2	248.7	243.6	243.6	238.4	235.9	225.6	223.1	215.3
72.5°	207.6	207.6	205.1	205.1	199.9	197.4	197.4	192.3	187.1	182.0	176.8
75°	166.6	166.6	166.6	164.0	161.5	156.3	156.3	153.8	148.7	143.5	138.4
77.5°	130.7	128.2	128.2	125.6	123.0	120.5	120.5	117.9	112.7	110.2	105.1
80°	94.9	92.2	92.2	92.2	87.1	89.7	87.1	84.6	82.1	79.4	76.9
82.5°	61.6	64.1	64.1	61.6	58.9	58.9	58.9	56.4	56.4	53.8	51.3
85°	35.9	35.9	35.9	35.9	33.3	33.3	33.3	30.8	30.8	30.8	28.2
87.5°	15.3	15.3	15.3	15.3	15.3	15.3	12.8	12.8	12.8	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584471

CATALOG NUMBER: HCC8W35D010MB-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2
2.5°	1909.7	1904.6	1902.1	1899.4	1899.4	1896.9	1894.3	1889.2	1889.2	1884.1	1881.5
5°	1919.9	1912.2	1907.1	1902.1	1899.4	1894.3	1889.2	1881.5	1878.9	1871.3	1863.6
7.5°	1922.6	1909.7	1904.6	1894.3	1889.2	1884.1	1873.8	1866.1	1855.8	1848.2	1838.0
10°	1912.2	1902.1	1889.2	1876.4	1873.8	1866.1	1850.8	1840.5	1827.7	1817.4	1802.0
12.5°	1896.9	1881.5	1868.6	1853.3	1845.6	1838.0	1822.5	1807.2	1789.2	1771.2	1755.9
15°	1871.3	1853.3	1835.3	1817.4	1807.2	1799.5	1781.5	1763.6	1745.6	1722.6	1707.2
17.5°	1832.8	1812.3	1794.4	1771.2	1761.1	1753.4	1730.3	1709.8	1686.7	1663.7	1648.2
20°	1784.1	1758.4	1737.9	1712.3	1704.6	1691.8	1668.7	1645.7	1620.1	1594.4	1576.4
22.5°	1720.0	1694.3	1671.3	1645.7	1632.9	1620.1	1596.9	1568.8	1543.1	1522.7	1504.7
25°	1645.7	1622.6	1594.4	1571.3	1556.0	1540.6	1515.0	1491.9	1468.7	1438.1	1420.1
27.5°	1563.6	1535.5	1515.0	1484.2	1468.7	1458.6	1430.4	1399.6	1379.1	1350.9	1330.4
30°	1471.4	1445.7	1422.6	1392.0	1376.5	1366.3	1340.7	1312.4	1291.9	1263.8	1243.3
32.5°	1374.0	1345.7	1317.6	1297.1	1279.1	1268.9	1240.6	1222.7	1197.0	1174.0	1150.9
35°	1268.9	1240.6	1220.2	1192.0	1181.7	1171.4	1148.4	1125.3	1102.3	1081.8	1063.8
37.5°	1156.1	1135.6	1112.5	1092.0	1084.3	1074.0	1045.9	1025.4	1007.4	986.9	971.5
40°	1045.9	1027.9	1012.5	992.1	979.2	971.5	951.0	933.1	912.5	899.7	884.4
42.5°	945.8	925.3	910.0	894.7	881.8	874.1	856.2	843.4	827.9	815.1	797.1
45°	840.8	830.6	812.6	799.8	792.1	781.8	769.0	753.7	740.8	730.5	717.7
47.5°	748.5	738.2	725.4	710.1	704.9	697.2	684.4	674.1	663.9	653.6	640.8
50°	663.9	651.1	640.8	630.6	625.5	617.8	605.0	599.8	592.2	581.9	574.2
52.5°	587.0	576.7	566.5	553.7	551.1	546.0	538.3	528.1	520.4	515.3	510.1
55°	517.8	507.6	499.8	489.6	487.0	482.0	471.7	466.5	461.3	456.3	451.2
57.5°	456.3	446.0	435.7	430.7	425.5	420.4	417.9	410.2	405.0	402.4	397.4
60°	399.9	389.6	381.9	374.3	371.7	369.1	364.0	358.9	353.8	348.6	346.1
62.5°	346.1	335.8	330.6	325.5	320.5	320.5	315.3	310.2	305.0	302.5	297.3
65°	297.3	292.2	284.5	276.9	274.2	274.2	266.6	264.0	261.4	256.4	251.2
67.5°	251.2	246.1	238.4	235.9	233.3	230.7	228.1	223.1	217.9	215.3	210.2
70°	210.2	205.1	199.9	197.4	194.8	192.3	187.1	184.6	179.5	176.8	174.3
72.5°	169.2	166.6	161.5	159.0	156.3	153.8	151.2	148.7	143.5	141.0	138.4
75°	135.9	133.3	128.2	125.6	123.0	123.0	120.5	115.4	112.7	112.7	110.2
77.5°	102.5	99.9	97.4	94.9	92.2	92.2	89.7	87.1	84.6	84.6	82.1
80°	74.4	71.8	69.2	69.2	69.2	66.6	64.1	64.1	61.6	61.6	58.9
82.5°	48.8	48.8	46.1	46.1	46.1	43.6	43.6	41.0	41.0	41.0	41.0
85°	28.2	28.2	28.2	25.6	25.6	25.6	25.6	25.6	25.6	23.1	25.6
87.5°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584471

CATALOG NUMBER: HCC8W35D010MB-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2
2.5°	1878.9	1876.4	1871.3	1871.3	1866.1	1866.1	1863.6	1861.0	1858.5	1855.8	1853.3
5°	1861.0	1850.8	1845.6	1843.0	1838.0	1835.3	1827.7	1822.5	1820.0	1814.9	1809.7
7.5°	1827.7	1817.4	1807.2	1804.5	1802.0	1791.7	1784.1	1776.4	1771.2	1766.2	1761.1
10°	1789.2	1779.0	1766.2	1761.1	1755.9	1743.1	1732.8	1725.1	1714.9	1704.6	1702.1
12.5°	1743.1	1727.8	1712.3	1707.2	1699.5	1686.7	1676.5	1663.7	1655.9	1643.1	1640.5
15°	1689.3	1671.3	1658.5	1645.7	1640.5	1627.7	1609.8	1599.6	1584.1	1579.1	1566.3
17.5°	1625.2	1607.2	1589.3	1584.1	1576.4	1558.5	1540.6	1527.8	1512.4	1504.7	1497.0
20°	1558.5	1535.5	1517.5	1512.4	1502.2	1486.7	1468.7	1455.9	1443.2	1427.8	1420.1
22.5°	1481.6	1455.9	1440.6	1427.8	1425.3	1407.3	1386.8	1376.5	1366.3	1353.5	1343.2
25°	1397.0	1374.0	1356.0	1345.7	1340.7	1325.2	1309.9	1297.1	1281.6	1274.0	1261.1
27.5°	1309.9	1294.4	1271.4	1261.1	1253.5	1240.6	1222.7	1215.0	1199.7	1189.4	1181.7
30°	1225.3	1202.2	1189.4	1176.6	1168.9	1156.1	1140.7	1132.9	1120.1	1109.9	1102.3
32.5°	1132.9	1117.6	1099.6	1094.6	1084.3	1071.5	1061.2	1048.4	1038.2	1027.9	1025.4
35°	1048.4	1027.9	1009.9	1004.9	997.1	984.3	979.2	971.5	958.6	956.1	945.8
37.5°	956.1	945.8	925.3	917.7	915.2	904.8	894.7	889.5	881.8	874.1	871.5
40°	869.0	856.2	845.9	838.2	833.1	825.4	815.1	812.6	807.5	797.1	794.6
42.5°	787.0	774.1	763.8	761.3	753.7	746.0	740.8	733.2	730.5	728.0	722.9
45°	707.5	699.8	689.6	686.9	684.4	674.1	669.1	663.9	658.8	656.3	651.1
47.5°	635.7	628.0	620.3	617.8	612.7	610.0	602.4	599.8	592.2	589.5	587.0
50°	566.5	561.4	556.2	553.7	548.6	546.0	540.9	535.7	530.6	528.1	525.4
52.5°	505.0	499.8	494.8	492.1	489.6	484.5	479.3	474.2	471.7	469.1	466.5
55°	446.0	440.9	438.3	435.7	433.2	430.7	423.0	420.4	417.9	415.2	410.2
57.5°	392.2	387.1	381.9	381.9	379.4	376.8	371.7	366.6	366.6	361.4	356.3
60°	343.5	338.3	333.3	330.6	328.1	323.0	320.5	317.8	315.3	312.7	307.6
62.5°	292.2	289.7	284.5	284.5	279.4	276.9	274.2	271.7	269.2	264.0	261.4
65°	248.7	246.1	240.9	238.4	238.4	235.9	230.7	228.1	225.6	225.6	223.1
67.5°	207.6	205.1	199.9	197.4	197.4	194.8	192.3	192.3	189.6	187.1	189.6
70°	171.8	166.6	166.6	164.0	164.0	161.5	159.0	159.0	159.0	161.5	161.5
72.5°	135.9	133.3	130.7	130.7	130.7	130.7	128.2	128.2	130.7	133.3	133.3
75°	107.7	105.1	105.1	105.1	102.5	102.5	105.1	105.1	107.7	107.7	107.7
77.5°	79.4	79.4	79.4	79.4	79.4	79.4	82.1	82.1	84.6	84.6	84.6
80°	58.9	58.9	58.9	58.9	58.9	61.6	61.6	61.6	61.6	61.6	64.1
82.5°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	43.6	43.6	43.6	43.6
85°	23.1	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584471

CATALOG NUMBER: HCC8W35D010MB-HM82555930-81WWW

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2	1889.2
2.5°	1850.8	1850.8	1850.8	1853.3	1848.2	1848.2	1848.2	1848.2
5°	1807.2	1804.5	1802.0	1804.5	1799.5	1799.5	1796.9	1796.9
7.5°	1753.4	1750.8	1748.2	1748.2	1743.1	1743.1	1740.6	1737.9
10°	1694.3	1689.3	1691.8	1686.7	1684.1	1681.5	1679.0	1676.5
12.5°	1630.2	1625.2	1622.6	1617.4	1612.4	1609.8	1612.4	1607.2
15°	1561.1	1553.4	1550.8	1545.7	1540.6	1538.0	1538.0	1535.5
17.5°	1484.2	1479.1	1476.5	1471.4	1468.7	1463.7	1461.1	1458.6
20°	1412.4	1399.6	1402.1	1397.0	1394.5	1384.2	1384.2	1386.8
22.5°	1332.9	1325.2	1320.1	1315.0	1312.4	1307.3	1307.3	1304.7
25°	1253.5	1245.8	1243.3	1238.1	1235.5	1230.5	1227.8	1227.8
27.5°	1176.6	1166.4	1166.4	1161.2	1156.1	1153.6	1150.9	1148.4
30°	1094.6	1086.8	1084.3	1084.3	1081.8	1081.8	1074.0	1076.6
32.5°	1017.7	1012.5	1009.9	1004.9	1004.9	1002.2	1002.2	994.6
35°	940.8	933.1	935.6	930.5	928.0	925.3	928.0	925.3
37.5°	866.4	861.2	861.2	856.2	856.2	853.6	851.1	856.2
40°	792.1	789.5	787.0	784.3	787.0	784.3	779.3	781.8
42.5°	717.7	717.7	715.2	715.2	712.6	712.6	712.6	712.6
45°	651.1	648.5	648.5	646.0	646.0	646.0	646.0	643.4
47.5°	584.5	581.9	581.9	581.9	579.4	579.4	576.7	579.4
50°	520.4	520.4	517.8	517.8	520.4	517.8	515.3	515.3
52.5°	461.3	461.3	458.8	458.8	456.3	453.7	456.3	456.3
55°	407.6	405.0	402.4	402.4	399.9	397.4	397.4	399.9
57.5°	356.3	353.8	351.1	351.1	346.1	343.5	343.5	343.5
60°	307.6	302.5	302.5	299.9	299.9	297.3	297.3	297.3
62.5°	261.4	258.9	258.9	258.9	258.9	256.4	256.4	256.4
65°	223.1	223.1	223.1	225.6	225.6	228.1	228.1	228.1
67.5°	192.3	194.8	194.8	194.8	197.4	197.4	197.4	194.8
70°	164.0	164.0	164.0	166.6	166.6	166.6	166.6	166.6
72.5°	135.9	135.9	135.9	135.9	135.9	135.9	135.9	135.9
75°	107.7	110.2	110.2	110.2	107.7	110.2	110.2	107.7
77.5°	84.6	84.6	84.6	84.6	84.6	84.6	84.6	84.6
80°	64.1	64.1	64.1	64.1	64.1	64.1	64.1	64.1
82.5°	43.6	43.6	43.6	43.6	43.6	43.6	43.6	43.6
85°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)