

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584470

Luminaire Tested: **HCC8W35D010SL-HM82555930-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010SL-HM82555930-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3194.3 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584470
CATALOG NUMBER: HCC8W35D010SL-HM82555930-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584470

CATALOG NUMBER: HCC8W35D010SL-HM82555930-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52881	52881	52881
5°	55067	52764	50545
10°	56910	52094	48080
15°	58348	50900	45581
20°	58460	48787	43323
25°	57477	45701	41077
30°	54400	42165	39153
35°	49600	37923	36763
40°	43132	33435	33950
45°	36998	28952	31076
50°	31604	24965	27915
55°	27703	21499	24257
60°	24663	18335	20389
65°	21882	14965	16278
70°	19411	11090	9241
75°	16191	5814	2752
80°	12750	1829	444
85°	9057	885	0



TEST NUMBER: P584470
 CATALOG NUMBER: HCC8W35D010SL-HM82555930-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	5.1
10°-20°	452.9	14.2
20°-30°	641.0	20.1
30°-40°	670.7	21.0
40°-50°	559.4	17.5
50°-60°	396.7	12.4
60°-70°	228.5	7.2
70°-80°	73.5	2.3
80°-90°	10.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1255.5	39.3
0°-40°	1926.2	60.3
0°-60°	2882.2	90.2
0°-90°	3194.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3194.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1715	1715	1715	1715	1715	
5°	1779	1756	1705	1653	1633	171
15°	1828	1753	1594	1469	1428	514
25°	1689	1564	1343	1236	1207	771
35°	1318	1202	1007	954	977	817
45°	848	779	664	672	713	657
55°	515	461	400	420	451	466
65°	300	251	205	205	223	300
75°	136	100	49	23	23	147
85°	26	13	2	0	0	32
90°	0	0	0	0	0	



TEST NUMBER: P584470

CATALOG NUMBER: HCC8W35D010SL-HM82555930-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9
2.5°	1750.8	1748.2	1745.6	1748.2	1745.6	1748.2	1745.6	1745.6	1743.1	1740.6	1740.6
5°	1779.0	1776.4	1776.4	1776.4	1773.9	1771.2	1771.2	1768.7	1763.6	1761.1	1755.9
7.5°	1796.9	1799.5	1799.5	1799.5	1794.4	1794.4	1789.2	1784.1	1779.0	1773.9	1766.2
10°	1817.5	1817.5	1814.9	1812.3	1807.2	1804.7	1802.0	1796.9	1789.2	1779.0	1771.2
12.5°	1825.2	1825.2	1822.5	1817.5	1814.9	1812.3	1809.7	1802.0	1791.8	1779.0	1768.7
15°	1827.7	1822.5	1820.0	1817.5	1812.3	1804.7	1804.7	1794.4	1781.5	1766.2	1753.4
17.5°	1807.2	1809.7	1804.7	1799.5	1791.8	1786.7	1779.0	1771.2	1755.9	1737.9	1725.1
20°	1781.5	1779.0	1776.4	1768.7	1758.4	1755.9	1748.2	1735.4	1722.6	1702.1	1684.1
22.5°	1740.6	1737.9	1732.8	1727.8	1717.5	1712.3	1704.6	1689.3	1671.3	1650.8	1630.4
25°	1689.3	1684.1	1676.5	1666.2	1658.5	1653.4	1643.2	1627.7	1607.2	1584.1	1563.6
27.5°	1607.2	1614.9	1609.8	1594.4	1586.8	1576.4	1573.9	1553.4	1535.5	1512.4	1489.4
30°	1527.8	1527.8	1520.1	1512.4	1499.5	1491.9	1481.7	1466.2	1448.3	1420.1	1402.1
32.5°	1427.8	1425.3	1415.0	1412.4	1402.1	1386.8	1384.2	1363.7	1345.8	1325.2	1302.2
35°	1317.6	1312.4	1302.2	1294.6	1289.4	1281.7	1274.0	1256.1	1238.1	1217.6	1202.2
37.5°	1192.0	1192.0	1189.4	1176.6	1171.4	1166.4	1158.7	1140.7	1130.4	1109.9	1094.6
40°	1071.5	1069.0	1061.2	1058.7	1053.5	1045.9	1040.7	1030.5	1015.1	999.7	984.4
42.5°	953.6	956.1	945.9	948.5	938.2	933.1	930.5	915.2	907.5	892.0	879.2
45°	848.4	845.9	840.8	838.2	833.1	827.9	822.8	815.1	802.3	787.0	779.3
47.5°	751.0	743.4	743.4	740.8	738.2	728.0	725.4	717.7	710.1	694.7	684.4
50°	658.8	658.8	658.8	656.3	648.5	646.0	640.8	633.1	625.5	615.2	599.8
52.5°	584.5	584.5	584.5	581.9	571.7	569.0	566.5	556.2	546.0	538.3	528.1
55°	515.3	517.8	515.3	510.1	502.4	502.4	494.8	489.6	479.3	471.7	461.3
57.5°	456.3	456.3	451.2	448.7	443.5	440.9	435.8	430.7	417.9	410.2	397.4
60°	399.9	397.4	397.4	392.2	387.1	381.9	379.4	371.7	366.6	353.8	343.5
62.5°	348.6	348.6	343.5	343.5	333.3	333.3	330.6	323.0	315.3	302.5	297.3
65°	299.9	299.9	297.3	294.8	287.0	284.5	282.0	274.2	266.6	258.9	251.2
67.5°	256.4	256.4	251.2	248.7	243.6	240.9	235.9	230.7	223.1	215.3	207.6
70°	215.3	212.8	210.2	207.6	202.5	199.9	194.8	189.6	182.0	176.8	169.2
72.5°	174.3	174.3	171.8	166.6	164.0	161.5	159.0	153.8	146.2	138.4	133.3
75°	135.9	135.9	135.9	130.7	125.6	123.0	123.0	117.9	112.7	105.1	99.9
77.5°	105.1	102.5	99.9	99.9	94.9	92.2	89.7	87.2	79.4	76.9	71.8
80°	71.8	74.4	71.8	69.2	66.6	64.1	64.1	58.9	56.4	51.3	46.1
82.5°	48.8	46.1	46.1	43.6	43.6	41.0	41.0	35.9	33.3	30.8	28.2
85°	25.6	25.6	23.1	23.1	23.1	20.5	20.5	18.0	18.0	15.3	12.8
87.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	5.2	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584470

CATALOG NUMBER: HCC8W35D010SL-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9
2.5°	1737.9	1732.8	1730.3	1730.3	1727.8	1725.1	1722.6	1720.0	1714.9	1714.9	1709.8
5°	1750.8	1745.6	1743.1	1735.4	1730.3	1730.3	1720.0	1717.5	1709.8	1704.6	1699.5
7.5°	1761.1	1750.8	1743.1	1735.4	1730.3	1725.1	1714.9	1704.6	1694.5	1684.1	1679.0
10°	1761.1	1750.8	1737.9	1725.1	1720.0	1714.9	1702.1	1686.7	1673.8	1663.7	1650.8
12.5°	1755.9	1740.6	1725.1	1714.9	1704.6	1697.0	1681.6	1666.2	1650.8	1630.4	1620.1
15°	1740.6	1720.0	1704.6	1686.7	1679.0	1666.2	1653.4	1630.4	1612.4	1594.4	1581.6
17.5°	1709.8	1684.1	1666.2	1648.2	1635.4	1627.7	1607.2	1586.8	1566.3	1545.7	1530.3
20°	1663.7	1640.5	1620.1	1596.9	1586.8	1576.4	1550.8	1530.3	1509.8	1486.7	1471.4
22.5°	1607.2	1584.1	1556.0	1538.0	1522.7	1509.8	1486.7	1463.7	1443.2	1422.6	1402.1
25°	1538.0	1515.0	1489.4	1461.1	1450.9	1438.1	1412.4	1389.3	1366.3	1343.2	1325.2
27.5°	1463.7	1432.9	1412.4	1381.7	1371.4	1358.5	1330.4	1304.7	1284.3	1266.3	1245.8
30°	1374.0	1350.9	1322.7	1294.6	1284.3	1271.4	1248.3	1225.3	1204.8	1184.2	1163.7
32.5°	1276.6	1253.5	1225.3	1204.8	1189.4	1179.2	1156.1	1135.6	1115.1	1094.6	1076.6
35°	1174.0	1148.4	1127.9	1107.4	1094.6	1081.8	1058.7	1040.7	1025.4	1007.4	989.4
37.5°	1069.0	1051.0	1030.5	1007.4	994.6	984.4	966.4	945.9	933.1	917.7	904.8
40°	966.4	945.9	928.0	907.5	897.2	889.5	871.5	856.2	843.4	830.6	822.8
42.5°	861.2	843.4	825.4	812.6	804.9	797.3	784.5	766.5	758.8	746.0	738.2
45°	763.8	748.5	735.7	717.7	712.6	707.5	692.1	679.3	671.6	663.9	658.8
47.5°	671.6	661.3	646.0	635.7	628.0	623.0	612.7	602.4	594.7	589.5	584.5
50°	592.2	579.4	569.0	558.9	553.7	546.0	535.7	530.6	525.4	520.4	520.4
52.5°	517.8	505.0	494.8	487.0	482.0	476.8	469.1	466.5	461.3	461.3	458.8
55°	448.7	440.9	430.7	420.4	417.9	415.2	410.2	405.0	402.4	399.9	402.4
57.5°	389.6	381.9	371.7	364.0	361.4	358.9	356.3	351.1	348.6	348.6	348.6
60°	335.8	328.1	320.5	312.7	312.7	307.6	305.0	302.5	299.9	297.3	297.3
62.5°	287.0	279.4	271.7	266.6	264.0	261.5	256.4	253.7	251.2	251.2	248.7
65°	243.6	233.3	230.7	223.1	220.4	217.9	215.3	210.2	207.6	205.1	202.5
67.5°	199.9	194.8	187.1	182.0	179.5	176.8	174.3	169.2	166.6	164.0	159.0
70°	161.5	156.3	151.2	146.2	143.5	141.0	135.9	130.7	128.2	123.0	115.4
72.5°	125.6	120.5	115.4	110.2	107.7	105.1	99.9	94.9	89.7	84.6	79.4
75°	94.9	89.7	82.1	76.9	74.4	74.4	66.6	61.6	56.4	48.8	43.6
77.5°	66.6	58.9	56.4	51.3	48.8	43.6	38.5	33.3	28.2	25.6	20.5
80°	43.6	38.5	33.3	30.8	28.2	25.6	23.1	18.0	12.8	10.3	7.7
82.5°	25.6	23.1	20.5	18.0	15.3	12.8	10.3	10.3	7.7	5.2	2.5
85°	12.8	10.3	7.7	7.7	5.2	5.2	5.2	2.5	2.5	2.5	2.5
87.5°	5.2	2.5	2.5	2.5	2.5	2.5	2.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584470

CATALOG NUMBER: HCC8W35D010SL-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9
2.5°	1707.3	1704.6	1702.1	1699.5	1699.5	1694.5	1694.5	1691.8	1686.7	1684.1	1684.1
5°	1691.8	1684.1	1679.0	1676.5	1673.8	1666.2	1663.7	1658.5	1653.4	1648.2	1645.7
7.5°	1668.8	1656.0	1650.8	1648.2	1640.5	1632.9	1627.7	1620.1	1612.4	1604.7	1602.1
10°	1640.5	1627.7	1614.9	1609.8	1602.1	1596.9	1586.8	1576.4	1568.8	1561.1	1553.4
12.5°	1604.7	1589.3	1576.4	1571.3	1563.6	1553.4	1538.0	1532.8	1520.1	1515.0	1504.7
15°	1563.6	1545.7	1532.8	1525.2	1517.5	1502.2	1491.9	1481.7	1468.9	1463.7	1453.4
17.5°	1512.4	1491.9	1479.1	1471.4	1466.2	1453.4	1438.1	1425.3	1412.4	1407.3	1399.6
20°	1450.9	1438.1	1420.1	1412.4	1407.3	1392.0	1376.5	1371.4	1361.2	1350.9	1343.2
22.5°	1381.7	1368.8	1350.9	1343.2	1340.7	1327.9	1315.0	1307.4	1299.6	1291.9	1284.3
25°	1309.9	1294.6	1279.1	1274.0	1268.9	1258.6	1248.3	1243.3	1235.5	1230.5	1225.3
27.5°	1233.0	1217.6	1204.8	1197.0	1192.0	1184.2	1179.2	1174.0	1168.9	1163.7	1161.2
30°	1150.9	1135.6	1125.3	1120.2	1115.1	1112.5	1104.8	1102.3	1099.6	1094.6	1097.1
32.5°	1069.0	1056.2	1045.9	1038.2	1038.2	1033.0	1030.5	1030.5	1027.9	1027.9	1027.9
35°	979.2	971.6	963.8	961.3	958.8	956.1	953.6	956.1	953.6	956.1	958.8
37.5°	897.2	889.5	884.4	881.8	879.2	881.8	879.2	879.2	881.8	886.9	889.5
40°	812.6	807.5	802.3	804.9	802.3	802.3	802.3	810.0	812.6	815.1	817.8
42.5°	733.2	728.0	725.4	725.4	728.0	725.4	730.5	733.2	738.2	746.0	751.0
45°	656.3	653.6	653.6	656.3	653.6	658.8	658.8	663.9	671.6	676.8	681.9
47.5°	584.5	584.5	584.5	587.0	587.0	589.5	594.7	597.3	602.4	607.5	612.7
50°	517.8	520.4	522.9	522.9	522.9	528.1	533.2	535.7	538.3	540.9	548.6
52.5°	458.8	461.3	461.3	464.0	466.5	469.1	471.7	476.8	479.3	484.5	487.0
55°	402.4	402.4	407.6	410.2	410.2	410.2	415.2	415.2	420.4	423.0	428.0
57.5°	348.6	351.1	351.1	353.8	353.8	356.3	358.9	361.4	364.0	366.6	369.1
60°	297.3	297.3	297.3	299.9	302.5	305.0	302.5	307.6	307.6	312.7	315.3
62.5°	248.7	251.2	251.2	251.2	251.2	251.2	251.2	253.7	256.4	258.9	261.5
65°	202.5	202.5	202.5	199.9	202.5	199.9	202.5	205.1	205.1	207.6	210.2
67.5°	156.3	156.3	151.2	151.2	153.8	153.8	153.8	153.8	151.2	156.3	156.3
70°	112.7	110.2	107.7	105.1	105.1	102.5	102.5	99.9	99.9	99.9	99.9
72.5°	74.4	69.2	64.1	61.6	58.9	58.9	53.8	51.3	53.8	53.8	53.8
75°	38.5	33.3	30.8	28.2	25.6	25.6	23.1	23.1	23.1	23.1	23.1
77.5°	15.3	12.8	10.3	10.3	7.7	7.7	7.7	7.7	7.7	7.7	7.7
80°	5.2	5.2	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
85°	2.5	0.0	0.0	2.5	0.0	2.5	2.5	2.5	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584470

CATALOG NUMBER: HCC8W35D010SL-HM82555930-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9	1714.9
2.5°	1681.6	1681.6	1679.0	1681.6	1676.5	1679.0	1676.5	1676.5
5°	1643.2	1638.0	1638.0	1638.0	1635.4	1635.4	1632.9	1632.9
7.5°	1596.9	1594.4	1591.9	1589.3	1586.8	1584.1	1584.1	1584.1
10°	1550.8	1545.7	1545.7	1543.1	1538.0	1535.5	1535.5	1535.5
12.5°	1497.0	1494.5	1491.9	1491.9	1481.7	1484.2	1481.7	1481.7
15°	1445.7	1443.2	1443.2	1435.4	1430.4	1430.4	1430.4	1427.8
17.5°	1392.0	1389.3	1386.8	1381.7	1376.5	1376.5	1374.0	1376.5
20°	1335.5	1333.0	1327.9	1327.9	1325.2	1322.7	1317.6	1320.2
22.5°	1279.1	1274.0	1271.4	1271.4	1268.9	1268.9	1263.8	1263.8
25°	1220.2	1217.6	1215.0	1217.6	1212.5	1212.5	1207.3	1207.3
27.5°	1158.7	1156.1	1156.1	1156.1	1153.6	1156.1	1153.6	1153.6
30°	1097.1	1097.1	1094.6	1094.6	1097.1	1094.6	1097.1	1099.6
32.5°	1030.5	1030.5	1033.0	1033.0	1035.6	1035.6	1035.6	1035.6
35°	961.3	966.4	966.4	968.9	971.6	974.1	974.1	976.6
37.5°	897.2	899.7	902.3	904.8	910.0	910.0	910.0	910.0
40°	827.9	830.6	835.6	833.1	843.4	845.9	843.4	843.4
42.5°	756.2	761.3	763.8	769.0	771.6	776.7	779.3	779.3
45°	689.6	692.1	697.2	702.4	704.9	712.6	712.6	712.6
47.5°	620.3	625.5	628.0	633.1	635.7	643.4	646.0	643.4
50°	553.7	558.9	563.9	563.9	571.7	574.2	579.4	581.9
52.5°	489.6	492.1	497.3	499.8	505.0	510.1	512.6	515.3
55°	428.0	430.7	435.8	435.8	443.5	446.0	451.2	451.2
57.5°	371.7	374.3	379.4	376.8	381.9	387.1	387.1	384.6
60°	317.8	317.8	317.8	323.0	325.5	328.1	330.6	330.6
62.5°	261.5	266.6	269.2	269.2	271.7	274.2	274.2	271.7
65°	210.2	215.3	217.9	217.9	220.4	220.4	220.4	223.1
67.5°	159.0	159.0	159.0	161.5	159.0	159.0	159.0	159.0
70°	99.9	99.9	99.9	99.9	97.4	99.9	99.9	102.5
72.5°	53.8	53.8	53.8	53.8	53.8	53.8	53.8	53.8
75°	23.1	23.1	23.1	25.6	23.1	23.1	23.1	23.1
77.5°	10.3	7.7	10.3	10.3	7.7	7.7	7.7	7.7
80°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
85°	0.0	2.5	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)