

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584480

Luminaire Tested: **HCC8S35D010MB-HM82555935-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MB-HM82555935-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3670.4 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584480
CATALOG NUMBER: HCC8S35D010MB-HM82555935-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584480

CATALOG NUMBER: HCC8S35D010MB-HM82555935-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59551	59551	59551
5°	60339	59299	58739
10°	60952	58694	57805
15°	61566	57451	56301
20°	61256	55333	54067
25°	59828	52023	51319
30°	56828	48293	48108
35°	51731	44066	44454
40°	45354	39437	40894
45°	39130	35084	37552
50°	34262	30799	34018
55°	30354	26478	29945
60°	27352	22264	24805
65°	24640	17876	19000
70°	21620	13019	10458
75°	18431	6755	2764
80°	14189	1829	462
85°	9128	0	0



TEST NUMBER: P584480
 CATALOG NUMBER: HCC8S35D010MB-HM82555935-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.2	5.0
10°-20°	512.2	14.0
20°-30°	727.0	19.8
30°-40°	765.3	20.9
40°-50°	651.0	17.7
50°-60°	470.5	12.8
60°-70°	267.6	7.3
70°-80°	84.3	2.3
80°-90°	10.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1421.4	38.7
0°-40°	2186.7	59.6
0°-60°	3308.2	90.1
0°-90°	3670.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3670.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1931	1931	1931	1931	1931	
5°	1949	1939	1916	1903	1898	186
15°	1928	1880	1800	1766	1764	543
25°	1758	1671	1529	1503	1508	805
35°	1374	1294	1171	1163	1181	855
45°	897	864	804	825	861	697
55°	565	523	492	521	557	509
65°	338	291	245	242	260	335
75°	155	119	57	26	23	166
85°	26	16	0	0	0	33
90°	0	0	0	0	0	



TEST NUMBER: P584480

CATALOG NUMBER: HCC8S35D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2
2.5°	1941.5	1944.1	1939.0	1939.0	1944.1	1939.0	1941.5	1941.5	1939.0	1939.0	1936.3
5°	1949.3	1946.6	1946.6	1946.6	1949.3	1944.1	1941.5	1944.1	1939.0	1939.0	1939.0
7.5°	1951.8	1951.8	1949.3	1946.6	1946.6	1946.6	1944.1	1941.5	1939.0	1933.8	1931.2
10°	1946.6	1946.6	1949.3	1944.1	1944.1	1939.0	1939.0	1933.8	1933.8	1928.5	1920.9
12.5°	1941.5	1939.0	1939.0	1933.8	1933.8	1928.5	1928.5	1920.9	1918.2	1910.6	1902.8
15°	1928.5	1926.0	1920.9	1918.2	1915.7	1913.1	1907.9	1905.4	1897.6	1887.3	1879.7
17.5°	1902.8	1900.3	1897.6	1892.5	1887.3	1884.8	1882.2	1874.5	1864.1	1856.4	1843.5
20°	1866.7	1864.1	1864.1	1856.4	1853.8	1846.1	1843.5	1833.2	1825.5	1809.9	1799.6
22.5°	1817.7	1820.4	1815.2	1809.9	1804.8	1797.1	1792.0	1781.7	1768.7	1753.3	1740.3
25°	1758.4	1761.1	1755.8	1750.6	1743.0	1737.8	1732.7	1717.2	1704.3	1686.2	1670.7
27.5°	1683.7	1683.7	1683.7	1678.5	1665.6	1663.1	1657.9	1642.5	1624.4	1608.9	1593.5
30°	1596.0	1593.5	1593.5	1585.7	1580.5	1570.2	1562.4	1549.6	1536.7	1518.6	1500.6
32.5°	1490.3	1492.8	1485.2	1480.0	1472.2	1472.2	1461.9	1451.6	1436.2	1418.1	1400.0
35°	1374.2	1376.9	1371.7	1369.1	1356.3	1353.6	1351.1	1338.2	1327.9	1314.9	1294.3
37.5°	1255.6	1253.1	1250.5	1250.5	1242.8	1237.7	1232.5	1224.7	1209.3	1199.0	1188.7
40°	1126.7	1126.7	1126.7	1124.2	1121.6	1116.4	1113.9	1108.6	1098.3	1088.0	1080.4
42.5°	1010.8	1010.8	1008.1	1005.6	1000.4	1003.0	997.8	992.7	982.4	974.6	969.4
45°	897.3	897.3	897.3	899.8	894.7	887.0	887.0	881.8	876.6	871.4	863.8
47.5°	796.7	804.5	799.3	796.7	799.3	789.0	789.0	783.9	778.7	773.5	763.2
50°	714.2	714.2	714.2	709.1	706.5	706.5	698.7	693.5	691.0	685.9	675.6
52.5°	639.4	634.2	634.2	631.7	629.1	623.9	623.9	618.8	608.5	603.3	595.6
55°	564.6	564.6	562.1	559.5	557.0	554.3	551.8	544.0	538.9	531.2	523.4
57.5°	497.6	502.8	500.2	495.0	489.9	489.9	484.7	479.6	471.9	464.1	456.3
60°	443.5	440.9	440.9	438.3	433.2	430.6	428.0	420.3	412.6	404.8	397.0
62.5°	386.7	386.7	386.7	381.6	376.4	373.9	371.3	366.1	355.8	348.0	342.9
65°	337.7	335.2	332.6	330.0	327.4	322.3	319.7	314.6	306.8	299.1	291.4
67.5°	288.7	286.2	286.2	283.6	275.9	273.3	273.3	265.6	257.8	250.1	242.4
70°	239.8	239.8	239.8	234.7	232.1	229.4	226.9	221.7	214.0	206.3	198.5
72.5°	198.5	196.0	196.0	193.4	185.7	183.1	180.5	175.3	167.6	162.4	157.3
75°	154.7	154.7	152.1	149.5	147.0	144.4	141.8	136.7	128.9	121.2	118.6
77.5°	118.6	116.0	116.0	113.5	108.3	105.7	105.7	100.5	92.8	87.7	82.5
80°	79.9	82.5	79.9	77.4	74.8	72.2	69.6	67.1	61.9	56.7	51.5
82.5°	49.0	51.5	49.0	49.0	46.4	43.8	43.8	38.7	36.1	33.5	30.9
85°	25.8	25.8	25.8	25.8	23.2	23.2	23.2	20.6	18.1	15.5	15.5
87.5°	7.8	10.3	7.8	7.8	7.8	7.8	7.8	7.8	5.2	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584480

CATALOG NUMBER: HCC8S35D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2
2.5°	1939.0	1936.3	1933.8	1933.8	1933.8	1933.8	1933.8	1931.2	1928.5	1928.5	1928.5
5°	1933.8	1933.8	1933.8	1931.2	1928.5	1928.5	1923.4	1920.9	1918.2	1915.7	1913.1
7.5°	1928.5	1923.4	1920.9	1918.2	1915.7	1915.7	1910.6	1905.4	1905.4	1900.3	1895.1
10°	1913.1	1910.6	1905.4	1900.3	1897.6	1895.1	1890.0	1882.2	1879.7	1874.5	1869.2
12.5°	1895.1	1890.0	1884.8	1874.5	1871.9	1869.2	1858.9	1851.3	1846.1	1843.5	1830.7
15°	1871.9	1861.6	1853.8	1841.0	1838.3	1833.2	1825.5	1817.7	1807.4	1799.6	1794.5
17.5°	1830.7	1820.4	1807.4	1794.5	1789.3	1789.3	1776.5	1766.2	1753.3	1748.1	1737.8
20°	1781.7	1768.7	1758.4	1743.0	1735.2	1727.5	1719.7	1704.3	1694.0	1686.2	1673.4
22.5°	1724.9	1706.9	1694.0	1678.5	1665.6	1657.9	1645.0	1632.0	1619.2	1611.4	1601.1
25°	1652.8	1637.2	1616.6	1601.1	1593.5	1583.2	1567.6	1554.8	1541.8	1529.0	1523.9
27.5°	1572.7	1552.1	1534.2	1516.1	1508.3	1500.6	1482.5	1467.1	1456.8	1443.8	1438.7
30°	1485.2	1464.6	1443.8	1428.4	1420.7	1407.8	1397.5	1379.4	1366.6	1356.3	1343.3
32.5°	1384.5	1369.1	1351.1	1327.9	1322.7	1312.4	1297.0	1289.2	1273.7	1265.9	1255.6
35°	1276.2	1265.9	1248.0	1229.9	1222.1	1216.9	1204.1	1188.7	1178.4	1170.6	1165.4
37.5°	1173.2	1160.3	1142.2	1129.4	1124.2	1116.4	1101.0	1093.2	1082.9	1077.7	1067.4
40°	1062.3	1049.3	1036.5	1028.7	1021.1	1015.9	1005.6	997.8	987.5	979.7	977.2
42.5°	954.0	946.3	935.9	925.6	923.1	915.3	910.1	902.5	894.7	892.2	884.4
45°	856.0	848.3	838.0	827.7	825.1	819.9	817.3	809.6	804.5	804.5	804.5
47.5°	758.0	750.3	740.0	734.9	737.4	727.1	727.1	724.6	719.4	719.4	721.9
50°	670.4	660.1	657.5	652.3	647.2	642.0	644.6	636.9	636.9	642.0	639.4
52.5°	587.9	577.6	574.9	569.8	567.3	567.3	564.6	564.6	562.1	564.6	564.6
55°	513.1	505.3	500.2	495.0	492.5	492.5	492.5	489.9	487.3	492.5	495.0
57.5°	446.0	443.5	438.3	430.6	428.0	425.4	422.9	422.9	422.9	422.9	425.4
60°	386.7	381.6	376.4	368.7	368.7	366.1	363.6	361.0	361.0	361.0	361.0
62.5°	335.2	327.4	319.7	314.6	312.0	309.4	306.8	301.7	301.7	301.7	301.7
65°	283.6	275.9	270.7	265.6	260.4	260.4	255.3	252.7	247.5	245.0	239.8
67.5°	234.7	229.4	224.3	216.6	214.0	211.4	206.3	203.7	196.0	193.4	190.8
70°	190.8	183.1	177.9	172.8	170.1	165.0	159.8	154.7	149.5	144.4	139.2
72.5°	149.5	141.8	136.7	131.5	126.4	126.4	118.6	113.5	105.7	100.5	92.8
75°	110.8	103.1	98.0	90.2	87.7	85.1	77.4	72.2	64.5	56.7	51.5
77.5°	74.8	69.6	64.5	56.7	51.5	51.5	43.8	38.7	33.5	25.8	23.2
80°	46.4	41.2	36.1	30.9	30.9	25.8	23.2	18.1	12.9	10.3	7.8
82.5°	25.8	23.2	20.6	15.5	15.5	12.9	10.3	7.8	5.2	2.6	2.6
85°	12.9	10.3	7.8	7.8	5.2	5.2	5.2	2.6	2.6	0.0	0.0
87.5°	5.2	2.6	2.6	2.6	2.6	2.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584480

CATALOG NUMBER: HCC8S35D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2
2.5°	1926.0	1926.0	1923.4	1923.4	1923.4	1920.9	1923.4	1920.9	1920.9	1920.9	1923.4
5°	1915.7	1910.6	1910.6	1907.9	1907.9	1905.4	1907.9	1905.4	1902.8	1900.3	1902.8
7.5°	1895.1	1890.0	1887.3	1884.8	1884.8	1884.8	1882.2	1879.7	1882.2	1874.5	1879.7
10°	1866.7	1864.1	1858.9	1856.4	1853.8	1856.4	1853.8	1848.6	1848.6	1848.6	1846.1
12.5°	1830.7	1825.5	1822.9	1820.4	1815.2	1815.2	1817.7	1812.6	1812.6	1807.4	1807.4
15°	1786.8	1781.7	1776.5	1776.5	1771.4	1771.4	1768.7	1768.7	1766.2	1763.6	1763.6
17.5°	1732.7	1724.9	1719.7	1722.4	1719.7	1717.2	1717.2	1712.1	1709.4	1712.1	1712.1
20°	1668.2	1663.1	1657.9	1660.4	1655.3	1652.8	1655.3	1647.6	1650.1	1650.1	1650.1
22.5°	1596.0	1593.5	1585.7	1585.7	1580.5	1577.9	1580.5	1580.5	1583.2	1580.5	1580.5
25°	1516.1	1510.9	1505.8	1505.8	1503.1	1500.6	1503.1	1505.8	1503.1	1505.8	1505.8
27.5°	1431.0	1423.2	1423.2	1418.1	1418.1	1420.7	1418.1	1420.7	1423.2	1423.2	1428.4
30°	1338.2	1335.5	1333.0	1330.4	1330.4	1333.0	1333.0	1333.0	1335.5	1340.7	1340.7
32.5°	1250.5	1245.3	1240.2	1240.2	1245.3	1242.8	1245.3	1245.3	1250.5	1250.5	1255.6
35°	1155.1	1155.1	1150.0	1152.5	1152.5	1152.5	1152.5	1157.6	1162.8	1165.4	1170.6
37.5°	1067.4	1059.8	1062.3	1062.3	1064.9	1062.3	1070.1	1070.1	1075.2	1075.2	1080.4
40°	972.1	972.1	974.6	972.1	974.6	974.6	979.7	984.9	987.5	992.7	995.3
42.5°	881.8	887.0	881.8	884.4	887.0	889.5	892.2	894.7	905.0	910.1	917.9
45°	799.3	801.8	804.5	807.0	804.5	809.6	812.1	817.3	825.1	827.7	830.2
47.5°	719.4	721.9	724.6	727.1	727.1	732.2	734.9	740.0	745.2	747.7	750.3
50°	642.0	647.2	649.8	649.8	652.3	657.5	662.6	662.6	667.8	675.6	678.1
52.5°	572.4	572.4	577.6	580.1	582.7	582.7	590.5	593.0	595.6	600.8	605.9
55°	495.0	502.8	505.3	505.3	510.5	515.6	518.3	520.8	520.8	531.2	531.2
57.5°	428.0	430.6	435.7	435.7	435.7	443.5	443.5	448.7	451.2	453.8	459.0
60°	361.0	366.1	366.1	368.7	366.1	371.3	373.9	379.0	381.6	384.2	386.7
62.5°	299.1	299.1	301.7	301.7	301.7	301.7	306.8	306.8	312.0	314.6	317.1
65°	239.8	239.8	239.8	239.8	239.8	239.8	239.8	239.8	242.4	242.4	247.5
67.5°	185.7	183.1	177.9	180.5	177.9	177.9	175.3	175.3	177.9	177.9	183.1
70°	134.1	131.5	126.4	126.4	123.8	121.2	118.6	116.0	113.5	113.5	113.5
72.5°	87.7	82.5	74.8	72.2	72.2	67.1	61.9	59.3	59.3	59.3	59.3
75°	43.8	38.7	33.5	30.9	30.9	25.8	28.4	25.8	25.8	25.8	25.8
77.5°	18.1	12.9	10.3	10.3	10.3	7.8	7.8	7.8	7.8	7.8	7.8
80°	5.2	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	2.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584480

CATALOG NUMBER: HCC8S35D010MB-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2
2.5°	1920.9	1920.9	1915.7	1918.2	1918.2	1918.2	1918.2	1918.2
5°	1897.6	1900.3	1897.6	1900.3	1900.3	1897.6	1897.6	1897.6
7.5°	1874.5	1877.0	1874.5	1877.0	1877.0	1877.0	1874.5	1874.5
10°	1846.1	1846.1	1846.1	1846.1	1846.1	1843.5	1846.1	1846.1
12.5°	1807.4	1807.4	1807.4	1809.9	1809.9	1807.4	1807.4	1804.8
15°	1766.2	1761.1	1763.6	1766.2	1763.6	1763.6	1763.6	1763.6
17.5°	1709.4	1712.1	1709.4	1709.4	1709.4	1709.4	1712.1	1709.4
20°	1650.1	1650.1	1652.8	1650.1	1650.1	1650.1	1650.1	1647.6
22.5°	1583.2	1580.5	1580.5	1583.2	1583.2	1580.5	1583.2	1583.2
25°	1508.3	1510.9	1508.3	1508.3	1510.9	1510.9	1510.9	1508.3
27.5°	1428.4	1431.0	1433.5	1431.0	1431.0	1431.0	1433.5	1436.2
30°	1345.8	1351.1	1345.8	1345.8	1351.1	1348.5	1351.1	1351.1
32.5°	1258.3	1265.9	1260.8	1265.9	1265.9	1268.6	1265.9	1268.6
35°	1170.6	1178.4	1178.4	1178.4	1180.9	1183.5	1183.5	1180.9
37.5°	1088.0	1090.7	1090.7	1095.8	1098.3	1101.0	1101.0	1098.3
40°	1003.0	1008.1	1010.8	1010.8	1010.8	1015.9	1021.1	1015.9
42.5°	920.4	923.1	925.6	925.6	930.7	933.4	935.9	935.9
45°	840.5	845.7	848.3	850.8	853.5	858.6	856.0	861.1
47.5°	758.0	765.8	768.4	770.9	776.1	778.7	781.2	783.9
50°	683.2	688.4	688.4	693.5	701.3	701.3	706.5	709.1
52.5°	608.5	611.1	613.6	616.3	621.4	626.6	626.6	631.7
55°	536.3	538.9	538.9	541.5	544.0	554.3	557.0	557.0
57.5°	461.5	461.5	466.6	469.3	471.9	477.0	477.0	477.0
60°	389.3	391.9	391.9	394.5	397.0	402.2	404.8	402.2
62.5°	317.1	319.7	319.7	322.3	327.4	330.0	327.4	327.4
65°	250.1	252.7	252.7	255.3	260.4	260.4	257.8	260.4
67.5°	183.1	183.1	183.1	183.1	183.1	183.1	183.1	183.1
70°	116.0	113.5	110.8	113.5	113.5	113.5	110.8	116.0
72.5°	56.7	59.3	59.3	59.3	59.3	59.3	59.3	56.7
75°	25.8	25.8	23.2	23.2	23.2	25.8	25.8	23.2
77.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
80°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)