

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584481

Luminaire Tested: **HCC8S35D010SL-HM82555935-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010SL-HM82555935-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3567.3 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584481
CATALOG NUMBER: HCC8S35D010SL-HM82555935-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P584481

CATALOG NUMBER: HCC8S35D010SL-HM82555935-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88				
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77				77				
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67				
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59				
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47				
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35				35				
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	58678	58678	58678
5°	59779	58420	57067
10°	60714	57401	54981
15°	61323	55973	52598
20°	61089	53811	50175
25°	59478	50706	47372
30°	56643	47004	44619
35°	51151	42903	41446
40°	44940	38507	38402
45°	38790	33845	35306
50°	33768	29686	31667
55°	29945	25784	27585
60°	26717	21789	22899
65°	24078	17687	18059
70°	21386	13253	10693
75°	18431	7685	4611
80°	14189	2752	1385
85°	9128	920	920



TEST NUMBER: P584481
 CATALOG NUMBER: HCC8S35D010SL-HM82555935-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.6	5.0
10°-20°	497.3	13.9
20°-30°	703.3	19.7
30°-40°	741.1	20.8
40°-50°	629.9	17.7
50°-60°	453.6	12.7
60°-70°	261.6	7.3
70°-80°	89.5	2.5
80°-90°	12.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1379.2	38.7
0°-40°	2120.4	59.4
0°-60°	3203.8	89.8
0°-90°	3567.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3567.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1903	1903	1903	1903	1903	
5°	1931	1918	1887	1854	1844	185
15°	1921	1862	1753	1676	1648	541
25°	1748	1658	1490	1413	1392	802
35°	1359	1279	1140	1098	1101	846
45°	890	848	776	781	810	691
55°	557	513	480	498	513	501
65°	330	284	242	237	248	328
75°	155	116	64	41	39	163
85°	26	16	3	3	3	35
90°	0	0	0	0	0	



TEST NUMBER: P584481

CATALOG NUMBER: HCC8S35D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9
2.5°	1920.9	1923.5	1920.9	1920.9	1918.4	1915.7	1913.2	1910.6	1905.4	1900.3	1900.3
5°	1931.2	1936.3	1931.2	1931.2	1923.5	1918.4	1913.2	1905.4	1895.1	1887.3	1887.3
7.5°	1939.0	1939.0	1939.0	1931.2	1926.0	1918.4	1905.4	1892.5	1879.7	1866.7	1861.6
10°	1939.0	1939.0	1936.3	1926.0	1920.9	1905.4	1892.5	1874.5	1856.4	1838.3	1833.2
12.5°	1931.2	1933.8	1928.7	1918.4	1905.4	1887.3	1869.4	1846.1	1825.5	1804.9	1794.6
15°	1920.9	1918.4	1913.2	1900.3	1884.8	1861.6	1843.6	1817.7	1789.5	1763.6	1753.3
17.5°	1895.1	1895.1	1887.3	1874.5	1853.9	1828.0	1799.8	1771.4	1740.5	1712.1	1699.1
20°	1861.6	1861.6	1851.3	1835.8	1815.2	1781.7	1750.8	1717.2	1681.2	1652.8	1639.8
22.5°	1812.6	1815.2	1802.3	1784.3	1761.1	1722.4	1691.5	1650.1	1614.1	1580.5	1570.2
25°	1748.1	1753.3	1740.5	1722.4	1691.5	1657.9	1619.2	1580.5	1539.3	1505.8	1490.3
27.5°	1673.4	1676.0	1663.1	1645.0	1614.1	1578.0	1539.3	1498.1	1459.4	1423.2	1407.8
30°	1590.8	1580.5	1575.4	1552.1	1518.7	1487.7	1443.9	1410.4	1369.1	1338.2	1320.1
32.5°	1474.9	1480.0	1464.6	1446.5	1420.7	1384.6	1348.5	1309.8	1271.2	1248.0	1235.0
35°	1358.8	1363.9	1356.3	1338.2	1309.8	1278.9	1242.8	1214.4	1180.9	1152.6	1139.7
37.5°	1237.7	1237.7	1232.5	1222.2	1201.5	1173.2	1137.0	1108.7	1080.4	1057.1	1049.4
40°	1116.4	1111.3	1108.7	1101.0	1082.9	1057.1	1033.9	1010.8	982.4	966.9	956.6
42.5°	997.8	997.8	992.7	985.0	966.9	954.0	930.8	905.0	884.4	868.9	868.9
45°	889.5	892.2	884.4	879.2	868.9	848.3	827.7	809.6	791.5	781.2	776.1
47.5°	794.2	794.2	786.4	781.2	770.9	752.9	734.9	719.4	706.5	698.8	696.2
50°	703.9	703.9	703.9	691.0	678.1	665.2	652.3	634.3	626.6	621.4	618.8
52.5°	626.6	623.9	623.9	613.6	600.8	585.3	572.4	557.0	549.2	544.0	546.6
55°	557.0	557.0	554.3	541.5	528.6	513.1	500.2	487.3	482.2	477.0	479.6
56°	528.6	528.6	526.0	515.6	500.2	487.3	471.9	459.0	451.2	453.8	453.8
57°	508.0	502.8	502.8	489.9	477.0	459.0	446.0	433.2	428.0	425.4	425.4
58°	482.2	479.6	477.0	464.1	451.2	435.7	422.9	410.0	402.2	402.2	399.7
59°	456.3	456.3	451.2	440.9	428.0	412.6	399.7	386.7	379.0	376.4	376.4
60°	433.2	435.7	428.0	417.7	407.4	389.3	373.9	363.6	355.8	353.3	353.3
61°	412.6	412.6	407.4	394.5	381.6	368.7	353.3	340.4	335.2	330.0	330.0
62°	394.5	389.3	386.7	373.9	361.0	345.5	332.6	319.7	312.0	306.8	309.4
63°	371.3	368.7	363.6	353.3	340.4	324.9	309.4	299.1	291.4	283.6	286.2
64°	353.3	350.7	342.9	332.6	319.7	304.3	288.8	278.4	273.3	265.6	263.0
65°	330.0	327.4	324.9	312.0	299.1	283.6	270.7	260.4	252.7	247.5	242.4
66°	309.4	312.0	306.8	296.5	281.1	268.1	250.1	239.8	234.7	226.9	221.7
67°	291.4	291.4	286.2	275.9	260.4	247.5	234.7	221.7	214.0	206.3	203.7
67.5°	281.1	281.1	275.9	263.0	252.7	237.2	224.3	214.0	203.7	198.5	193.4
68°	270.7	270.7	268.1	257.8	245.0	229.4	216.6	203.7	193.4	185.7	183.1
69°	252.7	255.3	250.1	239.8	226.9	211.4	198.5	188.2	177.9	170.1	165.0
70°	237.2	234.7	229.4	219.1	206.3	196.0	183.1	170.1	159.8	149.5	147.0
71°	216.6	216.6	211.4	203.7	190.8	177.9	165.0	154.7	144.4	131.5	128.9
72°	201.1	201.1	196.0	185.7	175.4	162.4	149.5	136.7	128.9	116.1	110.8
72.5°	190.8	193.4	188.2	177.9	167.6	152.1	141.8	131.5	118.6	108.3	103.1
73°	185.7	183.1	180.5	170.1	157.3	147.0	134.1	123.8	110.8	100.5	95.4



TEST NUMBER: P584481
 CATALOG NUMBER: HCC8S35D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	116.1	116.1	113.5	103.1	92.8	82.5	72.2	61.9	51.5	41.2	36.1
80°	79.9	82.5	77.4	72.2	64.5	54.1	43.8	36.1	25.8	20.6	15.5
82.5°	51.5	51.5	49.0	43.8	38.7	30.9	25.8	18.1	12.9	10.3	7.8
85°	25.8	28.4	25.8	23.2	18.1	15.5	12.9	7.8	5.2	2.6	2.6
87.5°	10.3	10.3	10.3	7.8	7.8	5.2	2.6	2.6	2.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584481

CATALOG NUMBER: HCC8S35D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9	1902.9
2.5°	1895.1	1895.1	1890.0	1887.3	1884.8	1882.2	1879.7	1877.0	1877.0	1879.7
5°	1879.7	1874.5	1864.2	1861.6	1853.9	1851.3	1846.1	1843.6	1846.1	1843.6
7.5°	1856.4	1846.1	1833.2	1828.0	1817.7	1812.6	1804.9	1804.9	1799.8	1802.3
10°	1825.5	1810.1	1794.6	1784.3	1776.5	1768.7	1763.6	1758.4	1755.9	1755.9
12.5°	1786.8	1768.7	1753.3	1737.8	1724.9	1719.7	1709.4	1709.4	1704.3	1701.8
15°	1743.0	1719.7	1701.8	1686.3	1676.0	1665.6	1657.9	1652.8	1647.6	1647.6
17.5°	1686.3	1665.6	1647.6	1629.5	1614.1	1606.3	1598.6	1590.8	1590.8	1585.7
20°	1624.4	1601.1	1585.7	1567.7	1554.8	1541.8	1531.5	1531.5	1526.4	1529.0
22.5°	1554.8	1526.4	1510.9	1498.1	1485.2	1474.9	1464.6	1464.6	1461.9	1459.4
25°	1477.4	1454.3	1436.2	1420.7	1412.9	1402.6	1400.1	1395.0	1392.3	1392.3
27.5°	1395.0	1376.9	1353.6	1346.0	1335.7	1330.5	1330.5	1327.9	1322.7	1325.3
30°	1307.3	1286.7	1273.7	1268.6	1258.3	1258.3	1255.6	1250.5	1250.5	1253.1
32.5°	1222.2	1201.5	1191.2	1188.7	1178.4	1178.4	1175.7	1178.4	1178.4	1180.9
35°	1129.4	1111.3	1108.7	1101.0	1098.4	1098.4	1098.4	1103.6	1108.7	1101.0
37.5°	1041.7	1028.7	1021.1	1018.4	1021.1	1021.1	1023.6	1031.4	1028.7	1026.2
40°	951.5	941.1	936.0	936.0	941.1	946.3	946.3	954.0	956.6	954.0
42.5°	861.1	853.5	853.5	856.0	861.1	863.8	871.5	879.2	881.8	884.4
45°	776.1	776.1	776.1	778.7	781.2	786.4	796.7	804.5	807.1	809.6
47.5°	693.6	691.0	698.8	701.3	709.1	711.6	719.4	729.7	732.2	734.9
50°	616.3	621.4	623.9	631.7	636.9	636.9	647.2	652.3	660.1	660.1
52.5°	544.0	551.8	554.3	562.1	564.6	567.3	572.4	580.2	585.3	585.3
55°	479.6	482.2	487.3	489.9	497.6	500.2	505.3	508.0	515.6	513.1
56°	451.2	456.3	459.0	464.1	469.3	471.9	477.0	479.6	484.7	487.3
57°	425.4	428.0	435.7	438.3	443.5	443.5	446.0	453.8	453.8	456.3
58°	399.7	404.8	407.4	410.0	415.1	417.7	422.9	425.4	428.0	425.4
59°	376.4	379.0	381.6	381.6	386.7	386.7	394.5	399.7	402.2	402.2
60°	353.3	353.3	355.8	358.4	363.6	366.1	366.1	371.3	371.3	371.3
61°	330.0	330.0	332.6	335.2	337.7	337.7	342.9	342.9	345.5	348.1
62°	309.4	306.8	306.8	309.4	309.4	314.6	317.1	319.7	322.3	319.7
63°	286.2	283.6	283.6	283.6	283.6	288.8	288.8	291.4	296.5	294.0
64°	260.4	260.4	260.4	260.4	263.0	263.0	268.1	270.7	273.3	275.9
65°	242.4	237.2	234.7	234.7	237.2	239.8	242.4	245.0	247.5	247.5
66°	221.7	216.6	214.0	214.0	214.0	214.0	219.1	219.1	224.3	224.3
67°	198.5	193.4	190.8	188.2	188.2	188.2	196.0	193.4	193.4	193.4
67.5°	190.8	183.1	180.5	177.9	175.4	180.5	177.9	180.5	180.5	177.9
68°	180.5	175.4	170.1	165.0	165.0	165.0	167.6	170.1	167.6	165.0
69°	159.8	157.3	149.5	144.4	141.8	144.4	141.8	144.4	141.8	144.4
70°	141.8	134.1	126.4	123.8	121.2	121.2	121.2	118.6	121.2	118.6
71°	123.8	116.1	108.3	103.1	100.5	100.5	98.0	100.5	98.0	100.5
72°	105.7	98.0	87.7	82.5	82.5	82.5	82.5	79.9	82.5	79.9
72.5°	98.0	87.7	79.9	74.8	72.2	72.2	72.2	72.2	69.6	72.2
73°	90.2	79.9	69.6	67.1	67.1	67.1	64.5	61.9	64.5	64.5



TEST NUMBER: P584481
CATALOG NUMBER: HCC8S35D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	30.9	23.2	20.6	20.6	20.6	20.6	20.6	20.6	18.1	18.1
80°	12.9	10.3	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
82.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
85°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	167.6	167.6	162.4	154.7	141.8	128.9	118.6	108.3	95.4	82.5	77.4
75°	154.7	152.1	147.0	139.2	128.9	116.1	105.7	92.8	82.5	69.6	64.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	74.8	61.9	56.7	51.5	51.5	51.5	49.0	49.0	49.0	51.5
75°	59.3	49.0	43.8	38.7	41.2	38.7	41.2	38.7	38.7	38.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)